

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007835

Luminaire Tested: S125IP-B375UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007835
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B375UB2750-4F0-XX-W2A-1_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1269.0 lumens
Efficiency: N/A
Efficacy: 136.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007835

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007835

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007835

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.7	0.1
90°-100°	30.2	2.4
100°-110°	89.8	7.1
110°-120°	152.3	12.0
120°-130°	200.4	15.8
130°-140°	224.6	17.7
140°-150°	220.1	17.3
150°-160°	184.9	14.6
160°-170°	122.9	9.7
170°-180°	43.0	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.7	0.1
90°-120°	272.3	21.5
90°-150°	917.4	72.3
90°-180°	1268.0	99.9
0°-180°	1269.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	3	6	7	8	2
95°	23	24	27	30	30	24
105°	81	82	84	87	88	86
115°	152	154	154	154	154	151
125°	222	225	225	224	224	199
135°	289	291	292	292	290	223
145°	350	352	353	353	352	219
155°	401	401	401	403	401	185
165°	436	435	436	437	435	123
175°	453	452	452	454	452	43
180°	454	454	454	454	454	

TEST NUMBER: P1007835

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	3.2	5.7	7.4	8.5
92.5°	10.6	12.4	15.6	18.0	18.7
95°	23.0	23.7	27.2	29.7	30.4
97.5°	35.4	35.7	40.7	42.8	43.1
100°	49.5	49.5	54.1	57.3	58.0
102.5°	64.7	66.5	68.3	71.8	72.9
105°	80.6	82.4	84.5	86.6	87.7
107.5°	98.0	99.7	101.5	102.6	102.6
110°	116.0	117.8	118.8	119.9	119.5

TEST NUMBER: P1007835

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	134.4	135.1	136.5	136.9	136.2
115°	152.4	153.8	154.5	154.2	153.8
117.5°	170.8	171.2	171.9	172.2	170.8
120°	187.8	189.6	189.9	189.9	188.5
122.5°	206.2	206.5	207.6	207.2	206.2
125°	222.4	224.6	224.9	224.2	223.9
127.5°	240.5	241.5	241.9	241.5	240.8
130°	256.4	258.2	258.9	258.5	257.8
132.5°	272.3	275.5	275.1	274.8	273.7
135°	289.3	291.4	291.8	291.8	290.3
137.5°	305.2	307.3	308.0	308.4	306.6
140°	320.4	322.2	323.2	323.9	322.2
142.5°	335.6	337.0	338.4	338.8	337.0
145°	350.5	351.9	352.9	352.9	351.9
147.5°	364.3	365.3	366.0	367.1	364.3
150°	378.0	377.7	379.1	379.1	378.4
152.5°	389.4	390.1	390.4	391.5	390.1
155°	401.0	401.0	401.4	402.8	401.0
157.5°	411.6	410.9	411.3	412.7	410.2
160°	420.8	419.8	420.1	421.5	419.8
162.5°	429.0	428.3	428.3	430.0	427.9
165°	436.0	435.3	435.7	437.1	435.0
167.5°	442.4	441.0	441.0	443.1	441.0
170°	447.4	445.9	445.9	448.1	445.6
172.5°	450.9	449.5	449.5	451.6	449.5
175°	453.4	452.0	452.0	454.1	451.6
177.5°	455.1	453.7	453.4	455.5	453.0
180°	454.4	454.4	454.4	454.4	454.4

(END OF REPORT)