

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028444

Luminaire Tested: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028444
REPORT IS A COMBINATION OF REPORTS P1004959 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8972.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	42	41	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	36	34
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	31	29
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	58	46	39	33	54	43	36	31	37	31	28	31	27	24	26	22	20
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10382	10382	10382	10382
5°	10373	11701	10373	8994
10°	10315	13149	10280	7775
15°	10203	13911	10133	6769
20°	10068	15017	9978	6118
25°	9891	16997	9780	5553
30°	9712	18067	9566	5149
35°	9480	14858	9347	4771
40°	9067	10090	8991	4433
45°	8526	7253	8515	4099
50°	7971	5578	8010	3791
55°	7346	4536	7332	3494
60°	6765	3717	6732	3102
65°	6087	3097	6125	2497
70°	5527	2486	5504	2079
75°	4669	1884	4669	1709
80°	3784	1149	3739	1149
85°	2664	604	2584	683

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14778 cd/sqm

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.4	1.7
10°-20°	455.5	5.1
20°-30°	722.3	8.1
30°-40°	872.8	9.7
40°-50°	777.1	8.7
50°-60°	595.9	6.6
60°-70°	387.0	4.3
70°-80°	187.8	2.1
80°-90°	46.5	0.5
90°-100°	52.7	0.6
100°-110°	350.6	3.9
110°-120°	631.3	7.0
120°-130°	810.4	9.0
130°-140°	871.6	9.7
140°-150°	818.0	9.1
150°-160°	661.7	7.4
160°-170°	427.9	4.8
170°-180°	147.6	1.6
0°-30°	1333.2	14.9
0°-40°	2206.0	24.6
0°-60°	3579.0	39.9
0°-90°	4200.3	46.8
90°-120°	1034.6	11.5
90°-150°	3534.6	39.4
90°-180°	4772.0	53.2
0°-180°	8972.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1620	1620	1620	1620	1620	
5°	1616	1857	1616	1428	1616	154
15°	1548	2231	1538	1086	1548	437
25°	1416	2671	1400	873	1416	652
35°	1233	2216	1216	712	1233	768
45°	964	991	963	560	964	744
55°	681	544	680	419	681	610
65°	423	309	426	249	423	423
75°	206	144	206	130	206	221
85°	47	31	45	35	47	53
90°	1	28	1	28	1	6
95°	66	24	66	24	66	80
105°	338	342	338	342	338	359
115°	636	631	636	631	636	630
125°	904	904	904	904	904	807
135°	1127	1123	1127	1123	1127	869
145°	1307	1304	1307	1304	1307	817
155°	1439	1429	1439	1429	1439	663
165°	1519	1511	1519	1511	1519	429
175°	1553	1546	1553	1546	1553	148
180°	1553	1553	1553	1553	1553	

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1621.7	1635.0	1639.0	1649.6	1661.6	1664.3	1670.9	1680.2	1685.5	1684.2	1684.2
5°	1616.4	1639.0	1654.9	1673.6	1696.2	1705.5	1713.5	1733.4	1749.4	1758.7	1774.7
7.5°	1607.0	1640.3	1666.9	1694.9	1729.4	1745.4	1762.7	1790.6	1819.9	1838.5	1855.8
10°	1592.4	1635.0	1672.2	1713.5	1760.0	1784.0	1805.3	1847.8	1883.8	1907.7	1947.6
12.5°	1571.1	1624.3	1676.2	1730.8	1789.3	1814.6	1843.8	1890.4	1941.0	1975.6	2008.8
15°	1548.5	1612.4	1668.2	1733.4	1803.9	1842.5	1879.8	1929.0	1974.2	2012.8	2051.4
17.5°	1521.9	1589.8	1658.9	1733.4	1813.3	1851.8	1883.8	1942.3	1990.2	2028.8	2063.4
20°	1490.0	1565.8	1644.3	1726.8	1807.9	1843.8	1874.4	1938.3	1980.9	2022.1	2071.3
22.5°	1455.4	1537.9	1621.7	1702.8	1782.7	1821.2	1857.2	1913.0	1959.6	2015.5	2079.3
25°	1415.5	1505.9	1591.1	1672.2	1748.1	1784.0	1815.9	1877.1	1942.3	2012.8	2084.6
27.5°	1375.6	1463.4	1545.9	1620.4	1702.8	1736.1	1768.0	1845.2	1922.3	1996.8	2095.3
30°	1331.7	1420.8	1492.6	1561.8	1641.6	1676.2	1716.1	1803.9	1891.7	1992.8	2112.6
32.5°	1282.4	1363.6	1430.1	1502.0	1573.8	1616.4	1666.9	1762.7	1863.8	1984.9	2137.9
35°	1233.2	1298.4	1359.6	1427.5	1513.9	1559.2	1608.4	1709.5	1835.9	1980.9	2159.1
37.5°	1170.7	1233.2	1281.1	1350.3	1439.4	1492.6	1541.9	1658.9	1802.6	1971.6	2157.8
40°	1106.8	1160.1	1205.3	1277.1	1374.2	1423.5	1476.7	1604.4	1768.0	1945.0	2125.9
42.5°	1037.7	1082.9	1132.1	1201.3	1295.7	1343.6	1404.8	1553.8	1720.1	1907.7	2043.4
45°	964.5	1008.4	1049.6	1121.5	1215.9	1267.8	1334.3	1487.3	1661.6	1829.2	1910.4
47.5°	892.7	931.2	975.1	1037.7	1133.4	1190.7	1258.5	1422.1	1583.1	1724.1	1730.8
50°	823.5	854.1	891.3	955.2	1055.0	1109.5	1180.0	1333.0	1490.0	1587.1	1521.9
52.5°	751.6	779.6	818.2	874.0	967.2	1031.0	1092.2	1245.2	1376.9	1442.1	1322.4
55°	681.1	705.1	745.0	807.5	888.7	937.9	1000.4	1142.8	1258.5	1259.8	1129.5
57.5°	612.0	633.2	666.5	722.4	798.2	855.4	912.6	1036.3	1114.8	1092.2	947.2
60°	550.8	564.1	594.7	649.2	719.7	761.0	822.1	925.9	977.8	936.6	780.9
62.5°	486.9	500.2	524.2	568.1	634.6	678.5	717.1	802.2	838.1	775.6	647.9
65°	423.0	439.0	456.3	490.9	553.4	582.7	617.3	679.8	714.4	641.2	530.8
67.5°	367.2	375.2	392.4	428.4	472.3	498.9	522.8	565.4	572.0	513.5	423.0
70°	315.3	318.0	333.9	355.2	388.5	404.4	424.4	449.7	449.7	401.8	329.9
72.5°	256.8	260.7	272.7	295.3	315.3	323.3	329.9	345.9	343.2	299.3	250.1
75°	206.2	208.9	218.2	228.8	236.8	251.4	256.8	254.1	252.8	215.5	187.6
77.5°	159.6	161.0	167.6	176.9	178.3	183.6	179.6	179.6	167.6	146.3	131.7
80°	117.1	118.4	121.1	123.7	123.7	123.7	123.7	117.1	109.1	95.8	91.8
82.5°	78.5	78.5	79.8	82.5	81.2	78.5	75.8	69.2	63.9	59.9	57.2
85°	46.6	46.6	47.9	46.6	41.2	39.9	37.2	35.9	34.6	33.3	33.3
87.5°	22.6	21.3	18.6	16.0	16.0	16.0	16.0	16.0	16.0	14.6	14.6
90°	1.2	3.2	5.3	7.3	9.4	10.4	11.3	13.1	14.8	16.6	18.4
92.5°	21.9	19.6	17.3	15.0	12.7	11.5	12.3	13.8	15.3	16.9	18.4
95°	65.6	64.8	64.1	63.3	62.6	62.2	57.3	47.6	37.9	28.1	18.4
97.5°	123.2	124.7	126.3	127.8	129.3	130.1	117.9	93.6	69.3	45.0	20.7
100°	192.3	193.1	193.9	194.6	195.4	195.8	196.3	197.3	198.4	199.4	200.4
102.5°	262.5	263.5	264.6	265.6	266.7	267.2	267.5	268.0	268.5	269.0	269.5
105°	338.5	339.5	340.6	341.6	342.7	343.2	343.2	343.2	343.2	343.2	343.2
107.5°	416.8	416.8	416.8	416.8	416.8	416.8	417.1	417.6	418.1	418.7	419.2
110°	492.8	492.8	492.8	492.8	492.8	492.8	493.1	493.6	494.1	494.7	495.2

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	564.2	565.0	565.8	566.5	567.3	567.7	567.8	568.1	568.3	568.6	568.8
115°	635.6	636.9	638.2	639.5	640.8	641.4	641.5	641.8	642.0	642.3	642.5
117.5°	710.5	710.5	710.5	710.5	710.5	710.5	711.0	712.0	713.1	714.1	715.1
120°	779.6	779.3	779.1	778.8	778.5	778.4	778.8	779.6	780.3	781.1	781.9
122.5°	840.6	841.9	843.2	844.5	845.8	846.4	846.5	846.8	847.0	847.3	847.5
125°	903.9	905.7	907.5	909.3	911.1	912.0	912.0	912.0	912.0	912.0	912.0
127.5°	965.0	966.3	967.5	968.8	970.1	970.7	970.6	970.3	970.1	969.8	969.6
130°	1020.2	1021.5	1022.8	1024.1	1025.4	1026.0	1026.1	1026.4	1026.7	1026.9	1027.2
132.5°	1075.5	1077.0	1078.6	1080.1	1081.6	1082.4	1082.0	1081.3	1080.5	1079.8	1079.0
135°	1127.3	1128.8	1130.4	1131.9	1133.4	1134.2	1133.9	1133.4	1132.9	1132.4	1131.9
137.5°	1175.7	1177.2	1178.8	1180.3	1181.8	1182.6	1182.3	1181.8	1181.3	1180.8	1180.3
140°	1222.9	1223.4	1223.9	1224.4	1224.9	1225.2	1225.1	1224.8	1224.6	1224.3	1224.1
142.5°	1265.5	1265.8	1266.0	1266.3	1266.6	1266.7	1267.0	1267.5	1268.0	1268.5	1269.0
145°	1307.0	1307.5	1308.0	1308.5	1309.0	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3
147.5°	1343.8	1343.8	1343.8	1343.8	1343.8	1343.8	1343.9	1344.2	1344.5	1344.7	1345.0
150°	1378.4	1377.9	1377.4	1376.9	1376.4	1376.1	1376.4	1376.9	1377.4	1377.9	1378.4
152.5°	1411.8	1410.5	1409.2	1407.9	1406.6	1406.0	1406.3	1406.8	1407.3	1407.8	1408.3
155°	1439.4	1437.9	1436.3	1434.8	1433.3	1432.5	1432.8	1433.3	1433.8	1434.3	1434.8
157.5°	1461.3	1460.5	1459.7	1459.0	1458.2	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8
160°	1484.3	1482.8	1481.2	1479.7	1478.2	1477.4	1477.5	1477.8	1478.0	1478.3	1478.5
162.5°	1502.7	1501.2	1499.6	1498.1	1496.6	1495.8	1495.9	1496.2	1496.5	1496.7	1497.0
165°	1518.8	1517.3	1515.7	1514.2	1512.7	1511.9	1512.0	1512.3	1512.6	1512.8	1513.1
167.5°	1531.5	1530.0	1528.4	1526.9	1525.4	1524.6	1524.7	1525.0	1525.3	1525.5	1525.8
170°	1541.9	1540.1	1538.3	1536.5	1534.7	1533.8	1533.9	1534.2	1534.5	1534.7	1535.0
172.5°	1548.8	1547.0	1545.2	1543.4	1541.6	1540.7	1541.0	1541.5	1542.0	1542.5	1543.0
175°	1553.4	1551.9	1550.3	1548.8	1547.3	1546.5	1546.6	1546.9	1547.1	1547.4	1547.6
177.5°	1556.8	1555.3	1553.7	1552.2	1550.7	1549.9	1550.0	1550.3	1550.6	1550.8	1551.1
180°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1690.9	1700.2	1708.2	1704.2	1720.1	1718.8	1721.5	1726.8	1728.1	1725.4	1720.1
5°	1782.7	1796.0	1818.6	1830.5	1827.9	1838.5	1843.8	1851.8	1859.8	1857.2	1857.2
7.5°	1885.1	1903.7	1926.3	1956.9	1960.9	1970.2	1986.2	1986.2	1995.5	1991.5	1990.2
10°	1974.2	1996.8	2032.8	2056.7	2067.3	2072.7	2088.6	2094.0	2104.6	2105.9	2105.9
12.5°	2047.4	2087.3	2111.2	2135.2	2140.5	2148.5	2160.5	2168.5	2172.4	2172.4	2168.5
15°	2086.0	2117.9	2145.8	2171.1	2185.7	2192.4	2204.4	2213.7	2219.0	2231.0	2233.6
17.5°	2101.9	2140.5	2185.7	2221.7	2246.9	2253.6	2277.5	2285.5	2296.2	2301.5	2308.1
20°	2124.6	2180.4	2235.0	2278.9	2302.8	2320.1	2345.4	2382.6	2393.3	2393.3	2389.3
22.5°	2144.5	2216.3	2290.8	2361.4	2381.3	2415.9	2462.5	2502.4	2518.3	2525.0	2519.7
25°	2168.5	2266.9	2364.0	2451.8	2506.4	2531.6	2594.2	2642.1	2660.7	2671.3	2674.0
27.5°	2209.7	2333.4	2457.1	2568.9	2624.8	2654.0	2719.2	2760.5	2783.1	2792.4	2785.7
30°	2256.3	2407.9	2551.6	2651.4	2688.6	2724.5	2767.1	2783.1	2777.7	2777.7	2797.7
32.5°	2304.1	2461.1	2588.8	2654.0	2667.3	2662.0	2644.7	2596.8	2568.9	2568.9	2586.2
35°	2330.8	2466.4	2531.6	2510.3	2458.5	2427.9	2333.4	2280.2	2220.3	2216.3	2236.3
37.5°	2316.1	2374.7	2348.0	2208.4	2137.9	2079.3	1931.7	1873.1	1829.2	1768.0	1862.5
40°	2213.7	2193.7	2055.4	1854.5	1776.0	1693.5	1576.5	1517.9	1456.7	1447.4	1470.0
42.5°	2040.7	1922.3	1720.1	1525.9	1446.1	1387.5	1298.4	1241.2	1202.6	1186.7	1213.3
45°	1825.2	1639.0	1436.8	1282.4	1194.6	1164.0	1082.9	1032.3	1003.1	991.1	1009.7
47.5°	1561.8	1374.2	1182.7	1052.3	1000.4	969.8	915.3	871.4	846.1	838.1	846.1
50°	1326.3	1133.4	972.5	888.7	842.1	816.8	771.6	743.7	723.7	718.4	731.7
52.5°	1122.8	947.2	824.8	750.3	719.7	698.4	666.5	642.6	630.6	625.3	634.6
55°	940.5	798.2	699.8	635.9	613.3	600.0	572.0	558.7	545.4	544.1	553.4
57.5°	779.6	681.1	590.7	545.4	538.8	518.8	494.9	482.9	476.3	474.9	478.9
60°	649.2	561.4	506.9	466.9	457.6	441.7	428.4	420.4	412.4	409.7	412.4
62.5°	540.1	470.9	427.0	400.4	387.1	383.1	368.5	359.2	357.9	357.9	360.5
65°	445.7	387.1	359.2	337.9	328.6	324.6	314.0	307.3	308.6	308.6	310.0
67.5°	363.2	320.6	295.3	284.7	276.7	275.4	264.7	262.1	259.4	259.4	262.1
70°	288.7	262.1	243.5	238.1	236.8	227.5	223.5	222.2	218.2	219.5	219.5
72.5°	226.2	208.9	198.2	190.2	191.6	186.2	180.9	180.9	178.3	182.3	182.3
75°	167.6	159.6	151.7	149.0	151.7	149.0	145.0	143.7	145.0	143.7	143.7
77.5°	123.7	119.7	117.1	115.7	115.7	110.4	107.8	110.4	105.1	107.8	107.8
80°	86.5	81.2	79.8	77.2	78.5	74.5	75.8	73.2	73.2	73.2	73.2
82.5°	54.5	53.2	53.2	53.2	51.9	51.9	51.9	51.9	51.9	51.9	50.6
85°	33.3	31.9	31.9	31.9	30.6	30.6	30.6	30.6	30.6	30.6	30.6
87.5°	13.3	14.6	14.6	16.0	14.6	13.3	13.3	13.3	14.6	14.6	13.3
90°	19.7	21.0	22.3	23.6	24.2	24.6	25.3	26.1	26.8	27.6	26.8
92.5°	19.7	21.0	22.3	23.6	24.2	24.3	24.6	24.8	25.1	25.3	25.1
95°	19.7	21.0	22.3	23.6	24.2	24.2	24.2	24.2	24.2	24.2	24.2
97.5°	21.2	21.7	22.2	22.7	23.0	23.1	23.4	23.7	23.9	24.2	23.9
100°	162.3	124.1	86.0	47.9	28.8	28.3	27.3	26.2	25.2	24.2	25.2
102.5°	270.0	270.5	271.0	271.5	271.8	261.0	239.5	218.0	196.5	175.0	196.5
105°	343.2	343.2	343.2	343.2	343.2	343.1	342.8	342.5	342.3	342.0	342.3
107.5°	419.4	419.7	419.9	420.2	420.3	419.8	418.8	417.7	416.7	415.7	416.7
110°	494.4	493.6	492.9	492.1	491.7	491.8	492.1	492.3	492.6	492.8	492.6

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	567.8	566.8	565.7	564.7	564.2	563.9	563.4	562.9	562.4	561.9	562.4
115°	641.5	640.5	639.4	638.4	637.9	637.1	635.6	634.1	632.5	631.0	632.5
117.5°	713.6	712.0	710.5	709.0	708.2	707.9	707.4	706.9	706.4	705.9	706.4
120°	781.4	780.9	780.4	779.9	779.6	779.0	777.7	776.4	775.1	773.8	775.1
122.5°	847.0	846.5	846.0	845.5	845.2	844.4	842.9	841.4	839.8	838.3	839.8
125°	911.0	910.0	908.9	907.9	907.4	907.0	906.2	905.5	904.7	903.9	904.7
127.5°	969.1	968.6	968.1	967.6	967.3	966.3	964.2	962.2	960.1	958.1	960.1
130°	1026.4	1025.6	1024.9	1024.1	1023.7	1023.1	1021.8	1020.5	1019.2	1017.9	1019.2
132.5°	1079.0	1079.0	1079.0	1079.0	1079.0	1078.4	1077.1	1075.8	1074.5	1073.2	1074.5
135°	1131.4	1130.9	1130.4	1129.9	1129.6	1128.8	1127.3	1125.8	1124.2	1122.7	1124.2
137.5°	1180.3	1180.3	1180.3	1180.3	1180.3	1179.7	1178.4	1177.1	1175.8	1174.5	1175.8
140°	1224.6	1225.1	1225.6	1226.1	1226.4	1225.6	1224.1	1222.6	1221.0	1219.5	1221.0
142.5°	1269.0	1269.0	1269.0	1269.0	1269.0	1268.2	1266.7	1265.2	1263.6	1262.1	1263.6
145°	1309.5	1309.8	1310.0	1310.3	1310.4	1309.6	1308.1	1306.6	1305.0	1303.5	1305.0
147.5°	1345.2	1345.5	1345.7	1346.0	1346.1	1345.2	1343.4	1341.7	1339.9	1338.1	1339.9
150°	1378.9	1379.4	1379.9	1380.4	1380.7	1379.7	1377.6	1375.6	1373.5	1371.5	1373.5
152.5°	1408.8	1409.3	1409.8	1410.3	1410.6	1409.7	1407.9	1406.1	1404.3	1402.5	1404.3
155°	1435.6	1436.3	1437.1	1437.8	1438.2	1437.2	1435.1	1433.1	1431.0	1429.0	1431.0
157.5°	1458.6	1459.4	1460.1	1460.9	1461.3	1460.3	1458.2	1456.2	1454.1	1452.1	1454.1
160°	1479.5	1480.6	1481.6	1482.7	1483.2	1482.2	1480.1	1478.0	1476.0	1473.9	1476.0
162.5°	1498.5	1500.1	1501.6	1503.1	1503.9	1502.7	1500.4	1498.1	1495.8	1493.5	1495.8
165°	1514.6	1516.2	1517.7	1519.2	1520.0	1519.0	1516.9	1514.9	1512.8	1510.8	1512.8
167.5°	1527.6	1529.4	1531.1	1532.9	1533.8	1532.7	1530.4	1528.1	1525.8	1523.5	1525.8
170°	1537.0	1539.1	1541.1	1543.2	1544.2	1543.0	1540.7	1538.4	1536.1	1533.8	1536.1
172.5°	1544.8	1546.6	1548.4	1550.2	1551.1	1549.9	1547.6	1545.3	1543.0	1540.7	1543.0
175°	1549.6	1551.7	1553.7	1555.8	1556.8	1555.7	1553.4	1551.1	1548.8	1546.5	1548.8
177.5°	1552.9	1554.7	1556.5	1558.3	1559.2	1558.2	1556.1	1554.0	1552.0	1549.9	1552.0
180°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1726.8	1717.5	1721.5	1717.5	1713.5	1709.5	1700.2	1686.9	1676.2	1668.2	1666.9
5°	1859.8	1847.8	1839.9	1835.9	1827.9	1817.2	1799.9	1780.0	1756.0	1746.7	1728.1
7.5°	1982.2	1978.2	1959.6	1956.9	1951.6	1931.7	1902.4	1875.8	1845.2	1819.9	1796.0
10°	2097.9	2088.6	2075.3	2056.7	2054.0	2028.8	2000.8	1963.6	1923.7	1899.7	1857.2
12.5°	2169.8	2159.1	2144.5	2132.5	2125.9	2109.9	2071.3	2034.1	1998.2	1954.3	1917.0
15°	2221.7	2208.4	2181.8	2172.4	2164.5	2143.2	2115.2	2076.7	2028.8	1998.2	1945.0
17.5°	2292.2	2276.2	2249.6	2232.3	2217.7	2184.4	2144.5	2092.6	2047.4	2012.8	1964.9
20°	2373.3	2349.4	2314.8	2292.2	2270.9	2232.3	2176.4	2115.2	2050.1	2007.5	1958.3
22.5°	2507.7	2462.5	2407.9	2376.0	2346.7	2280.2	2213.7	2137.9	2064.7	2000.8	1941.0
25°	2638.1	2592.8	2525.0	2481.1	2435.9	2358.7	2270.9	2165.8	2072.7	1998.2	1919.7
27.5°	2759.1	2712.6	2650.0	2596.8	2552.9	2437.2	2321.4	2203.0	2084.6	1982.2	1902.4
30°	2787.1	2767.1	2719.2	2672.7	2632.7	2526.3	2391.9	2241.6	2099.3	1967.6	1878.4
32.5°	2618.1	2667.3	2679.3	2672.7	2647.4	2571.5	2447.8	2289.5	2120.6	1960.9	1838.5
35°	2266.9	2356.0	2447.8	2497.0	2521.0	2531.6	2458.5	2313.5	2135.2	1950.3	1811.9
37.5°	1879.8	1966.2	2111.2	2184.4	2265.6	2372.0	2401.3	2308.1	2128.5	1942.3	1769.4
40°	1544.5	1654.9	1774.7	1841.2	1911.7	2103.3	2248.3	2237.6	2107.3	1913.0	1736.1
42.5°	1257.2	1326.3	1431.4	1504.6	1591.1	1805.3	1999.5	2095.3	2043.4	1877.1	1693.5
45°	1048.3	1101.5	1176.0	1250.5	1303.7	1498.0	1728.1	1885.1	1934.3	1813.3	1628.3
47.5°	883.3	923.3	988.4	1035.0	1092.2	1245.2	1444.7	1665.6	1769.4	1722.8	1559.2
50°	757.0	788.9	840.8	870.0	920.6	1052.3	1204.0	1435.4	1592.4	1597.7	1467.4
52.5°	646.5	678.5	722.4	747.7	778.2	867.4	1020.4	1215.9	1396.9	1463.4	1362.3
55°	562.7	581.4	617.3	637.2	665.2	751.6	848.8	1015.0	1204.0	1313.0	1249.2
57.5°	485.6	505.5	528.1	544.1	564.1	633.2	721.0	846.1	1033.7	1152.1	1130.8
60°	423.0	435.0	456.3	468.3	486.9	532.1	593.3	718.4	867.4	979.1	991.1
62.5°	364.5	375.2	389.8	400.4	412.4	448.3	493.6	582.7	713.1	834.1	850.1
65°	314.0	323.3	331.3	340.6	349.9	372.5	411.1	480.3	581.4	694.4	729.0
67.5°	268.7	271.4	283.4	284.7	290.0	307.3	335.2	391.1	464.3	554.8	600.0
70°	224.8	230.1	232.8	236.8	242.1	254.1	276.7	306.0	360.5	433.7	476.3
72.5°	182.3	183.6	187.6	190.2	195.6	204.9	215.5	238.1	272.7	325.9	364.5
75°	145.0	146.3	149.0	150.3	154.3	157.0	162.3	178.3	202.2	234.1	262.1
77.5°	109.1	111.7	114.4	114.4	115.7	118.4	121.1	126.4	138.4	159.6	183.6
80°	74.5	75.8	75.8	77.2	75.8	79.8	83.8	90.5	95.8	102.4	114.4
82.5°	51.9	51.9	51.9	53.2	53.2	54.5	54.5	55.9	57.2	61.2	66.5
85°	31.9	31.9	33.3	30.6	31.9	33.3	33.3	31.9	33.3	34.6	35.9
87.5°	13.3	13.3	14.6	14.6	14.6	14.6	13.3	14.6	13.3	14.6	14.6
90°	26.1	25.3	24.6	24.2	23.6	22.3	21.0	19.7	18.4	16.6	14.8
92.5°	24.8	24.6	24.3	24.2	23.6	22.3	21.0	19.7	18.4	16.9	15.3
95°	24.2	24.2	24.2	24.2	23.6	22.3	21.0	19.7	18.4	28.1	37.9
97.5°	23.7	23.4	23.1	23.0	22.7	22.2	21.7	21.2	20.7	45.0	69.3
100°	26.2	27.3	28.3	28.8	47.9	86.0	124.1	162.3	200.4	199.4	198.4
102.5°	218.0	239.5	261.0	271.8	271.5	271.0	270.5	270.0	269.5	269.0	268.5
105°	342.5	342.8	343.1	343.2	343.2	343.2	343.2	343.2	343.2	343.2	343.2
107.5°	417.7	418.8	419.8	420.3	420.2	419.9	419.7	419.4	419.2	418.7	418.1
110°	492.3	492.1	491.8	491.7	492.1	492.9	493.6	494.4	495.2	494.7	494.1

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	562.9	563.4	563.9	564.2	564.7	565.7	566.8	567.8	568.8	568.6	568.3
115°	634.1	635.6	637.1	637.9	638.4	639.4	640.5	641.5	642.5	642.3	642.0
117.5°	706.9	707.4	707.9	708.2	709.0	710.5	712.0	713.6	715.1	714.1	713.1
120°	776.4	777.7	779.0	779.6	779.9	780.4	780.9	781.4	781.9	781.1	780.3
122.5°	841.4	842.9	844.4	845.2	845.5	846.0	846.5	847.0	847.5	847.3	847.0
125°	905.5	906.2	907.0	907.4	907.9	908.9	910.0	911.0	912.0	912.0	912.0
127.5°	962.2	964.2	966.3	967.3	967.6	968.1	968.6	969.1	969.6	969.8	970.1
130°	1020.5	1021.8	1023.1	1023.7	1024.1	1024.9	1025.6	1026.4	1027.2	1026.9	1026.7
132.5°	1075.8	1077.1	1078.4	1079.0	1079.0	1079.0	1079.0	1079.0	1079.0	1079.8	1080.5
135°	1125.8	1127.3	1128.8	1129.6	1129.9	1130.4	1130.9	1131.4	1131.9	1132.4	1132.9
137.5°	1177.1	1178.4	1179.7	1180.3	1180.3	1180.3	1180.3	1180.3	1180.3	1180.8	1181.3
140°	1222.6	1224.1	1225.6	1226.4	1226.1	1225.6	1225.1	1224.6	1224.1	1224.3	1224.6
142.5°	1265.2	1266.7	1268.2	1269.0	1269.0	1269.0	1269.0	1269.0	1269.0	1268.5	1268.0
145°	1306.6	1308.1	1309.6	1310.4	1310.3	1310.0	1309.8	1309.5	1309.3	1309.3	1309.3
147.5°	1341.7	1343.4	1345.2	1346.1	1346.0	1345.7	1345.5	1345.2	1345.0	1344.7	1344.5
150°	1375.6	1377.6	1379.7	1380.7	1380.4	1379.9	1379.4	1378.9	1378.4	1377.9	1377.4
152.5°	1406.1	1407.9	1409.7	1410.6	1410.3	1409.8	1409.3	1408.8	1408.3	1407.8	1407.3
155°	1433.1	1435.1	1437.2	1438.2	1437.8	1437.1	1436.3	1435.6	1434.8	1434.3	1433.8
157.5°	1456.2	1458.2	1460.3	1461.3	1460.9	1460.1	1459.4	1458.6	1457.8	1457.8	1457.8
160°	1478.0	1480.1	1482.2	1483.2	1482.7	1481.6	1480.6	1479.5	1478.5	1478.3	1478.0
162.5°	1498.1	1500.4	1502.7	1503.9	1503.1	1501.6	1500.1	1498.5	1497.0	1496.7	1496.5
165°	1514.9	1516.9	1519.0	1520.0	1519.2	1517.7	1516.2	1514.6	1513.1	1512.8	1512.6
167.5°	1528.1	1530.4	1532.7	1533.8	1532.9	1531.1	1529.4	1527.6	1525.8	1525.5	1525.3
170°	1538.4	1540.7	1543.0	1544.2	1543.2	1541.1	1539.1	1537.0	1535.0	1534.7	1534.5
172.5°	1545.3	1547.6	1549.9	1551.1	1550.2	1548.4	1546.6	1544.8	1543.0	1542.5	1542.0
175°	1551.1	1553.4	1555.7	1556.8	1555.8	1553.7	1551.7	1549.6	1547.6	1547.4	1547.1
177.5°	1554.0	1556.1	1558.2	1559.2	1558.3	1556.5	1554.7	1552.9	1551.1	1550.8	1550.6
180°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1662.9	1654.9	1649.6	1648.3	1640.3	1633.7	1625.7	1624.3	1620.4	1609.7	1603.1
5°	1714.8	1696.2	1692.2	1680.2	1660.3	1645.6	1627.0	1616.4	1604.4	1584.4	1568.5
7.5°	1768.0	1742.7	1724.1	1706.8	1678.9	1652.3	1625.7	1604.4	1583.1	1553.8	1529.9
10°	1819.9	1781.3	1758.7	1733.4	1694.9	1654.9	1617.7	1587.1	1552.5	1517.9	1483.3
12.5°	1867.8	1818.6	1785.3	1749.4	1701.5	1652.3	1604.4	1561.8	1525.9	1479.3	1440.8
15°	1897.1	1842.5	1809.3	1774.7	1702.8	1648.3	1592.4	1537.9	1490.0	1440.8	1404.8
17.5°	1914.4	1853.2	1815.9	1784.0	1710.8	1636.3	1564.5	1505.9	1454.1	1395.5	1347.6
20°	1906.4	1846.5	1811.9	1781.3	1696.2	1621.7	1544.5	1476.7	1411.5	1351.6	1301.1
22.5°	1889.1	1826.6	1788.0	1760.0	1684.2	1596.4	1511.3	1438.1	1370.2	1310.4	1253.2
25°	1851.8	1790.6	1757.4	1722.8	1648.3	1564.5	1478.0	1399.5	1327.7	1263.8	1200.0
27.5°	1818.6	1744.1	1709.5	1678.9	1600.4	1525.9	1440.8	1354.3	1281.1	1214.6	1150.7
30°	1780.0	1696.2	1658.9	1617.7	1547.2	1476.7	1391.5	1311.7	1235.9	1165.4	1104.2
32.5°	1738.8	1641.6	1599.1	1552.5	1480.7	1414.2	1342.3	1263.8	1188.0	1118.8	1055.0
35°	1685.5	1581.8	1532.6	1488.6	1414.2	1347.6	1281.1	1215.9	1140.1	1066.9	1005.7
37.5°	1635.0	1520.6	1468.7	1418.1	1339.7	1275.8	1221.3	1160.1	1086.9	1016.4	957.8
40°	1577.8	1446.1	1392.9	1346.3	1265.2	1194.6	1145.4	1097.5	1033.7	965.8	902.0
42.5°	1525.9	1376.9	1321.0	1273.1	1188.0	1121.5	1074.9	1035.0	979.1	916.6	851.4
45°	1454.1	1302.4	1245.2	1194.6	1108.2	1045.6	997.8	963.2	919.3	860.7	802.2
47.5°	1387.5	1230.6	1168.0	1106.8	1028.4	964.5	920.6	894.0	864.7	812.8	753.0
50°	1306.4	1148.1	1084.2	1033.7	944.5	890.0	846.1	827.5	800.9	751.6	703.7
52.5°	1218.6	1068.3	1008.4	947.2	864.7	811.5	772.9	751.6	730.4	694.4	649.2
55°	1116.2	979.1	923.3	868.7	786.2	737.0	702.4	679.8	667.8	634.6	601.3
57.5°	1017.7	888.7	836.8	786.2	714.4	658.5	635.9	615.9	598.7	574.7	546.8
60°	917.9	800.9	745.0	699.8	637.2	586.7	568.1	548.1	534.8	516.2	496.2
62.5°	803.5	703.7	661.2	618.6	565.4	525.5	504.2	488.2	470.9	459.0	441.7
65°	682.5	612.0	570.7	538.8	488.2	452.3	436.4	425.7	411.1	399.1	385.8
67.5°	569.4	513.5	496.2	461.6	423.0	391.1	379.1	365.8	353.9	347.2	335.2
70°	460.3	420.4	403.1	393.8	351.2	329.9	319.3	314.0	299.3	292.7	284.7
72.5°	356.5	341.9	329.9	318.0	290.0	276.7	264.7	259.4	248.8	243.5	240.8
75°	263.4	254.1	247.4	246.1	234.1	220.8	208.9	206.2	198.2	192.9	190.2
77.5°	184.9	182.3	180.9	182.3	174.3	166.3	163.6	161.0	151.7	150.3	150.3
80°	121.1	127.7	127.7	126.4	123.7	122.4	118.4	115.7	110.4	109.1	110.4
82.5°	74.5	78.5	79.8	82.5	81.2	79.8	77.2	75.8	77.2	74.5	75.8
85°	37.2	39.9	45.2	45.2	46.6	46.6	46.6	45.2	42.6	43.9	42.6
87.5°	14.6	16.0	16.0	16.0	14.6	18.6	20.0	20.0	20.0	17.3	17.3
90°	13.1	11.3	10.4	9.4	7.3	5.3	3.2	1.2	3.2	5.3	7.3
92.5°	13.8	12.3	11.5	12.7	15.0	17.3	19.6	21.9	19.6	17.3	15.0
95°	47.6	57.3	62.2	62.6	63.3	64.1	64.8	65.6	64.8	64.1	63.3
97.5°	93.6	117.9	130.1	129.3	127.8	126.3	124.7	123.2	124.7	126.3	127.8
100°	197.3	196.3	195.8	195.4	194.6	193.9	193.1	192.3	193.1	193.9	194.6
102.5°	268.0	267.5	267.2	266.7	265.6	264.6	263.5	262.5	263.5	264.6	265.6
105°	343.2	343.2	343.2	342.7	341.6	340.6	339.5	338.5	339.5	340.6	341.6
107.5°	417.6	417.1	416.8	416.8	416.8	416.8	416.8	416.8	416.8	416.8	416.8
110°	493.6	493.1	492.8	492.8	492.8	492.8	492.8	492.8	492.8	492.8	492.8

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	568.1	567.8	567.7	567.3	566.5	565.8	565.0	564.2	565.0	565.8	566.5
115°	641.8	641.5	641.4	640.8	639.5	638.2	636.9	635.6	636.9	638.2	639.5
117.5°	712.0	711.0	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
120°	779.6	778.8	778.4	778.5	778.8	779.1	779.3	779.6	779.3	779.1	778.8
122.5°	846.8	846.5	846.4	845.8	844.5	843.2	841.9	840.6	841.9	843.2	844.5
125°	912.0	912.0	912.0	911.1	909.3	907.5	905.7	903.9	905.7	907.5	909.3
127.5°	970.3	970.6	970.7	970.1	968.8	967.5	966.3	965.0	966.3	967.5	968.8
130°	1026.4	1026.1	1026.0	1025.4	1024.1	1022.8	1021.5	1020.2	1021.5	1022.8	1024.1
132.5°	1081.3	1082.0	1082.4	1081.6	1080.1	1078.6	1077.0	1075.5	1077.0	1078.6	1080.1
135°	1133.4	1133.9	1134.2	1133.4	1131.9	1130.4	1128.8	1127.3	1128.8	1130.4	1131.9
137.5°	1181.8	1182.3	1182.6	1181.8	1180.3	1178.8	1177.2	1175.7	1177.2	1178.8	1180.3
140°	1224.8	1225.1	1225.2	1224.9	1224.4	1223.9	1223.4	1222.9	1223.4	1223.9	1224.4
142.5°	1267.5	1267.0	1266.7	1266.6	1266.3	1266.0	1265.8	1265.5	1265.8	1266.0	1266.3
145°	1309.3	1309.3	1309.3	1309.0	1308.5	1308.0	1307.5	1307.0	1307.5	1308.0	1308.5
147.5°	1344.2	1343.9	1343.8	1343.8	1343.8	1343.8	1343.8	1343.8	1343.8	1343.8	1343.8
150°	1376.9	1376.4	1376.1	1376.4	1376.9	1377.4	1377.9	1378.4	1377.9	1377.4	1376.9
152.5°	1406.8	1406.3	1406.0	1406.6	1407.9	1409.2	1410.5	1411.8	1410.5	1409.2	1407.9
155°	1433.3	1432.8	1432.5	1433.3	1434.8	1436.3	1437.9	1439.4	1437.9	1436.3	1434.8
157.5°	1457.8	1457.8	1457.8	1458.2	1459.0	1459.7	1460.5	1461.3	1460.5	1459.7	1459.0
160°	1477.8	1477.5	1477.4	1478.2	1479.7	1481.2	1482.8	1484.3	1482.8	1481.2	1479.7
162.5°	1496.2	1495.9	1495.8	1496.6	1498.1	1499.6	1501.2	1502.7	1501.2	1499.6	1498.1
165°	1512.3	1512.0	1511.9	1512.7	1514.2	1515.7	1517.3	1518.8	1517.3	1515.7	1514.2
167.5°	1525.0	1524.7	1524.6	1525.4	1526.9	1528.4	1530.0	1531.5	1530.0	1528.4	1526.9
170°	1534.2	1533.9	1533.8	1534.7	1536.5	1538.3	1540.1	1541.9	1540.1	1538.3	1536.5
172.5°	1541.5	1541.0	1540.7	1541.6	1543.4	1545.2	1547.0	1548.8	1547.0	1545.2	1543.4
175°	1546.9	1546.6	1546.5	1547.3	1548.8	1550.3	1551.9	1553.4	1551.9	1550.3	1548.8
177.5°	1550.3	1550.0	1549.9	1550.7	1552.2	1553.7	1555.3	1556.8	1555.3	1553.7	1552.2
180°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1599.1	1593.7	1589.8	1585.8	1568.5	1549.8	1547.2	1543.2	1535.2	1544.5	1540.5
5°	1557.8	1545.9	1539.2	1521.9	1500.6	1484.7	1471.4	1455.4	1448.7	1443.4	1442.1
7.5°	1507.3	1496.6	1484.7	1467.4	1440.8	1414.2	1394.2	1378.2	1364.9	1358.3	1358.3
10°	1458.1	1444.7	1428.8	1399.5	1374.2	1341.0	1319.7	1303.7	1285.1	1274.5	1265.2
12.5°	1407.5	1392.9	1378.2	1341.0	1311.7	1277.1	1246.5	1226.6	1217.3	1205.3	1189.3
15°	1356.9	1334.3	1319.7	1282.4	1245.2	1210.6	1190.7	1169.4	1148.1	1136.1	1130.8
17.5°	1303.7	1287.8	1263.8	1223.9	1182.7	1152.1	1122.8	1102.9	1077.6	1065.6	1053.6
20°	1255.8	1231.9	1207.9	1168.0	1128.1	1086.9	1057.6	1033.7	1017.7	1008.4	997.8
22.5°	1198.6	1176.0	1156.1	1113.5	1069.6	1031.0	999.1	984.5	968.5	953.9	943.2
25°	1149.4	1126.8	1106.8	1060.3	1012.4	976.5	952.5	933.9	916.6	910.0	899.3
27.5°	1097.5	1076.2	1049.6	1003.1	960.5	929.9	904.6	887.3	874.0	860.7	852.7
30°	1048.3	1024.4	1000.4	949.9	915.3	884.7	860.7	839.4	828.8	822.1	808.8
32.5°	1000.4	969.8	949.9	903.3	870.0	840.8	820.8	802.2	788.9	776.9	766.3
35°	948.5	915.3	895.3	856.7	822.1	792.9	775.6	762.3	746.3	735.7	730.4
37.5°	899.3	871.4	851.4	811.5	776.9	753.0	734.3	717.1	710.4	695.8	693.1
40°	846.1	822.1	803.5	764.9	733.0	714.4	694.4	678.5	666.5	659.8	650.5
42.5°	798.2	778.2	758.3	722.4	691.8	669.2	654.5	639.9	629.3	618.6	612.0
45°	754.3	733.0	714.4	679.8	649.2	629.3	614.6	597.3	594.7	580.0	573.4
47.5°	707.7	689.1	673.2	637.2	609.3	589.3	572.0	560.1	548.1	542.8	533.5
50°	662.5	643.9	625.3	593.3	568.1	548.1	530.8	517.5	510.9	502.9	494.9
52.5°	613.3	598.7	584.0	550.8	525.5	508.2	493.6	476.3	469.6	463.0	457.6
55°	572.0	550.8	534.8	506.9	484.2	465.6	449.7	436.4	429.7	424.4	417.7
57.5°	516.2	502.9	489.6	464.3	443.0	424.4	408.4	397.8	389.8	385.8	387.1
60°	468.3	453.6	445.7	419.1	397.8	383.1	368.5	357.9	349.9	345.9	344.6
62.5°	417.7	407.1	392.4	373.8	352.5	339.2	328.6	320.6	307.3	306.0	302.0
65°	368.5	360.5	347.2	329.9	312.6	300.7	288.7	278.0	272.7	266.1	262.1
67.5°	320.6	312.6	300.7	286.0	274.0	262.1	251.4	240.8	231.5	226.2	223.5
70°	274.0	267.4	259.4	242.1	227.5	218.2	210.2	203.5	194.2	191.6	190.2
72.5°	228.8	222.2	218.2	203.5	190.2	182.3	174.3	167.6	163.6	162.3	158.3
75°	187.6	180.9	175.6	162.3	154.3	149.0	141.0	138.4	134.4	133.0	131.7
77.5°	146.3	139.7	138.4	129.0	119.7	117.1	114.4	109.1	109.1	109.1	106.4
80°	105.1	103.8	102.4	93.1	89.1	86.5	85.1	81.2	78.5	75.8	74.5
82.5°	70.5	69.2	67.8	63.9	59.9	58.5	57.2	54.5	54.5	55.9	53.2
85°	42.6	39.9	38.6	37.2	34.6	34.6	35.9	34.6	34.6	34.6	33.3
87.5°	16.0	16.0	16.0	16.0	17.3	14.6	16.0	16.0	14.6	14.6	13.3
90°	9.4	10.4	11.3	13.1	14.8	16.6	18.4	19.7	21.0	22.3	23.6
92.5°	12.7	11.5	12.3	13.8	15.3	16.9	18.4	19.7	21.0	22.3	23.6
95°	62.6	62.2	57.3	47.6	37.9	28.1	18.4	19.7	21.0	22.3	23.6
97.5°	129.3	130.1	117.9	93.6	69.3	45.0	20.7	21.2	21.7	22.2	22.7
100°	195.4	195.8	196.3	197.3	198.4	199.4	200.4	162.3	124.1	86.0	47.9
102.5°	266.7	267.2	267.5	268.0	268.5	269.0	269.5	270.0	270.5	271.0	271.5
105°	342.7	343.2	343.2	343.2	343.2	343.2	343.2	343.2	343.2	343.2	343.2
107.5°	416.8	416.8	417.1	417.6	418.1	418.7	419.2	419.4	419.7	419.9	420.2
110°	492.8	492.8	493.1	493.6	494.1	494.7	495.2	494.4	493.6	492.9	492.1

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	567.3	567.7	567.8	568.1	568.3	568.6	568.8	567.8	566.8	565.7	564.7
115°	640.8	641.4	641.5	641.8	642.0	642.3	642.5	641.5	640.5	639.4	638.4
117.5°	710.5	710.5	711.0	712.0	713.1	714.1	715.1	713.6	712.0	710.5	709.0
120°	778.5	778.4	778.8	779.6	780.3	781.1	781.9	781.4	780.9	780.4	779.9
122.5°	845.8	846.4	846.5	846.8	847.0	847.3	847.5	847.0	846.5	846.0	845.5
125°	911.1	912.0	912.0	912.0	912.0	912.0	912.0	911.0	910.0	908.9	907.9
127.5°	970.1	970.7	970.6	970.3	970.1	969.8	969.6	969.1	968.6	968.1	967.6
130°	1025.4	1026.0	1026.1	1026.4	1026.7	1026.9	1027.2	1026.4	1025.6	1024.9	1024.1
132.5°	1081.6	1082.4	1082.0	1081.3	1080.5	1079.8	1079.0	1079.0	1079.0	1079.0	1079.0
135°	1133.4	1134.2	1133.9	1133.4	1132.9	1132.4	1131.9	1131.4	1130.9	1130.4	1129.9
137.5°	1181.8	1182.6	1182.3	1181.8	1181.3	1180.8	1180.3	1180.3	1180.3	1180.3	1180.3
140°	1224.9	1225.2	1225.1	1224.8	1224.6	1224.3	1224.1	1224.6	1225.1	1225.6	1226.1
142.5°	1266.6	1266.7	1267.0	1267.5	1268.0	1268.5	1269.0	1269.0	1269.0	1269.0	1269.0
145°	1309.0	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3	1309.5	1309.8	1310.0	1310.3
147.5°	1343.8	1343.8	1343.9	1344.2	1344.5	1344.7	1345.0	1345.2	1345.5	1345.7	1346.0
150°	1376.4	1376.1	1376.4	1376.9	1377.4	1377.9	1378.4	1378.9	1379.4	1379.9	1380.4
152.5°	1406.6	1406.0	1406.3	1406.8	1407.3	1407.8	1408.3	1408.8	1409.3	1409.8	1410.3
155°	1433.3	1432.5	1432.8	1433.3	1433.8	1434.3	1434.8	1435.6	1436.3	1437.1	1437.8
157.5°	1458.2	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1458.6	1459.4	1460.1	1460.9
160°	1478.2	1477.4	1477.5	1477.8	1478.0	1478.3	1478.5	1479.5	1480.6	1481.6	1482.7
162.5°	1496.6	1495.8	1495.9	1496.2	1496.5	1496.7	1497.0	1498.5	1500.1	1501.6	1503.1
165°	1512.7	1511.9	1512.0	1512.3	1512.6	1512.8	1513.1	1514.6	1516.2	1517.7	1519.2
167.5°	1525.4	1524.6	1524.7	1525.0	1525.3	1525.5	1525.8	1527.6	1529.4	1531.1	1532.9
170°	1534.7	1533.8	1533.9	1534.2	1534.5	1534.7	1535.0	1537.0	1539.1	1541.1	1543.2
172.5°	1541.6	1540.7	1541.0	1541.5	1542.0	1542.5	1543.0	1544.8	1546.6	1548.4	1550.2
175°	1547.3	1546.5	1546.6	1546.9	1547.1	1547.4	1547.6	1549.6	1551.7	1553.7	1555.8
177.5°	1550.7	1549.9	1550.0	1550.3	1550.6	1550.8	1551.1	1552.9	1554.7	1556.5	1558.3
180°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1533.9	1536.5	1529.9	1527.2	1521.9	1528.6	1529.9	1528.6	1540.5	1535.2	1537.9
5°	1444.7	1439.4	1435.4	1426.1	1426.1	1427.5	1431.4	1424.8	1428.8	1438.1	1436.8
7.5°	1346.3	1343.6	1345.0	1334.3	1326.3	1329.0	1326.3	1338.3	1345.0	1342.3	1347.6
10°	1257.2	1262.5	1250.5	1245.2	1239.9	1245.2	1243.9	1246.5	1254.5	1259.8	1269.1
12.5°	1185.3	1184.0	1177.3	1172.0	1162.7	1165.4	1173.4	1170.7	1172.0	1184.0	1182.7
15°	1117.5	1109.5	1104.2	1092.2	1094.9	1085.6	1093.5	1102.9	1106.8	1117.5	1124.1
17.5°	1049.6	1048.3	1041.7	1040.3	1025.7	1021.7	1029.7	1032.3	1036.3	1041.7	1051.0
20°	992.4	991.1	981.8	979.1	967.2	975.1	972.5	977.8	980.5	991.1	995.1
22.5°	940.5	933.9	931.2	927.2	923.3	921.9	927.2	925.9	935.2	939.2	940.5
25°	892.7	887.3	886.0	879.4	876.7	872.7	876.7	880.7	891.3	895.3	900.6
27.5°	848.8	844.8	842.1	836.8	832.8	832.8	835.5	840.8	844.8	847.4	850.1
30°	808.8	806.2	798.2	795.5	791.6	791.6	791.6	794.2	800.9	808.8	812.8
32.5°	767.6	762.3	757.0	757.0	753.0	753.0	754.3	757.0	763.6	764.9	771.6
35°	727.7	722.4	718.4	715.7	717.1	711.7	714.4	718.4	726.4	729.0	733.0
37.5°	689.1	687.8	679.8	675.8	678.5	678.5	677.1	679.8	685.1	690.4	693.1
40°	646.5	643.9	643.9	639.9	641.2	635.9	639.9	642.6	645.2	650.5	654.5
42.5°	609.3	606.6	601.3	602.6	598.7	598.7	601.3	602.6	606.6	613.3	615.9
45°	569.4	569.4	566.7	562.7	564.1	560.1	562.7	564.1	569.4	576.0	573.4
47.5°	530.8	529.5	529.5	524.2	526.8	522.8	526.8	528.1	530.8	534.8	533.5
50°	493.6	489.6	490.9	489.6	488.2	488.2	490.9	490.9	493.6	493.6	497.5
52.5°	455.0	455.0	452.3	453.6	456.3	453.6	457.6	453.6	456.3	457.6	460.3
55°	420.4	417.7	419.1	417.7	423.0	419.1	423.0	420.4	423.0	421.7	424.4
57.5°	383.1	379.1	380.5	379.1	383.1	381.8	385.8	381.8	383.1	384.5	388.5
60°	340.6	340.6	340.6	337.9	341.9	341.9	340.6	340.6	345.9	348.5	347.2
62.5°	300.7	299.3	295.3	294.0	295.3	292.7	298.0	296.7	299.3	302.0	304.6
65°	256.8	254.1	252.8	250.1	250.1	248.8	250.1	255.4	256.8	258.1	264.7
67.5°	220.8	219.5	218.2	214.2	214.2	216.8	216.8	216.8	224.8	220.8	226.2
70°	188.9	186.2	183.6	182.3	182.3	183.6	184.9	186.2	184.9	190.2	191.6
72.5°	158.3	159.6	157.0	157.0	157.0	155.6	155.6	158.3	159.6	158.3	159.6
75°	131.7	131.7	130.4	131.7	131.7	130.4	130.4	133.0	133.0	131.7	135.7
77.5°	106.4	105.1	102.4	99.8	101.1	99.8	101.1	99.8	103.8	107.8	105.1
80°	74.5	73.2	73.2	73.2	74.5	73.2	75.8	73.2	74.5	74.5	75.8
82.5°	53.2	54.5	54.5	53.2	54.5	53.2	54.5	54.5	54.5	53.2	54.5
85°	34.6	34.6	34.6	34.6	33.3	34.6	34.6	34.6	35.9	34.6	35.9
87.5°	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	16.0	14.6	16.0
90°	24.2	24.6	25.3	26.1	26.8	27.6	26.8	26.1	25.3	24.6	24.2
92.5°	24.2	24.3	24.6	24.8	25.1	25.3	25.1	24.8	24.6	24.3	24.2
95°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
97.5°	23.0	23.1	23.4	23.7	23.9	24.2	23.9	23.7	23.4	23.1	23.0
100°	28.8	28.3	27.3	26.2	25.2	24.2	25.2	26.2	27.3	28.3	28.8
102.5°	271.8	261.0	239.5	218.0	196.5	175.0	196.5	218.0	239.5	261.0	271.8
105°	343.2	343.1	342.8	342.5	342.3	342.0	342.3	342.5	342.8	343.1	343.2
107.5°	420.3	419.8	418.8	417.7	416.7	415.7	416.7	417.7	418.8	419.8	420.3
110°	491.7	491.8	492.1	492.3	492.6	492.8	492.6	492.3	492.1	491.8	491.7

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	564.2	563.9	563.4	562.9	562.4	561.9	562.4	562.9	563.4	563.9	564.2
115°	637.9	637.1	635.6	634.1	632.5	631.0	632.5	634.1	635.6	637.1	637.9
117.5°	708.2	707.9	707.4	706.9	706.4	705.9	706.4	706.9	707.4	707.9	708.2
120°	779.6	779.0	777.7	776.4	775.1	773.8	775.1	776.4	777.7	779.0	779.6
122.5°	845.2	844.4	842.9	841.4	839.8	838.3	839.8	841.4	842.9	844.4	845.2
125°	907.4	907.0	906.2	905.5	904.7	903.9	904.7	905.5	906.2	907.0	907.4
127.5°	967.3	966.3	964.2	962.2	960.1	958.1	960.1	962.2	964.2	966.3	967.3
130°	1023.7	1023.1	1021.8	1020.5	1019.2	1017.9	1019.2	1020.5	1021.8	1023.1	1023.7
132.5°	1079.0	1078.4	1077.1	1075.8	1074.5	1073.2	1074.5	1075.8	1077.1	1078.4	1079.0
135°	1129.6	1128.8	1127.3	1125.8	1124.2	1122.7	1124.2	1125.8	1127.3	1128.8	1129.6
137.5°	1180.3	1179.7	1178.4	1177.1	1175.8	1174.5	1175.8	1177.1	1178.4	1179.7	1180.3
140°	1226.4	1225.6	1224.1	1222.6	1221.0	1219.5	1221.0	1222.6	1224.1	1225.6	1226.4
142.5°	1269.0	1268.2	1266.7	1265.2	1263.6	1262.1	1263.6	1265.2	1266.7	1268.2	1269.0
145°	1310.4	1309.6	1308.1	1306.6	1305.0	1303.5	1305.0	1306.6	1308.1	1309.6	1310.4
147.5°	1346.1	1345.2	1343.4	1341.7	1339.9	1338.1	1339.9	1341.7	1343.4	1345.2	1346.1
150°	1380.7	1379.7	1377.6	1375.6	1373.5	1371.5	1373.5	1375.6	1377.6	1379.7	1380.7
152.5°	1410.6	1409.7	1407.9	1406.1	1404.3	1402.5	1404.3	1406.1	1407.9	1409.7	1410.6
155°	1438.2	1437.2	1435.1	1433.1	1431.0	1429.0	1431.0	1433.1	1435.1	1437.2	1438.2
157.5°	1461.3	1460.3	1458.2	1456.2	1454.1	1452.1	1454.1	1456.2	1458.2	1460.3	1461.3
160°	1483.2	1482.2	1480.1	1478.0	1476.0	1473.9	1476.0	1478.0	1480.1	1482.2	1483.2
162.5°	1503.9	1502.7	1500.4	1498.1	1495.8	1493.5	1495.8	1498.1	1500.4	1502.7	1503.9
165°	1520.0	1519.0	1516.9	1514.9	1512.8	1510.8	1512.8	1514.9	1516.9	1519.0	1520.0
167.5°	1533.8	1532.7	1530.4	1528.1	1525.8	1523.5	1525.8	1528.1	1530.4	1532.7	1533.8
170°	1544.2	1543.0	1540.7	1538.4	1536.1	1533.8	1536.1	1538.4	1540.7	1543.0	1544.2
172.5°	1551.1	1549.9	1547.6	1545.3	1543.0	1540.7	1543.0	1545.3	1547.6	1549.9	1551.1
175°	1556.8	1555.7	1553.4	1551.1	1548.8	1546.5	1548.8	1551.1	1553.4	1555.7	1556.8
177.5°	1559.2	1558.2	1556.1	1554.0	1552.0	1549.9	1552.0	1554.0	1556.1	1558.2	1559.2
180°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1532.6	1539.2	1533.9	1529.9	1540.5	1545.9	1545.9	1555.2	1564.5	1572.5	1573.8
5°	1438.1	1448.7	1451.4	1450.1	1466.0	1474.0	1491.3	1500.6	1513.9	1523.2	1533.9
7.5°	1351.6	1366.3	1367.6	1370.2	1394.2	1407.5	1422.1	1446.1	1464.7	1478.0	1490.0
10°	1265.2	1274.5	1283.8	1295.7	1319.7	1342.3	1363.6	1388.9	1412.8	1426.1	1443.4
12.5°	1200.0	1206.6	1217.3	1225.2	1250.5	1270.5	1298.4	1333.0	1367.6	1378.2	1399.5
15°	1132.1	1136.1	1157.4	1165.4	1186.7	1219.9	1237.2	1270.5	1307.7	1327.7	1351.6
17.5°	1053.6	1077.6	1090.9	1100.2	1126.8	1153.4	1181.3	1215.9	1263.8	1282.4	1299.7
20°	997.8	1015.0	1029.7	1041.7	1065.6	1105.5	1130.8	1158.7	1204.0	1225.2	1250.5
22.5°	948.5	963.2	976.5	989.8	1005.7	1041.7	1070.9	1109.5	1154.7	1174.7	1204.0
25°	902.0	916.6	924.6	940.5	961.8	987.1	1021.7	1056.3	1101.5	1124.1	1152.1
27.5°	856.7	871.4	886.0	899.3	913.9	937.9	961.8	1005.7	1052.3	1078.9	1102.9
30°	818.2	824.8	838.1	852.7	867.4	890.0	917.9	948.5	1001.7	1025.7	1055.0
32.5°	775.6	787.6	796.9	807.5	826.1	844.8	870.0	908.6	951.2	973.8	1005.7
35°	735.7	746.3	753.0	771.6	783.6	803.5	828.8	863.4	899.3	924.6	952.5
37.5°	697.1	707.7	715.7	726.4	742.3	759.6	786.2	811.5	854.1	875.4	907.3
40°	657.2	666.5	675.8	687.8	702.4	723.7	739.7	771.6	806.2	830.1	854.1
42.5°	618.6	623.9	634.6	647.9	662.5	681.1	703.7	729.0	763.6	784.9	806.2
45°	577.4	586.7	598.7	608.0	621.3	639.9	659.8	682.5	717.1	738.3	761.0
47.5°	538.8	545.4	553.4	568.1	585.3	598.7	619.9	641.2	673.2	693.1	714.4
50°	498.9	505.5	517.5	526.8	540.1	557.4	577.4	600.0	630.6	643.9	665.2
52.5°	461.6	464.3	476.3	485.6	498.9	518.8	534.8	554.8	584.0	598.7	619.9
55°	424.4	427.0	433.7	443.0	457.6	473.6	490.9	513.5	538.8	552.1	572.0
57.5°	385.8	388.5	395.1	401.8	416.4	431.0	451.0	469.6	494.9	506.9	525.5
60°	347.2	347.2	353.9	363.2	373.8	387.1	404.4	427.0	445.7	460.3	473.6
62.5°	306.0	310.0	314.0	320.6	332.6	348.5	363.2	379.1	401.8	412.4	424.4
65°	264.7	268.7	276.7	283.4	292.7	303.3	321.9	335.2	352.5	364.5	375.2
67.5°	228.8	232.8	238.1	246.1	252.8	264.7	278.0	291.3	310.0	318.0	325.9
70°	191.6	195.6	199.6	210.2	216.8	226.2	235.5	248.8	264.7	270.1	276.7
72.5°	162.3	163.6	169.0	171.6	180.9	188.9	199.6	207.5	219.5	226.2	231.5
75°	137.0	137.0	138.4	141.0	146.3	151.7	159.6	167.6	178.3	182.3	188.9
77.5°	107.8	111.7	110.4	113.1	115.7	118.4	125.1	130.4	141.0	143.7	146.3
80°	77.2	78.5	82.5	86.5	86.5	90.5	94.5	95.8	102.4	106.4	106.4
82.5°	55.9	57.2	55.9	57.2	58.5	59.9	63.9	69.2	69.2	70.5	73.2
85°	34.6	34.6	35.9	37.2	37.2	35.9	38.6	37.2	38.6	41.2	41.2
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	23.6	22.3	21.0	19.7	18.4	16.6	14.8	13.1	11.3	10.4	9.4
92.5°	23.6	22.3	21.0	19.7	18.4	16.9	15.3	13.8	12.3	11.5	12.7
95°	23.6	22.3	21.0	19.7	18.4	28.1	37.9	47.6	57.3	62.2	62.6
97.5°	22.7	22.2	21.7	21.2	20.7	45.0	69.3	93.6	117.9	130.1	129.3
100°	47.9	86.0	124.1	162.3	200.4	199.4	198.4	197.3	196.3	195.8	195.4
102.5°	271.5	271.0	270.5	270.0	269.5	269.0	268.5	268.0	267.5	267.2	266.7
105°	343.2	343.2	343.2	343.2	343.2	343.2	343.2	343.2	343.2	343.2	342.7
107.5°	420.2	419.9	419.7	419.4	419.2	418.7	418.1	417.6	417.1	416.8	416.8
110°	492.1	492.9	493.6	494.4	495.2	494.7	494.1	493.6	493.1	492.8	492.8

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	564.7	565.7	566.8	567.8	568.8	568.6	568.3	568.1	567.8	567.7	567.3
115°	638.4	639.4	640.5	641.5	642.5	642.3	642.0	641.8	641.5	641.4	640.8
117.5°	709.0	710.5	712.0	713.6	715.1	714.1	713.1	712.0	711.0	710.5	710.5
120°	779.9	780.4	780.9	781.4	781.9	781.1	780.3	779.6	778.8	778.4	778.5
122.5°	845.5	846.0	846.5	847.0	847.5	847.3	847.0	846.8	846.5	846.4	845.8
125°	907.9	908.9	910.0	911.0	912.0	912.0	912.0	912.0	912.0	912.0	911.1
127.5°	967.6	968.1	968.6	969.1	969.6	969.8	970.1	970.3	970.6	970.7	970.1
130°	1024.1	1024.9	1025.6	1026.4	1027.2	1026.9	1026.7	1026.4	1026.1	1026.0	1025.4
132.5°	1079.0	1079.0	1079.0	1079.0	1079.0	1079.8	1080.5	1081.3	1082.0	1082.4	1081.6
135°	1129.9	1130.4	1130.9	1131.4	1131.9	1132.4	1132.9	1133.4	1133.9	1134.2	1133.4
137.5°	1180.3	1180.3	1180.3	1180.3	1180.3	1180.8	1181.3	1181.8	1182.3	1182.6	1181.8
140°	1226.1	1225.6	1225.1	1224.6	1224.1	1224.3	1224.6	1224.8	1225.1	1225.2	1224.9
142.5°	1269.0	1269.0	1269.0	1269.0	1269.0	1268.5	1268.0	1267.5	1267.0	1266.7	1266.6
145°	1310.3	1310.0	1309.8	1309.5	1309.3	1309.3	1309.3	1309.3	1309.3	1309.3	1309.0
147.5°	1346.0	1345.7	1345.5	1345.2	1345.0	1344.7	1344.5	1344.2	1343.9	1343.8	1343.8
150°	1380.4	1379.9	1379.4	1378.9	1378.4	1377.9	1377.4	1376.9	1376.4	1376.1	1376.4
152.5°	1410.3	1409.8	1409.3	1408.8	1408.3	1407.8	1407.3	1406.8	1406.3	1406.0	1406.6
155°	1437.8	1437.1	1436.3	1435.6	1434.8	1434.3	1433.8	1433.3	1432.8	1432.5	1433.3
157.5°	1460.9	1460.1	1459.4	1458.6	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1458.2
160°	1482.7	1481.6	1480.6	1479.5	1478.5	1478.3	1478.0	1477.8	1477.5	1477.4	1478.2
162.5°	1503.1	1501.6	1500.1	1498.5	1497.0	1496.7	1496.5	1496.2	1495.9	1495.8	1496.6
165°	1519.2	1517.7	1516.2	1514.6	1513.1	1512.8	1512.6	1512.3	1512.0	1511.9	1512.7
167.5°	1532.9	1531.1	1529.4	1527.6	1525.8	1525.5	1525.3	1525.0	1524.7	1524.6	1525.4
170°	1543.2	1541.1	1539.1	1537.0	1535.0	1534.7	1534.5	1534.2	1533.9	1533.8	1534.7
172.5°	1550.2	1548.4	1546.6	1544.8	1543.0	1542.5	1542.0	1541.5	1541.0	1540.7	1541.6
175°	1555.8	1553.7	1551.7	1549.6	1547.6	1547.4	1547.1	1546.9	1546.6	1546.5	1547.3
177.5°	1558.3	1556.5	1554.7	1552.9	1551.1	1550.8	1550.6	1550.3	1550.0	1549.9	1550.7
180°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1620.4	1620.4	1620.4	1620.4
2.5°	1583.1	1595.1	1607.0	1621.7
5°	1551.2	1572.5	1595.1	1616.4
7.5°	1516.6	1547.2	1576.5	1607.0
10°	1478.0	1516.6	1549.8	1592.4
12.5°	1435.4	1476.7	1523.2	1571.1
15°	1392.9	1444.7	1494.0	1548.5
17.5°	1353.0	1402.2	1456.7	1521.9
20°	1305.1	1359.6	1420.8	1490.0
22.5°	1254.5	1314.4	1380.9	1455.4
25°	1211.9	1273.1	1337.0	1415.5
27.5°	1165.4	1229.2	1291.8	1375.6
30°	1112.2	1181.3	1245.2	1331.7
32.5°	1061.6	1130.8	1201.3	1282.4
35°	1012.4	1080.2	1150.7	1233.2
37.5°	965.8	1027.0	1096.2	1170.7
40°	921.9	977.8	1039.0	1106.8
42.5°	866.1	931.2	988.4	1037.7
45°	818.2	871.4	924.6	964.5
47.5°	762.3	815.5	860.7	892.7
50°	715.7	758.3	795.5	823.5
52.5°	659.8	699.8	730.4	751.6
55°	605.3	639.9	666.5	681.1
57.5°	556.1	578.7	598.7	612.0
60°	501.5	518.8	536.1	550.8
62.5°	443.0	461.6	470.9	486.9
65°	391.1	403.1	417.7	423.0
67.5°	340.6	347.2	356.5	367.2
70°	287.4	291.3	300.7	315.3
72.5°	240.8	244.8	251.4	256.8
75°	191.6	195.6	200.9	206.2
77.5°	150.3	151.7	154.3	159.6
80°	109.1	113.1	115.7	117.1
82.5°	75.8	77.2	77.2	78.5
85°	47.9	45.2	45.2	46.6
87.5°	17.3	20.0	20.0	22.6
90°	7.3	5.3	3.2	1.2
92.5°	15.0	17.3	19.6	21.9
95°	63.3	64.1	64.8	65.6
97.5°	127.8	126.3	124.7	123.2
100°	194.6	193.9	193.1	192.3
102.5°	265.6	264.6	263.5	262.5
105°	341.6	340.6	339.5	338.5
107.5°	416.8	416.8	416.8	416.8
110°	492.8	492.8	492.8	492.8

TEST NUMBER: P1028444

CATALOG NUMBER: S125RDIP-B1090D1270UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	566.5	565.8	565.0	564.2
115°	639.5	638.2	636.9	635.6
117.5°	710.5	710.5	710.5	710.5
120°	778.8	779.1	779.3	779.6
122.5°	844.5	843.2	841.9	840.6
125°	909.3	907.5	905.7	903.9
127.5°	968.8	967.5	966.3	965.0
130°	1024.1	1022.8	1021.5	1020.2
132.5°	1080.1	1078.6	1077.0	1075.5
135°	1131.9	1130.4	1128.8	1127.3
137.5°	1180.3	1178.8	1177.2	1175.7
140°	1224.4	1223.9	1223.4	1222.9
142.5°	1266.3	1266.0	1265.8	1265.5
145°	1308.5	1308.0	1307.5	1307.0
147.5°	1343.8	1343.8	1343.8	1343.8
150°	1376.9	1377.4	1377.9	1378.4
152.5°	1407.9	1409.2	1410.5	1411.8
155°	1434.8	1436.3	1437.9	1439.4
157.5°	1459.0	1459.7	1460.5	1461.3
160°	1479.7	1481.2	1482.8	1484.3
162.5°	1498.1	1499.6	1501.2	1502.7
165°	1514.2	1515.7	1517.3	1518.8
167.5°	1526.9	1528.4	1530.0	1531.5
170°	1536.5	1538.3	1540.1	1541.9
172.5°	1543.4	1545.2	1547.0	1548.8
175°	1548.8	1550.3	1551.9	1553.4
177.5°	1552.2	1553.7	1555.3	1556.8
180°	1553.4	1553.4	1553.4	1553.4

(END OF REPORT)