

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007845

Luminaire Tested: S125IP-B375UB2750-4F0-XX-W2A_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B375UB2750-4F0-XX-W2A_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1466.0 lumens
Efficiency: N/A
Efficacy: 157.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007845

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007845

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007845

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.7	0.0
90°-100°	16.2	1.1
100°-110°	107.7	7.3
110°-120°	193.9	13.2
120°-130°	248.8	17.0
130°-140°	267.6	18.3
140°-150°	251.2	17.1
150°-160°	203.2	13.9
160°-170°	131.4	9.0
170°-180°	45.3	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.7	0.0
90°-120°	317.7	21.7
90°-150°	1085.4	74.0
90°-180°	1465.0	99.9
0°-180°	1466.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	3	6	7	8	1
95°	20	19	6	7	7	25
105°	104	105	105	105	105	110
115°	195	197	197	196	194	194
125°	278	280	280	279	278	248
135°	346	348	348	347	345	267
145°	401	402	402	402	400	251
155°	442	440	441	442	439	204
165°	466	464	465	467	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	

TEST NUMBER: P1007845

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	3.2	5.7	7.4	8.5
92.5°	6.7	3.5	5.7	7.4	7.8
95°	20.2	19.1	5.7	7.4	7.4
97.5°	37.8	40.0	6.4	7.1	7.4
100°	59.1	60.1	61.5	8.8	7.4
102.5°	80.6	82.0	82.7	83.5	53.7
105°	104.0	105.4	105.4	105.4	105.0
107.5°	128.0	128.0	128.7	129.1	127.7
110°	151.3	151.3	152.1	151.0	151.3



TEST NUMBER: P1007845

CATALOG NUMBER: S125IP-B375UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	173.3	174.3	174.7	173.3	172.6
115°	195.2	197.0	197.3	195.9	193.8
117.5°	218.2	218.2	219.6	217.5	216.8
120°	239.4	239.0	240.1	239.4	237.6
122.5°	258.1	259.9	260.3	259.5	257.4
125°	277.6	280.1	280.1	278.6	277.6
127.5°	296.3	298.1	297.7	297.0	294.2
130°	313.3	315.1	315.4	314.4	312.6
132.5°	330.3	332.4	331.3	331.3	329.6
135°	346.2	348.3	347.6	346.9	344.8
137.5°	361.0	363.2	362.4	362.4	360.7
140°	375.5	376.2	375.9	376.6	374.5
142.5°	388.6	389.0	389.7	389.7	387.6
145°	401.3	402.1	402.1	402.4	400.3
147.5°	412.7	412.7	413.0	413.4	410.9
150°	423.3	422.6	423.3	424.0	421.1
152.5°	433.5	431.8	432.5	433.2	430.7
155°	442.0	439.9	440.6	441.7	438.8
157.5°	448.7	447.7	447.7	448.7	445.9
160°	455.8	453.7	454.0	455.4	452.6
162.5°	461.5	459.3	459.7	461.8	458.6
165°	466.4	464.3	464.6	466.8	463.9
167.5°	470.3	468.2	468.5	471.0	467.8
170°	473.5	471.0	471.4	474.2	471.0
172.5°	475.6	473.1	473.8	476.3	473.1
175°	477.0	474.9	475.2	478.1	474.9
177.5°	478.1	476.0	476.3	478.8	476.0
180°	477.0	477.0	477.0	477.0	477.0

(END OF REPORT)