

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028455

Luminaire Tested: S125RDIP-B1090D1270UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028455
REPORT IS A COMBINATION OF REPORTS P1004980 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB30-4F0-XX-W2A-F4
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8534.9 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028455

CATALOG NUMBER: S125RDIP-B1090D1270UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028455

CATALOG NUMBER: S125RDIP-B1090D1270UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49		
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42		
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35		
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34	30		
4	75	64	56	50	69	59	53	47	51	45	41	42	39	35	35	32	30	26		
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23		
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	25	23	20		
7	59	46	38	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18		
8	54	42	34	29	50	39	32	28	34	28	24	29	25	21	24	21	18	16		
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15		
10	47	35	28	23	44	33	27	22	29	23	20	25	20	17	21	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11384	11384	11384
5°	11385	11100	11118
10°	11275	10821	10726
15°	11115	10429	10209
20°	10918	9958	9667
25°	10691	9498	9086
30°	10414	8992	8476
35°	10131	8479	7827
40°	9862	7951	7194
45°	9538	7382	6531
50°	9210	6778	5856
55°	8829	6182	5157
60°	8439	5502	4432
65°	7976	4741	3650
70°	7434	3859	2872
75°	6684	2902	2093
80°	5639	1880	1411
85°	4220	1009	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9538 cd/sqm

TEST NUMBER: P1028455

CATALOG NUMBER: S125RDIP-B1090D1270UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	2.0
10°-20°	467.3	5.5
20°-30°	677.6	7.9
30°-40°	772.0	9.0
40°-50°	752.5	8.8
50°-60°	633.3	7.4
60°-70°	443.8	5.2
70°-80°	227.5	2.7
80°-90°	59.1	0.7
90°-100°	433.7	5.1
100°-110°	900.8	10.6
110°-120°	841.4	9.9
120°-130°	680.8	8.0
130°-140°	547.0	6.4
140°-150°	412.9	4.8
150°-160°	290.7	3.4
160°-170°	171.4	2.0
170°-180°	55.7	0.7
0°-30°	1312.2	15.4
0°-40°	2084.2	24.4
0°-60°	3470.0	40.7
0°-90°	4200.3	49.2
90°-120°	2175.9	25.5
90°-150°	3816.8	44.7
90°-180°	4335.0	50.8
0°-180°	8534.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1774	1769	1754	1767	1765	168
15°	1687	1679	1651	1649	1637	476
25°	1530	1510	1460	1443	1428	704
35°	1318	1286	1225	1186	1168	825
45°	1079	1040	966	913	892	832
55°	819	776	700	640	619	732
65°	554	509	438	384	364	549
75°	295	255	199	169	160	312
85°	74	50	43	42	40	81
90°	1	10	19	24	27	7
95°	38	113	1029	467	273	40
105°	131	183	842	1658	1538	138
115°	234	283	676	1457	1714	231
125°	325	381	648	1159	1350	289
135°	381	458	643	971	1122	296
145°	444	508	646	804	885	278
155°	506	545	629	711	742	233
165°	553	568	604	640	650	156
175°	575	575	579	586	584	55
180°	576	576	576	576	576	

TEST NUMBER: P1028455

CATALOG NUMBER: S125RDIP-B1090D1270UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1776.8	1776.8	1776.8	1776.8	1776.8
2.5°	1780.8	1776.8	1763.4	1776.8	1775.5
5°	1774.1	1768.8	1754.0	1767.4	1764.7
7.5°	1760.7	1755.4	1737.9	1748.6	1746.0
10°	1740.6	1736.6	1717.8	1721.8	1717.8
12.5°	1717.8	1712.4	1685.6	1688.3	1681.5
15°	1686.9	1678.9	1650.7	1649.3	1637.3
17.5°	1654.7	1642.6	1609.1	1602.4	1593.0
20°	1615.8	1602.4	1559.4	1552.7	1540.6
22.5°	1572.8	1559.4	1513.8	1499.0	1489.6
25°	1529.9	1509.8	1460.1	1442.7	1427.9
27.5°	1481.6	1457.4	1405.1	1382.3	1367.5
30°	1427.9	1402.4	1346.0	1315.2	1303.1
32.5°	1375.6	1344.7	1287.0	1252.1	1236.0
35°	1317.9	1285.6	1225.3	1186.3	1167.5
37.5°	1262.8	1223.9	1162.2	1116.6	1097.8
40°	1203.8	1163.5	1099.1	1048.1	1032.0
42.5°	1142.1	1100.4	1033.3	985.0	959.5
45°	1079.0	1040.1	966.2	912.6	892.4
47.5°	1013.2	973.0	899.1	844.1	821.3
50°	951.5	907.2	830.7	774.3	754.2
52.5°	884.4	838.8	767.6	705.9	685.8
55°	818.6	775.7	700.5	640.1	618.7
57.5°	751.5	705.9	633.4	574.4	555.6
60°	687.1	640.1	567.7	508.6	488.5
62.5°	618.7	574.4	500.6	446.9	426.8
65°	554.3	508.6	437.5	383.8	363.7
67.5°	489.8	444.2	375.8	324.8	308.7
70°	424.1	378.4	311.3	269.7	253.6
72.5°	359.7	315.4	253.6	216.1	206.7
75°	295.2	255.0	198.6	169.1	159.7
77.5°	229.5	197.3	150.3	127.5	119.4
80°	174.5	142.3	104.7	92.6	89.9
82.5°	120.8	92.6	69.8	65.8	64.4
85°	73.8	49.7	42.9	41.6	40.3
87.5°	30.9	21.5	20.1	20.1	18.8
90°	1.2	10.4	18.6	24.4	26.7
92.5°	17.4	95.2	463.3	123.6	85.9
95°	38.3	113.2	1028.8	466.8	272.9
97.5°	59.2	122.5	1111.2	843.0	598.0
100°	81.3	140.5	1048.5	1191.3	905.7
102.5°	105.7	160.8	938.2	1486.2	1249.4
105°	131.2	183.4	841.8	1657.5	1538.5
107.5°	155.6	207.2	769.8	1705.6	1712.7
110°	182.3	232.2	722.2	1659.8	1791.6

TEST NUMBER: P1028455

CATALOG NUMBER: S125RDIP-B1090D1270UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	209.0	257.2	694.4	1564.1	1782.3
115°	234.5	282.7	675.8	1456.6	1713.8
117.5°	257.8	308.8	665.3	1359.1	1610.5
120°	281.0	333.8	658.4	1277.2	1510.6
122.5°	305.4	358.2	652.6	1211.6	1422.4
125°	325.1	380.8	647.9	1158.8	1350.4
127.5°	341.4	402.9	645.6	1113.5	1284.2
130°	356.5	423.8	643.3	1067.6	1232.0
132.5°	368.1	442.4	643.3	1018.3	1179.7
135°	380.8	458.0	643.3	971.3	1121.6
137.5°	397.1	472.6	644.4	922.0	1061.3
140°	411.0	484.8	645.6	876.6	997.4
142.5°	427.3	496.4	646.7	837.8	938.2
145°	443.5	508.0	645.6	804.1	884.8
147.5°	461.0	518.4	643.3	775.0	837.2
150°	476.1	527.8	639.8	751.2	798.9
152.5°	492.3	537.0	635.1	731.0	768.7
155°	506.3	544.6	629.3	711.2	742.0
157.5°	519.0	552.1	623.5	692.6	717.6
160°	531.8	557.9	617.7	674.0	693.2
162.5°	542.2	563.8	610.8	657.2	671.1
165°	552.7	567.8	603.8	640.4	650.2
167.5°	559.7	570.1	596.8	624.7	630.5
170°	566.6	573.0	591.0	609.6	613.1
172.5°	571.3	574.2	584.0	597.4	596.8
175°	574.8	574.8	579.4	586.4	584.0
177.5°	577.1	574.8	575.9	579.4	575.9
180°	575.9	575.9	575.9	575.9	575.9

(END OF REPORT)