

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028467

Luminaire Tested: S125RDIP-B1090D1270UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028467
REPORT IS A COMBINATION OF REPORTS P1004992 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB40-4F0-XX-W2A-F4
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8486.8 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028467

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028467

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34
4	75	64	56	50	69	59	53	47	51	45	41	42	39	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	25	23
7	58	46	38	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	34	29	50	39	32	28	34	28	24	29	25	21	24	21	18
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	27	22	29	23	20	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11319	11319	11319
5°	11321	11037	11055
10°	11210	10759	10664
15°	11052	10369	10150
20°	10855	9901	9611
25°	10629	9444	9034
30°	10354	8941	8427
35°	10072	8431	7783
40°	9805	7906	7153
45°	9484	7339	6494
50°	9157	6739	5823
55°	8778	6147	5127
60°	8391	5470	4407
65°	7930	4714	3629
70°	7392	3838	2856
75°	6648	2886	2082
80°	5607	1869	1403
85°	4197	1004	790

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9484 cd/sqm

TEST NUMBER: P1028467

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.3	2.0
10°-20°	464.7	5.5
20°-30°	673.8	7.9
30°-40°	767.6	9.0
40°-50°	748.2	8.8
50°-60°	629.6	7.4
60°-70°	441.2	5.2
70°-80°	226.2	2.7
80°-90°	58.7	0.7
90°-100°	431.3	5.1
100°-110°	895.9	10.6
110°-120°	836.8	9.9
120°-130°	677.1	8.0
130°-140°	544.0	6.4
140°-150°	410.6	4.8
150°-160°	289.1	3.4
160°-170°	170.4	2.0
170°-180°	55.4	0.7
0°-30°	1304.7	15.4
0°-40°	2072.3	24.4
0°-60°	3450.1	40.7
0°-90°	4176.3	49.2
90°-120°	2163.9	25.5
90°-150°	3795.6	44.7
90°-180°	4311.0	50.8
0°-180°	8486.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1767	1767	1767	1767	1767	
5°	1764	1759	1744	1757	1755	167
15°	1677	1669	1641	1640	1628	473
25°	1521	1501	1452	1434	1420	700
35°	1310	1278	1218	1180	1161	821
45°	1073	1034	961	907	887	827
55°	814	771	696	636	615	728
65°	551	506	435	382	362	546
75°	294	254	198	168	159	310
85°	73	49	43	41	40	80
90°	1	10	18	24	27	7
95°	38	113	1023	464	271	40
105°	130	182	837	1648	1530	137
115°	233	281	672	1449	1704	230
125°	323	379	644	1152	1343	287
135°	379	456	640	966	1115	294
145°	441	505	642	800	880	276
155°	503	542	626	707	738	232
165°	550	565	600	637	647	155
175°	572	572	576	583	581	54
180°	573	573	573	573	573	

TEST NUMBER: P1028467

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1766.7	1766.7	1766.7	1766.7	1766.7
2.5°	1770.7	1766.7	1753.3	1766.7	1765.3
5°	1764.0	1758.7	1744.0	1757.3	1754.7
7.5°	1750.7	1745.3	1728.0	1738.6	1736.0
10°	1730.6	1726.6	1708.0	1712.0	1708.0
12.5°	1708.0	1702.6	1675.9	1678.6	1671.9
15°	1677.3	1669.3	1641.2	1639.9	1627.9
17.5°	1645.2	1633.2	1599.9	1593.2	1583.9
20°	1606.5	1593.2	1550.5	1543.8	1531.8
22.5°	1563.8	1550.5	1505.1	1490.5	1481.1
25°	1521.1	1501.1	1451.8	1434.4	1419.7
27.5°	1473.1	1449.1	1397.1	1374.4	1359.7
30°	1419.7	1394.4	1338.3	1307.7	1295.6
32.5°	1367.7	1337.0	1279.6	1244.9	1228.9
35°	1310.3	1278.3	1218.3	1179.6	1160.9
37.5°	1255.6	1216.9	1155.5	1110.2	1091.5
40°	1196.9	1156.9	1092.8	1042.1	1026.1
42.5°	1135.5	1094.2	1027.4	979.4	954.1
45°	1072.8	1034.1	960.7	907.4	887.3
47.5°	1007.4	967.4	894.0	839.3	816.6
50°	946.0	902.0	826.0	769.9	749.9
52.5°	879.3	834.0	763.2	701.9	681.8
55°	813.9	771.2	696.5	636.5	615.1
57.5°	747.2	701.9	629.8	571.1	552.4
60°	683.2	636.5	564.4	505.7	485.7
62.5°	615.1	571.1	497.7	444.3	424.3
65°	551.1	505.7	435.0	381.6	361.6
67.5°	487.0	441.7	373.6	322.9	306.9
70°	421.7	376.3	309.6	268.2	252.2
72.5°	357.6	313.6	252.2	214.8	205.5
75°	293.6	253.5	197.5	168.1	158.8
77.5°	228.2	196.1	149.4	126.8	118.8
80°	173.5	141.4	104.1	92.1	89.4
82.5°	120.1	92.1	69.4	65.4	64.0
85°	73.4	49.4	42.7	41.4	40.0
87.5°	30.7	21.3	20.0	20.0	18.7
90°	1.2	10.4	18.5	24.2	26.6
92.5°	17.3	94.7	460.7	123.0	85.4
95°	38.1	112.6	1023.1	464.2	271.4
97.5°	58.9	121.8	1105.0	838.3	594.7
100°	80.8	139.7	1042.7	1184.8	900.7
102.5°	105.1	160.0	933.0	1478.0	1242.4
105°	130.5	182.4	837.1	1648.4	1530.0
107.5°	154.7	206.1	765.6	1696.2	1703.2
110°	181.3	230.9	718.2	1650.6	1781.7

TEST NUMBER: P1028467

CATALOG NUMBER: S125RDIP-B1090D1270UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	207.8	255.8	690.5	1555.4	1772.4
115°	233.2	281.2	672.0	1448.6	1704.3
117.5°	256.3	307.2	661.6	1351.6	1601.6
120°	279.4	332.0	654.7	1270.2	1502.2
122.5°	303.7	356.2	648.9	1205.0	1414.5
125°	323.3	378.7	644.3	1152.4	1342.9
127.5°	339.5	400.7	642.0	1107.4	1277.1
130°	354.5	421.4	639.7	1061.8	1225.1
132.5°	366.0	439.9	639.7	1012.7	1173.2
135°	378.7	455.5	639.7	965.9	1115.4
137.5°	394.9	470.0	640.9	916.8	1055.4
140°	408.8	482.1	642.0	871.8	991.9
142.5°	424.9	493.6	643.2	833.1	933.0
145°	441.1	505.2	642.0	799.6	879.9
147.5°	458.4	515.6	639.7	770.8	832.5
150°	473.4	524.8	636.2	747.1	794.4
152.5°	489.6	534.0	631.6	726.9	764.4
155°	503.4	541.6	625.8	707.2	737.8
157.5°	516.1	549.0	620.1	688.8	713.6
160°	528.8	554.8	614.3	670.3	689.3
162.5°	539.2	560.6	607.4	653.6	667.4
165°	549.6	564.7	600.4	636.8	646.6
167.5°	556.6	567.0	593.5	621.2	627.0
170°	563.5	569.8	587.7	606.2	609.7
172.5°	568.1	571.0	580.8	594.1	593.5
175°	571.6	571.6	576.2	583.1	580.8
177.5°	573.9	571.6	572.7	576.2	572.7
180°	572.7	572.7	572.7	572.7	572.7

(END OF REPORT)