

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028473

Luminaire Tested: S125RDIP-B1090D1270UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028473
REPORT IS A COMBINATION OF REPORTS P1004998 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB50-4F0-XX-W2A-F4
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8206.5 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028473

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028473

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34
4	75	64	56	50	69	59	53	47	51	45	41	42	39	35	35	32	30
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	25	23
7	58	46	38	33	54	43	36	31	37	32	28	31	27	24	26	23	20
8	54	42	34	29	50	39	32	28	34	28	24	29	25	21	24	21	18
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	27	22	29	23	20	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1028473

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.0
10°-20°	449.3	5.5
20°-30°	651.5	7.9
30°-40°	742.2	9.0
40°-50°	723.5	8.8
50°-60°	608.8	7.4
60°-70°	426.7	5.2
70°-80°	218.7	2.7
80°-90°	56.8	0.7
90°-100°	417.0	5.1
100°-110°	866.3	10.6
110°-120°	809.1	9.9
120°-130°	654.7	8.0
130°-140°	526.1	6.4
140°-150°	397.1	4.8
150°-160°	279.6	3.4
160°-170°	164.8	2.0
170°-180°	53.6	0.7
0°-30°	1261.6	15.4
0°-40°	2003.8	24.4
0°-60°	3336.1	40.7
0°-90°	4038.2	49.2
90°-120°	2092.5	25.5
90°-150°	3670.4	44.7
90°-180°	4168.0	50.8
0°-180°	8206.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	1	10	18	24	26	7
95°	37	109	989	449	262	38
105°	126	176	810	1594	1480	133
115°	226	272	650	1401	1648	222
125°	313	366	623	1114	1299	278
135°	366	440	619	934	1079	284
145°	426	488	621	773	851	267
155°	487	524	605	684	714	224
165°	532	546	581	616	625	150
175°	553	553	557	564	562	53
180°	554	554	554	554	554	

TEST NUMBER: P1028473

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	1.1	10.0	17.9	23.5	25.7
92.5°	16.7	91.6	445.5	118.9	82.6
95°	36.8	108.8	989.3	448.9	262.4
97.5°	56.9	117.8	1068.6	810.6	575.0
100°	78.2	135.2	1008.3	1145.6	870.9
102.5°	101.6	154.6	902.2	1429.2	1201.5
105°	126.2	176.4	809.5	1593.9	1479.5
107.5°	149.6	199.4	740.3	1640.2	1647.0
110°	175.3	223.3	694.5	1596.2	1722.9

TEST NUMBER: P1028473

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	201.0	247.4	667.7	1504.0	1714.0
115°	225.6	271.8	649.9	1400.8	1648.1
117.5°	247.9	297.0	639.8	1307.0	1548.7
120°	270.2	321.0	633.1	1228.2	1452.7
122.5°	293.7	344.4	627.5	1165.2	1367.8
125°	312.6	366.2	623.1	1114.4	1298.6
127.5°	328.3	387.4	620.8	1070.8	1234.9
130°	342.8	407.6	618.6	1026.7	1184.7
132.5°	354.0	425.4	618.6	979.2	1134.5
135°	366.2	440.5	618.6	934.0	1078.6
137.5°	381.9	454.4	619.7	886.6	1020.6
140°	395.3	466.2	620.8	843.0	959.2
142.5°	410.9	477.4	621.9	805.7	902.2
145°	426.5	488.5	620.8	773.2	850.8
147.5°	443.3	498.6	618.6	745.3	805.1
150°	457.8	507.5	615.2	722.4	768.2
152.5°	473.4	516.4	610.8	702.9	739.2
155°	486.8	523.7	605.2	684.0	713.5
157.5°	499.1	531.0	599.6	666.0	690.1
160°	511.4	536.5	594.0	648.2	666.6
162.5°	521.4	542.1	587.3	632.0	645.4
165°	531.5	546.0	580.6	615.8	625.3
167.5°	538.2	548.2	573.9	600.8	606.3
170°	544.9	551.0	568.3	586.2	589.6
172.5°	549.4	552.2	561.6	574.4	573.9
175°	552.7	552.7	557.2	563.9	561.6
177.5°	554.9	552.7	553.8	557.2	553.8
180°	553.8	553.8	553.8	553.8	553.8

(END OF REPORT)