

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028484

Luminaire Tested: S125RDIP-B1090D375UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028484
REPORT IS A COMBINATION OF REPORTS P1005019 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D375UB30-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5474.0 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028484

CATALOG NUMBER: S125RDIP-B1090D375UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028484

CATALOG NUMBER: S125RDIP-B1090D375UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69
2	95	88	81	76	90	84	78	73	76	72	68	70	66	63	64	61	59
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50
4	80	69	61	54	76	66	58	53	61	54	50	56	51	46	51	47	43
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38
6	68	55	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	34	30
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27
9	55	42	34	29	52	41	33	29	38	32	27	35	30	26	33	28	25
10	51	39	31	26	49	38	31	26	35	29	25	33	27	24	30	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11384	11384	11384
5°	11385	11100	11118
10°	11275	10821	10726
15°	11115	10429	10209
20°	10918	9958	9667
25°	10691	9498	9086
30°	10414	8992	8476
35°	10131	8479	7827
40°	9862	7951	7194
45°	9538	7382	6531
50°	9210	6778	5856
55°	8829	6182	5157
60°	8439	5502	4432
65°	7976	4741	3650
70°	7434	3859	2872
75°	6684	2902	2093
80°	5639	1880	1411
85°	4220	1009	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9538 cd/sqm

TEST NUMBER: P1028484

CATALOG NUMBER: S125RDIP-B1090D375UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	3.1
10°-20°	467.3	8.5
20°-30°	677.6	12.4
30°-40°	772.0	14.1
40°-50°	752.5	13.7
50°-60°	633.3	11.6
60°-70°	443.8	8.1
70°-80°	227.5	4.2
80°-90°	57.5	1.0
90°-100°	30.4	0.6
100°-110°	90.3	1.6
110°-120°	153.1	2.8
120°-130°	201.5	3.7
130°-140°	225.8	4.1
140°-150°	221.4	4.0
150°-160°	185.9	3.4
160°-170°	123.6	2.3
170°-180°	43.3	0.8
0°-30°	1312.2	24.0
0°-40°	2084.2	38.1
0°-60°	3470.0	63.4
0°-90°	4198.7	76.7
90°-120°	273.8	5.0
90°-150°	922.5	16.9
90°-180°	1275.0	23.3
0°-180°	5474.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1774	1769	1754	1767	1765	168
15°	1687	1679	1651	1649	1637	476
25°	1530	1510	1460	1443	1428	704
35°	1318	1286	1225	1186	1168	825
45°	1079	1040	966	913	892	832
55°	819	776	700	640	619	732
65°	554	509	438	384	364	549
75°	295	255	199	169	160	312
85°	74	50	43	42	40	81
90°	0	3	6	8	8	6
95°	23	24	27	30	31	24
105°	81	83	85	87	88	86
115°	153	155	155	155	155	152
125°	224	226	226	225	225	200
135°	291	293	293	293	292	224
145°	352	354	355	355	354	220
155°	403	403	404	405	403	186
165°	438	438	438	440	437	124
175°	456	454	454	457	454	43
180°	457	457	457	457	457	

TEST NUMBER: P1028484

CATALOG NUMBER: S125RDIP-B1090D375UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1776.8	1776.8	1776.8	1776.8	1776.8
2.5°	1780.8	1776.8	1763.4	1776.8	1775.5
5°	1774.1	1768.8	1754.0	1767.4	1764.7
7.5°	1760.7	1755.4	1737.9	1748.6	1746.0
10°	1740.6	1736.6	1717.8	1721.8	1717.8
12.5°	1717.8	1712.4	1685.6	1688.3	1681.5
15°	1686.9	1678.9	1650.7	1649.3	1637.3
17.5°	1654.7	1642.6	1609.1	1602.4	1593.0
20°	1615.8	1602.4	1559.4	1552.7	1540.6
22.5°	1572.8	1559.4	1513.8	1499.0	1489.6
25°	1529.9	1509.8	1460.1	1442.7	1427.9
27.5°	1481.6	1457.4	1405.1	1382.3	1367.5
30°	1427.9	1402.4	1346.0	1315.2	1303.1
32.5°	1375.6	1344.7	1287.0	1252.1	1236.0
35°	1317.9	1285.6	1225.3	1186.3	1167.5
37.5°	1262.8	1223.9	1162.2	1116.6	1097.8
40°	1203.8	1163.5	1099.1	1048.1	1032.0
42.5°	1142.1	1100.4	1033.3	985.0	959.5
45°	1079.0	1040.1	966.2	912.6	892.4
47.5°	1013.2	973.0	899.1	844.1	821.3
50°	951.5	907.2	830.7	774.3	754.2
52.5°	884.4	838.8	767.6	705.9	685.8
55°	818.6	775.7	700.5	640.1	618.7
57.5°	751.5	705.9	633.4	574.4	555.6
60°	687.1	640.1	567.7	508.6	488.5
62.5°	618.7	574.4	500.6	446.9	426.8
65°	554.3	508.6	437.5	383.8	363.7
67.5°	489.8	444.2	375.8	324.8	308.7
70°	424.1	378.4	311.3	269.7	253.6
72.5°	359.7	315.4	253.6	216.1	206.7
75°	295.2	255.0	198.6	169.1	159.7
77.5°	229.5	197.3	150.3	127.5	119.4
80°	174.5	142.3	104.7	92.6	89.9
82.5°	120.8	92.6	69.8	65.8	64.4
85°	73.8	49.7	42.9	41.6	40.3
87.5°	30.9	21.5	20.1	20.1	18.8
90°	0.4	3.2	5.7	7.5	8.5
92.5°	10.7	12.4	15.6	18.1	18.8
95°	23.1	23.8	27.4	29.9	30.6
97.5°	35.6	35.9	40.9	43.0	43.4
100°	49.8	49.8	54.4	57.6	58.3
102.5°	65.1	66.9	68.6	72.2	73.3
105°	81.1	82.9	85.0	87.1	88.2
107.5°	98.5	100.3	102.1	103.1	103.1
110°	116.6	118.4	119.5	120.5	120.2

TEST NUMBER: P1028484

CATALOG NUMBER: S125RDIP-B1090D375UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.1	135.8	137.3	137.6	136.9
115°	153.3	154.7	155.4	155.0	154.7
117.5°	171.8	172.1	172.8	173.2	171.8
120°	188.8	190.6	191.0	191.0	189.5
122.5°	207.3	207.7	208.7	208.4	207.3
125°	223.7	225.8	226.2	225.4	225.1
127.5°	241.8	242.9	243.2	242.9	242.2
130°	257.8	259.6	260.3	259.9	259.2
132.5°	273.8	277.0	276.7	276.3	275.2
135°	290.9	293.0	293.4	293.4	291.9
137.5°	306.9	309.0	309.7	310.1	308.3
140°	322.2	323.9	325.0	325.7	323.9
142.5°	337.5	338.9	340.3	340.7	338.9
145°	352.4	353.8	354.9	354.9	353.8
147.5°	366.3	367.3	368.0	369.1	366.3
150°	380.1	379.8	381.2	381.2	380.5
152.5°	391.5	392.2	392.6	393.6	392.2
155°	403.2	403.2	403.6	405.0	403.2
157.5°	413.9	413.2	413.6	415.0	412.5
160°	423.2	422.1	422.4	423.9	422.1
162.5°	431.3	430.6	430.6	432.4	430.3
165°	438.5	437.7	438.1	439.5	437.4
167.5°	444.9	443.4	443.4	445.6	443.4
170°	449.8	448.4	448.4	450.5	448.1
172.5°	453.4	452.0	452.0	454.1	452.0
175°	455.9	454.5	454.5	456.6	454.1
177.5°	457.7	456.2	455.9	458.0	455.5
180°	456.9	456.9	456.9	456.9	456.9

(END OF REPORT)