

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007872

Luminaire Tested: S125IP-B610UB2750-4F0-XX-W2A_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007872
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B610UB2750-4F0-XX-W2A_2700K
Description: Define 5 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2350.0 lumens
Efficiency: N/A
Efficacy: 152.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007872

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1007872

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007872

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.1	0.0
90°-100°	26.0	1.1
100°-110°	172.6	7.3
110°-120°	310.8	13.2
120°-130°	398.9	17.0
130°-140°	429.0	18.3
140°-150°	402.7	17.1
150°-160°	325.7	13.9
160°-170°	210.6	9.0
170°-180°	72.6	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.1	0.0
90°-120°	509.3	21.7
90°-150°	1739.8	74.0
90°-180°	2349.0	100.0
0°-180°	2350.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	9	12	14	2
95°	32	31	9	12	12	40
105°	167	169	169	169	168	177
115°	313	316	316	314	311	310
125°	445	449	449	447	445	397
135°	555	558	557	556	553	428
145°	643	644	644	645	642	402
155°	708	705	706	708	703	326
165°	748	744	745	748	744	211
175°	765	761	762	766	761	73
180°	765	765	765	765	765	

TEST NUMBER: P1007872

CATALOG NUMBER: S125IP-B610UB2750-4FO-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.3	30.6	9.1	11.9	11.9
97.5°	60.7	64.1	10.2	11.3	11.9
100°	94.7	96.4	98.6	14.2	11.9
102.5°	129.2	131.5	132.6	133.8	86.2
105°	166.6	168.9	168.9	168.9	168.3
107.5°	205.2	205.2	206.3	206.9	204.6
110°	242.6	242.6	243.7	242.0	242.6

TEST NUMBER: P1007872

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	277.7	279.4	280.0	277.7	276.6
115°	312.9	315.7	316.3	314.0	310.6
117.5°	349.7	349.7	352.0	348.6	347.5
120°	383.7	383.2	384.9	383.7	380.9
122.5°	413.8	416.6	417.2	416.1	412.7
125°	445.0	448.9	448.9	446.7	445.0
127.5°	475.0	477.8	477.3	476.1	471.6
130°	502.2	505.0	505.6	503.9	501.1
132.5°	529.4	532.8	531.1	531.1	528.3
135°	554.9	558.3	557.2	556.1	552.7
137.5°	578.7	582.1	581.0	581.0	578.2
140°	602.0	603.1	602.5	603.7	600.3
142.5°	622.9	623.5	624.6	624.6	621.2
145°	643.4	644.5	644.5	645.1	641.7
147.5°	661.5	661.5	662.1	662.6	658.7
150°	678.5	677.4	678.5	679.6	675.1
152.5°	694.9	692.1	693.2	694.4	690.4
155°	708.5	705.1	706.3	708.0	703.4
157.5°	719.3	717.6	717.6	719.3	714.8
160°	730.6	727.2	727.8	730.1	725.5
162.5°	739.7	736.3	736.9	740.3	735.2
165°	747.7	744.3	744.8	748.2	743.7
167.5°	753.9	750.5	751.1	755.0	749.9
170°	759.0	755.0	755.6	760.1	755.0
172.5°	762.4	758.4	759.6	763.5	758.4
175°	764.7	761.3	761.8	766.4	761.3
177.5°	766.4	763.0	763.5	767.5	763.0
180°	764.7	764.7	764.7	764.7	764.7

(END OF REPORT)