

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007874

Luminaire Tested: S125IP-B610UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007874
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B610UB2750-4F0-XX-W2A_3500K
Description: Define 5 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2380.0 lumens
Efficiency: N/A
Efficacy: 154.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007874

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007874

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007874

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.2	0.0
90°-100°	26.3	1.1
100°-110°	174.8	7.3
110°-120°	314.7	13.2
120°-130°	404.0	17.0
130°-140°	434.5	18.3
140°-150°	407.8	17.1
150°-160°	329.9	13.9
160°-170°	213.3	9.0
170°-180°	73.6	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.2	0.0
90°-120°	515.8	21.7
90°-150°	1762.1	74.0
90°-180°	2379.0	100.0
0°-180°	2380.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	9	12	14	2
95°	33	31	9	12	12	40
105°	169	171	171	171	170	179
115°	317	320	320	318	315	314
125°	451	455	455	452	451	403
135°	562	566	564	563	560	433
145°	652	653	653	653	650	408
155°	718	714	715	717	712	331
165°	757	754	754	758	753	214
175°	774	771	772	776	771	74
180°	774	774	774	774	774	

TEST NUMBER: P1007874

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	5.2	9.2	12.1	13.8
92.5°	10.9	5.7	9.2	12.1	12.6
95°	32.7	31.0	9.2	12.1	12.1
97.5°	61.4	64.9	10.3	11.5	12.1
100°	95.9	97.6	99.9	14.4	12.1
102.5°	130.9	133.2	134.3	135.5	87.3
105°	168.8	171.1	171.1	171.1	170.5
107.5°	207.8	207.8	209.0	209.5	207.2
110°	245.7	245.7	246.8	245.1	245.7

TEST NUMBER: P1007874

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.3	283.0	283.6	281.3	280.1
115°	316.9	319.8	320.3	318.0	314.6
117.5°	354.2	354.2	356.5	353.1	351.9
120°	388.6	388.1	389.8	388.6	385.8
122.5°	419.1	421.9	422.5	421.4	417.9
125°	450.6	454.7	454.7	452.4	450.6
127.5°	481.1	483.9	483.4	482.2	477.6
130°	508.6	511.5	512.1	510.3	507.5
132.5°	536.2	539.6	537.9	537.9	535.0
135°	562.0	565.5	564.3	563.2	559.7
137.5°	586.1	589.6	588.4	588.4	585.6
140°	609.7	610.8	610.2	611.4	607.9
142.5°	630.9	631.5	632.6	632.6	629.2
145°	651.6	652.7	652.7	653.3	649.8
147.5°	669.9	669.9	670.5	671.1	667.1
150°	687.2	686.0	687.2	688.3	683.7
152.5°	703.8	700.9	702.1	703.2	699.2
155°	717.6	714.1	715.3	717.0	712.4
157.5°	728.5	726.8	726.8	728.5	723.9
160°	740.0	736.5	737.1	739.4	734.8
162.5°	749.2	745.7	746.3	749.7	744.6
165°	757.2	753.8	754.3	757.8	753.2
167.5°	763.5	760.1	760.6	764.7	759.5
170°	768.7	764.7	765.2	769.8	764.7
172.5°	772.1	768.1	769.3	773.3	768.1
175°	774.4	771.0	771.5	776.1	771.0
177.5°	776.1	772.7	773.3	777.3	772.7
180°	774.4	774.4	774.4	774.4	774.4

(END OF REPORT)