

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007875

Luminaire Tested: S125IP-B610UB2750-4F0-XX-W2A_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007875
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B610UB2750-4F0-XX-W2A_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2357.0 lumens
Efficiency: N/A
Efficacy: 153.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007875

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007875

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007875

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.1	0.0
90°-100°	26.0	1.1
100°-110°	173.1	7.3
110°-120°	311.7	13.2
120°-130°	400.1	17.0
130°-140°	430.3	18.3
140°-150°	403.9	17.1
150°-160°	326.7	13.9
160°-170°	211.3	9.0
170°-180°	72.9	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.1	0.0
90°-120°	510.8	21.7
90°-150°	1745.0	74.0
90°-180°	2356.0	100.0
0°-180°	2357.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	9	12	14	2
95°	32	31	9	12	12	40
105°	167	169	169	169	169	177
115°	314	317	317	315	312	311
125°	446	450	450	448	446	399
135°	557	560	559	558	554	429
145°	645	646	646	647	644	404
155°	711	707	708	710	706	327
165°	750	746	747	750	746	212
175°	767	764	764	769	764	73
180°	767	767	767	767	767	

TEST NUMBER: P1007875

CATALOG NUMBER: S125IP-B610UB2750-4FO-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	5.1	9.1	11.9	13.6
92.5°	10.8	5.7	9.1	11.9	12.5
95°	32.4	30.7	9.1	11.9	11.9
97.5°	60.8	64.2	10.2	11.4	11.9
100°	94.9	96.6	98.9	14.2	11.9
102.5°	129.6	131.9	133.0	134.2	86.4
105°	167.1	169.4	169.4	169.4	168.9
107.5°	205.8	205.8	206.9	207.5	205.2
110°	243.3	243.3	244.5	242.8	243.3

TEST NUMBER: P1007875

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.6	280.3	280.8	278.6	277.4
115°	313.8	316.7	317.2	315.0	311.5
117.5°	350.8	350.8	353.1	349.6	348.5
120°	384.9	384.3	386.0	384.9	382.0
122.5°	415.0	417.9	418.4	417.3	413.9
125°	446.3	450.3	450.3	448.0	446.3
127.5°	476.4	479.3	478.7	477.6	473.0
130°	503.7	506.6	507.1	505.4	502.6
132.5°	531.0	534.4	532.7	532.7	529.9
135°	556.6	560.0	558.9	557.7	554.3
137.5°	580.5	583.9	582.7	582.7	579.9
140°	603.8	604.9	604.3	605.5	602.1
142.5°	624.8	625.4	626.5	626.5	623.1
145°	645.3	646.4	646.4	647.0	643.6
147.5°	663.5	663.5	664.0	664.6	660.6
150°	680.5	679.4	680.5	681.7	677.1
152.5°	697.0	694.2	695.3	696.4	692.5
155°	710.7	707.2	708.4	710.1	705.5
157.5°	721.5	719.7	719.7	721.5	716.9
160°	732.8	729.4	730.0	732.3	727.7
162.5°	741.9	738.5	739.1	742.5	737.4
165°	749.9	746.5	747.0	750.4	745.9
167.5°	756.1	752.7	753.3	757.3	752.2
170°	761.2	757.3	757.8	762.4	757.3
172.5°	764.7	760.7	761.8	765.8	760.7
175°	766.9	763.5	764.1	768.6	763.5
177.5°	768.6	765.2	765.8	769.8	765.2
180°	766.9	766.9	766.9	766.9	766.9

(END OF REPORT)