

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028490

Luminaire Tested: S125RDIP-B1090D375UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028490
REPORT IS A COMBINATION OF REPORTS P1005025 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D375UB35-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5497.0 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028490

CATALOG NUMBER: S125RDIP-B1090D375UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028490

CATALOG NUMBER: S125RDIP-B1090D375UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69
2	95	88	81	76	90	84	78	73	76	72	68	70	66	63	64	61	59
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50
4	80	69	61	54	76	66	58	53	61	54	50	56	51	47	51	47	44
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38
6	68	55	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	34	30
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27
9	55	42	34	29	52	41	33	29	38	32	27	35	30	26	33	28	25
10	51	39	31	26	49	38	31	26	35	29	25	33	27	24	30	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11433	11433	11433
5°	11434	11148	11166
10°	11323	10867	10771
15°	11162	10474	10253
20°	10964	10001	9708
25°	10737	9539	9125
30°	10458	9031	8512
35°	10174	8515	7861
40°	9903	7985	7225
45°	9579	7414	6560
50°	9250	6807	5881
55°	8867	6209	5179
60°	8476	5525	4451
65°	8009	4762	3665
70°	7466	3876	2884
75°	6714	2915	2102
80°	5662	1887	1418
85°	4237	1013	798

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9579 cd/sqm

TEST NUMBER: P1028490

CATALOG NUMBER: S125RDIP-B1090D375UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.9	3.1
10°-20°	469.3	8.5
20°-30°	680.5	12.4
30°-40°	775.3	14.1
40°-50°	755.7	13.7
50°-60°	636.0	11.6
60°-70°	445.7	8.1
70°-80°	228.5	4.2
80°-90°	57.7	1.0
90°-100°	30.5	0.6
100°-110°	90.6	1.6
110°-120°	153.7	2.8
120°-130°	202.3	3.7
130°-140°	226.7	4.1
140°-150°	222.2	4.0
150°-160°	186.7	3.4
160°-170°	124.1	2.3
170°-180°	43.4	0.8
0°-30°	1317.8	24.0
0°-40°	2093.2	38.1
0°-60°	3484.9	63.4
0°-90°	4216.7	76.7
90°-120°	274.8	5.0
90°-150°	926.1	16.8
90°-180°	1280.0	23.3
0°-180°	5497.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1784	1784	1784	1784	1784	
5°	1782	1776	1762	1775	1772	169
15°	1694	1686	1658	1656	1644	478
25°	1536	1516	1466	1449	1434	707
35°	1324	1291	1230	1191	1173	829
45°	1084	1044	970	916	896	836
55°	822	779	704	643	621	735
65°	557	511	439	386	365	551
75°	296	256	200	170	160	313
85°	74	50	43	42	40	81
90°	0	3	6	8	9	6
95°	23	24	28	30	31	24
105°	81	83	85	88	88	87
115°	154	155	156	156	155	152
125°	224	227	227	226	226	201
135°	292	294	294	294	293	225
145°	354	355	356	356	355	221
155°	405	405	405	407	405	186
165°	440	440	440	441	439	124
175°	458	456	456	458	456	43
180°	459	459	459	459	459	

TEST NUMBER: P1028490

CATALOG NUMBER: S125RDIP-B1090D375UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.4	1784.4	1784.4	1784.4	1784.4
2.5°	1788.5	1784.4	1771.0	1784.4	1783.1
5°	1781.7	1776.4	1761.5	1775.0	1772.3
7.5°	1768.3	1762.9	1745.4	1756.1	1753.4
10°	1748.1	1744.0	1725.1	1729.2	1725.1
12.5°	1725.1	1719.7	1692.8	1695.5	1688.8
15°	1694.1	1686.1	1657.8	1656.4	1644.3
17.5°	1661.8	1649.7	1616.0	1609.2	1599.8
20°	1622.7	1609.2	1566.1	1559.4	1547.2
22.5°	1579.6	1566.1	1520.3	1505.5	1496.0
25°	1536.5	1516.2	1466.4	1448.8	1434.0
27.5°	1487.9	1463.7	1411.1	1388.2	1373.4
30°	1434.0	1408.4	1351.8	1320.8	1308.7
32.5°	1381.5	1350.5	1292.5	1257.5	1241.3
35°	1323.5	1291.2	1230.5	1191.4	1172.6
37.5°	1268.2	1229.2	1167.2	1121.3	1102.5
40°	1208.9	1168.5	1103.8	1052.6	1036.4
42.5°	1146.9	1105.2	1037.8	989.3	963.7
45°	1083.6	1044.5	970.4	916.5	896.3
47.5°	1017.6	977.1	903.0	847.7	824.8
50°	955.6	911.1	834.3	777.7	757.4
52.5°	888.2	842.4	770.9	708.9	688.7
55°	822.1	779.0	703.5	642.9	621.3
57.5°	754.7	708.9	636.1	576.8	558.0
60°	690.1	642.9	570.1	510.8	490.6
62.5°	621.3	576.8	502.7	448.8	428.6
65°	556.6	510.8	439.4	385.5	365.2
67.5°	491.9	446.1	377.4	326.2	310.0
70°	425.9	380.1	312.7	270.9	254.7
72.5°	361.2	316.7	254.7	217.0	207.6
75°	296.5	256.1	199.5	169.8	160.4
77.5°	230.5	198.1	150.9	128.0	120.0
80°	175.2	142.9	105.1	93.0	90.3
82.5°	121.3	93.0	70.1	66.0	64.7
85°	74.1	49.9	43.1	41.8	40.4
87.5°	31.0	21.6	20.2	20.2	18.9
90°	0.4	3.2	5.7	7.5	8.6
92.5°	10.7	12.5	15.7	18.2	18.9
95°	23.2	23.9	27.5	30.0	30.7
97.5°	35.7	36.1	41.1	43.2	43.6
100°	50.0	50.0	54.6	57.8	58.5
102.5°	65.3	67.1	68.9	72.5	73.5
105°	81.4	83.2	85.3	87.5	88.5
107.5°	98.9	100.7	102.5	103.5	103.5
110°	117.1	118.9	119.9	121.0	120.7

TEST NUMBER: P1028490

CATALOG NUMBER: S125RDIP-B1090D375UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.7	136.4	137.8	138.2	137.4
115°	153.9	155.3	156.0	155.6	155.3
117.5°	172.4	172.8	173.5	173.9	172.4
120°	189.6	191.3	191.7	191.7	190.3
122.5°	208.1	208.5	209.6	209.2	208.1
125°	224.5	226.7	227.0	226.3	226.0
127.5°	242.8	243.8	244.2	243.8	243.1
130°	258.8	260.6	261.3	261.0	260.2
132.5°	274.9	278.1	277.7	277.4	276.3
135°	292.0	294.2	294.5	294.5	293.1
137.5°	308.1	310.2	310.9	311.3	309.5
140°	323.4	325.2	326.3	327.0	325.2
142.5°	338.8	340.2	341.6	342.0	340.2
145°	353.8	355.2	356.3	356.3	355.2
147.5°	367.7	368.8	369.5	370.6	367.7
150°	381.6	381.3	382.7	382.7	382.0
152.5°	393.0	393.8	394.1	395.2	393.8
155°	404.8	404.8	405.2	406.6	404.8
157.5°	415.5	414.8	415.2	416.6	414.1
160°	424.8	423.7	424.1	425.5	423.7
162.5°	433.0	432.3	432.3	434.1	432.0
165°	440.2	439.5	439.8	441.2	439.1
167.5°	446.6	445.2	445.2	447.3	445.2
170°	451.6	450.2	450.2	452.3	449.8
172.5°	455.2	453.7	453.7	455.9	453.7
175°	457.7	456.2	456.2	458.4	455.9
177.5°	459.4	458.0	457.7	459.8	457.3
180°	458.7	458.7	458.7	458.7	458.7

(END OF REPORT)