

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007893

Luminaire Tested: S125IP-B850UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007893
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B850UB2750-4F0-XX-W2A-1_3000K
Description: Define 5 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2740.0 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007893

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007893

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007893

CATALOG NUMBER: S125IP-B850UB2750-4FO-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	65.2	2.4
100°-110°	193.8	7.1
110°-120°	328.7	12.0
120°-130°	432.8	15.8
130°-140°	485.0	17.7
140°-150°	475.3	17.3
150°-160°	399.3	14.6
160°-170°	265.4	9.7
170°-180°	92.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	587.8	21.5
90°-150°	1980.9	72.3
90°-180°	2738.0	99.9
0°-180°	2740.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	16	18	3
95°	50	51	59	64	66	52
105°	174	178	182	187	189	186
115°	329	332	334	333	332	326
125°	480	485	486	484	483	430
135°	625	629	630	630	627	481
145°	757	760	762	762	760	473
155°	866	866	867	870	866	399
165°	942	940	941	944	939	266
175°	979	976	976	980	975	93
180°	981	981	981	981	981	

TEST NUMBER: P1007893

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	6.9	12.2	16.0	18.3
92.5°	22.9	26.7	33.6	38.9	40.5
95°	49.6	51.2	58.8	64.1	65.7
97.5°	76.4	77.1	87.8	92.4	93.2
100°	106.9	106.9	116.8	123.7	125.2
102.5°	139.7	143.6	147.4	155.0	157.3
105°	174.1	177.9	182.5	187.1	189.4
107.5°	211.5	215.3	219.1	221.4	221.4
110°	250.5	254.3	256.6	258.9	258.1

TEST NUMBER: P1007893

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.2	291.7	294.7	295.5	294.0
115°	329.1	332.2	333.7	332.9	332.2
117.5°	368.8	369.6	371.1	371.9	368.8
120°	405.5	409.3	410.0	410.0	407.0
122.5°	445.2	445.9	448.2	447.5	445.2
125°	480.3	484.9	485.6	484.1	483.3
127.5°	519.2	521.5	522.3	521.5	520.0
130°	553.6	557.4	558.9	558.2	556.7
132.5°	588.0	594.8	594.1	593.3	591.0
135°	624.6	629.2	630.0	630.0	626.9
137.5°	659.0	663.6	665.1	665.8	662.0
140°	691.8	695.6	697.9	699.4	695.6
142.5°	724.6	727.7	730.8	731.5	727.7
145°	756.7	759.8	762.1	762.1	759.8
147.5°	786.5	788.8	790.3	792.6	786.5
150°	816.3	815.5	818.6	818.6	817.0
152.5°	840.7	842.2	843.0	845.3	842.2
155°	865.9	865.9	866.7	869.7	865.9
157.5°	888.8	887.3	888.1	891.1	885.8
160°	908.7	906.4	907.1	910.2	906.4
162.5°	926.2	924.7	924.7	928.5	923.9
165°	941.5	940.0	940.7	943.8	939.2
167.5°	955.2	952.2	952.2	956.8	952.2
170°	965.9	962.9	962.9	967.5	962.1
172.5°	973.6	970.5	970.5	975.1	970.5
175°	978.9	975.9	975.9	980.4	975.1
177.5°	982.7	979.7	978.9	983.5	978.2
180°	981.2	981.2	981.2	981.2	981.2

(END OF REPORT)