

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007894

Luminaire Tested: S125IP-B850UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007894
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B850UB2750-4F0-XX-W2A-1_3500K
Description: Define 5 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2752.0 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007894

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007894

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007894

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	65.5	2.4
100°-110°	194.7	7.1
110°-120°	330.2	12.0
120°-130°	434.7	15.8
130°-140°	487.1	17.7
140°-150°	477.4	17.3
150°-160°	401.0	14.6
160°-170°	266.6	9.7
170°-180°	93.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	590.4	21.5
90°-150°	1989.6	72.3
90°-180°	2750.0	99.9
0°-180°	2752.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	16	18	3
95°	50	51	59	64	66	52
105°	175	179	183	188	190	186
115°	330	334	335	334	334	327
125°	482	487	488	486	486	432
135°	627	632	633	633	630	484
145°	760	763	765	765	763	475
155°	870	870	870	874	870	401
165°	946	944	945	948	943	267
175°	983	980	980	985	979	93
180°	986	986	986	986	986	

TEST NUMBER: P1007894

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	6.9	12.3	16.1	18.4
92.5°	23.0	26.8	33.7	39.1	40.6
95°	49.9	51.4	59.1	64.4	66.0
97.5°	76.7	77.5	88.2	92.8	93.6
100°	107.4	107.4	117.3	124.2	125.8
102.5°	140.3	144.2	148.0	155.7	158.0
105°	174.9	178.7	183.3	187.9	190.2
107.5°	212.4	216.3	220.1	222.4	222.4
110°	251.6	255.4	257.7	260.0	259.2

TEST NUMBER: P1007894

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.4	293.0	296.0	296.8	295.3
115°	330.5	333.6	335.1	334.4	333.6
117.5°	370.4	371.2	372.7	373.5	370.4
120°	407.2	411.1	411.8	411.8	408.8
122.5°	447.1	447.9	450.2	449.4	447.1
125°	482.4	487.0	487.8	486.2	485.5
127.5°	521.5	523.8	524.6	523.8	522.3
130°	556.0	559.9	561.4	560.6	559.1
132.5°	590.5	597.4	596.7	595.9	593.6
135°	627.3	632.0	632.7	632.7	629.6
137.5°	661.9	666.5	668.0	668.8	664.9
140°	694.8	698.7	701.0	702.5	698.7
142.5°	727.8	730.9	734.0	734.7	730.9
145°	760.0	763.1	765.4	765.4	763.1
147.5°	789.9	792.2	793.8	796.1	789.9
150°	819.8	819.1	822.1	822.1	820.6
152.5°	844.4	845.9	846.7	849.0	845.9
155°	869.7	869.7	870.5	873.5	869.7
157.5°	892.7	891.2	891.9	895.0	889.6
160°	912.6	910.3	911.1	914.2	910.3
162.5°	930.3	928.8	928.8	932.6	928.0
165°	945.6	944.1	944.9	947.9	943.3
167.5°	959.4	956.4	956.4	961.0	956.4
170°	970.2	967.1	967.1	971.7	966.3
172.5°	977.8	974.8	974.8	979.4	974.8
175°	983.2	980.1	980.1	984.7	979.4
177.5°	987.0	984.0	983.2	987.8	982.4
180°	985.5	985.5	985.5	985.5	985.5

(END OF REPORT)