

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007895

Luminaire Tested: S125IP-B850UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B850UB2750-4F0-XX-W2A-1_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2725.0 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007895

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007895

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007895

CATALOG NUMBER: S125IP-B850UB2750-4FO-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	64.9	2.4
100°-110°	192.8	7.1
110°-120°	326.9	12.0
120°-130°	430.4	15.8
130°-140°	482.3	17.7
140°-150°	472.7	17.3
150°-160°	397.1	14.6
160°-170°	264.0	9.7
170°-180°	92.4	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	584.6	21.5
90°-150°	1970.1	72.3
90°-180°	2723.0	99.9
0°-180°	2725.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	16	18	3
95°	49	51	58	64	65	52
105°	173	177	182	186	188	185
115°	327	330	332	331	330	324
125°	478	482	483	482	481	428
135°	621	626	626	626	624	479
145°	753	756	758	758	756	470
155°	861	861	862	865	861	397
165°	936	935	936	939	934	264
175°	974	970	970	975	970	93
180°	976	976	976	976	976	

TEST NUMBER: P1007895

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	6.8	12.2	15.9	18.2
92.5°	22.8	26.6	33.4	38.7	40.2
95°	49.4	50.9	58.5	63.8	65.3
97.5°	75.9	76.7	87.3	91.9	92.6
100°	106.3	106.3	116.2	123.0	124.5
102.5°	139.0	142.8	146.6	154.2	156.4
105°	173.1	176.9	181.5	186.1	188.3
107.5°	210.4	214.2	217.9	220.2	220.2
110°	249.1	252.9	255.2	257.4	256.7

TEST NUMBER: P1007895

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	290.1	293.1	293.9	292.4
115°	327.3	330.3	331.9	331.1	330.3
117.5°	366.8	367.6	369.1	369.8	366.8
120°	403.2	407.0	407.8	407.8	404.8
122.5°	442.7	443.5	445.8	445.0	442.7
125°	477.7	482.2	483.0	481.5	480.7
127.5°	516.4	518.7	519.4	518.7	517.2
130°	550.6	554.4	555.9	555.1	553.6
132.5°	584.7	591.6	590.8	590.1	587.8
135°	621.2	625.8	626.5	626.5	623.5
137.5°	655.4	659.9	661.4	662.2	658.4
140°	688.0	691.8	694.1	695.6	691.8
142.5°	720.7	723.7	726.8	727.5	723.7
145°	752.6	755.6	757.9	757.9	755.6
147.5°	782.2	784.5	786.0	788.3	782.2
150°	811.8	811.0	814.1	814.1	812.6
152.5°	836.1	837.6	838.4	840.7	837.6
155°	861.2	861.2	861.9	865.0	861.2
157.5°	883.9	882.4	883.2	886.2	880.9
160°	903.7	901.4	902.2	905.2	901.4
162.5°	921.2	919.6	919.6	923.4	918.9
165°	936.3	934.8	935.6	938.6	934.1
167.5°	950.0	947.0	947.0	951.5	947.0
170°	960.6	957.6	957.6	962.2	956.9
172.5°	968.2	965.2	965.2	969.8	965.2
175°	973.6	970.5	970.5	975.1	969.8
177.5°	977.4	974.3	973.6	978.1	972.8
180°	975.8	975.8	975.8	975.8	975.8

(END OF REPORT)