

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007896

Luminaire Tested: S125IP-B850UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007896
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B850UB2750-4F0-XX-W2A-1_5000K
Description: Define 5 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2635.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007896

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007896

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007896

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	62.7	2.4
100°-110°	186.4	7.1
110°-120°	316.1	12.0
120°-130°	416.2	15.8
130°-140°	466.4	17.7
140°-150°	457.1	17.3
150°-160°	384.0	14.6
160°-170°	255.2	9.7
170°-180°	89.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	565.3	21.5
90°-150°	1905.0	72.3
90°-180°	2634.0	100.0
0°-180°	2635.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	15	18	3
95°	48	49	56	62	63	50
105°	167	171	176	180	182	179
115°	316	319	321	320	319	313
125°	462	466	467	466	465	414
135°	601	605	606	606	603	463
145°	728	731	733	733	731	455
155°	833	833	834	836	833	384
165°	905	904	905	908	903	255
175°	941	938	938	943	938	89
180°	944	944	944	944	944	

TEST NUMBER: P1007896

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.7	6.6	11.7	15.4	17.6
92.5°	22.0	25.7	32.3	37.5	38.9
95°	47.7	49.2	56.5	61.7	63.2
97.5°	73.4	74.2	84.4	88.9	89.6
100°	102.8	102.8	112.4	119.0	120.4
102.5°	134.4	138.1	141.7	149.1	151.3
105°	167.4	171.1	175.5	179.9	182.1
107.5°	203.4	207.1	210.8	213.0	213.0
110°	240.9	244.5	246.7	248.9	248.2

TEST NUMBER: P1007896

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	279.0	280.5	283.4	284.2	282.7
115°	316.5	319.4	320.9	320.2	319.4
117.5°	354.7	355.4	356.9	357.6	354.7
120°	389.9	393.6	394.3	394.3	391.4
122.5°	428.1	428.8	431.0	430.3	428.1
125°	461.9	466.3	467.0	465.6	464.8
127.5°	499.3	501.5	502.3	501.5	500.1
130°	532.4	536.1	537.5	536.8	535.3
132.5°	565.4	572.0	571.3	570.6	568.4
135°	600.7	605.1	605.8	605.8	602.9
137.5°	633.7	638.1	639.6	640.3	636.7
140°	665.3	669.0	671.2	672.6	669.0
142.5°	696.9	699.8	702.7	703.5	699.8
145°	727.7	730.7	732.9	732.9	730.7
147.5°	756.4	758.6	760.0	762.2	756.4
150°	785.0	784.3	787.2	787.2	785.7
152.5°	808.5	810.0	810.7	812.9	810.0
155°	832.7	832.7	833.5	836.4	832.7
157.5°	854.8	853.3	854.0	857.0	851.8
160°	873.8	871.6	872.4	875.3	871.6
162.5°	890.7	889.3	889.3	892.9	888.5
165°	905.4	904.0	904.7	907.6	903.2
167.5°	918.6	915.7	915.7	920.1	915.7
170°	928.9	926.0	926.0	930.4	925.2
172.5°	936.3	933.3	933.3	937.7	933.3
175°	941.4	938.5	938.5	942.9	937.7
177.5°	945.1	942.1	941.4	945.8	940.7
180°	943.6	943.6	943.6	943.6	943.6

(END OF REPORT)