

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028502

Luminaire Tested: S125RDIP-B1090D375UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028502
REPORT IS A COMBINATION OF REPORTS P1005037 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D375UB50-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5263.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028502

CATALOG NUMBER: S125RDIP-B1090D375UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028502

CATALOG NUMBER: S125RDIP-B1090D375UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69
2	95	88	81	76	90	84	78	73	76	72	68	70	66	63	64	61	59
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	53	50
4	80	69	61	54	76	66	58	53	61	54	50	56	51	46	51	47	43
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38
6	68	55	47	41	65	53	46	40	49	43	38	45	40	36	42	37	34
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	34	30
8	59	46	38	32	56	44	37	32	41	35	30	38	33	29	35	31	27
9	55	42	34	29	52	41	33	29	38	32	27	35	30	26	33	28	25
10	51	39	31	26	49	38	31	26	35	29	25	33	27	24	30	26	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1028502

CATALOG NUMBER: S125RDIP-B1090D375UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	3.1
10°-20°	449.3	8.5
20°-30°	651.5	12.4
30°-40°	742.2	14.1
40°-50°	723.5	13.7
50°-60°	608.8	11.6
60°-70°	426.7	8.1
70°-80°	218.7	4.2
80°-90°	55.2	1.0
90°-100°	29.2	0.6
100°-110°	86.8	1.6
110°-120°	147.2	2.8
120°-130°	193.8	3.7
130°-140°	217.2	4.1
140°-150°	212.9	4.0
150°-160°	178.8	3.4
160°-170°	118.9	2.3
170°-180°	41.6	0.8
0°-30°	1261.6	24.0
0°-40°	2003.8	38.1
0°-60°	3336.1	63.4
0°-90°	4036.7	76.7
90°-120°	263.2	5.0
90°-150°	887.1	16.9
90°-180°	1226.0	23.3
0°-180°	5263.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	0	3	6	7	8	6
95°	22	23	26	29	29	23
105°	78	80	82	84	85	83
115°	147	149	149	149	149	146
125°	215	217	218	217	216	193
135°	280	282	282	282	281	216
145°	339	340	341	341	340	212
155°	388	388	388	390	388	179
165°	422	421	421	423	421	119
175°	438	437	437	439	437	42
180°	439	439	439	439	439	

TEST NUMBER: P1028502

CATALOG NUMBER: S125RDIP-B1090D375UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	0.3	3.1	5.5	7.2	8.2
92.5°	10.3	12.0	15.0	17.4	18.1
95°	22.2	22.9	26.3	28.7	29.4
97.5°	34.2	34.5	39.3	41.4	41.7
100°	47.9	47.9	52.3	55.4	56.1
102.5°	62.6	64.3	66.0	69.4	70.4
105°	78.0	79.7	81.7	83.8	84.8
107.5°	94.7	96.4	98.1	99.2	99.2
110°	112.2	113.9	114.9	115.9	115.6

TEST NUMBER: P1028502

CATALOG NUMBER: S125RDIP-B1090D375UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	129.9	130.6	132.0	132.3	131.6
115°	147.4	148.7	149.4	149.1	148.7
117.5°	165.2	165.5	166.2	166.5	165.2
120°	181.6	183.3	183.6	183.6	182.3
122.5°	199.4	199.7	200.7	200.4	199.4
125°	215.1	217.1	217.5	216.8	216.4
127.5°	232.5	233.5	233.9	233.5	232.9
130°	247.9	249.6	250.3	250.0	249.3
132.5°	263.3	266.4	266.0	265.7	264.7
135°	279.7	281.8	282.1	282.1	280.7
137.5°	295.1	297.1	297.8	298.2	296.5
140°	309.8	311.5	312.5	313.2	311.5
142.5°	324.5	325.9	327.2	327.6	325.9
145°	338.9	340.2	341.3	341.3	340.2
147.5°	352.2	353.2	353.9	354.9	352.2
150°	365.5	365.2	366.6	366.6	365.9
152.5°	376.5	377.2	377.5	378.5	377.2
155°	387.8	387.8	388.1	389.5	387.8
157.5°	398.0	397.3	397.7	399.0	396.7
160°	406.9	405.9	406.2	407.6	405.9
162.5°	414.8	414.1	414.1	415.8	413.7
165°	421.6	420.9	421.3	422.6	420.6
167.5°	427.8	426.4	426.4	428.5	426.4
170°	432.6	431.2	431.2	433.2	430.8
172.5°	436.0	434.6	434.6	436.7	434.6
175°	438.4	437.0	437.0	439.1	436.7
177.5°	440.1	438.7	438.4	440.4	438.0
180°	439.4	439.4	439.4	439.4	439.4

(END OF REPORT)