

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007902

Luminaire Tested: S125IP-B850UB2750-4F0-XX-W2A_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007902
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B850UB2750-4F0-XX-W2A_2700K
Description: Define 5 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3139.0 lumens
Efficiency: N/A
Efficacy: 148.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007902

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007902

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007902

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.0
90°-100°	34.7	1.1
100°-110°	230.5	7.3
110°-120°	415.1	13.2
120°-130°	532.8	17.0
130°-140°	573.1	18.3
140°-150°	537.9	17.1
150°-160°	435.1	13.9
160°-170°	281.4	9.0
170°-180°	97.0	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.0
90°-120°	680.3	21.7
90°-150°	2324.0	74.0
90°-180°	3137.0	99.9
0°-180°	3139.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	16	18	2
95°	43	41	12	16	16	53
105°	223	226	226	226	225	236
115°	418	422	422	420	415	414
125°	594	600	600	597	594	531
135°	741	746	744	743	738	571
145°	859	861	861	862	857	537
155°	946	942	943	946	940	436
165°	999	994	995	999	993	282
175°	1021	1017	1018	1024	1017	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1007902

CATALOG NUMBER: S125IP-B850UB2750-4FO-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	6.8	12.1	15.9	18.2
92.5°	14.4	7.6	12.1	15.9	16.7
95°	43.2	40.9	12.1	15.9	15.9
97.5°	81.0	85.6	13.6	15.1	15.9
100°	126.4	128.7	131.7	18.9	15.9
102.5°	172.6	175.7	177.2	178.7	115.1
105°	222.6	225.6	225.6	225.6	224.9
107.5°	274.1	274.1	275.6	276.4	273.3
110°	324.1	324.1	325.6	323.3	324.1

TEST NUMBER: P1007902

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.0	373.3	374.0	371.0	369.5
115°	417.9	421.7	422.5	419.5	414.9
117.5°	467.2	467.2	470.2	465.6	464.1
120°	512.6	511.8	514.1	512.6	508.8
122.5°	552.7	556.5	557.3	555.7	551.2
125°	594.4	599.7	599.7	596.6	594.4
127.5°	634.5	638.3	637.5	636.0	629.9
130°	670.8	674.6	675.4	673.1	669.3
132.5°	707.2	711.7	709.4	709.4	705.7
135°	741.2	745.8	744.3	742.8	738.2
137.5°	773.0	777.6	776.1	776.1	772.3
140°	804.1	805.6	804.8	806.4	801.8
142.5°	832.1	832.9	834.4	834.4	829.8
145°	859.4	860.9	860.9	861.6	857.1
147.5°	883.6	883.6	884.3	885.1	879.8
150°	906.3	904.8	906.3	907.8	901.8
152.5°	928.3	924.5	926.0	927.5	922.2
155°	946.4	941.9	943.4	945.7	939.6
157.5°	960.8	958.5	958.5	960.8	954.8
160°	976.0	971.4	972.2	975.2	969.1
162.5°	988.1	983.5	984.3	988.8	982.0
165°	998.7	994.1	994.9	999.4	993.4
167.5°	1007.0	1002.5	1003.2	1008.5	1001.7
170°	1013.8	1008.5	1009.3	1015.3	1008.5
172.5°	1018.4	1013.1	1014.6	1019.9	1013.1
175°	1021.4	1016.8	1017.6	1023.7	1016.8
177.5°	1023.7	1019.1	1019.9	1025.2	1019.1
180°	1021.4	1021.4	1021.4	1021.4	1021.4

(END OF REPORT)