

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007905

Luminaire Tested: S125IP-B850UB2750-4F0-XX-W2A_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B850UB2750-4F0-XX-W2A_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3149.0 lumens
Efficiency: N/A
Efficacy: 149.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007905

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007905

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007905

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.0
90°-100°	34.8	1.1
100°-110°	231.2	7.3
110°-120°	416.4	13.2
120°-130°	534.5	17.0
130°-140°	574.9	18.3
140°-150°	539.6	17.1
150°-160°	436.4	13.9
160°-170°	282.3	9.0
170°-180°	97.3	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.0
90°-120°	682.5	21.7
90°-150°	2331.4	74.0
90°-180°	3147.0	99.9
0°-180°	3149.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	16	18	2
95°	43	41	12	16	16	53
105°	223	226	226	226	226	237
115°	419	423	424	421	416	416
125°	596	602	602	598	596	533
135°	744	748	747	745	741	573
145°	862	864	864	864	860	539
155°	949	945	946	949	943	437
165°	1002	997	998	1003	996	283
175°	1025	1020	1021	1027	1020	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1007905

CATALOG NUMBER: S125IP-B850UB2750-4FO-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	6.8	12.2	16.0	18.2
92.5°	14.4	7.6	12.2	16.0	16.7
95°	43.3	41.0	12.2	16.0	16.0
97.5°	81.3	85.8	13.7	15.2	16.0
100°	126.8	129.1	132.2	19.0	16.0
102.5°	173.2	176.2	177.7	179.3	115.5
105°	223.3	226.3	226.3	226.3	225.6
107.5°	275.0	275.0	276.5	277.2	274.2
110°	325.1	325.1	326.6	324.3	325.1

TEST NUMBER: P1007905

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.2	374.5	375.2	372.2	370.7
115°	419.3	423.1	423.8	420.8	416.2
117.5°	468.6	468.6	471.7	467.1	465.6
120°	514.2	513.5	515.7	514.2	510.4
122.5°	554.5	558.3	559.0	557.5	553.0
125°	596.3	601.6	601.6	598.5	596.3
127.5°	636.5	640.3	639.5	638.0	632.0
130°	673.0	676.8	677.5	675.2	671.4
132.5°	709.4	714.0	711.7	711.7	707.9
135°	743.6	748.2	746.6	745.1	740.6
137.5°	775.5	780.1	778.5	778.5	774.7
140°	806.6	808.2	807.4	808.9	804.4
142.5°	834.8	835.5	837.0	837.0	832.5
145°	862.1	863.6	863.6	864.4	859.8
147.5°	886.4	886.4	887.2	887.9	882.6
150°	909.2	907.7	909.2	910.7	904.6
152.5°	931.2	927.4	928.9	930.5	925.1
155°	949.4	944.9	946.4	948.7	942.6
157.5°	963.9	961.6	961.6	963.9	957.8
160°	979.1	974.5	975.3	978.3	972.2
162.5°	991.2	986.7	987.4	992.0	985.1
165°	1001.9	997.3	998.1	1002.6	996.5
167.5°	1010.2	1005.7	1006.4	1011.7	1004.9
170°	1017.0	1011.7	1012.5	1018.6	1011.7
172.5°	1021.6	1016.3	1017.8	1023.1	1016.3
175°	1024.6	1020.1	1020.8	1026.9	1020.1
177.5°	1026.9	1022.4	1023.1	1028.4	1022.4
180°	1024.6	1024.6	1024.6	1024.6	1024.6

(END OF REPORT)