

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007906

Luminaire Tested: S125IP-B850UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B850UB2750-4F0-XX-W2A_5000K
Description: Define 5 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3045.0 lumens
Efficiency: N/A
Efficacy: 144.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007906

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007906

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007906

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.0
90°-100°	33.6	1.1
100°-110°	223.6	7.3
110°-120°	402.7	13.2
120°-130°	516.9	17.0
130°-140°	555.9	18.3
140°-150°	521.7	17.1
150°-160°	422.0	13.9
160°-170°	272.9	9.0
170°-180°	94.1	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.0
90°-120°	659.9	21.7
90°-150°	2254.4	74.0
90°-180°	3044.0	100.0
0°-180°	3045.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	7	12	15	18	2
95°	42	40	12	15	15	51
105°	216	219	219	219	218	229
115°	405	409	410	407	402	402
125°	577	582	582	579	577	515
135°	719	724	722	720	716	554
145°	834	835	835	836	831	521
155°	918	914	915	917	912	423
165°	969	964	965	970	964	274
175°	991	986	987	993	986	94
180°	991	991	991	991	991	

TEST NUMBER: P1007906

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.7	6.6	11.8	15.4	17.6
92.5°	14.0	7.3	11.8	15.4	16.2
95°	41.9	39.7	11.8	15.4	15.4
97.5°	78.6	83.0	13.2	14.7	15.4
100°	122.7	124.9	127.8	18.4	15.4
102.5°	167.5	170.4	171.9	173.3	111.6
105°	215.9	218.9	218.9	218.9	218.1
107.5°	265.9	265.9	267.3	268.1	265.1
110°	314.4	314.4	315.8	313.6	314.4

TEST NUMBER: P1007906

CATALOG NUMBER: S125IP-B850UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	359.9	362.1	362.8	359.9	358.4
115°	405.4	409.1	409.8	406.9	402.5
117.5°	453.2	453.2	456.1	451.7	450.2
120°	497.2	496.5	498.7	497.2	493.6
122.5°	536.2	539.8	540.6	539.1	534.7
125°	576.6	581.7	581.7	578.8	576.6
127.5°	615.5	619.2	618.4	617.0	611.1
130°	650.7	654.4	655.1	652.9	649.3
132.5°	686.0	690.4	688.2	688.2	684.5
135°	719.0	723.5	722.0	720.5	716.1
137.5°	749.9	754.3	752.8	752.8	749.2
140°	780.0	781.5	780.7	782.2	777.8
142.5°	807.2	807.9	809.4	809.4	805.0
145°	833.6	835.1	835.1	835.8	831.4
147.5°	857.1	857.1	857.9	858.6	853.5
150°	879.2	877.7	879.2	880.6	874.8
152.5°	900.5	896.8	898.3	899.7	894.6
155°	918.1	913.7	915.2	917.4	911.5
157.5°	932.0	929.8	929.8	932.0	926.2
160°	946.7	942.3	943.1	946.0	940.1
162.5°	958.5	954.1	954.8	959.2	952.6
165°	968.8	964.4	965.1	969.5	963.6
167.5°	976.8	972.4	973.2	978.3	971.7
170°	983.5	978.3	979.0	984.9	978.3
172.5°	987.9	982.7	984.2	989.3	982.7
175°	990.8	986.4	987.1	993.0	986.4
177.5°	993.0	988.6	989.3	994.5	988.6
180°	990.8	990.8	990.8	990.8	990.8

(END OF REPORT)