

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007790

Luminaire Tested: S125IP-B1090UB35-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1090UB35-4F0-XX-W2A-1
Description: Define 5 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3562.0 lumens
Efficiency: N/A
Efficacy: 125.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007790

CATALOG NUMBER: S125IP-B1090UB35-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P1007790

CATALOG NUMBER: S125IP-B1090UB35-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007790

CATALOG NUMBER: S125IP-B1090UB35-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	84.8	2.4
100°-110°	252.0	7.1
110°-120°	427.4	12.0
120°-130°	562.6	15.8
130°-140°	630.4	17.7
140°-150°	617.9	17.3
150°-160°	519.1	14.6
160°-170°	345.0	9.7
170°-180°	120.7	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	764.2	21.5
90°-150°	2575.2	72.3
90°-180°	3560.0	99.9
0°-180°	3562.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	4
95°	64	66	76	83	85	67
105°	226	231	237	243	246	241
115°	428	432	434	433	432	423
125°	624	630	631	629	628	559
135°	812	818	819	819	815	626
145°	984	988	991	991	988	615
155°	1126	1126	1127	1131	1126	519
165°	1224	1222	1223	1227	1221	345
175°	1273	1269	1269	1275	1268	121
180°	1276	1276	1276	1276	1276	

TEST NUMBER: P1007790

CATALOG NUMBER: S125IP-B1090UB35-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	8.9	15.9	20.8	23.8
92.5°	29.8	34.7	43.7	50.6	52.6
95°	64.5	66.5	76.4	83.4	85.4
97.5°	99.3	100.3	114.2	120.1	121.1
100°	139.0	139.0	151.9	160.8	162.8
102.5°	181.7	186.6	191.6	201.5	204.5
105°	226.3	231.3	237.2	243.2	246.2
107.5°	275.0	279.9	284.9	287.9	287.9
110°	325.6	330.6	333.5	336.5	335.5

TEST NUMBER: P1007790

CATALOG NUMBER: S125IP-B1090UB35-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.2	379.2	383.2	384.2	382.2
115°	427.8	431.8	433.8	432.8	431.8
117.5°	479.5	480.4	482.4	483.4	479.5
120°	527.1	532.1	533.1	533.1	529.1
122.5°	578.7	579.7	582.7	581.7	578.7
125°	624.4	630.3	631.3	629.3	628.4
127.5°	675.0	678.0	679.0	678.0	676.0
130°	719.7	724.6	726.6	725.6	723.7
132.5°	764.3	773.3	772.3	771.3	768.3
135°	812.0	818.0	818.9	818.9	815.0
137.5°	856.7	862.6	864.6	865.6	860.6
140°	899.4	904.3	907.3	909.3	904.3
142.5°	942.0	946.0	950.0	951.0	946.0
145°	983.7	987.7	990.7	990.7	987.7
147.5°	1022.4	1025.4	1027.4	1030.4	1022.4
150°	1061.2	1060.2	1064.1	1064.1	1062.1
152.5°	1092.9	1094.9	1095.9	1098.9	1094.9
155°	1125.7	1125.7	1126.7	1130.6	1125.7
157.5°	1155.5	1153.5	1154.5	1158.4	1151.5
160°	1181.3	1178.3	1179.3	1183.3	1178.3
162.5°	1204.1	1202.1	1202.1	1207.1	1201.1
165°	1224.0	1222.0	1223.0	1226.9	1221.0
167.5°	1241.8	1237.8	1237.8	1243.8	1237.8
170°	1255.7	1251.7	1251.7	1257.7	1250.8
172.5°	1265.6	1261.7	1261.7	1267.6	1261.7
175°	1272.6	1268.6	1268.6	1274.6	1267.6
177.5°	1277.6	1273.6	1272.6	1278.5	1271.6
180°	1275.6	1275.6	1275.6	1275.6	1275.6

(END OF REPORT)