

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028561

Luminaire Tested: S125RDIP-B1090D850UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028561
REPORT IS A COMBINATION OF REPORTS P1005118 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D850UB50-4F0-XX-W2A-F4
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6778.6 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028561

CATALOG NUMBER: S125RDIP-B1090D850UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1028561

CATALOG NUMBER: S125RDIP-B1090D850UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	100	96	92	89	93	90	86	83	78	76	73	68	66	64	58	57	55
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	40
4	77	66	58	52	71	62	55	49	54	49	44	47	43	40	41	38	35
5	70	59	51	45	66	55	48	43	49	43	38	43	38	34	37	33	31
6	65	53	45	39	61	50	42	37	44	38	34	39	34	30	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20
10	49	37	29	25	46	35	28	24	31	25	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10945	10945	10945
5°	10946	10672	10689
10°	10839	10403	10312
15°	10686	10027	9815
20°	10496	9574	9294
25°	10279	9132	8735
30°	10012	8646	8148
35°	9739	8152	7525
40°	9481	7645	6917
45°	9170	7097	6279
50°	8855	6516	5630
55°	8488	5944	4958
60°	8114	5290	4261
65°	7668	4558	3510
70°	7147	3710	2762
75°	6426	2791	2012
80°	5419	1806	1356
85°	4059	971	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9170 cd/sqm

TEST NUMBER: P1028561

CATALOG NUMBER: S125RDIP-B1090D850UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	2.4
10°-20°	449.3	6.6
20°-30°	651.5	9.6
30°-40°	742.2	10.9
40°-50°	723.5	10.7
50°-60°	608.8	9.0
60°-70°	426.7	6.3
70°-80°	218.7	3.2
80°-90°	56.0	0.8
90°-100°	274.3	4.0
100°-110°	569.7	8.4
110°-120°	532.1	7.8
120°-130°	430.6	6.4
130°-140°	345.9	5.1
140°-150°	261.1	3.9
150°-160°	183.9	2.7
160°-170°	108.4	1.6
170°-180°	35.2	0.5
0°-30°	1261.6	18.6
0°-40°	2003.8	29.6
0°-60°	3336.1	49.2
0°-90°	4037.5	59.6
90°-120°	1376.1	20.3
90°-150°	2413.7	35.6
90°-180°	2741.0	40.4
0°-180°	6778.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1706	1700	1686	1699	1697	162
15°	1622	1614	1587	1586	1574	457
25°	1471	1452	1404	1387	1373	677
35°	1267	1236	1178	1141	1122	793
45°	1037	1000	929	877	858	800
55°	787	746	674	615	595	704
65°	533	489	421	369	350	528
75°	284	245	191	163	154	300
85°	71	48	41	40	39	78
90°	1	7	12	15	17	6
95°	24	72	651	295	173	25
105°	83	116	532	1048	973	87
115°	148	179	427	921	1084	146
125°	206	241	410	733	854	183
135°	241	290	407	614	709	187
145°	280	321	408	508	560	176
155°	320	344	398	450	469	147
165°	350	359	382	405	411	98
175°	364	364	366	371	369	35
180°	364	364	364	364	364	

TEST NUMBER: P1028561

CATALOG NUMBER: S125RDIP-B1090D850UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.3	1708.3	1708.3	1708.3	1708.3
2.5°	1712.1	1708.3	1695.4	1708.3	1707.0
5°	1705.7	1700.5	1686.3	1699.2	1696.6
7.5°	1692.8	1687.6	1670.8	1681.2	1678.6
10°	1673.4	1669.5	1651.5	1655.4	1651.5
12.5°	1651.5	1646.3	1620.5	1623.1	1616.6
15°	1621.8	1614.1	1587.0	1585.7	1574.1
17.5°	1590.8	1579.2	1547.0	1540.5	1531.5
20°	1553.4	1540.5	1499.2	1492.8	1481.2
22.5°	1512.1	1499.2	1455.4	1441.2	1432.1
25°	1470.9	1451.5	1403.8	1387.0	1372.8
27.5°	1424.4	1401.2	1350.9	1328.9	1314.7
30°	1372.8	1348.3	1294.1	1264.4	1252.8
32.5°	1322.5	1292.8	1237.3	1203.8	1188.3
35°	1267.0	1236.0	1178.0	1140.6	1122.5
37.5°	1214.1	1176.7	1117.3	1073.5	1055.4
40°	1157.3	1118.6	1056.7	1007.7	992.2
42.5°	1098.0	1058.0	993.5	947.0	922.5
45°	1037.3	999.9	929.0	877.4	858.0
47.5°	974.1	935.4	864.4	811.6	789.6
50°	914.8	872.2	798.6	744.5	725.1
52.5°	850.3	806.4	738.0	678.7	659.3
55°	787.0	745.7	673.5	615.4	594.8
57.5°	722.5	678.7	609.0	552.2	534.2
60°	660.6	615.4	545.8	489.0	469.6
62.5°	594.8	552.2	481.3	429.6	410.3
65°	532.9	489.0	420.6	369.0	349.7
67.5°	470.9	427.1	361.3	312.2	296.8
70°	407.7	363.8	299.3	259.3	243.9
72.5°	345.8	303.2	243.9	207.7	198.7
75°	283.8	245.1	191.0	162.6	153.5
77.5°	220.6	189.7	144.5	122.6	114.8
80°	167.7	136.8	100.6	89.0	86.4
82.5°	116.1	89.0	67.1	63.2	61.9
85°	71.0	47.7	41.3	40.0	38.7
87.5°	29.7	20.6	19.4	19.4	18.1
90°	0.7	6.6	11.7	15.4	16.9
92.5°	11.0	60.2	293.0	78.2	54.3
95°	24.2	71.6	650.6	295.2	172.6
97.5°	37.4	77.5	702.7	533.1	378.2
100°	51.4	88.8	663.1	753.4	572.7
102.5°	66.8	101.7	593.3	939.9	790.1
105°	83.0	116.0	532.4	1048.2	972.9
107.5°	98.4	131.0	486.8	1078.6	1083.1
110°	115.3	146.9	456.7	1049.7	1133.0



TEST NUMBER: P1028561

CATALOG NUMBER: S125RDIP-B1090D850UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	132.2	162.6	439.1	989.1	1127.1
115°	148.3	178.8	427.4	921.2	1083.8
117.5°	163.0	195.3	420.7	859.5	1018.5
120°	177.7	211.1	416.3	807.7	955.3
122.5°	193.1	226.5	412.7	766.2	899.5
125°	205.6	240.8	409.7	732.8	854.0
127.5°	215.9	254.8	408.3	704.2	812.1
130°	225.4	268.0	406.8	675.2	779.1
132.5°	232.8	279.8	406.8	644.0	746.0
135°	240.8	289.7	406.8	614.2	709.3
137.5°	251.1	298.8	407.5	583.0	671.1
140°	259.9	306.6	408.3	554.4	630.8
142.5°	270.2	313.9	409.0	529.8	593.3
145°	280.5	321.2	408.3	508.5	559.5
147.5°	291.5	327.8	406.8	490.1	529.4
150°	301.1	333.8	404.6	475.1	505.2
152.5°	311.3	339.6	401.7	462.2	486.1
155°	320.1	344.4	398.0	449.8	469.2
157.5°	328.2	349.2	394.3	438.0	453.8
160°	336.3	352.8	390.6	426.2	438.4
162.5°	342.9	356.5	386.2	415.6	424.4
165°	349.5	359.1	381.8	405.0	411.2
167.5°	353.9	360.6	377.4	395.0	398.7
170°	358.3	362.4	373.8	385.5	387.7
172.5°	361.3	363.1	369.3	377.8	377.4
175°	363.5	363.5	366.4	370.8	369.3
177.5°	364.9	363.5	364.2	366.4	364.2
180°	364.2	364.2	364.2	364.2	364.2

(END OF REPORT)