

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907653

Luminaire Tested: DFN2DIP-4P3F0-030D020US840-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907653
REPORT IS A COMBINATION OF REPORTS P900552 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US840-RLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4574.6 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907653

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907653

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	100	96	92	88		93	89	86	83		77	75	72		66	64	63		56	54	53
2	91	84	78	73		85	79	73	69		68	64	61		58	56	53		50	48	46
3	84	74	67	62		78	70	63	58		61	56	52		52	49	46		44	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	51	46		66	56	49	43		49	43	39		42	38	35		36	33	31
6	65	54	46	40		61	50	43	38		44	39	34		39	34	31		33	30	27
7	61	49	41	35		56	46	39	34		40	35	30		35	31	27		30	27	24
8	56	44	37	31		52	42	35	30		37	31	27		32	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	28	25		30	25	22		26	23	20
10	49	37	30	25		46	35	29	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1427	1427	1427
5°	1428	1403	1413
10°	1413	1375	1366
15°	1393	1328	1295
20°	1366	1265	1207
25°	1339	1194	1123
30°	1303	1121	1016
35°	1267	1043	922
40°	1231	963	814
45°	1189	873	716
50°	1145	783	621
55°	1099	686	529
60°	1046	586	435
65°	985	484	391
70°	911	389	353
75°	818	341	320
80°	684	283	276
85°	464	184	205

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1189 cd/sqm

TEST NUMBER: P907653

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	2.6
10°-20°	322.1	7.0
20°-30°	452.3	9.9
30°-40°	493.0	10.8
40°-50°	453.1	9.9
50°-60°	355.9	7.8
60°-70°	231.6	5.1
70°-80°	119.2	2.6
80°-90°	31.6	0.7
90°-100°	22.5	0.5
100°-110°	83.8	1.8
110°-120°	222.2	4.9
120°-130°	368.6	8.1
130°-140°	391.5	8.6
140°-150°	363.9	8.0
150°-160°	292.5	6.4
160°-170°	188.5	4.1
170°-180°	64.9	1.4
0°-30°	891.8	19.5
0°-40°	1384.8	30.3
0°-60°	2193.8	48.0
0°-90°	2576.3	56.3
90°-120°	328.5	7.2
90°-150°	1452.4	31.7
90°-180°	1998.0	43.7
0°-180°	4574.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1252	1252	1252	1252	1252	
5°	1252	1246	1232	1242	1238	119
15°	1191	1178	1140	1118	1107	336
25°	1081	1045	970	924	906	497
35°	932	874	774	703	678	583
45°	762	686	567	486	459	588
55°	579	491	368	300	279	517
65°	391	299	197	159	155	388
75°	208	129	91	83	82	220
85°	49	25	22	22	22	56
90°	0	6	10	12	13	4
95°	32	16	19	22	21	38
105°	150	165	30	35	38	160
115°	284	292	304	76	40	279
125°	401	407	417	420	422	358
135°	496	504	508	514	512	383
145°	576	575	584	587	584	360
155°	634	629	635	638	634	292
165°	668	665	666	670	666	189
175°	683	680	681	684	679	65
180°	682	682	682	682	682	

TEST NUMBER: P907653

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1252.1	1252.1	1252.1	1252.1	1252.1
2.5°	1257.8	1252.1	1239.6	1251.0	1248.8
5°	1252.1	1246.5	1231.7	1241.9	1238.5
7.5°	1241.9	1235.2	1219.3	1223.8	1218.1
10°	1228.3	1220.4	1197.8	1194.3	1187.6
12.5°	1211.3	1201.1	1170.5	1163.8	1151.2
15°	1190.9	1178.4	1139.9	1118.4	1107.1
17.5°	1167.1	1149.0	1101.4	1076.5	1058.3
20°	1139.9	1117.2	1060.6	1032.4	1007.3
22.5°	1110.5	1084.4	1018.7	980.2	963.2
25°	1081.1	1044.7	970.0	923.5	906.5
27.5°	1045.9	1007.3	924.6	871.4	845.3
30°	1008.6	965.4	874.7	817.1	786.4
32.5°	972.2	920.1	827.3	759.2	730.8
35°	931.5	873.6	774.0	702.6	677.6
37.5°	891.8	829.4	724.1	645.8	617.6
40°	849.9	781.9	672.0	591.5	562.1
42.5°	806.8	734.4	619.9	535.9	507.7
45°	761.5	685.5	566.6	486.0	458.9
47.5°	718.4	638.0	515.6	435.1	410.2
50°	670.9	590.4	465.7	387.5	363.8
52.5°	624.3	539.4	418.2	343.4	321.8
55°	579.0	490.6	368.2	300.3	278.8
57.5°	532.6	441.9	324.2	260.6	242.5
60°	484.9	394.4	277.6	219.8	201.8
62.5°	438.6	347.9	237.9	183.6	174.6
65°	390.9	299.1	197.1	158.6	155.2
67.5°	345.7	253.8	158.6	139.4	135.9
70°	298.0	209.6	131.4	120.1	115.5
72.5°	252.7	168.7	109.9	100.9	98.6
75°	208.4	129.2	90.7	82.7	81.6
77.5°	164.3	91.7	71.4	66.9	64.5
80°	123.5	65.7	54.3	49.9	49.9
82.5°	86.0	44.2	37.4	35.1	35.1
85°	48.7	24.8	21.5	21.5	21.5
87.5°	18.2	9.0	9.0	8.0	8.0
90°	0.5	6.0	9.8	12.3	13.3
92.5°	12.3	10.4	11.8	12.8	13.3
95°	32.0	15.8	19.2	21.7	21.2
97.5°	57.7	17.3	25.1	26.7	27.2
100°	87.4	19.7	28.1	32.0	33.0
102.5°	119.9	118.9	29.1	34.5	36.1
105°	150.0	164.7	30.1	35.4	37.5
107.5°	185.0	197.2	31.1	36.5	38.5
110°	218.5	228.8	86.3	37.1	39.0

TEST NUMBER: P907653

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	250.0	258.9	250.5	38.0	39.5
115°	283.6	292.0	304.4	75.9	40.5
117.5°	312.7	322.6	330.9	260.4	131.2
120°	345.3	352.6	361.5	367.5	300.8
122.5°	372.8	380.7	390.6	393.5	394.2
125°	401.0	407.4	416.8	420.2	421.7
127.5°	426.7	433.5	441.0	445.9	446.4
130°	450.8	458.7	464.1	469.6	469.1
132.5°	475.4	481.9	487.3	491.7	491.3
135°	496.2	504.1	508.5	513.5	512.5
137.5°	517.9	523.8	528.8	533.7	532.2
140°	539.1	543.1	548.5	552.9	550.5
142.5°	556.8	560.4	566.7	570.7	568.2
145°	575.6	575.1	583.5	586.9	584.5
147.5°	591.9	590.4	598.7	601.2	599.3
150°	607.6	604.2	612.1	615.0	612.6
152.5°	621.0	617.0	624.4	627.4	623.9
155°	633.8	629.3	635.3	638.2	634.3
157.5°	644.2	640.3	644.7	648.1	644.2
160°	653.1	650.1	653.1	656.0	652.6
162.5°	660.9	657.9	660.5	663.9	659.4
165°	667.8	664.9	666.3	669.8	666.3
167.5°	673.3	670.2	671.8	675.3	670.8
170°	677.7	674.7	675.7	679.1	674.7
172.5°	680.6	677.7	678.7	682.2	677.7
175°	683.1	679.6	680.6	684.1	679.1
177.5°	684.1	680.6	681.2	684.6	680.1
180°	681.7	681.7	681.7	681.7	681.7

TEST NUMBER: P907653

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.92	9.80	9.83	10.73	11.91	4.88	5.76	5.79	6.69	7.87
	3H	10.60	11.39	11.52	12.32	13.52	6.07	6.86	6.99	7.79	8.99
	4H	11.20	11.95	12.14	12.89	14.10	6.51	7.26	7.45	8.20	9.41
	6H	11.63	12.31	12.57	13.26	14.48	6.83	7.52	7.78	8.46	9.69
	8H	11.75	12.41	12.70	13.36	14.59	6.92	7.58	7.87	8.53	9.76
	12H	11.81	12.43	12.77	13.39	14.64	6.96	7.59	7.92	8.54	9.79
4H	2H	8.94	9.69	9.88	10.63	11.84	5.48	6.23	6.42	7.16	8.38
	3H	10.77	11.39	11.72	12.36	13.59	6.83	7.45	7.78	8.41	9.64
	4H	11.46	12.03	12.42	12.99	14.24	7.37	7.94	8.33	8.90	10.15
	6H	11.98	12.46	12.95	13.45	14.70	7.79	8.27	8.76	9.26	10.51
	8H	12.15	12.60	13.12	13.58	14.85	7.91	8.37	8.89	9.35	10.61
	12H	12.24	12.65	13.24	13.65	14.92	7.98	8.39	8.97	9.38	10.65
8H	4H	11.43	11.89	12.41	12.87	14.13	7.65	8.11	8.63	9.09	10.35
	6H	11.99	12.37	12.99	13.39	14.66	8.17	8.54	9.16	9.56	10.83
	8H	12.21	12.54	13.22	13.55	14.83	8.35	8.68	9.36	9.69	10.98
	12H	12.35	12.64	13.36	13.64	14.97	8.47	8.76	9.48	9.76	11.09
12H	4H	11.39	11.80	12.38	12.79	14.06	7.66	8.07	8.65	9.06	10.34
	6H	11.97	12.30	12.98	13.31	14.59	8.21	8.54	9.22	9.55	10.84
	8H	12.19	12.48	13.20	13.48	14.81	8.42	8.71	9.43	9.71	11.04