

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028596

Luminaire Tested: S125RDIP-B1270D1270UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028596
REPORT IS A COMBINATION OF REPORTS P1005163 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB27-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8977.0 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028596

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028596

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	54	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13142	13142	13142
5°	13143	12814	12834
10°	13015	12491	12381
15°	12831	12039	11785
20°	12603	11495	11159
25°	12341	10964	10488
30°	12021	10380	9784
35°	11694	9788	9036
40°	11384	9179	8305
45°	11010	8521	7540
50°	10632	7823	6760
55°	10192	7137	5954
60°	9742	6351	5116
65°	9206	5473	4213
70°	8580	4455	3316
75°	7717	3350	2417
80°	6508	2169	1630
85°	4871	1166	919

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11010 cd/sqm

TEST NUMBER: P1028596

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.0	2.2
10°-20°	539.5	6.0
20°-30°	782.2	8.7
30°-40°	891.2	9.9
40°-50°	868.6	9.7
50°-60°	731.0	8.1
60°-70°	512.3	5.7
70°-80°	262.6	2.9
80°-90°	67.8	0.8
90°-100°	98.4	1.1
100°-110°	292.2	3.3
110°-120°	495.6	5.5
120°-130°	652.5	7.3
130°-140°	731.2	8.1
140°-150°	716.7	8.0
150°-160°	602.0	6.7
160°-170°	400.2	4.5
170°-180°	140.0	1.6
0°-30°	1514.8	16.9
0°-40°	2405.9	26.8
0°-60°	4005.6	44.6
0°-90°	4848.3	54.0
90°-120°	886.2	9.9
90°-150°	2986.5	33.3
90°-180°	4129.0	46.0
0°-180°	8977.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2051	2051	2051	2051	2051	
5°	2048	2042	2025	2040	2037	194
15°	1947	1938	1906	1904	1890	549
25°	1766	1743	1686	1665	1648	813
35°	1521	1484	1414	1370	1348	953
45°	1246	1201	1115	1053	1030	961
55°	945	895	809	739	714	845
65°	640	587	505	443	420	634
75°	341	294	229	195	184	360
85°	85	57	50	48	46	93
90°	1	10	18	24	28	10
95°	75	77	89	97	99	78
105°	262	268	275	282	286	280
115°	496	501	503	502	501	491
125°	724	731	732	730	729	649
135°	942	949	950	950	945	726
145°	1141	1146	1149	1149	1146	713
155°	1306	1306	1307	1311	1306	601
165°	1420	1417	1418	1423	1416	401
175°	1476	1471	1471	1478	1470	140
180°	1479	1479	1479	1479	1479	

TEST NUMBER: P1028596

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2051.1	2051.1	2051.1	2051.1	2051.1
2.5°	2055.7	2051.1	2035.6	2051.1	2049.5
5°	2048.0	2041.8	2024.8	2040.2	2037.1
7.5°	2032.5	2026.3	2006.2	2018.6	2015.5
10°	2009.3	2004.6	1982.9	1987.6	1982.9
12.5°	1982.9	1976.7	1945.7	1948.8	1941.1
15°	1947.3	1938.0	1905.5	1903.9	1890.0
17.5°	1910.1	1896.2	1857.4	1849.7	1838.9
20°	1865.2	1849.7	1800.1	1792.4	1778.4
22.5°	1815.6	1800.1	1747.5	1730.4	1719.6
25°	1766.0	1742.8	1685.5	1665.4	1648.3
27.5°	1710.3	1682.4	1622.0	1595.6	1578.6
30°	1648.3	1618.9	1553.8	1518.2	1504.2
32.5°	1587.9	1552.3	1485.6	1445.4	1426.8
35°	1521.3	1484.1	1414.4	1369.5	1347.8
37.5°	1457.8	1412.8	1341.6	1288.9	1267.2
40°	1389.6	1343.1	1268.8	1209.9	1191.3
42.5°	1318.3	1270.3	1192.9	1137.1	1107.7
45°	1245.5	1200.6	1115.4	1053.4	1030.2
47.5°	1169.6	1123.1	1037.9	974.4	948.1
50°	1098.4	1047.2	958.9	893.9	870.6
52.5°	1020.9	968.2	886.1	814.9	791.6
55°	945.0	895.4	808.7	739.0	714.2
57.5°	867.5	814.9	731.2	663.0	641.4
60°	793.2	739.0	655.3	587.1	563.9
62.5°	714.2	663.0	577.8	515.9	492.6
65°	639.8	587.1	505.0	443.1	419.8
67.5°	565.4	512.8	433.8	374.9	356.3
70°	489.5	436.9	359.4	311.4	292.8
72.5°	415.2	364.1	292.8	249.4	238.6
75°	340.8	294.3	229.3	195.2	184.4
77.5°	264.9	227.7	173.5	147.2	137.9
80°	201.4	164.2	120.8	106.9	103.8
82.5°	139.4	106.9	80.6	75.9	74.4
85°	85.2	57.3	49.6	48.0	46.5
87.5°	35.6	24.8	23.2	23.2	21.7
90°	1.2	10.4	18.4	24.2	27.6
92.5°	34.5	40.3	50.7	58.7	61.0
95°	74.8	77.1	88.6	96.7	99.0
97.5°	115.1	116.3	132.4	139.3	140.5
100°	161.2	161.2	176.1	186.5	188.8
102.5°	210.7	216.4	222.2	233.7	237.2
105°	262.5	268.2	275.1	282.1	285.5
107.5°	318.9	324.6	330.4	333.9	333.9
110°	377.6	383.4	386.8	390.3	389.1

TEST NUMBER: P1028596

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	437.5	439.8	444.4	445.5	443.2
115°	496.2	500.8	503.1	501.9	500.8
117.5°	556.0	557.2	559.5	560.6	556.0
120°	611.3	617.1	618.2	618.2	613.6
122.5°	671.2	672.3	675.8	674.6	671.2
125°	724.1	731.0	732.2	729.9	728.7
127.5°	782.8	786.3	787.4	786.3	784.0
130°	834.6	840.4	842.7	841.6	839.2
132.5°	886.4	896.8	895.7	894.5	891.1
135°	941.7	948.6	949.8	949.8	945.2
137.5°	993.5	1000.4	1002.7	1003.9	998.1
140°	1043.0	1048.8	1052.2	1054.5	1048.8
142.5°	1092.5	1097.1	1101.7	1102.9	1097.1
145°	1140.9	1145.5	1148.9	1148.9	1145.5
147.5°	1185.8	1189.2	1191.5	1195.0	1185.8
150°	1230.7	1229.5	1234.1	1234.1	1231.8
152.5°	1267.5	1269.8	1271.0	1274.4	1269.8
155°	1305.5	1305.5	1306.6	1311.3	1305.5
157.5°	1340.0	1337.7	1338.9	1343.5	1335.4
160°	1370.0	1366.5	1367.7	1372.3	1366.5
162.5°	1396.4	1394.1	1394.1	1399.9	1393.0
165°	1419.5	1417.2	1418.3	1422.9	1416.0
167.5°	1440.2	1435.6	1435.6	1442.5	1435.6
170°	1456.3	1451.7	1451.7	1458.6	1450.6
172.5°	1467.8	1463.2	1463.2	1470.1	1463.2
175°	1475.9	1471.3	1471.3	1478.2	1470.1
177.5°	1481.6	1477.0	1475.9	1482.8	1474.7
180°	1479.3	1479.3	1479.3	1479.3	1479.3

(END OF REPORT)