

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028614

Luminaire Tested: S125RDIP-B1270D1270UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028614
REPORT IS A COMBINATION OF REPORTS P1005191 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB40-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9003.0 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028614

CATALOG NUMBER: S125RDIP-B1270D1270UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028614

CATALOG NUMBER: S125RDIP-B1270D1270UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	54	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13179	13179	13179
5°	13181	12851	12872
10°	13053	12527	12417
15°	12868	12074	11818
20°	12639	11528	11191
25°	12376	10996	10519
30°	12056	10411	9812
35°	11728	9816	9062
40°	11416	9205	8328
45°	11042	8546	7561
50°	10662	7846	6779
55°	10221	7158	5970
60°	9771	6369	5131
65°	9233	5489	4225
70°	8605	4468	3325
75°	7739	3359	2424
80°	6528	2176	1634
85°	4888	1169	921

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11042 cd/sqm

TEST NUMBER: P1028614

CATALOG NUMBER: S125RDIP-B1270D1270UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.6	2.2
10°-20°	541.0	6.0
20°-30°	784.5	8.7
30°-40°	893.8	9.9
40°-50°	871.1	9.7
50°-60°	733.1	8.1
60°-70°	513.8	5.7
70°-80°	263.4	2.9
80°-90°	68.0	0.8
90°-100°	98.7	1.1
100°-110°	293.1	3.3
110°-120°	497.1	5.5
120°-130°	654.4	7.3
130°-140°	733.3	8.1
140°-150°	718.7	8.0
150°-160°	603.7	6.7
160°-170°	401.3	4.5
170°-180°	140.4	1.6
0°-30°	1519.1	16.9
0°-40°	2412.9	26.8
0°-60°	4017.2	44.6
0°-90°	4862.3	54.0
90°-120°	888.8	9.9
90°-150°	2995.2	33.3
90°-180°	4141.0	46.0
0°-180°	9003.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2057	2057	2057	2057	2057	
5°	2054	2048	2031	2046	2043	195
15°	1953	1944	1911	1909	1895	551
25°	1771	1748	1690	1670	1653	815
35°	1526	1488	1418	1373	1352	955
45°	1249	1204	1119	1056	1033	963
55°	948	898	811	741	716	847
65°	642	589	506	444	421	635
75°	342	295	230	196	185	361
85°	86	58	50	48	47	94
90°	1	10	18	24	28	10
95°	75	77	89	97	99	78
105°	263	269	276	283	286	281
115°	498	502	504	503	502	492
125°	726	733	734	732	731	651
135°	944	951	952	952	948	728
145°	1144	1149	1152	1152	1149	715
155°	1309	1309	1310	1315	1309	603
165°	1424	1421	1422	1427	1420	402
175°	1480	1476	1476	1482	1474	141
180°	1484	1484	1484	1484	1484	

TEST NUMBER: P1028614

CATALOG NUMBER: S125RDIP-B1270D1270UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2057.0	2057.0	2057.0	2057.0	2057.0
2.5°	2061.7	2057.0	2041.5	2057.0	2055.5
5°	2053.9	2047.7	2030.6	2046.1	2043.0
7.5°	2038.4	2032.2	2012.0	2024.4	2021.3
10°	2015.1	2010.4	1988.7	1993.3	1988.7
12.5°	1988.7	1982.4	1951.4	1954.5	1946.7
15°	1952.9	1943.6	1911.0	1909.4	1895.4
17.5°	1915.6	1901.7	1862.8	1855.0	1844.2
20°	1870.6	1855.0	1805.3	1797.6	1783.6
22.5°	1820.9	1805.3	1752.5	1735.4	1724.5
25°	1771.1	1747.8	1690.4	1670.2	1653.1
27.5°	1715.2	1687.3	1626.7	1600.2	1583.2
30°	1653.1	1623.6	1558.3	1522.6	1508.6
32.5°	1592.5	1556.7	1489.9	1449.5	1430.9
35°	1525.7	1488.4	1418.5	1373.4	1351.7
37.5°	1462.0	1416.9	1345.5	1292.6	1270.9
40°	1393.6	1347.0	1272.4	1213.4	1194.7
42.5°	1322.1	1274.0	1196.3	1140.4	1110.9
45°	1249.1	1204.1	1118.6	1056.5	1033.2
47.5°	1173.0	1126.4	1040.9	977.2	950.8
50°	1101.5	1050.3	961.7	896.4	873.1
52.5°	1023.8	971.0	888.7	817.2	793.9
55°	947.7	898.0	811.0	741.1	716.2
57.5°	870.0	817.2	733.3	665.0	643.2
60°	795.5	741.1	657.2	588.8	565.5
62.5°	716.2	665.0	579.5	517.4	494.1
65°	641.7	588.8	506.5	444.3	421.0
67.5°	567.1	514.3	435.0	376.0	357.3
70°	490.9	438.1	360.4	312.3	293.6
72.5°	416.4	365.1	293.6	250.1	239.3
75°	341.8	295.2	229.9	195.8	184.9
77.5°	265.7	228.4	174.0	147.6	138.3
80°	202.0	164.7	121.2	107.2	104.1
82.5°	139.8	107.2	80.8	76.1	74.6
85°	85.5	57.5	49.7	48.2	46.6
87.5°	35.7	24.9	23.3	23.3	21.8
90°	1.2	10.4	18.5	24.2	27.7
92.5°	34.6	40.4	50.8	58.9	61.2
95°	75.0	77.4	88.9	97.0	99.3
97.5°	115.5	116.6	132.8	139.7	140.9
100°	161.6	161.6	176.7	187.0	189.4
102.5°	211.3	217.1	222.8	234.4	237.8
105°	263.2	269.0	275.9	282.9	286.3
107.5°	319.8	325.6	331.4	334.8	334.8
110°	378.7	384.5	387.9	391.4	390.2

TEST NUMBER: P1028614

CATALOG NUMBER: S125RDIP-B1270D1270UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	438.7	441.0	445.7	446.8	444.5
115°	497.6	502.2	504.5	503.4	502.2
117.5°	557.7	558.8	561.1	562.3	557.7
120°	613.1	618.9	620.0	620.0	615.4
122.5°	673.1	674.3	677.7	676.6	673.1
125°	726.2	733.2	734.3	732.0	730.8
127.5°	785.1	788.6	789.7	788.6	786.3
130°	837.1	842.8	845.1	844.0	841.7
132.5°	889.0	899.4	898.3	897.1	893.6
135°	944.4	951.4	952.5	952.5	947.9
137.5°	996.4	1003.3	1005.6	1006.8	1001.0
140°	1046.0	1051.8	1055.3	1057.6	1051.8
142.5°	1095.7	1100.3	1104.9	1106.1	1100.3
145°	1144.2	1148.8	1152.3	1152.3	1148.8
147.5°	1189.2	1192.7	1195.0	1198.4	1189.2
150°	1234.2	1233.1	1237.7	1237.7	1235.4
152.5°	1271.2	1273.5	1274.7	1278.1	1273.5
155°	1309.3	1309.3	1310.4	1315.1	1309.3
157.5°	1343.9	1341.6	1342.8	1347.4	1339.3
160°	1373.9	1370.5	1371.6	1376.3	1370.5
162.5°	1400.5	1398.2	1398.2	1404.0	1397.0
165°	1423.6	1421.3	1422.4	1427.1	1420.1
167.5°	1444.4	1439.8	1439.8	1446.7	1439.8
170°	1460.5	1455.9	1455.9	1462.8	1454.8
172.5°	1472.1	1467.5	1467.5	1474.4	1467.5
175°	1480.2	1475.5	1475.5	1482.5	1474.4
177.5°	1485.9	1481.3	1480.2	1487.1	1479.0
180°	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)