

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028629

Luminaire Tested: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028629
REPORT IS A COMBINATION OF REPORTS P1005216 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6207.0 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79		
1	105	101	97	94	100	97	93	90	89	86	84	81	79	78	75	73	72	68		
2	96	89	83	78	92	85	80	75	79	74	70	72	69	66	67	64	61	58		
3	88	79	71	65	84	76	69	64	70	64	60	64	60	56	59	56	53	50		
4	81	70	62	56	77	67	60	54	62	56	52	58	53	49	53	49	46	43		
5	75	63	55	48	71	61	53	47	56	50	45	52	47	43	48	44	40	38		
6	69	57	48	42	66	55	47	42	51	44	40	47	42	38	44	39	36	33		
7	64	51	43	38	61	50	42	37	46	40	35	43	38	34	40	36	32	30		
8	60	47	39	34	57	45	38	33	42	36	31	40	34	30	37	32	29	27		
9	56	43	35	30	53	42	34	30	39	33	28	37	31	27	34	30	26	24		
10	52	40	32	27	50	38	31	27	36	30	26	34	29	25	32	27	24	22		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12195	12195	12195	12195
5°	12184	13744	12184	10564
10°	12116	15445	12075	9132
15°	11985	16340	11902	7951
20°	11825	17639	11720	7187
25°	11618	19966	11488	6523
30°	11408	21222	11236	6048
35°	11135	17452	10979	5605
40°	10650	11852	10561	5207
45°	10015	8520	10001	4815
50°	9363	6552	9408	4453
55°	8629	5327	8612	4103
60°	7945	4367	7907	3644
65°	7150	3638	7195	2933
70°	6491	2920	6465	2442
75°	5484	2213	5484	2007
80°	4443	1349	4392	1349
85°	3127	709	3036	802

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17358 cd/sqm

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	2.9
10°-20°	535.1	8.6
20°-30°	848.4	13.7
30°-40°	1025.2	16.5
40°-50°	912.8	14.7
50°-60°	699.9	11.3
60°-70°	454.6	7.3
70°-80°	220.6	3.6
80°-90°	52.6	0.8
90°-100°	30.4	0.5
100°-110°	90.3	1.5
110°-120°	153.1	2.5
120°-130°	201.5	3.2
130°-140°	225.8	3.6
140°-150°	221.4	3.6
150°-160°	185.9	3.0
160°-170°	123.6	2.0
170°-180°	43.3	0.7
0°-30°	1566.0	25.2
0°-40°	2591.2	41.7
0°-60°	4203.9	67.7
0°-90°	4931.7	79.5
90°-120°	273.8	4.4
90°-150°	922.5	14.9
90°-180°	1275.0	20.5
0°-180°	6207.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1903	1903	1903	1903	1903	
5°	1899	2181	1899	1677	1899	180
15°	1819	2620	1806	1275	1819	513
25°	1663	3138	1644	1025	1663	766
35°	1449	2603	1428	836	1449	902
45°	1133	1164	1131	658	1133	874
55°	800	639	798	492	800	717
65°	497	362	500	292	497	497
75°	242	169	242	153	242	260
85°	55	36	53	41	55	62
90°	0	8	0	8	0	5
95°	23	31	23	31	23	24
105°	81	88	81	88	81	86
115°	153	155	153	155	153	152
125°	224	225	224	225	224	200
135°	291	292	291	292	291	224
145°	352	354	352	354	352	220
155°	403	403	403	403	403	186
165°	438	437	438	437	438	124
175°	456	454	456	454	456	43
180°	457	457	457	457	457	

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1904.8	1920.5	1925.2	1937.7	1951.7	1954.8	1962.7	1973.6	1979.8	1978.3	1978.3
5°	1898.6	1925.2	1943.9	1965.8	1992.3	2003.3	2012.7	2036.1	2054.9	2065.8	2084.5
7.5°	1887.7	1926.7	1958.0	1990.8	2031.4	2050.2	2070.5	2103.3	2137.7	2159.5	2179.9
10°	1870.5	1920.5	1964.2	2012.7	2067.4	2095.5	2120.5	2170.5	2212.7	2240.8	2287.7
12.5°	1845.5	1908.0	1968.9	2033.0	2101.7	2131.4	2165.8	2220.5	2279.9	2320.5	2359.6
15°	1818.9	1893.9	1959.5	2036.1	2118.9	2164.2	2208.0	2265.8	2318.9	2364.3	2409.6
17.5°	1787.6	1867.3	1948.6	2036.1	2129.9	2175.2	2212.7	2281.4	2337.7	2383.0	2423.6
20°	1750.1	1839.2	1931.4	2028.3	2123.6	2165.8	2201.7	2276.7	2326.7	2375.2	2433.0
22.5°	1709.5	1806.4	1904.8	2000.2	2093.9	2139.2	2181.4	2247.1	2301.7	2367.4	2442.4
25°	1662.6	1768.9	1868.9	1964.2	2053.3	2095.5	2133.0	2204.9	2281.4	2364.3	2448.6
27.5°	1615.8	1718.9	1815.8	1903.3	2000.2	2039.2	2076.7	2167.4	2258.0	2345.5	2461.1
30°	1564.2	1668.9	1753.3	1834.5	1928.3	1968.9	2015.8	2118.9	2222.1	2340.8	2481.4
32.5°	1506.4	1601.7	1679.8	1764.2	1848.6	1898.6	1958.0	2070.5	2189.2	2331.4	2511.1
35°	1448.6	1525.1	1597.0	1676.7	1778.3	1831.4	1889.2	2008.0	2156.4	2326.7	2536.1
37.5°	1375.1	1448.6	1504.8	1586.1	1690.8	1753.3	1811.1	1948.6	2117.4	2315.8	2534.6
40°	1300.1	1362.6	1415.7	1500.1	1614.2	1672.0	1734.5	1884.5	2076.7	2284.6	2497.1
42.5°	1218.8	1272.0	1329.8	1411.1	1522.0	1578.3	1650.1	1825.1	2020.5	2240.8	2400.2
45°	1132.9	1184.5	1232.9	1317.3	1428.2	1489.2	1567.3	1747.0	1951.7	2148.6	2243.9
47.5°	1048.5	1093.8	1145.4	1218.8	1331.4	1398.5	1478.2	1670.4	1859.5	2025.2	2033.0
50°	967.3	1003.2	1047.0	1122.0	1239.2	1303.2	1386.0	1565.8	1750.1	1864.2	1787.6
52.5°	882.9	915.7	961.0	1026.6	1136.0	1211.0	1282.9	1462.6	1617.3	1693.9	1553.2
55°	800.1	828.2	875.1	948.5	1043.8	1101.7	1175.1	1342.3	1478.2	1479.8	1326.7
57.5°	718.8	743.8	782.9	848.5	937.6	1004.8	1072.0	1217.3	1309.5	1282.9	1112.6
60°	646.9	662.6	698.5	762.6	845.4	893.8	965.7	1087.6	1148.5	1100.1	917.3
62.5°	571.9	587.5	615.7	667.2	745.4	796.9	842.3	942.3	984.5	911.0	761.0
65°	496.9	515.7	536.0	576.6	650.1	684.4	725.1	798.5	839.1	753.2	623.5
67.5°	431.3	440.7	461.0	503.2	554.7	586.0	614.1	664.1	671.9	603.2	496.9
70°	370.3	373.5	392.2	417.2	456.3	475.0	498.5	528.2	528.2	471.9	387.5
72.5°	301.6	306.3	320.3	346.9	370.3	379.7	387.5	406.3	403.2	351.6	293.8
75°	242.2	245.3	256.3	268.8	278.1	295.3	301.6	298.5	296.9	253.1	220.3
77.5°	187.5	189.1	196.9	207.8	209.4	215.6	211.0	211.0	196.9	171.9	154.7
80°	137.5	139.1	142.2	145.3	145.3	145.3	145.3	137.5	128.1	112.5	107.8
82.5°	92.2	92.2	93.8	96.9	95.3	92.2	89.1	81.3	75.0	70.3	67.2
85°	54.7	54.7	56.3	54.7	48.4	46.9	43.8	42.2	40.6	39.1	39.1
87.5°	26.6	25.0	21.9	18.8	18.8	18.8	18.8	18.8	18.8	17.2	17.2
90°	0.4	1.0	1.6	2.3	2.9	3.2	3.5	4.0	4.6	5.1	5.7
92.5°	10.7	11.1	11.5	11.8	12.2	12.4	12.8	13.5	14.2	14.9	15.6
95°	23.1	23.3	23.4	23.6	23.7	23.8	24.2	25.0	25.8	26.6	27.4
97.5°	35.6	35.7	35.7	35.8	35.9	35.9	36.5	37.6	38.7	39.8	40.9
100°	49.8	49.8	49.8	49.8	49.8	49.8	50.3	51.3	52.4	53.4	54.4
102.5°	65.1	65.5	65.9	66.3	66.7	66.9	67.1	67.5	67.8	68.2	68.6
105°	81.1	81.5	81.9	82.3	82.7	82.9	83.1	83.6	84.1	84.5	85.0
107.5°	98.5	98.9	99.3	99.7	100.1	100.3	100.5	100.9	101.3	101.7	102.1
110°	116.6	117.0	117.4	117.8	118.2	118.4	118.5	118.8	119.0	119.3	119.5

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	135.1	135.3	135.4	135.6	135.7	135.8	136.0	136.3	136.6	137.0	137.3
115°	153.3	153.6	153.9	154.2	154.5	154.7	154.8	154.9	155.1	155.2	155.4
117.5°	171.8	171.9	171.9	172.0	172.1	172.1	172.2	172.3	172.5	172.6	172.8
120°	188.8	189.2	189.6	190.0	190.4	190.6	190.6	190.7	190.8	190.9	191.0
122.5°	207.3	207.4	207.5	207.6	207.7	207.7	207.8	208.0	208.3	208.5	208.7
125°	223.7	224.2	224.6	225.1	225.6	225.8	225.8	225.9	226.0	226.1	226.2
127.5°	241.8	242.0	242.3	242.5	242.8	242.9	242.9	243.0	243.1	243.1	243.2
130°	257.8	258.2	258.6	259.0	259.4	259.6	259.7	259.8	260.0	260.1	260.3
132.5°	273.8	274.5	275.2	275.9	276.6	277.0	277.0	276.9	276.8	276.8	276.7
135°	290.9	291.4	291.8	292.3	292.8	293.0	293.0	293.1	293.2	293.3	293.4
137.5°	306.9	307.4	307.8	308.3	308.8	309.0	309.1	309.2	309.4	309.5	309.7
140°	322.2	322.6	323.0	323.3	323.7	323.9	324.0	324.3	324.5	324.8	325.0
142.5°	337.5	337.8	338.1	338.4	338.7	338.9	339.1	339.4	339.7	340.0	340.3
145°	352.4	352.7	353.0	353.3	353.6	353.8	353.9	354.2	354.4	354.7	354.9
147.5°	366.3	366.5	366.7	367.0	367.2	367.3	367.4	367.5	367.7	367.8	368.0
150°	380.1	380.0	380.0	379.9	379.8	379.8	380.0	380.3	380.6	380.9	381.2
152.5°	391.5	391.7	391.8	392.0	392.1	392.2	392.2	392.3	392.4	392.5	392.6
155°	403.2	403.2	403.2	403.2	403.2	403.2	403.2	403.3	403.4	403.5	403.6
157.5°	413.9	413.7	413.6	413.4	413.3	413.2	413.2	413.3	413.4	413.5	413.6
160°	423.2	423.0	422.7	422.5	422.2	422.1	422.1	422.2	422.3	422.3	422.4
162.5°	431.3	431.1	431.0	430.8	430.7	430.6	430.6	430.6	430.6	430.6	430.6
165°	438.5	438.3	438.1	438.0	437.8	437.7	437.7	437.8	437.9	438.0	438.1
167.5°	444.9	444.6	444.2	443.9	443.6	443.4	443.4	443.4	443.4	443.4	443.4
170°	449.8	449.5	449.2	448.9	448.6	448.4	448.4	448.4	448.4	448.4	448.4
172.5°	453.4	453.1	452.8	452.5	452.2	452.0	452.0	452.0	452.0	452.0	452.0
175°	455.9	455.6	455.3	455.0	454.7	454.5	454.5	454.5	454.5	454.5	454.5
177.5°	457.7	457.4	457.0	456.7	456.4	456.2	456.2	456.1	456.0	456.0	455.9
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1986.1	1997.0	2006.4	2001.7	2020.5	2018.9	2022.0	2028.3	2029.9	2026.7	2020.5
5°	2093.9	2109.5	2136.1	2150.2	2147.0	2159.5	2165.8	2175.2	2184.5	2181.4	2181.4
7.5°	2214.2	2236.1	2262.7	2298.6	2303.3	2314.2	2333.0	2333.0	2343.9	2339.2	2337.7
10°	2318.9	2345.5	2387.7	2415.8	2428.3	2434.6	2453.3	2459.6	2472.1	2473.6	2473.6
12.5°	2404.9	2451.8	2479.9	2508.0	2514.3	2523.6	2537.7	2547.1	2551.8	2551.8	2547.1
15°	2450.2	2487.7	2520.5	2550.2	2567.4	2575.2	2589.3	2600.2	2606.5	2620.5	2623.6
17.5°	2468.9	2514.3	2567.4	2609.6	2639.3	2647.1	2675.2	2684.6	2697.1	2703.3	2711.2
20°	2495.5	2561.1	2625.2	2676.8	2704.9	2725.2	2754.9	2798.7	2811.2	2811.2	2806.5
22.5°	2519.0	2603.3	2690.8	2773.7	2797.1	2837.7	2892.4	2939.3	2958.0	2965.9	2959.6
25°	2547.1	2662.7	2776.8	2879.9	2944.0	2973.7	3047.1	3103.4	3125.3	3137.8	3140.9
27.5°	2595.5	2740.8	2886.2	3017.4	3083.1	3117.4	3194.0	3242.4	3269.0	3280.0	3272.1
30°	2650.2	2828.4	2997.1	3114.3	3158.1	3200.3	3250.3	3269.0	3262.8	3262.8	3286.2
32.5°	2706.5	2890.9	3040.9	3117.4	3133.1	3126.8	3106.5	3050.2	3017.4	3017.4	3037.7
35°	2737.7	2897.1	2973.7	2948.7	2887.7	2851.8	2740.8	2678.3	2608.0	2603.3	2626.8
37.5°	2720.5	2789.3	2758.0	2594.0	2511.1	2442.4	2268.9	2200.2	2148.6	2076.7	2187.7
40°	2600.2	2576.8	2414.3	2178.3	2086.1	1989.2	1851.7	1783.0	1711.1	1700.1	1726.7
42.5°	2397.1	2258.0	2020.5	1792.3	1698.6	1629.8	1525.1	1457.9	1412.6	1393.9	1425.1
45°	2143.9	1925.2	1687.6	1506.4	1403.2	1367.3	1272.0	1212.6	1178.2	1164.2	1186.0
47.5°	1834.5	1614.2	1389.2	1236.0	1175.1	1139.2	1075.1	1023.5	993.8	984.5	993.8
50°	1557.9	1331.4	1142.3	1043.8	989.1	959.5	906.3	873.5	850.1	843.8	859.4
52.5°	1318.9	1112.6	968.8	881.3	845.4	820.4	782.9	754.7	740.7	734.4	745.4
55°	1104.8	937.6	821.9	746.9	720.4	704.7	671.9	656.3	640.7	639.1	650.1
57.5°	915.7	800.1	693.8	640.7	632.9	609.4	581.3	567.2	559.4	557.9	562.5
60°	762.6	659.4	595.4	548.5	537.5	518.8	503.2	493.8	484.4	481.3	484.4
62.5°	634.4	553.2	501.6	470.4	454.7	450.0	432.8	421.9	420.3	420.3	423.5
65°	523.5	454.7	421.9	396.9	386.0	381.3	368.8	361.0	362.5	362.5	364.1
67.5°	426.6	376.6	346.9	334.4	325.0	323.5	311.0	307.8	304.7	304.7	307.8
70°	339.1	307.8	286.0	279.7	278.1	267.2	262.5	261.0	256.3	257.8	257.8
72.5°	265.6	245.3	232.8	223.5	225.0	218.8	212.5	212.5	209.4	214.1	214.1
75°	196.9	187.5	178.1	175.0	178.1	175.0	170.3	168.8	170.3	168.8	168.8
77.5°	145.3	140.6	137.5	135.9	135.9	129.7	126.6	129.7	123.4	126.6	126.6
80°	101.6	95.3	93.8	90.6	92.2	87.5	89.1	85.9	85.9	85.9	85.9
82.5°	64.1	62.5	62.5	62.5	60.9	60.9	60.9	60.9	60.9	60.9	59.4
85°	39.1	37.5	37.5	37.5	35.9	35.9	35.9	35.9	35.9	35.9	35.9
87.5°	15.6	17.2	17.2	18.8	17.2	15.6	15.6	15.6	17.2	17.2	15.6
90°	6.1	6.5	6.9	7.3	7.5	7.6	7.8	8.1	8.3	8.5	8.3
92.5°	16.2	16.7	17.3	17.8	18.1	18.2	18.3	18.5	18.6	18.8	18.6
95°	28.0	28.5	29.1	29.6	29.9	30.0	30.1	30.3	30.4	30.6	30.4
97.5°	41.4	41.8	42.3	42.8	43.0	43.0	43.1	43.2	43.3	43.4	43.3
100°	55.1	55.8	56.5	57.2	57.6	57.7	57.8	58.0	58.1	58.3	58.1
102.5°	69.4	70.2	71.0	71.8	72.2	72.3	72.6	72.8	73.1	73.3	73.1
105°	85.5	85.9	86.4	86.9	87.1	87.2	87.5	87.7	88.0	88.2	88.0
107.5°	102.3	102.5	102.8	103.0	103.1	103.1	103.1	103.1	103.1	103.1	103.1
110°	119.7	119.9	120.2	120.4	120.5	120.5	120.4	120.3	120.3	120.2	120.3

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	137.4	137.4	137.5	137.6	137.6	137.5	137.4	137.2	137.1	136.9	137.1
115°	155.3	155.2	155.1	155.0	155.0	155.0	154.9	154.8	154.8	154.7	154.8
117.5°	172.9	173.0	173.1	173.2	173.2	173.0	172.7	172.4	172.1	171.8	172.1
120°	191.0	191.0	191.0	191.0	191.0	190.8	190.5	190.2	189.8	189.5	189.8
122.5°	208.6	208.6	208.5	208.4	208.4	208.3	208.0	207.8	207.5	207.3	207.5
125°	226.0	225.8	225.7	225.5	225.4	225.4	225.3	225.2	225.2	225.1	225.2
127.5°	243.1	243.1	243.0	242.9	242.9	242.8	242.7	242.5	242.4	242.2	242.4
130°	260.2	260.1	260.0	259.9	259.9	259.8	259.7	259.5	259.4	259.2	259.4
132.5°	276.6	276.5	276.4	276.3	276.3	276.2	275.9	275.7	275.4	275.2	275.4
135°	293.4	293.4	293.4	293.4	293.4	293.2	292.9	292.6	292.2	291.9	292.2
137.5°	309.8	309.9	310.0	310.1	310.1	309.9	309.5	309.1	308.7	308.3	308.7
140°	325.2	325.3	325.5	325.6	325.7	325.5	325.1	324.7	324.3	323.9	324.3
142.5°	340.4	340.5	340.6	340.7	340.7	340.5	340.1	339.7	339.3	338.9	339.3
145°	354.9	354.9	354.9	354.9	354.9	354.8	354.5	354.3	354.0	353.8	354.0
147.5°	368.2	368.5	368.7	369.0	369.1	368.8	368.2	367.5	366.9	366.3	366.9
150°	381.2	381.2	381.2	381.2	381.2	381.1	381.0	380.8	380.7	380.5	380.7
152.5°	392.8	393.0	393.3	393.5	393.6	393.4	393.1	392.8	392.5	392.2	392.5
155°	403.9	404.2	404.5	404.8	405.0	404.8	404.4	404.0	403.6	403.2	403.6
157.5°	413.9	414.2	414.5	414.8	415.0	414.7	414.2	413.6	413.1	412.5	413.1
160°	422.7	423.1	423.4	423.7	423.9	423.7	423.3	422.9	422.5	422.1	422.5
162.5°	431.0	431.4	431.8	432.2	432.4	432.2	431.7	431.2	430.8	430.3	430.8
165°	438.4	438.7	439.0	439.3	439.5	439.3	438.8	438.3	437.9	437.4	437.9
167.5°	443.9	444.4	444.9	445.4	445.6	445.4	444.9	444.4	443.9	443.4	443.9
170°	448.9	449.3	449.8	450.3	450.5	450.2	449.7	449.2	448.6	448.1	448.6
172.5°	452.5	452.9	453.4	453.9	454.1	453.9	453.4	452.9	452.5	452.0	452.5
175°	455.0	455.4	455.9	456.4	456.6	456.3	455.8	455.2	454.7	454.1	454.7
177.5°	456.4	456.8	457.3	457.8	458.0	457.7	457.2	456.6	456.1	455.5	456.1
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	2028.3	2017.3	2022.0	2017.3	2012.7	2008.0	1997.0	1981.4	1968.9	1959.5	1958.0
5°	2184.5	2170.5	2161.1	2156.4	2147.0	2134.5	2114.2	2090.8	2062.7	2051.7	2029.9
7.5°	2328.3	2323.6	2301.7	2298.6	2292.4	2268.9	2234.6	2203.3	2167.4	2137.7	2109.5
10°	2464.3	2453.3	2437.7	2415.8	2412.7	2383.0	2350.2	2306.4	2259.6	2231.4	2181.4
12.5°	2548.6	2536.1	2519.0	2504.9	2497.1	2478.3	2433.0	2389.3	2347.1	2295.5	2251.7
15°	2609.6	2594.0	2562.7	2551.8	2542.4	2517.4	2484.6	2439.3	2383.0	2347.1	2284.6
17.5°	2692.4	2673.7	2642.4	2622.1	2604.9	2565.8	2519.0	2458.0	2404.9	2364.3	2308.0
20°	2787.7	2759.6	2719.0	2692.4	2667.4	2622.1	2556.5	2484.6	2408.0	2358.0	2300.2
22.5°	2945.5	2892.4	2828.4	2790.8	2756.5	2678.3	2600.2	2511.1	2425.2	2350.2	2279.9
25°	3098.7	3045.6	2965.9	2914.3	2861.2	2770.5	2667.4	2544.0	2434.6	2347.1	2254.9
27.5°	3240.9	3186.2	3112.7	3050.2	2998.7	2862.7	2726.8	2587.7	2448.6	2328.3	2234.6
30°	3273.7	3250.3	3194.0	3139.3	3092.4	2967.4	2809.6	2633.0	2465.8	2311.1	2206.4
32.5°	3075.2	3133.1	3147.1	3139.3	3109.6	3020.6	2875.2	2689.3	2490.8	2303.3	2159.5
35°	2662.7	2767.4	2875.2	2933.0	2961.2	2973.7	2887.7	2717.4	2508.0	2290.8	2128.3
37.5°	2208.0	2309.6	2479.9	2565.8	2661.2	2786.2	2820.5	2711.2	2500.2	2281.4	2078.3
40°	1814.2	1943.9	2084.5	2162.7	2245.5	2470.5	2640.8	2628.3	2475.2	2247.1	2039.2
42.5°	1476.7	1557.9	1681.4	1767.3	1868.9	2120.5	2348.6	2461.1	2400.2	2204.9	1989.2
45°	1231.3	1293.9	1381.4	1468.9	1531.4	1759.5	2029.9	2214.2	2272.1	2129.9	1912.7
47.5°	1037.6	1084.5	1161.0	1215.7	1282.9	1462.6	1697.0	1956.4	2078.3	2023.6	1831.4
50°	889.1	926.6	987.6	1022.0	1081.3	1236.0	1414.2	1686.1	1870.5	1876.7	1723.6
52.5°	759.4	796.9	848.5	878.2	914.1	1018.8	1198.5	1428.2	1640.8	1718.9	1600.1
55°	661.0	682.9	725.1	748.5	781.3	882.9	997.0	1192.3	1414.2	1542.3	1467.3
57.5°	570.4	593.8	620.4	639.1	662.6	743.8	846.9	993.8	1214.2	1353.2	1328.2
60°	496.9	511.0	536.0	550.0	571.9	625.1	696.9	843.8	1018.8	1150.1	1164.2
62.5°	428.2	440.7	457.8	470.4	484.4	526.6	579.7	684.4	837.6	979.8	998.5
65°	368.8	379.7	389.1	400.0	411.0	437.5	482.9	564.1	682.9	815.7	856.3
67.5°	315.7	318.8	332.8	334.4	340.7	361.0	393.8	459.4	545.4	651.6	704.7
70°	264.1	270.3	273.5	278.1	284.4	298.5	325.0	359.4	423.5	509.4	559.4
72.5°	214.1	215.6	220.3	223.5	229.7	240.6	253.1	279.7	320.3	382.8	428.2
75°	170.3	171.9	175.0	176.6	181.3	184.4	190.6	209.4	237.5	275.0	307.8
77.5°	128.1	131.3	134.4	134.4	135.9	139.1	142.2	148.4	162.5	187.5	215.6
80°	87.5	89.1	89.1	90.6	89.1	93.8	98.4	106.3	112.5	120.3	134.4
82.5°	60.9	60.9	60.9	62.5	62.5	64.1	64.1	65.6	67.2	71.9	78.1
85°	37.5	37.5	39.1	35.9	37.5	39.1	39.1	37.5	39.1	40.6	42.2
87.5°	15.6	15.6	17.2	17.2	17.2	17.2	15.6	17.2	15.6	17.2	17.2
90°	8.1	7.8	7.6	7.5	7.3	6.9	6.5	6.1	5.7	5.1	4.6
92.5°	18.5	18.3	18.2	18.1	17.8	17.3	16.7	16.2	15.6	14.9	14.2
95°	30.3	30.1	30.0	29.9	29.6	29.1	28.5	28.0	27.4	26.6	25.8
97.5°	43.2	43.1	43.0	43.0	42.8	42.3	41.8	41.4	40.9	39.8	38.7
100°	58.0	57.8	57.7	57.6	57.2	56.5	55.8	55.1	54.4	53.4	52.4
102.5°	72.8	72.6	72.3	72.2	71.8	71.0	70.2	69.4	68.6	68.2	67.8
105°	87.7	87.5	87.2	87.1	86.9	86.4	85.9	85.5	85.0	84.5	84.1
107.5°	103.1	103.1	103.1	103.1	103.0	102.8	102.5	102.3	102.1	101.7	101.3
110°	120.3	120.4	120.5	120.5	120.4	120.2	119.9	119.7	119.5	119.3	119.0

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	137.2	137.4	137.5	137.6	137.6	137.5	137.4	137.4	137.3	137.0	136.6
115°	154.8	154.9	155.0	155.0	155.0	155.1	155.2	155.3	155.4	155.2	155.1
117.5°	172.4	172.7	173.0	173.2	173.2	173.1	173.0	172.9	172.8	172.6	172.5
120°	190.2	190.5	190.8	191.0	191.0	191.0	191.0	191.0	191.0	190.9	190.8
122.5°	207.8	208.0	208.3	208.4	208.4	208.5	208.6	208.6	208.7	208.5	208.3
125°	225.2	225.3	225.4	225.4	225.5	225.7	225.8	226.0	226.2	226.1	226.0
127.5°	242.5	242.7	242.8	242.9	242.9	243.0	243.1	243.1	243.2	243.1	243.1
130°	259.5	259.7	259.8	259.9	259.9	260.0	260.1	260.2	260.3	260.1	260.0
132.5°	275.7	275.9	276.2	276.3	276.3	276.4	276.5	276.6	276.7	276.8	276.8
135°	292.6	292.9	293.2	293.4	293.4	293.4	293.4	293.4	293.4	293.3	293.2
137.5°	309.1	309.5	309.9	310.1	310.1	310.0	309.9	309.8	309.7	309.5	309.4
140°	324.7	325.1	325.5	325.7	325.6	325.5	325.3	325.2	325.0	324.8	324.5
142.5°	339.7	340.1	340.5	340.7	340.7	340.6	340.5	340.4	340.3	340.0	339.7
145°	354.3	354.5	354.8	354.9	354.9	354.9	354.9	354.9	354.9	354.7	354.4
147.5°	367.5	368.2	368.8	369.1	369.0	368.7	368.5	368.2	368.0	367.8	367.7
150°	380.8	381.0	381.1	381.2	381.2	381.2	381.2	381.2	381.2	380.9	380.6
152.5°	392.8	393.1	393.4	393.6	393.5	393.3	393.0	392.8	392.6	392.5	392.4
155°	404.0	404.4	404.8	405.0	404.8	404.5	404.2	403.9	403.6	403.5	403.4
157.5°	413.6	414.2	414.7	415.0	414.8	414.5	414.2	413.9	413.6	413.5	413.4
160°	422.9	423.3	423.7	423.9	423.7	423.4	423.1	422.7	422.4	422.3	422.3
162.5°	431.2	431.7	432.2	432.4	432.2	431.8	431.4	431.0	430.6	430.6	430.6
165°	438.3	438.8	439.3	439.5	439.3	439.0	438.7	438.4	438.1	438.0	437.9
167.5°	444.4	444.9	445.4	445.6	445.4	444.9	444.4	443.9	443.4	443.4	443.4
170°	449.2	449.7	450.2	450.5	450.3	449.8	449.3	448.9	448.4	448.4	448.4
172.5°	452.9	453.4	453.9	454.1	453.9	453.4	452.9	452.5	452.0	452.0	452.0
175°	455.2	455.8	456.3	456.6	456.4	455.9	455.4	455.0	454.5	454.5	454.5
177.5°	456.6	457.2	457.7	458.0	457.8	457.3	456.8	456.4	455.9	456.0	456.0
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1953.3	1943.9	1937.7	1936.1	1926.7	1918.9	1909.5	1908.0	1903.3	1890.8	1883.0
5°	2014.2	1992.3	1987.7	1973.6	1950.2	1933.0	1911.1	1898.6	1884.5	1861.1	1842.3
7.5°	2076.7	2047.0	2025.2	2004.8	1972.0	1940.8	1909.5	1884.5	1859.5	1825.1	1797.0
10°	2137.7	2092.4	2065.8	2036.1	1990.8	1943.9	1900.2	1864.2	1823.6	1783.0	1742.3
12.5°	2193.9	2136.1	2097.0	2054.9	1998.6	1940.8	1884.5	1834.5	1792.3	1737.6	1692.3
15°	2228.3	2164.2	2125.2	2084.5	2000.2	1936.1	1870.5	1806.4	1750.1	1692.3	1650.1
17.5°	2248.6	2176.7	2133.0	2095.5	2009.5	1922.0	1837.6	1768.9	1707.9	1639.2	1582.9
20°	2239.2	2168.9	2128.3	2092.4	1992.3	1904.8	1814.2	1734.5	1657.9	1587.6	1528.2
22.5°	2218.9	2145.5	2100.2	2067.4	1978.3	1875.2	1775.1	1689.2	1609.5	1539.2	1472.0
25°	2175.2	2103.3	2064.2	2023.6	1936.1	1837.6	1736.1	1643.9	1559.5	1484.5	1409.5
27.5°	2136.1	2048.6	2008.0	1972.0	1879.8	1792.3	1692.3	1590.8	1504.8	1426.7	1351.7
30°	2090.8	1992.3	1948.6	1900.2	1817.3	1734.5	1634.5	1540.7	1451.7	1368.9	1297.0
32.5°	2042.4	1928.3	1878.3	1823.6	1739.2	1661.1	1576.7	1484.5	1395.4	1314.2	1239.2
35°	1979.8	1858.0	1800.1	1748.6	1661.1	1582.9	1504.8	1428.2	1339.2	1253.2	1181.3
37.5°	1920.5	1786.1	1725.1	1665.8	1573.6	1498.6	1434.5	1362.6	1276.7	1193.8	1125.1
40°	1853.3	1698.6	1636.1	1581.4	1486.1	1403.2	1345.4	1289.2	1214.2	1134.5	1059.5
42.5°	1792.3	1617.3	1551.7	1495.4	1395.4	1317.3	1262.6	1215.7	1150.1	1076.6	1000.1
45°	1707.9	1529.8	1462.6	1403.2	1301.7	1228.2	1172.0	1131.3	1079.8	1011.0	942.3
47.5°	1629.8	1445.4	1372.0	1300.1	1207.9	1132.9	1081.3	1050.1	1015.7	954.8	884.4
50°	1534.5	1348.5	1273.5	1214.2	1109.5	1045.4	993.8	972.0	940.7	882.9	826.6
52.5°	1431.4	1254.8	1184.5	1112.6	1015.7	953.2	907.9	882.9	857.9	815.7	762.6
55°	1311.0	1150.1	1084.5	1020.4	923.5	865.7	825.1	798.5	784.4	745.4	706.3
57.5°	1195.4	1043.8	982.9	923.5	839.1	773.5	746.9	723.5	703.2	675.1	642.2
60°	1078.2	940.7	875.1	821.9	748.5	689.1	667.2	643.8	628.2	606.3	582.9
62.5°	943.8	826.6	776.6	726.6	664.1	617.2	592.2	573.5	553.2	539.1	518.8
65°	801.6	718.8	670.4	632.9	573.5	531.3	512.5	500.0	482.9	468.8	453.2
67.5°	668.8	603.2	582.9	542.2	496.9	459.4	445.3	429.7	415.7	407.8	393.8
70°	540.7	493.8	473.5	462.5	412.5	387.5	375.0	368.8	351.6	343.8	334.4
72.5°	418.8	401.6	387.5	373.5	340.7	325.0	311.0	304.7	292.2	286.0	282.8
75°	309.4	298.5	290.6	289.1	275.0	259.4	245.3	242.2	232.8	226.6	223.5
77.5°	217.2	214.1	212.5	214.1	204.7	195.3	192.2	189.1	178.1	176.6	176.6
80°	142.2	150.0	150.0	148.4	145.3	143.8	139.1	135.9	129.7	128.1	129.7
82.5°	87.5	92.2	93.8	96.9	95.3	93.8	90.6	89.1	90.6	87.5	89.1
85°	43.8	46.9	53.1	53.1	54.7	54.7	54.7	53.1	50.0	51.6	50.0
87.5°	17.2	18.8	18.8	18.8	17.2	21.9	23.4	23.4	23.4	20.3	20.3
90°	4.0	3.5	3.2	2.9	2.3	1.6	1.0	0.4	1.0	1.6	2.3
92.5°	13.5	12.8	12.4	12.2	11.8	11.5	11.1	10.7	11.1	11.5	11.8
95°	25.0	24.2	23.8	23.7	23.6	23.4	23.3	23.1	23.3	23.4	23.6
97.5°	37.6	36.5	35.9	35.9	35.8	35.7	35.7	35.6	35.7	35.7	35.8
100°	51.3	50.3	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8	49.8
102.5°	67.5	67.1	66.9	66.7	66.3	65.9	65.5	65.1	65.5	65.9	66.3
105°	83.6	83.1	82.9	82.7	82.3	81.9	81.5	81.1	81.5	81.9	82.3
107.5°	100.9	100.5	100.3	100.1	99.7	99.3	98.9	98.5	98.9	99.3	99.7
110°	118.8	118.5	118.4	118.2	117.8	117.4	117.0	116.6	117.0	117.4	117.8

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	136.3	136.0	135.8	135.7	135.6	135.4	135.3	135.1	135.3	135.4	135.6
115°	154.9	154.8	154.7	154.5	154.2	153.9	153.6	153.3	153.6	153.9	154.2
117.5°	172.3	172.2	172.1	172.1	172.0	171.9	171.9	171.8	171.9	171.9	172.0
120°	190.7	190.6	190.6	190.4	190.0	189.6	189.2	188.8	189.2	189.6	190.0
122.5°	208.0	207.8	207.7	207.7	207.6	207.5	207.4	207.3	207.4	207.5	207.6
125°	225.9	225.8	225.8	225.6	225.1	224.6	224.2	223.7	224.2	224.6	225.1
127.5°	243.0	242.9	242.9	242.8	242.5	242.3	242.0	241.8	242.0	242.3	242.5
130°	259.8	259.7	259.6	259.4	259.0	258.6	258.2	257.8	258.2	258.6	259.0
132.5°	276.9	277.0	277.0	276.6	275.9	275.2	274.5	273.8	274.5	275.2	275.9
135°	293.1	293.0	293.0	292.8	292.3	291.8	291.4	290.9	291.4	291.8	292.3
137.5°	309.2	309.1	309.0	308.8	308.3	307.8	307.4	306.9	307.4	307.8	308.3
140°	324.3	324.0	323.9	323.7	323.3	323.0	322.6	322.2	322.6	323.0	323.3
142.5°	339.4	339.1	338.9	338.7	338.4	338.1	337.8	337.5	337.8	338.1	338.4
145°	354.2	353.9	353.8	353.6	353.3	353.0	352.7	352.4	352.7	353.0	353.3
147.5°	367.5	367.4	367.3	367.2	367.0	366.7	366.5	366.3	366.5	366.7	367.0
150°	380.3	380.0	379.8	379.8	379.9	380.0	380.0	380.1	380.0	380.0	379.9
152.5°	392.3	392.2	392.2	392.1	392.0	391.8	391.7	391.5	391.7	391.8	392.0
155°	403.3	403.2	403.2	403.2	403.2	403.2	403.2	403.2	403.2	403.2	403.2
157.5°	413.3	413.2	413.2	413.3	413.4	413.6	413.7	413.9	413.7	413.6	413.4
160°	422.2	422.1	422.1	422.2	422.5	422.7	423.0	423.2	423.0	422.7	422.5
162.5°	430.6	430.6	430.6	430.7	430.8	431.0	431.1	431.3	431.1	431.0	430.8
165°	437.8	437.7	437.7	437.8	438.0	438.1	438.3	438.5	438.3	438.1	438.0
167.5°	443.4	443.4	443.4	443.6	443.9	444.2	444.6	444.9	444.6	444.2	443.9
170°	448.4	448.4	448.4	448.6	448.9	449.2	449.5	449.8	449.5	449.2	448.9
172.5°	452.0	452.0	452.0	452.2	452.5	452.8	453.1	453.4	453.1	452.8	452.5
175°	454.5	454.5	454.5	454.7	455.0	455.3	455.6	455.9	455.6	455.3	455.0
177.5°	456.1	456.2	456.2	456.4	456.7	457.0	457.4	457.7	457.4	457.0	456.7
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1878.3	1872.0	1867.3	1862.6	1842.3	1820.5	1817.3	1812.6	1803.3	1814.2	1809.5
5°	1829.8	1815.8	1808.0	1787.6	1762.6	1743.9	1728.3	1709.5	1701.7	1695.4	1693.9
7.5°	1770.5	1758.0	1743.9	1723.6	1692.3	1661.1	1637.6	1618.9	1603.3	1595.4	1595.4
10°	1712.6	1697.0	1678.3	1643.9	1614.2	1575.1	1550.1	1531.4	1509.5	1497.0	1486.1
12.5°	1653.3	1636.1	1618.9	1575.1	1540.7	1500.1	1464.2	1440.7	1429.8	1415.7	1397.0
15°	1593.9	1567.3	1550.1	1506.4	1462.6	1422.0	1398.5	1373.5	1348.5	1334.5	1328.2
17.5°	1531.4	1512.6	1484.5	1437.6	1389.2	1353.2	1318.9	1295.4	1265.7	1251.7	1237.6
20°	1475.1	1447.0	1418.9	1372.0	1325.1	1276.7	1242.3	1214.2	1195.4	1184.5	1172.0
22.5°	1407.9	1381.4	1357.9	1307.9	1256.4	1211.0	1173.5	1156.3	1137.6	1120.4	1107.9
25°	1350.1	1323.5	1300.1	1245.4	1189.2	1147.0	1118.8	1097.0	1076.6	1068.8	1056.3
27.5°	1289.2	1264.2	1232.9	1178.2	1128.2	1092.3	1062.6	1042.3	1026.6	1011.0	1001.6
30°	1231.3	1203.2	1175.1	1115.7	1075.1	1039.1	1011.0	986.0	973.5	965.7	950.1
32.5°	1175.1	1139.2	1115.7	1061.0	1022.0	987.6	964.1	942.3	926.6	912.6	900.1
35°	1114.2	1075.1	1051.6	1006.3	965.7	931.3	911.0	895.4	876.6	864.1	857.9
37.5°	1056.3	1023.5	1000.1	953.2	912.6	884.4	862.6	842.3	834.4	817.3	814.1
40°	993.8	965.7	943.8	898.5	861.0	839.1	815.7	796.9	782.9	775.1	764.1
42.5°	937.6	914.1	890.7	848.5	812.6	786.0	768.8	751.6	739.1	726.6	718.8
45°	886.0	861.0	839.1	798.5	762.6	739.1	721.9	701.6	698.5	681.3	673.5
47.5°	831.3	809.4	790.7	748.5	715.7	692.2	671.9	657.9	643.8	637.6	626.6
50°	778.2	756.3	734.4	696.9	667.2	643.8	623.5	607.9	600.0	590.7	581.3
52.5°	720.4	703.2	686.0	646.9	617.2	596.9	579.7	559.4	551.6	543.8	537.5
55°	671.9	646.9	628.2	595.4	568.8	546.9	528.2	512.5	504.7	498.5	490.7
57.5°	606.3	590.7	575.0	545.4	520.4	498.5	479.7	467.2	457.8	453.2	454.7
60°	550.0	532.9	523.5	492.2	467.2	450.0	432.8	420.3	411.0	406.3	404.7
62.5°	490.7	478.2	461.0	439.1	414.1	398.5	386.0	376.6	361.0	359.4	354.7
65°	432.8	423.5	407.8	387.5	367.2	353.2	339.1	326.6	320.3	312.5	307.8
67.5°	376.6	367.2	353.2	336.0	321.9	307.8	295.3	282.8	271.9	265.6	262.5
70°	321.9	314.1	304.7	284.4	267.2	256.3	246.9	239.1	228.1	225.0	223.5
72.5°	268.8	261.0	256.3	239.1	223.5	214.1	204.7	196.9	192.2	190.6	186.0
75°	220.3	212.5	206.3	190.6	181.3	175.0	165.6	162.5	157.8	156.3	154.7
77.5°	171.9	164.1	162.5	151.6	140.6	137.5	134.4	128.1	128.1	128.1	125.0
80°	123.4	121.9	120.3	109.4	104.7	101.6	100.0	95.3	92.2	89.1	87.5
82.5°	82.8	81.3	79.7	75.0	70.3	68.8	67.2	64.1	64.1	65.6	62.5
85°	50.0	46.9	45.3	43.8	40.6	40.6	42.2	40.6	40.6	40.6	39.1
87.5°	18.8	18.8	18.8	18.8	20.3	17.2	18.8	18.8	17.2	17.2	15.6
90°	2.9	3.2	3.5	4.0	4.6	5.1	5.7	6.1	6.5	6.9	7.3
92.5°	12.2	12.4	12.8	13.5	14.2	14.9	15.6	16.2	16.7	17.3	17.8
95°	23.7	23.8	24.2	25.0	25.8	26.6	27.4	28.0	28.5	29.1	29.6
97.5°	35.9	35.9	36.5	37.6	38.7	39.8	40.9	41.4	41.8	42.3	42.8
100°	49.8	49.8	50.3	51.3	52.4	53.4	54.4	55.1	55.8	56.5	57.2
102.5°	66.7	66.9	67.1	67.5	67.8	68.2	68.6	69.4	70.2	71.0	71.8
105°	82.7	82.9	83.1	83.6	84.1	84.5	85.0	85.5	85.9	86.4	86.9
107.5°	100.1	100.3	100.5	100.9	101.3	101.7	102.1	102.3	102.5	102.8	103.0
110°	118.2	118.4	118.5	118.8	119.0	119.3	119.5	119.7	119.9	120.2	120.4

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	135.7	135.8	136.0	136.3	136.6	137.0	137.3	137.4	137.4	137.5	137.6
115°	154.5	154.7	154.8	154.9	155.1	155.2	155.4	155.3	155.2	155.1	155.0
117.5°	172.1	172.1	172.2	172.3	172.5	172.6	172.8	172.9	173.0	173.1	173.2
120°	190.4	190.6	190.6	190.7	190.8	190.9	191.0	191.0	191.0	191.0	191.0
122.5°	207.7	207.7	207.8	208.0	208.3	208.5	208.7	208.6	208.6	208.5	208.4
125°	225.6	225.8	225.8	225.9	226.0	226.1	226.2	226.0	225.8	225.7	225.5
127.5°	242.8	242.9	242.9	243.0	243.1	243.1	243.2	243.1	243.1	243.0	242.9
130°	259.4	259.6	259.7	259.8	260.0	260.1	260.3	260.2	260.1	260.0	259.9
132.5°	276.6	277.0	277.0	276.9	276.8	276.8	276.7	276.6	276.5	276.4	276.3
135°	292.8	293.0	293.0	293.1	293.2	293.3	293.4	293.4	293.4	293.4	293.4
137.5°	308.8	309.0	309.1	309.2	309.4	309.5	309.7	309.8	309.9	310.0	310.1
140°	323.7	323.9	324.0	324.3	324.5	324.8	325.0	325.2	325.3	325.5	325.6
142.5°	338.7	338.9	339.1	339.4	339.7	340.0	340.3	340.4	340.5	340.6	340.7
145°	353.6	353.8	353.9	354.2	354.4	354.7	354.9	354.9	354.9	354.9	354.9
147.5°	367.2	367.3	367.4	367.5	367.7	367.8	368.0	368.2	368.5	368.7	369.0
150°	379.8	379.8	380.0	380.3	380.6	380.9	381.2	381.2	381.2	381.2	381.2
152.5°	392.1	392.2	392.2	392.3	392.4	392.5	392.6	392.8	393.0	393.3	393.5
155°	403.2	403.2	403.2	403.3	403.4	403.5	403.6	403.9	404.2	404.5	404.8
157.5°	413.3	413.2	413.2	413.3	413.4	413.5	413.6	413.9	414.2	414.5	414.8
160°	422.2	422.1	422.1	422.2	422.3	422.3	422.4	422.7	423.1	423.4	423.7
162.5°	430.7	430.6	430.6	430.6	430.6	430.6	430.6	431.0	431.4	431.8	432.2
165°	437.8	437.7	437.7	437.8	437.9	438.0	438.1	438.4	438.7	439.0	439.3
167.5°	443.6	443.4	443.4	443.4	443.4	443.4	443.4	443.9	444.4	444.9	445.4
170°	448.6	448.4	448.4	448.4	448.4	448.4	448.4	448.9	449.3	449.8	450.3
172.5°	452.2	452.0	452.0	452.0	452.0	452.0	452.0	452.5	452.9	453.4	453.9
175°	454.7	454.5	454.5	454.5	454.5	454.5	454.5	455.0	455.4	455.9	456.4
177.5°	456.4	456.2	456.2	456.1	456.0	456.0	455.9	456.4	456.8	457.3	457.8
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1801.7	1804.8	1797.0	1793.9	1787.6	1795.5	1797.0	1795.5	1809.5	1803.3	1806.4
5°	1697.0	1690.8	1686.1	1675.1	1675.1	1676.7	1681.4	1673.6	1678.3	1689.2	1687.6
7.5°	1581.4	1578.3	1579.8	1567.3	1557.9	1561.1	1557.9	1572.0	1579.8	1576.7	1582.9
10°	1476.7	1482.9	1468.9	1462.6	1456.4	1462.6	1461.1	1464.2	1473.6	1479.8	1490.7
12.5°	1392.3	1390.7	1382.9	1376.7	1365.7	1368.9	1378.2	1375.1	1376.7	1390.7	1389.2
15°	1312.6	1303.2	1297.0	1282.9	1286.0	1275.1	1284.5	1295.4	1300.1	1312.6	1320.4
17.5°	1232.9	1231.3	1223.5	1222.0	1204.8	1200.1	1209.5	1212.6	1217.3	1223.5	1234.5
20°	1165.7	1164.2	1153.2	1150.1	1136.0	1145.4	1142.3	1148.5	1151.7	1164.2	1168.8
22.5°	1104.8	1097.0	1093.8	1089.1	1084.5	1082.9	1089.1	1087.6	1098.5	1103.2	1104.8
25°	1048.5	1042.3	1040.7	1032.9	1029.8	1025.1	1029.8	1034.5	1047.0	1051.6	1057.9
27.5°	997.0	992.3	989.1	982.9	978.2	978.2	981.3	987.6	992.3	995.4	998.5
30°	950.1	947.0	937.6	934.4	929.8	929.8	929.8	932.9	940.7	950.1	954.8
32.5°	901.6	895.4	889.1	889.1	884.4	884.4	886.0	889.1	896.9	898.5	906.3
35°	854.8	848.5	843.8	840.7	842.3	836.0	839.1	843.8	853.2	856.3	861.0
37.5°	809.4	807.9	798.5	793.8	796.9	796.9	795.4	798.5	804.8	811.0	814.1
40°	759.4	756.3	756.3	751.6	753.2	746.9	751.6	754.7	757.9	764.1	768.8
42.5°	715.7	712.6	706.3	707.9	703.2	703.2	706.3	707.9	712.6	720.4	723.5
45°	668.8	668.8	665.7	661.0	662.6	657.9	661.0	662.6	668.8	676.6	673.5
47.5°	623.5	621.9	621.9	615.7	618.8	614.1	618.8	620.4	623.5	628.2	626.6
50°	579.7	575.0	576.6	575.0	573.5	573.5	576.6	576.6	579.7	579.7	584.4
52.5°	534.4	534.4	531.3	532.9	536.0	532.9	537.5	532.9	536.0	537.5	540.7
55°	493.8	490.7	492.2	490.7	496.9	492.2	496.9	493.8	496.9	495.4	498.5
57.5°	450.0	445.3	446.9	445.3	450.0	448.5	453.2	448.5	450.0	451.6	456.3
60°	400.0	400.0	400.0	396.9	401.6	401.6	400.0	400.0	406.3	409.4	407.8
62.5°	353.2	351.6	346.9	345.3	346.9	343.8	350.0	348.5	351.6	354.7	357.8
65°	301.6	298.5	296.9	293.8	293.8	292.2	293.8	300.0	301.6	303.1	311.0
67.5°	259.4	257.8	256.3	251.6	251.6	254.7	254.7	254.7	264.1	259.4	265.6
70°	221.9	218.8	215.6	214.1	214.1	215.6	217.2	218.8	217.2	223.5	225.0
72.5°	186.0	187.5	184.4	184.4	184.4	182.8	182.8	186.0	187.5	186.0	187.5
75°	154.7	154.7	153.1	154.7	154.7	153.1	153.1	156.3	156.3	154.7	159.4
77.5°	125.0	123.4	120.3	117.2	118.8	117.2	118.8	117.2	121.9	126.6	123.4
80°	87.5	85.9	85.9	85.9	87.5	85.9	89.1	85.9	87.5	87.5	89.1
82.5°	62.5	64.1	64.1	62.5	64.1	62.5	64.1	64.1	64.1	62.5	64.1
85°	40.6	40.6	40.6	40.6	39.1	40.6	40.6	40.6	42.2	40.6	42.2
87.5°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	18.8	17.2	18.8
90°	7.5	7.6	7.8	8.1	8.3	8.5	8.3	8.1	7.8	7.6	7.5
92.5°	18.1	18.2	18.3	18.5	18.6	18.8	18.6	18.5	18.3	18.2	18.1
95°	29.9	30.0	30.1	30.3	30.4	30.6	30.4	30.3	30.1	30.0	29.9
97.5°	43.0	43.0	43.1	43.2	43.3	43.4	43.3	43.2	43.1	43.0	43.0
100°	57.6	57.7	57.8	58.0	58.1	58.3	58.1	58.0	57.8	57.7	57.6
102.5°	72.2	72.3	72.6	72.8	73.1	73.3	73.1	72.8	72.6	72.3	72.2
105°	87.1	87.2	87.5	87.7	88.0	88.2	88.0	87.7	87.5	87.2	87.1
107.5°	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1	103.1
110°	120.5	120.5	120.4	120.3	120.3	120.2	120.3	120.3	120.4	120.5	120.5

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	137.6	137.5	137.4	137.2	137.1	136.9	137.1	137.2	137.4	137.5	137.6
115°	155.0	155.0	154.9	154.8	154.8	154.7	154.8	154.8	154.9	155.0	155.0
117.5°	173.2	173.0	172.7	172.4	172.1	171.8	172.1	172.4	172.7	173.0	173.2
120°	191.0	190.8	190.5	190.2	189.8	189.5	189.8	190.2	190.5	190.8	191.0
122.5°	208.4	208.3	208.0	207.8	207.5	207.3	207.5	207.8	208.0	208.3	208.4
125°	225.4	225.4	225.3	225.2	225.2	225.1	225.2	225.2	225.3	225.4	225.4
127.5°	242.9	242.8	242.7	242.5	242.4	242.2	242.4	242.5	242.7	242.8	242.9
130°	259.9	259.8	259.7	259.5	259.4	259.2	259.4	259.5	259.7	259.8	259.9
132.5°	276.3	276.2	275.9	275.7	275.4	275.2	275.4	275.7	275.9	276.2	276.3
135°	293.4	293.2	292.9	292.6	292.2	291.9	292.2	292.6	292.9	293.2	293.4
137.5°	310.1	309.9	309.5	309.1	308.7	308.3	308.7	309.1	309.5	309.9	310.1
140°	325.7	325.5	325.1	324.7	324.3	323.9	324.3	324.7	325.1	325.5	325.7
142.5°	340.7	340.5	340.1	339.7	339.3	338.9	339.3	339.7	340.1	340.5	340.7
145°	354.9	354.8	354.5	354.3	354.0	353.8	354.0	354.3	354.5	354.8	354.9
147.5°	369.1	368.8	368.2	367.5	366.9	366.3	366.9	367.5	368.2	368.8	369.1
150°	381.2	381.1	381.0	380.8	380.7	380.5	380.7	380.8	381.0	381.1	381.2
152.5°	393.6	393.4	393.1	392.8	392.5	392.2	392.5	392.8	393.1	393.4	393.6
155°	405.0	404.8	404.4	404.0	403.6	403.2	403.6	404.0	404.4	404.8	405.0
157.5°	415.0	414.7	414.2	413.6	413.1	412.5	413.1	413.6	414.2	414.7	415.0
160°	423.9	423.7	423.3	422.9	422.5	422.1	422.5	422.9	423.3	423.7	423.9
162.5°	432.4	432.2	431.7	431.2	430.8	430.3	430.8	431.2	431.7	432.2	432.4
165°	439.5	439.3	438.8	438.3	437.9	437.4	437.9	438.3	438.8	439.3	439.5
167.5°	445.6	445.4	444.9	444.4	443.9	443.4	443.9	444.4	444.9	445.4	445.6
170°	450.5	450.2	449.7	449.2	448.6	448.1	448.6	449.2	449.7	450.2	450.5
172.5°	454.1	453.9	453.4	452.9	452.5	452.0	452.5	452.9	453.4	453.9	454.1
175°	456.6	456.3	455.8	455.2	454.7	454.1	454.7	455.2	455.8	456.3	456.6
177.5°	458.0	457.7	457.2	456.6	456.1	455.5	456.1	456.6	457.2	457.7	458.0
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3	1903.3
2.5°	1800.1	1808.0	1801.7	1797.0	1809.5	1815.8	1815.8	1826.7	1837.6	1847.0	1848.6
5°	1689.2	1701.7	1704.8	1703.3	1722.0	1731.4	1751.7	1762.6	1778.3	1789.2	1801.7
7.5°	1587.6	1604.8	1606.4	1609.5	1637.6	1653.3	1670.4	1698.6	1720.5	1736.1	1750.1
10°	1486.1	1497.0	1507.9	1522.0	1550.1	1576.7	1601.7	1631.4	1659.5	1675.1	1695.4
12.5°	1409.5	1417.3	1429.8	1439.2	1468.9	1492.3	1525.1	1565.8	1606.4	1618.9	1643.9
15°	1329.8	1334.5	1359.5	1368.9	1393.9	1432.9	1453.2	1492.3	1536.1	1559.5	1587.6
17.5°	1237.6	1265.7	1281.4	1292.3	1323.5	1354.8	1387.6	1428.2	1484.5	1506.4	1526.7
20°	1172.0	1192.3	1209.5	1223.5	1251.7	1298.5	1328.2	1361.0	1414.2	1439.2	1468.9
22.5°	1114.2	1131.3	1147.0	1162.6	1181.3	1223.5	1257.9	1303.2	1356.4	1379.8	1414.2
25°	1059.5	1076.6	1086.0	1104.8	1129.8	1159.5	1200.1	1240.7	1293.9	1320.4	1353.2
27.5°	1006.3	1023.5	1040.7	1056.3	1073.5	1101.7	1129.8	1181.3	1236.0	1267.3	1295.4
30°	961.0	968.8	984.5	1001.6	1018.8	1045.4	1078.2	1114.2	1176.7	1204.8	1239.2
32.5°	911.0	925.1	936.0	948.5	970.4	992.3	1022.0	1067.3	1117.3	1143.8	1181.3
35°	864.1	876.6	884.4	906.3	920.4	943.8	973.5	1014.1	1056.3	1086.0	1118.8
37.5°	818.8	831.3	840.7	853.2	871.9	892.3	923.5	953.2	1003.2	1028.2	1065.7
40°	771.9	782.9	793.8	807.9	825.1	850.1	868.8	906.3	947.0	975.1	1003.2
42.5°	726.6	732.9	745.4	761.0	778.2	800.1	826.6	856.3	896.9	921.9	947.0
45°	678.2	689.1	703.2	714.1	729.7	751.6	775.1	801.6	842.3	867.3	893.8
47.5°	632.9	640.7	650.1	667.2	687.6	703.2	728.2	753.2	790.7	814.1	839.1
50°	586.0	593.8	607.9	618.8	634.4	654.7	678.2	704.7	740.7	756.3	781.3
52.5°	542.2	545.4	559.4	570.4	586.0	609.4	628.2	651.6	686.0	703.2	728.2
55°	498.5	501.6	509.4	520.4	537.5	556.3	576.6	603.2	632.9	648.5	671.9
57.5°	453.2	456.3	464.1	471.9	489.1	506.3	529.7	551.6	581.3	595.4	617.2
60°	407.8	407.8	415.7	426.6	439.1	454.7	475.0	501.6	523.5	540.7	556.3
62.5°	359.4	364.1	368.8	376.6	390.7	409.4	426.6	445.3	471.9	484.4	498.5
65°	311.0	315.7	325.0	332.8	343.8	356.3	378.2	393.8	414.1	428.2	440.7
67.5°	268.8	273.5	279.7	289.1	296.9	311.0	326.6	342.2	364.1	373.5	382.8
70°	225.0	229.7	234.4	246.9	254.7	265.6	276.6	292.2	311.0	317.2	325.0
72.5°	190.6	192.2	198.5	201.6	212.5	221.9	234.4	243.8	257.8	265.6	271.9
75°	161.0	161.0	162.5	165.6	171.9	178.1	187.5	196.9	209.4	214.1	221.9
77.5°	126.6	131.3	129.7	132.8	135.9	139.1	146.9	153.1	165.6	168.8	171.9
80°	90.6	92.2	96.9	101.6	101.6	106.3	110.9	112.5	120.3	125.0	125.0
82.5°	65.6	67.2	65.6	67.2	68.8	70.3	75.0	81.3	81.3	82.8	85.9
85°	40.6	40.6	42.2	43.8	43.8	42.2	45.3	43.8	45.3	48.4	48.4
87.5°	20.3	18.8	18.8	18.8	18.8	18.8	20.3	18.8	20.3	20.3	20.3
90°	7.3	6.9	6.5	6.1	5.7	5.1	4.6	4.0	3.5	3.2	2.9
92.5°	17.8	17.3	16.7	16.2	15.6	14.9	14.2	13.5	12.8	12.4	12.2
95°	29.6	29.1	28.5	28.0	27.4	26.6	25.8	25.0	24.2	23.8	23.7
97.5°	42.8	42.3	41.8	41.4	40.9	39.8	38.7	37.6	36.5	35.9	35.9
100°	57.2	56.5	55.8	55.1	54.4	53.4	52.4	51.3	50.3	49.8	49.8
102.5°	71.8	71.0	70.2	69.4	68.6	68.2	67.8	67.5	67.1	66.9	66.7
105°	86.9	86.4	85.9	85.5	85.0	84.5	84.1	83.6	83.1	82.9	82.7
107.5°	103.0	102.8	102.5	102.3	102.1	101.7	101.3	100.9	100.5	100.3	100.1
110°	120.4	120.2	119.9	119.7	119.5	119.3	119.0	118.8	118.5	118.4	118.2

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	137.6	137.5	137.4	137.4	137.3	137.0	136.6	136.3	136.0	135.8	135.7
115°	155.0	155.1	155.2	155.3	155.4	155.2	155.1	154.9	154.8	154.7	154.5
117.5°	173.2	173.1	173.0	172.9	172.8	172.6	172.5	172.3	172.2	172.1	172.1
120°	191.0	191.0	191.0	191.0	191.0	190.9	190.8	190.7	190.6	190.6	190.4
122.5°	208.4	208.5	208.6	208.6	208.7	208.5	208.3	208.0	207.8	207.7	207.7
125°	225.5	225.7	225.8	226.0	226.2	226.1	226.0	225.9	225.8	225.8	225.6
127.5°	242.9	243.0	243.1	243.1	243.2	243.1	243.1	243.0	242.9	242.9	242.8
130°	259.9	260.0	260.1	260.2	260.3	260.1	260.0	259.8	259.7	259.6	259.4
132.5°	276.3	276.4	276.5	276.6	276.7	276.8	276.8	276.9	277.0	277.0	276.6
135°	293.4	293.4	293.4	293.4	293.4	293.3	293.2	293.1	293.0	293.0	292.8
137.5°	310.1	310.0	309.9	309.8	309.7	309.5	309.4	309.2	309.1	309.0	308.8
140°	325.6	325.5	325.3	325.2	325.0	324.8	324.5	324.3	324.0	323.9	323.7
142.5°	340.7	340.6	340.5	340.4	340.3	340.0	339.7	339.4	339.1	338.9	338.7
145°	354.9	354.9	354.9	354.9	354.9	354.7	354.4	354.2	353.9	353.8	353.6
147.5°	369.0	368.7	368.5	368.2	368.0	367.8	367.7	367.5	367.4	367.3	367.2
150°	381.2	381.2	381.2	381.2	381.2	380.9	380.6	380.3	380.0	379.8	379.8
152.5°	393.5	393.3	393.0	392.8	392.6	392.5	392.4	392.3	392.2	392.2	392.1
155°	404.8	404.5	404.2	403.9	403.6	403.5	403.4	403.3	403.2	403.2	403.2
157.5°	414.8	414.5	414.2	413.9	413.6	413.5	413.4	413.3	413.2	413.2	413.3
160°	423.7	423.4	423.1	422.7	422.4	422.3	422.3	422.2	422.1	422.1	422.2
162.5°	432.2	431.8	431.4	431.0	430.6	430.6	430.6	430.6	430.6	430.6	430.7
165°	439.3	439.0	438.7	438.4	438.1	438.0	437.9	437.8	437.7	437.7	437.8
167.5°	445.4	444.9	444.4	443.9	443.4	443.4	443.4	443.4	443.4	443.4	443.6
170°	450.3	449.8	449.3	448.9	448.4	448.4	448.4	448.4	448.4	448.4	448.6
172.5°	453.9	453.4	452.9	452.5	452.0	452.0	452.0	452.0	452.0	452.0	452.2
175°	456.4	455.9	455.4	455.0	454.5	454.5	454.5	454.5	454.5	454.5	454.7
177.5°	457.8	457.3	456.8	456.4	455.9	456.0	456.0	456.1	456.2	456.2	456.4
180°	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9	456.9

TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1903.3	1903.3	1903.3	1903.3
2.5°	1859.5	1873.6	1887.7	1904.8
5°	1822.0	1847.0	1873.6	1898.6
7.5°	1781.4	1817.3	1851.7	1887.7
10°	1736.1	1781.4	1820.5	1870.5
12.5°	1686.1	1734.5	1789.2	1845.5
15°	1636.1	1697.0	1754.8	1818.9
17.5°	1589.2	1647.0	1711.1	1787.6
20°	1532.9	1597.0	1668.9	1750.1
22.5°	1473.6	1543.9	1622.0	1709.5
25°	1423.6	1495.4	1570.4	1662.6
27.5°	1368.9	1443.9	1517.3	1615.8
30°	1306.4	1387.6	1462.6	1564.2
32.5°	1247.0	1328.2	1411.1	1506.4
35°	1189.2	1268.9	1351.7	1448.6
37.5°	1134.5	1206.3	1287.6	1375.1
40°	1082.9	1148.5	1220.4	1300.1
42.5°	1017.3	1093.8	1161.0	1218.8
45°	961.0	1023.5	1086.0	1132.9
47.5°	895.4	957.9	1011.0	1048.5
50°	840.7	890.7	934.4	967.3
52.5°	775.1	821.9	857.9	882.9
55°	711.0	751.6	782.9	800.1
57.5°	653.2	679.7	703.2	718.8
60°	589.1	609.4	629.7	646.9
62.5°	520.4	542.2	553.2	571.9
65°	459.4	473.5	490.7	496.9
67.5°	400.0	407.8	418.8	431.3
70°	337.5	342.2	353.2	370.3
72.5°	282.8	287.5	295.3	301.6
75°	225.0	229.7	236.0	242.2
77.5°	176.6	178.1	181.3	187.5
80°	128.1	132.8	135.9	137.5
82.5°	89.1	90.6	90.6	92.2
85°	56.3	53.1	53.1	54.7
87.5°	20.3	23.4	23.4	26.6
90°	2.3	1.6	1.0	0.4
92.5°	11.8	11.5	11.1	10.7
95°	23.6	23.4	23.3	23.1
97.5°	35.8	35.7	35.7	35.6
100°	49.8	49.8	49.8	49.8
102.5°	66.3	65.9	65.5	65.1
105°	82.3	81.9	81.5	81.1
107.5°	99.7	99.3	98.9	98.5
110°	117.8	117.4	117.0	116.6



TEST NUMBER: P1028629

CATALOG NUMBER: S125RDIP-B1270D375UB30-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	135.6	135.4	135.3	135.1
115°	154.2	153.9	153.6	153.3
117.5°	172.0	171.9	171.9	171.8
120°	190.0	189.6	189.2	188.8
122.5°	207.6	207.5	207.4	207.3
125°	225.1	224.6	224.2	223.7
127.5°	242.5	242.3	242.0	241.8
130°	259.0	258.6	258.2	257.8
132.5°	275.9	275.2	274.5	273.8
135°	292.3	291.8	291.4	290.9
137.5°	308.3	307.8	307.4	306.9
140°	323.3	323.0	322.6	322.2
142.5°	338.4	338.1	337.8	337.5
145°	353.3	353.0	352.7	352.4
147.5°	367.0	366.7	366.5	366.3
150°	379.9	380.0	380.0	380.1
152.5°	392.0	391.8	391.7	391.5
155°	403.2	403.2	403.2	403.2
157.5°	413.4	413.6	413.7	413.9
160°	422.5	422.7	423.0	423.2
162.5°	430.8	431.0	431.1	431.3
165°	438.0	438.1	438.3	438.5
167.5°	443.9	444.2	444.6	444.9
170°	448.9	449.2	449.5	449.8
172.5°	452.5	452.8	453.1	453.4
175°	455.0	455.3	455.6	455.9
177.5°	456.7	457.0	457.4	457.7
180°	456.9	456.9	456.9	456.9

(END OF REPORT)