

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924019

Luminaire Tested: DFN2DIP-4P3F0-030D020US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924019
REPORT IS A COMBINATION OF REPORTS P900551 AND P897473
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US950-FLLONL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4722.3 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924019

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P924019

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1269	1269	1269
5°	1270	1251	1259
10°	1259	1233	1242
15°	1240	1212	1215
20°	1214	1183	1187
25°	1188	1148	1155
30°	1156	1116	1115
35°	1126	1078	1072
40°	1089	1040	1031
45°	1051	1001	989
50°	1011	961	941
55°	968	914	897
60°	920	859	846
65°	867	802	786
70°	799	732	721
75°	706	648	660
80°	593	540	546
85°	418	358	357

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1051 cd/sqm

TEST NUMBER: P924019

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	2.2
10°-20°	294.9	6.2
20°-30°	433.4	9.2
30°-40°	503.4	10.7
40°-50°	502.7	10.6
50°-60°	438.4	9.3
60°-70°	324.1	6.9
70°-80°	183.3	3.9
80°-90°	49.5	1.0
90°-100°	21.2	0.4
100°-110°	79.1	1.7
110°-120°	209.9	4.4
120°-130°	348.2	7.4
130°-140°	369.8	7.8
140°-150°	343.7	7.3
150°-160°	276.4	5.9
160°-170°	178.1	3.8
170°-180°	61.3	1.3
0°-30°	833.1	17.6
0°-40°	1336.5	28.3
0°-60°	2277.6	48.2
0°-90°	2834.5	60.0
90°-120°	310.3	6.6
90°-150°	1372.0	29.1
90°-180°	1888.0	40.0
0°-180°	4722.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1114	1114	1114	1114	1114	
5°	1114	1109	1098	1106	1104	106
15°	1060	1054	1040	1044	1039	299
25°	959	951	933	935	933	441
35°	828	817	800	793	788	517
45°	674	666	650	638	634	520
55°	510	503	490	478	472	456
65°	344	337	327	317	312	340
75°	180	178	172	166	168	192
85°	44	43	42	38	38	49
90°	0	6	9	12	13	4
95°	30	15	18	20	20	36
105°	142	156	28	34	35	151
115°	268	276	288	72	38	264
125°	379	385	394	397	398	338
135°	469	476	480	485	484	362
145°	544	543	551	554	552	340
155°	599	594	600	603	599	276
165°	631	628	629	633	629	178
175°	645	642	643	646	642	61
180°	644	644	644	644	644	

TEST NUMBER: P924019

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1113.6	1113.6	1113.6	1113.6	1113.6
2.5°	1120.1	1114.7	1102.9	1113.6	1111.6
5°	1113.6	1109.4	1097.6	1106.2	1104.1
7.5°	1106.2	1099.8	1087.9	1096.6	1094.4
10°	1094.4	1086.9	1074.1	1082.6	1079.5
12.5°	1078.3	1071.9	1059.1	1064.4	1062.3
15°	1060.1	1053.8	1039.8	1044.1	1038.7
17.5°	1037.6	1031.3	1017.3	1022.6	1017.3
20°	1013.0	1006.6	991.6	994.7	990.5
22.5°	988.4	978.8	964.8	964.8	962.6
25°	959.4	950.9	932.7	934.8	932.7
27.5°	927.3	919.8	905.9	902.8	897.4
30°	895.2	886.6	870.6	867.4	863.1
32.5°	861.0	854.6	837.4	830.9	826.6
35°	827.8	817.1	799.9	793.4	788.1
37.5°	790.3	780.7	763.5	755.9	750.6
40°	751.8	743.2	726.0	716.5	712.2
42.5°	714.3	705.7	688.6	677.8	671.4
45°	673.6	666.1	650.0	638.2	633.9
47.5°	633.9	626.5	609.3	597.5	591.1
50°	592.1	586.8	571.8	556.8	551.5
52.5°	551.5	544.0	530.1	518.3	510.8
55°	509.8	503.3	490.5	477.7	472.3
57.5°	467.9	462.6	448.7	435.8	431.5
60°	426.2	422.0	407.0	395.1	392.0
62.5°	385.5	378.0	367.3	356.6	352.3
65°	343.8	337.3	326.6	317.0	311.7
67.5°	301.0	295.5	285.9	278.5	274.2
70°	261.3	257.0	247.4	239.8	235.6
72.5°	220.7	216.3	210.9	203.5	200.3
75°	179.8	177.8	172.4	166.0	168.2
77.5°	143.5	139.2	137.0	133.8	130.7
80°	107.1	106.0	103.8	100.6	98.5
82.5°	72.8	72.8	71.8	67.4	67.4
85°	43.9	42.8	41.8	38.5	37.5
87.5°	19.3	17.2	15.0	11.8	10.7
90°	0.5	5.6	9.3	11.6	12.6
92.5°	11.6	9.8	11.2	12.1	12.6
95°	30.2	14.9	18.1	20.5	20.0
97.5°	54.5	16.3	23.8	25.2	25.7
100°	82.5	18.6	26.5	30.2	31.2
102.5°	113.2	112.3	27.5	32.6	34.1
105°	141.7	155.6	28.4	33.5	35.4
107.5°	174.8	186.3	29.4	34.4	36.3
110°	206.4	216.2	81.6	35.0	36.8



TEST NUMBER: P924019

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	236.2	244.6	236.7	35.9	37.3
115°	267.9	275.8	287.5	71.7	38.3
117.5°	295.4	304.7	312.6	246.0	123.9
120°	326.2	333.1	341.5	347.2	284.2
122.5°	352.2	359.7	369.0	371.8	372.3
125°	378.8	384.8	393.7	397.0	398.4
127.5°	403.1	409.6	416.6	421.2	421.7
130°	425.9	433.3	438.5	443.6	443.1
132.5°	449.1	455.2	460.3	464.5	464.1
135°	468.8	476.2	480.3	485.1	484.2
137.5°	489.2	494.8	499.5	504.2	502.8
140°	509.2	513.1	518.1	522.3	520.0
142.5°	526.0	529.4	535.4	539.1	536.7
145°	543.8	543.3	551.2	554.5	552.2
147.5°	559.1	557.7	565.6	567.9	566.1
150°	574.0	570.8	578.2	581.0	578.7
152.5°	586.6	582.9	589.9	592.7	589.4
155°	598.7	594.5	600.2	602.9	599.2
157.5°	608.6	604.8	609.0	612.3	608.6
160°	617.0	614.1	617.0	619.7	616.5
162.5°	624.3	621.5	623.9	627.2	623.0
165°	630.9	628.1	629.4	632.8	629.4
167.5°	636.0	633.2	634.6	637.9	633.6
170°	640.2	637.4	638.3	641.6	637.4
172.5°	643.0	640.2	641.2	644.4	640.2
175°	645.3	642.0	643.0	646.2	641.6
177.5°	646.2	643.0	643.5	646.7	642.5
180°	643.9	643.9	643.9	643.9	643.9

TEST NUMBER: P924019

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US950-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.94	9.90	9.81	10.79	11.91	8.50	9.46	9.36	10.35	11.47
	3H	10.61	11.47	11.48	12.36	13.51	10.12	10.98	10.99	11.87	13.02
	4H	11.20	12.01	12.09	12.91	14.07	10.70	11.52	11.60	12.42	13.57
	6H	11.60	12.35	12.50	13.26	14.43	11.10	11.85	12.00	12.76	13.93
	8H	11.70	12.42	12.62	13.34	14.51	11.20	11.92	12.12	12.84	14.01
	12H	11.75	12.43	12.67	13.35	14.55	11.24	11.92	12.16	12.85	14.04
4H	2H	9.41	10.23	10.31	11.13	12.29	9.06	9.87	9.96	10.77	11.93
	3H	11.28	11.96	12.19	12.90	14.07	10.87	11.55	11.78	12.49	13.66
	4H	12.00	12.62	12.92	13.55	14.74	11.57	12.19	12.49	13.12	14.32
	6H	12.51	13.05	13.45	14.00	15.20	12.08	12.62	13.02	13.57	14.77
	8H	12.66	13.16	13.60	14.11	15.32	12.22	12.72	13.16	13.67	14.88
	12H	12.74	13.19	13.69	14.15	15.37	12.29	12.74	13.25	13.70	14.92
8H	4H	12.20	12.70	13.13	13.64	14.86	11.82	12.32	12.76	13.27	14.48
	6H	12.83	13.24	13.79	14.23	15.44	12.44	12.86	13.41	13.85	15.06
	8H	13.04	13.41	14.02	14.39	15.62	12.65	13.02	13.62	14.00	15.22
	12H	13.18	13.50	14.15	14.47	15.75	12.77	13.09	13.74	14.06	15.34
12H	4H	12.19	12.64	13.14	13.60	14.82	11.82	12.27	12.77	13.23	14.45
	6H	12.85	13.22	13.83	14.20	15.43	12.48	12.85	13.46	13.83	15.06
	8H	13.10	13.42	14.07	14.39	15.67	12.72	13.04	13.69	14.01	15.29