

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028638

Luminaire Tested: S125RDIP-B1270D375UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028638
REPORT IS A COMBINATION OF REPORTS P1005225 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D375UB35-4F0-XX-W2A-F1
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6190.0 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028638

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1028638

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83
1	105	100	96	93	100	96	93	89	88	85	83	81	79	77	74	72	71
2	96	88	82	77	91	84	79	74	78	73	69	71	68	65	66	63	60
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45
5	74	62	54	47	70	60	52	46	55	49	44	51	46	42	47	43	39
6	68	56	47	41	65	54	46	40	50	43	39	46	41	37	43	38	35
7	63	51	42	37	61	49	41	36	46	39	34	42	37	33	39	35	31
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	34	29	25
10	52	39	32	27	49	38	31	26	36	29	25	33	28	24	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13313	13313	13313
5°	13314	12981	13001
10°	13184	12653	12542
15°	12997	12195	11938
20°	12766	11645	11304
25°	12501	11107	10624
30°	12177	10515	9911
35°	11847	9915	9153
40°	11532	9299	8413
45°	11153	8632	7638
50°	10769	7925	6848
55°	10325	7230	6030
60°	9869	6433	5182
65°	9326	5544	4268
70°	8693	4514	3359
75°	7816	3394	2447
80°	6592	2198	1650
85°	4934	1180	930

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11153 cd/sqm

TEST NUMBER: P1028638

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	3.2
10°-20°	546.5	8.8
20°-30°	792.4	12.8
30°-40°	902.8	14.6
40°-50°	879.9	14.2
50°-60°	740.5	12.0
60°-70°	518.9	8.4
70°-80°	266.0	4.3
80°-90°	67.1	1.1
90°-100°	30.5	0.5
100°-110°	90.6	1.5
110°-120°	153.7	2.5
120°-130°	202.3	3.3
130°-140°	226.7	3.7
140°-150°	222.2	3.6
150°-160°	186.7	3.0
160°-170°	124.1	2.0
170°-180°	43.4	0.7
0°-30°	1534.4	24.8
0°-40°	2437.2	39.4
0°-60°	4057.7	65.6
0°-90°	4909.7	79.3
90°-120°	274.8	4.4
90°-150°	926.1	15.0
90°-180°	1280.0	20.7
0°-180°	6190.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2068	2051	2067	2064	197
15°	1973	1963	1930	1929	1914	556
25°	1789	1766	1707	1687	1670	823
35°	1541	1503	1433	1387	1365	965
45°	1262	1216	1130	1067	1044	973
55°	957	907	819	749	723	856
65°	648	595	512	449	425	642
75°	345	298	232	198	187	365
85°	86	58	50	49	47	95
90°	0	3	6	8	9	7
95°	23	24	28	30	31	24
105°	81	83	85	88	88	87
115°	154	155	156	156	155	152
125°	224	227	227	226	226	201
135°	292	294	294	294	293	225
145°	354	355	356	356	355	221
155°	405	405	405	407	405	186
165°	440	440	440	441	439	124
175°	458	456	456	458	456	43
180°	459	459	459	459	459	

TEST NUMBER: P1028638

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2077.8	2077.8	2077.8	2077.8	2077.8
2.5°	2082.5	2077.8	2062.1	2077.8	2076.2
5°	2074.6	2068.3	2051.1	2066.8	2063.6
7.5°	2058.9	2052.6	2032.2	2044.8	2041.7
10°	2035.4	2030.7	2008.7	2013.4	2008.7
12.5°	2008.7	2002.4	1971.0	1974.2	1966.3
15°	1972.6	1963.2	1930.2	1928.7	1914.5
17.5°	1935.0	1920.8	1881.6	1873.7	1862.8
20°	1889.4	1873.7	1823.5	1815.7	1801.6
22.5°	1839.2	1823.5	1770.2	1752.9	1741.9
25°	1789.0	1765.5	1707.4	1687.0	1669.7
27.5°	1732.5	1704.3	1643.1	1616.4	1599.1
30°	1669.7	1639.9	1574.0	1537.9	1523.8
32.5°	1608.5	1572.4	1505.0	1464.2	1445.3
35°	1541.1	1503.4	1432.8	1387.3	1365.3
37.5°	1476.7	1431.2	1359.0	1305.7	1283.7
40°	1407.7	1360.6	1285.3	1225.6	1206.8
42.5°	1335.5	1286.8	1208.4	1151.9	1122.1
45°	1261.7	1216.2	1129.9	1067.1	1043.6
47.5°	1184.8	1137.7	1051.4	987.1	960.4
50°	1112.6	1060.8	971.4	905.5	881.9
52.5°	1034.2	980.8	897.6	825.5	801.9
55°	957.3	907.1	819.2	748.6	723.4
57.5°	878.8	825.5	740.7	671.7	649.7
60°	803.5	748.6	663.8	594.8	571.2
62.5°	723.4	671.7	585.3	522.6	499.0
65°	648.1	594.8	511.6	448.8	425.3
67.5°	572.8	519.4	439.4	379.8	360.9
70°	495.9	442.5	364.1	315.4	296.6
72.5°	420.6	368.8	296.6	252.7	241.7
75°	345.2	298.2	232.3	197.7	186.7
77.5°	268.4	230.7	175.8	149.1	139.7
80°	204.0	166.3	122.4	108.3	105.1
82.5°	141.2	108.3	81.6	76.9	75.3
85°	86.3	58.1	50.2	48.6	47.1
87.5°	36.1	25.1	23.5	23.5	22.0
90°	0.4	3.2	5.7	7.5	8.6
92.5°	10.7	12.5	15.7	18.2	18.9
95°	23.2	23.9	27.5	30.0	30.7
97.5°	35.7	36.1	41.1	43.2	43.6
100°	50.0	50.0	54.6	57.8	58.5
102.5°	65.3	67.1	68.9	72.5	73.5
105°	81.4	83.2	85.3	87.5	88.5
107.5°	98.9	100.7	102.5	103.5	103.5
110°	117.1	118.9	119.9	121.0	120.7

TEST NUMBER: P1028638

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.7	136.4	137.8	138.2	137.4
115°	153.9	155.3	156.0	155.6	155.3
117.5°	172.4	172.8	173.5	173.9	172.4
120°	189.6	191.3	191.7	191.7	190.3
122.5°	208.1	208.5	209.6	209.2	208.1
125°	224.5	226.7	227.0	226.3	226.0
127.5°	242.8	243.8	244.2	243.8	243.1
130°	258.8	260.6	261.3	261.0	260.2
132.5°	274.9	278.1	277.7	277.4	276.3
135°	292.0	294.2	294.5	294.5	293.1
137.5°	308.1	310.2	310.9	311.3	309.5
140°	323.4	325.2	326.3	327.0	325.2
142.5°	338.8	340.2	341.6	342.0	340.2
145°	353.8	355.2	356.3	356.3	355.2
147.5°	367.7	368.8	369.5	370.6	367.7
150°	381.6	381.3	382.7	382.7	382.0
152.5°	393.0	393.8	394.1	395.2	393.8
155°	404.8	404.8	405.2	406.6	404.8
157.5°	415.5	414.8	415.2	416.6	414.1
160°	424.8	423.7	424.1	425.5	423.7
162.5°	433.0	432.3	432.3	434.1	432.0
165°	440.2	439.5	439.8	441.2	439.1
167.5°	446.6	445.2	445.2	447.3	445.2
170°	451.6	450.2	450.2	452.3	449.8
172.5°	455.2	453.7	453.7	455.9	453.7
175°	457.7	456.2	456.2	458.4	455.9
177.5°	459.4	458.0	457.7	459.8	457.3
180°	458.7	458.7	458.7	458.7	458.7

(END OF REPORT)