

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902397

Luminaire Tested: DFN2DIP-4P4F0-080D030US830-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902397
REPORT IS A COMBINATION OF REPORTS P900610 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D030US830-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9208.7 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 108.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902397

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902397

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	59	57	55
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	32	29
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2022	2022	2022
5°	2025	1990	2003
10°	2005	1952	1939
15°	1978	1888	1839
20°	1941	1800	1716
25°	1904	1700	1597
30°	1854	1599	1446
35°	1805	1489	1313
40°	1755	1376	1161
45°	1697	1250	1023
50°	1637	1123	888
55°	1575	988	758
60°	1502	846	625
65°	1419	701	563
70°	1318	566	511
75°	1191	501	467
80°	1008	422	407
85°	704	285	311

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1697 cd/sqm

TEST NUMBER: P902397

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.1	3.2
10°-20°	801.8	8.7
20°-30°	1125.7	12.2
30°-40°	1227.1	13.3
40°-50°	1127.8	12.2
50°-60°	885.7	9.6
60°-70°	576.5	6.3
70°-80°	296.8	3.2
80°-90°	77.4	0.8
90°-100°	31.5	0.3
100°-110°	117.3	1.3
110°-120°	311.1	3.4
120°-130°	516.0	5.6
130°-140°	548.1	6.0
140°-150°	509.4	5.5
150°-160°	409.6	4.4
160°-170°	263.9	2.9
170°-180°	90.8	1.0
0°-30°	2219.6	24.1
0°-40°	3446.7	37.4
0°-60°	5460.2	59.3
0°-90°	6411.0	69.6
90°-120°	459.9	5.0
90°-150°	2033.4	22.1
90°-180°	2798.0	30.4
0°-180°	9208.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3116	3116	3116	3116	3116	
5°	3116	3102	3066	3091	3083	296
15°	2964	2933	2837	2784	2756	835
25°	2691	2600	2414	2299	2256	1237
35°	2318	2174	1926	1749	1686	1451
45°	1895	1706	1410	1210	1142	1464
55°	1441	1221	916	747	694	1288
65°	973	744	491	395	386	965
75°	519	321	226	206	203	549
85°	121	62	54	54	54	139
90°	1	8	14	17	19	9
95°	45	22	27	30	30	53
105°	210	231	42	50	52	224
115°	397	409	426	106	57	391
125°	561	570	584	588	590	501
135°	695	706	712	719	718	537
145°	806	805	817	822	818	504
155°	887	881	889	894	888	409
165°	935	931	933	938	933	264
175°	956	952	953	958	951	91
180°	954	954	954	954	954	

TEST NUMBER: P902397

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3116.4	3116.4	3116.4	3116.4	3116.4
2.5°	3130.5	3116.4	3085.3	3113.7	3108.0
5°	3116.4	3102.4	3065.5	3091.0	3082.6
7.5°	3091.0	3074.2	3034.7	3045.8	3031.7
10°	3057.1	3037.4	2981.2	2972.5	2955.7
12.5°	3015.0	2989.6	2913.2	2896.4	2865.3
15°	2964.1	2933.0	2837.2	2783.7	2755.5
17.5°	2904.8	2859.7	2741.2	2679.3	2634.0
20°	2837.2	2780.7	2639.8	2569.5	2507.2
22.5°	2763.9	2699.0	2535.3	2439.6	2397.4
25°	2690.6	2600.3	2414.1	2298.7	2256.2
27.5°	2603.2	2507.2	2301.3	2168.8	2103.8
30°	2510.2	2402.7	2177.2	2033.5	1957.2
32.5°	2419.8	2290.0	2059.0	1889.6	1819.0
35°	2318.4	2174.4	1926.4	1748.7	1686.4
37.5°	2219.6	2064.4	1802.2	1607.4	1537.1
40°	2115.3	1946.2	1672.4	1472.2	1398.8
42.5°	2008.1	1827.7	1542.8	1334.0	1263.6
45°	1895.3	1706.2	1410.2	1209.8	1142.2
47.5°	1788.2	1588.0	1283.4	1082.9	1021.0
50°	1669.6	1469.5	1159.2	964.4	905.4
52.5°	1553.9	1342.3	1040.7	854.6	801.1
55°	1441.1	1221.2	916.5	747.4	693.9
57.5°	1325.6	1099.9	806.7	648.8	603.5
60°	1207.0	981.5	690.9	547.2	502.1
62.5°	1091.6	865.9	592.2	456.9	434.5
65°	973.1	744.4	490.7	395.0	386.3
67.5°	860.3	631.7	395.0	346.8	338.5
70°	741.8	521.9	327.1	298.9	287.6
72.5°	629.0	420.1	273.5	251.1	245.3
75°	518.9	321.4	225.6	205.9	203.2
77.5°	409.1	228.3	177.8	166.4	160.7
80°	307.3	163.7	135.3	124.1	124.1
82.5°	214.2	110.1	93.0	87.4	87.4
85°	121.2	61.9	53.5	53.5	53.5
87.5°	45.1	22.4	22.4	19.8	19.8
90°	0.7	8.3	13.8	17.3	18.6
92.5°	17.3	14.5	16.6	18.0	18.6
95°	44.9	22.1	26.9	30.4	29.7
97.5°	80.8	24.2	35.2	37.3	38.0
100°	122.2	27.6	39.4	44.9	46.3
102.5°	167.8	166.5	40.7	48.3	50.4
105°	209.9	230.6	42.1	49.7	52.5
107.5°	258.9	276.2	43.5	51.1	53.9
110°	305.9	320.4	120.8	51.8	54.6

TEST NUMBER: P902397

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	350.2	362.5	350.8	53.2	55.2
115°	397.0	408.8	426.0	106.3	56.6
117.5°	437.8	451.6	463.4	364.6	183.7
120°	483.3	493.7	506.1	514.4	421.2
122.5°	522.0	533.1	547.0	551.0	551.8
125°	561.4	570.3	583.5	588.3	590.4
127.5°	597.3	606.9	617.4	624.2	624.9
130°	631.1	642.2	649.8	657.3	656.8
132.5°	665.6	674.7	682.2	688.4	687.8
135°	694.7	705.8	711.9	718.9	717.5
137.5°	725.0	733.3	740.3	747.2	745.1
140°	754.7	760.3	767.8	774.0	770.6
142.5°	779.7	784.5	793.4	798.9	795.5
145°	805.9	805.1	816.9	821.7	818.2
147.5°	828.6	826.5	838.3	841.7	839.0
150°	850.7	845.9	857.0	861.0	857.6
152.5°	869.3	863.8	874.2	878.4	873.5
155°	887.3	881.2	889.4	893.5	888.1
157.5°	901.8	896.4	902.6	907.4	901.8
160°	914.3	910.1	914.3	918.4	913.5
162.5°	925.3	921.1	924.6	929.4	923.2
165°	934.9	930.9	932.9	937.7	932.9
167.5°	942.5	938.4	940.5	945.4	939.1
170°	948.8	944.6	946.0	950.8	944.6
172.5°	952.9	948.8	950.2	955.0	948.8
175°	956.3	951.5	952.9	957.7	950.8
177.5°	957.7	952.9	953.7	958.5	952.3
180°	954.3	954.3	954.3	954.3	954.3

TEST NUMBER: P902397

CATALOG NUMBER: DFN2DIP-4P4F0-080D030US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.27	12.30	12.05	13.09	14.05	7.24	8.26	8.01	9.05	10.01
	3H	12.97	13.89	13.76	14.69	15.68	8.44	9.35	9.23	10.16	11.15
	4H	13.59	14.45	14.40	15.27	16.27	8.90	9.76	9.71	10.57	11.58
	6H	14.03	14.82	14.85	15.64	16.66	9.23	10.03	10.05	10.85	11.86
	8H	14.16	14.92	14.99	15.76	16.78	9.33	10.08	10.16	10.92	11.94
	12H	14.23	14.95	15.07	15.78	16.83	9.38	10.10	10.21	10.93	11.97
4H	2H	11.32	12.18	12.13	12.99	13.99	7.86	8.72	8.67	9.53	10.53
	3H	13.17	13.88	13.99	14.73	15.75	9.23	9.94	10.05	10.79	11.81
	4H	13.87	14.52	14.71	15.37	16.41	9.78	10.43	10.62	11.28	12.33
	6H	14.40	14.96	15.26	15.83	16.89	10.22	10.78	11.07	11.64	12.70
	8H	14.59	15.11	15.44	15.97	17.04	10.35	10.87	11.20	11.73	12.80
	12H	14.69	15.16	15.57	16.05	17.12	10.42	10.89	11.30	11.78	12.85
8H	4H	13.86	14.38	14.71	15.24	16.31	10.08	10.60	10.94	11.47	12.53
	6H	14.43	14.87	15.32	15.77	16.84	10.61	11.04	11.49	11.95	13.01
	8H	14.66	15.04	15.55	15.94	17.02	10.80	11.19	11.70	12.09	13.17
	12H	14.81	15.14	15.70	16.03	17.17	10.93	11.27	11.83	12.16	13.30
12H	4H	13.82	14.29	14.69	15.17	16.24	10.10	10.57	10.97	11.45	12.52
	6H	14.41	14.79	15.30	15.69	16.78	10.66	11.04	11.55	11.94	13.03
	8H	14.64	14.98	15.54	15.87	17.01	10.88	11.22	11.78	12.11	13.25

END OF REPORT