

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P902435

Luminaire Tested: DFN2DIP-HX2F0-020D060US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P902435
REPORT IS A COMBINATION OF REPORTS P900711 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-020D060US830-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7464.9 lumens
Efficiency: N/A
Efficacy: 117.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 63.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P902435

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P902435

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1728	1728	1728
5°	1728	1700	1712
10°	1712	1673	1686
15°	1683	1641	1647
20°	1647	1599	1606
25°	1610	1549	1560
30°	1565	1502	1503
35°	1522	1448	1442
40°	1469	1393	1384
45°	1417	1338	1325
50°	1359	1279	1256
55°	1298	1212	1192
60°	1230	1133	1119
65°	1154	1050	1033
70°	1059	949	939
75°	928	828	849
80°	768	674	684
85°	520	423	424

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1743 cd/sqm

TEST NUMBER: P902435

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	0.9
10°-20°	194.2	2.6
20°-30°	285.5	3.8
30°-40°	331.5	4.4
40°-50°	331.1	4.4
50°-60°	288.7	3.9
60°-70°	213.4	2.9
70°-80°	120.8	1.6
80°-90°	35.2	0.5
90°-100°	62.9	0.8
100°-110°	234.6	3.1
110°-120°	622.2	8.3
120°-130°	1032.0	13.8
130°-140°	1096.2	14.7
140°-150°	1018.8	13.6
150°-160°	819.1	11.0
160°-170°	527.8	7.1
170°-180°	181.7	2.4
0°-30°	548.7	7.4
0°-40°	880.3	11.8
0°-60°	1500.2	20.1
0°-90°	1869.6	25.0
90°-120°	919.8	12.3
90°-150°	4066.8	54.5
90°-180°	5595.0	75.0
0°-180°	7464.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	734	731	723	729	727	70
15°	698	694	685	688	684	197
25°	632	626	614	616	614	291
35°	545	538	527	523	519	340
45°	444	439	428	420	418	342
55°	336	332	323	315	311	300
65°	226	222	215	209	205	224
75°	118	117	114	109	111	126
85°	29	28	28	25	25	32
90°	1	17	28	35	37	7
95°	90	44	54	61	59	106
105°	420	461	84	99	105	449
115°	794	818	852	213	113	782
125°	1123	1141	1167	1177	1181	1001
135°	1389	1412	1424	1438	1435	1073
145°	1612	1610	1634	1643	1636	1008
155°	1775	1762	1779	1787	1776	818
165°	1870	1862	1866	1876	1866	528
175°	1913	1903	1906	1915	1902	182
180°	1909	1909	1909	1909	1909	

TEST NUMBER: P902435

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	733.5	733.5	733.5	733.5	733.5
2.5°	737.7	734.2	726.4	733.5	732.2
5°	733.5	730.8	722.9	728.6	727.2
7.5°	728.6	724.3	716.6	722.3	720.9
10°	720.9	716.0	707.5	713.0	711.0
12.5°	710.2	706.1	697.6	701.1	699.6
15°	698.2	694.1	684.9	687.7	684.2
17.5°	683.4	679.3	670.1	673.5	670.1
20°	667.2	663.0	653.1	655.3	652.4
22.5°	651.0	644.7	635.5	635.5	634.0
25°	632.0	626.3	614.3	615.7	614.3
27.5°	610.8	605.9	596.7	594.6	591.1
30°	589.7	584.0	573.4	571.4	568.4
32.5°	567.0	562.9	551.6	547.3	544.5
35°	545.3	538.2	526.9	522.6	519.1
37.5°	520.6	514.2	502.8	497.9	494.4
40°	495.1	489.5	478.2	471.9	469.0
42.5°	470.4	464.8	453.6	446.5	442.2
45°	443.7	438.8	428.1	420.4	417.5
47.5°	417.5	412.6	401.3	393.5	389.4
50°	390.0	386.5	376.6	366.7	363.3
52.5°	363.3	358.3	349.1	341.4	336.5
55°	335.7	331.5	323.0	314.6	311.0
57.5°	308.2	304.7	295.5	287.1	284.2
60°	280.7	278.0	268.1	260.2	258.2
62.5°	253.9	248.9	242.0	234.9	232.1
65°	226.4	222.2	215.2	208.8	205.3
67.5°	198.2	194.6	188.3	183.4	180.6
70°	172.1	169.3	162.9	158.0	155.2
72.5°	145.3	142.5	138.9	134.0	132.0
75°	118.5	117.2	113.5	109.3	110.7
77.5°	94.5	91.7	90.2	88.1	86.1
80°	70.6	69.8	68.4	66.3	64.8
82.5°	48.0	48.0	47.3	44.5	44.5
85°	28.8	28.2	27.5	25.4	24.7
87.5°	12.7	11.3	9.9	7.8	7.1
90°	1.3	16.6	27.5	34.6	37.2
92.5°	34.6	29.0	33.1	35.9	37.2
95°	89.7	44.1	53.8	60.9	59.4
97.5°	161.6	48.4	70.3	74.6	76.0
100°	244.5	55.2	78.7	89.7	92.5
102.5°	335.5	332.9	81.5	96.6	100.9
105°	419.8	461.3	84.3	99.3	105.0
107.5°	517.9	552.3	87.1	102.2	107.7
110°	611.9	640.7	241.8	103.7	109.1

TEST NUMBER: P902435

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.2	725.0	701.5	106.2	110.6
115°	794.1	817.6	852.2	212.7	113.3
117.5°	875.5	903.1	926.7	729.2	367.3
120°	966.8	987.4	1012.4	1028.9	842.4
122.5°	1044.0	1066.1	1093.8	1102.0	1103.5
125°	1122.8	1140.8	1167.0	1176.7	1180.7
127.5°	1194.6	1213.9	1234.7	1248.5	1249.8
130°	1262.3	1284.4	1299.5	1314.8	1313.4
132.5°	1331.3	1349.3	1364.4	1376.9	1375.5
135°	1389.4	1411.6	1423.8	1437.8	1434.9
137.5°	1450.0	1466.6	1480.5	1494.3	1490.3
140°	1509.4	1520.6	1535.7	1548.1	1541.2
142.5°	1559.2	1569.0	1586.9	1597.8	1590.9
145°	1611.7	1610.2	1633.7	1643.4	1636.5
147.5°	1657.2	1653.0	1676.5	1683.4	1678.0
150°	1701.5	1691.8	1713.9	1722.1	1715.2
152.5°	1738.7	1727.7	1748.3	1756.7	1747.0
155°	1774.6	1762.3	1778.9	1787.1	1776.0
157.5°	1803.6	1792.6	1805.1	1814.8	1803.6
160°	1828.5	1820.1	1828.5	1836.7	1827.1
162.5°	1850.5	1842.3	1849.2	1858.9	1846.4
165°	1869.9	1861.7	1865.8	1875.5	1865.8
167.5°	1885.1	1876.8	1881.0	1890.7	1878.2
170°	1897.6	1889.2	1892.1	1901.7	1889.2
172.5°	1905.8	1897.6	1900.4	1910.1	1897.6
175°	1912.7	1903.0	1905.8	1915.4	1901.7
177.5°	1915.4	1905.8	1907.2	1916.9	1904.5
180°	1908.6	1908.6	1908.6	1908.6	1908.6

TEST NUMBER: P902435

CATALOG NUMBER: DFN2DIP-HX2F0-020D060US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.09	6.77	7.24	7.90	9.49	5.67	6.35	6.82	7.48	9.07
	3H	7.71	8.32	8.87	9.46	11.06	7.25	7.86	8.41	9.00	10.60
	4H	8.28	8.85	9.44	9.99	11.60	7.82	8.39	8.98	9.53	11.14
	6H	8.65	9.18	9.82	10.32	11.94	8.19	8.72	9.36	9.86	11.48
	8H	8.74	9.24	9.91	10.40	12.01	8.28	8.78	9.45	9.94	11.55
	12H	8.77	9.25	9.95	10.40	12.03	8.31	8.78	9.48	9.94	11.57
4H	2H	6.52	7.10	7.69	8.24	9.85	6.18	6.76	7.35	7.90	9.51
	3H	8.34	8.82	9.52	9.99	11.61	7.96	8.44	9.13	9.61	11.23
	4H	9.03	9.47	10.21	10.63	12.27	8.63	9.08	9.81	10.23	11.87
	6H	9.51	9.89	10.69	11.07	12.69	9.11	9.49	10.29	10.67	12.30
	8H	9.64	9.99	10.82	11.17	12.81	9.25	9.60	10.43	10.77	12.41
	12H	9.69	10.01	10.89	11.20	12.85	9.29	9.61	10.49	10.79	12.44
8H	4H	9.20	9.55	10.38	10.72	12.37	8.85	9.20	10.03	10.37	12.02
	6H	9.79	10.08	10.99	11.30	12.94	9.44	9.73	10.64	10.94	12.59
	8H	10.00	10.25	11.20	11.44	13.10	9.64	9.89	10.84	11.08	12.74
	12H	10.10	10.32	11.31	11.51	13.21	9.73	9.96	10.94	11.14	12.84
12H	4H	9.17	9.49	10.37	10.67	12.32	8.83	9.15	10.03	10.33	11.98
	6H	9.82	10.07	11.02	11.26	12.92	9.47	9.73	10.68	10.92	12.58
	8H	10.03	10.25	11.24	11.44	13.13	9.69	9.91	10.89	11.10	12.79

END OF REPORT