

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007783

Luminaire Tested: S125IP-B1090UB2750-4F0-XX-W2A_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1090UB2750-4F0-XX-W2A_3000K
Description: Define 5 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4098.0 lumens
Efficiency: N/A
Efficacy: 143.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007783

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007783

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007783

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.0
90°-100°	45.3	1.1
100°-110°	300.9	7.3
110°-120°	541.9	13.2
120°-130°	695.6	17.0
130°-140°	748.1	18.3
140°-150°	702.2	17.1
150°-160°	568.0	13.9
160°-170°	367.3	9.0
170°-180°	126.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.0
90°-120°	888.1	21.7
90°-150°	3034.1	74.0
90°-180°	4096.0	100.0
0°-180°	4098.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	3
95°	56	53	16	21	21	69
105°	291	295	295	295	294	308
115°	546	551	552	548	542	541
125°	776	783	783	779	776	693
135°	968	974	972	970	964	746
145°	1122	1124	1124	1125	1119	702
155°	1236	1230	1232	1235	1227	569
165°	1304	1298	1299	1305	1297	368
175°	1333	1328	1328	1336	1328	127
180°	1333	1333	1333	1333	1333	

TEST NUMBER: P1007783

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	8.9	15.8	20.8	23.7
92.5°	18.8	9.9	15.8	20.8	21.7
95°	56.3	53.4	15.8	20.8	20.8
97.5°	105.8	111.7	17.8	19.8	20.8
100°	165.1	168.0	172.0	24.7	20.8
102.5°	225.4	229.3	231.3	233.3	150.2
105°	290.6	294.6	294.6	294.6	293.6
107.5°	357.8	357.8	359.8	360.8	356.8
110°	423.1	423.1	425.0	422.1	423.1

TEST NUMBER: P1007783

CATALOG NUMBER: S125IP-B1090UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	484.3	487.3	488.3	484.3	482.4
115°	545.6	550.6	551.6	547.6	541.7
117.5°	609.9	609.9	613.8	607.9	605.9
120°	669.2	668.2	671.2	669.2	664.2
122.5°	721.6	726.5	727.5	725.5	719.6
125°	775.9	782.9	782.9	778.9	775.9
127.5°	828.3	833.3	832.3	830.3	822.4
130°	875.8	880.7	881.7	878.7	873.8
132.5°	923.2	929.2	926.2	926.2	921.2
135°	967.7	973.6	971.7	969.7	963.7
137.5°	1009.2	1015.1	1013.2	1013.2	1008.2
140°	1049.7	1051.7	1050.7	1052.7	1046.8
142.5°	1086.3	1087.3	1089.3	1089.3	1083.4
145°	1121.9	1123.9	1123.9	1124.9	1118.9
147.5°	1153.5	1153.5	1154.5	1155.5	1148.6
150°	1183.2	1181.2	1183.2	1185.2	1177.3
152.5°	1211.9	1206.9	1208.9	1210.9	1203.9
155°	1235.6	1229.6	1231.6	1234.6	1226.7
157.5°	1254.4	1251.4	1251.4	1254.4	1246.4
160°	1274.1	1268.2	1269.2	1273.1	1265.2
162.5°	1289.9	1284.0	1285.0	1290.9	1282.0
165°	1303.8	1297.8	1298.8	1304.8	1296.9
167.5°	1314.7	1308.7	1309.7	1316.6	1307.7
170°	1323.5	1316.6	1317.6	1325.5	1316.6
172.5°	1329.5	1322.6	1324.5	1331.5	1322.6
175°	1333.4	1327.5	1328.5	1336.4	1327.5
177.5°	1336.4	1330.5	1331.5	1338.4	1330.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4

(END OF REPORT)