

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007803

Luminaire Tested: S125IP-B1270UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1270UB2750-4F0-XX-W2A-1_3000K
Description: Define 5 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4167.0 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007803

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007803

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007803

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.3	0.1
90°-100°	99.2	2.4
100°-110°	294.8	7.1
110°-120°	499.9	12.0
120°-130°	658.2	15.8
130°-140°	737.5	17.7
140°-150°	722.9	17.3
150°-160°	607.2	14.6
160°-170°	403.6	9.7
170°-180°	141.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.3	0.1
90°-120°	894.0	21.5
90°-150°	3012.5	72.3
90°-180°	4165.0	100.0
0°-180°	4167.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	19	24	28	5
95°	76	78	89	98	100	79
105°	265	271	278	284	288	282
115°	500	505	508	506	505	495
125°	730	737	739	736	735	654
135°	950	957	958	958	953	732
145°	1151	1156	1159	1159	1156	719
155°	1317	1317	1318	1323	1317	607
165°	1432	1430	1431	1435	1428	404
175°	1489	1484	1484	1491	1483	141
180°	1492	1492	1492	1492	1492	

TEST NUMBER: P1007803

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	10.5	18.6	24.4	27.9
92.5°	34.8	40.6	51.1	59.2	61.5
95°	75.5	77.8	89.4	97.5	99.9
97.5°	116.1	117.3	133.5	140.5	141.7
100°	162.6	162.6	177.7	188.1	190.4
102.5°	212.5	218.3	224.1	235.7	239.2
105°	264.8	270.6	277.5	284.5	288.0
107.5°	321.7	327.5	333.3	336.8	336.8
110°	380.9	386.7	390.2	393.7	392.5

TEST NUMBER: P1007803

CATALOG NUMBER: S125IP-B1270UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	441.3	443.6	448.2	449.4	447.1
115°	500.5	505.1	507.5	506.3	505.1
117.5°	560.9	562.1	564.4	565.5	560.9
120°	616.6	622.4	623.6	623.6	619.0
122.5°	677.0	678.2	681.7	680.5	677.0
125°	730.4	737.4	738.6	736.2	735.1
127.5°	789.7	793.1	794.3	793.1	790.8
130°	841.9	847.7	850.0	848.9	846.6
132.5°	894.2	904.6	903.5	902.3	898.8
135°	949.9	956.9	958.0	958.0	953.4
137.5°	1002.2	1009.1	1011.5	1012.6	1006.8
140°	1052.1	1057.9	1061.4	1063.7	1057.9
142.5°	1102.0	1106.7	1111.3	1112.5	1106.7
145°	1150.8	1155.5	1158.9	1158.9	1155.5
147.5°	1196.1	1199.6	1201.9	1205.4	1196.1
150°	1241.4	1240.2	1244.9	1244.9	1242.6
152.5°	1278.6	1280.9	1282.0	1285.5	1280.9
155°	1316.9	1316.9	1318.0	1322.7	1316.9
157.5°	1351.7	1349.4	1350.5	1355.2	1347.1
160°	1381.9	1378.4	1379.6	1384.2	1378.4
162.5°	1408.6	1406.3	1406.3	1412.1	1405.1
165°	1431.8	1429.5	1430.7	1435.3	1428.4
167.5°	1452.7	1448.1	1448.1	1455.1	1448.1
170°	1469.0	1464.4	1464.4	1471.3	1463.2
172.5°	1480.6	1476.0	1476.0	1482.9	1476.0
175°	1488.7	1484.1	1484.1	1491.1	1482.9
177.5°	1494.5	1489.9	1488.7	1495.7	1487.6
180°	1492.2	1492.2	1492.2	1492.2	1492.2

(END OF REPORT)