

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910643

Luminaire Tested: DFN2DIP-HX2F0-040D020US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910643
REPORT IS A COMBINATION OF REPORTS P900675 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D020US850-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6587.5 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910643

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P910643

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		71
1	102	97	93	90	95	92	88	85	81	79	76		72	70	68		63
2	92	85	79	73	87	80	75	70	71	67	63		63	60	57		56
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49
4	77	66	58	52	72	63	55	50	56	50	45		50	45	41		44
5	71	59	51	44	67	56	48	43	50	44	39		45	40	36		40
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33
8	56	44	36	30	53	42	34	29	38	31	27		34	29	25		30
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4067	4067	4067
5°	4067	4000	4030
10°	4027	3937	3967
15°	3962	3862	3875
20°	3875	3763	3781
25°	3789	3646	3672
30°	3683	3536	3537
35°	3581	3408	3394
40°	3458	3278	3258
45°	3334	3148	3117
50°	3198	3011	2956
55°	3056	2853	2806
60°	2894	2666	2633
65°	2717	2471	2431
70°	2492	2234	2211
75°	2183	1950	1998
80°	1806	1586	1612
85°	1227	996	997

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3334 cd/sqm

TEST NUMBER: P910643

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.5
10°-20°	457.1	6.9
20°-30°	671.7	10.2
30°-40°	780.2	11.8
40°-50°	779.2	11.8
50°-60°	679.5	10.3
60°-70°	502.3	7.6
70°-80°	284.2	4.3
80°-90°	76.3	1.2
90°-100°	24.7	0.4
100°-110°	92.0	1.4
110°-120°	244.0	3.7
120°-130°	404.8	6.1
130°-140°	429.9	6.5
140°-150°	399.6	6.1
150°-160°	321.3	4.9
160°-170°	207.0	3.1
170°-180°	71.2	1.1
0°-30°	1291.3	19.6
0°-40°	2071.5	31.4
0°-60°	3530.2	53.6
0°-90°	4393.0	66.7
90°-120°	360.7	5.5
90°-150°	1595.0	24.2
90°-180°	2194.0	33.3
0°-180°	6587.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1726	1720	1701	1714	1711	164
15°	1643	1633	1612	1618	1610	463
25°	1487	1474	1446	1449	1446	684
35°	1283	1266	1240	1230	1222	801
45°	1044	1032	1007	989	983	806
55°	790	780	760	740	732	706
65°	533	523	506	491	483	527
75°	279	276	267	257	261	298
85°	68	66	65	60	58	76
90°	1	6	11	14	15	6
95°	35	17	21	24	23	42
105°	165	181	33	39	41	176
115°	311	321	334	83	44	307
125°	440	447	458	462	463	393
135°	545	554	558	564	563	421
145°	632	632	641	645	642	395
155°	696	691	698	701	697	321
165°	733	730	732	736	732	207
175°	750	746	748	751	746	71
180°	749	749	749	749	749	

TEST NUMBER: P910643

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1736.1	1727.8	1709.5	1726.0	1722.9
5°	1726.0	1719.5	1701.2	1714.4	1711.3
7.5°	1714.4	1704.5	1686.2	1699.7	1696.3
10°	1696.3	1684.7	1664.8	1678.0	1673.0
12.5°	1671.3	1661.4	1641.5	1649.9	1646.4
15°	1643.1	1633.2	1611.6	1618.3	1610.0
17.5°	1608.3	1598.4	1576.8	1585.0	1576.8
20°	1570.0	1560.1	1537.0	1541.8	1535.4
22.5°	1532.0	1517.0	1495.4	1495.4	1492.0
25°	1487.1	1473.9	1445.7	1448.9	1445.7
27.5°	1437.3	1425.6	1404.2	1399.2	1391.0
30°	1387.6	1374.3	1349.4	1344.4	1337.8
32.5°	1334.5	1324.6	1298.0	1288.0	1281.2
35°	1283.0	1266.5	1239.9	1229.9	1221.6
37.5°	1224.9	1209.9	1183.3	1171.8	1163.5
40°	1165.2	1151.8	1125.2	1110.4	1103.8
42.5°	1107.1	1093.7	1067.3	1050.6	1040.7
45°	1044.0	1032.5	1007.4	989.3	982.6
47.5°	982.6	970.9	944.4	926.1	916.3
50°	917.8	909.5	886.3	863.0	854.7
52.5°	854.7	843.2	821.7	803.4	791.7
55°	790.2	780.1	760.2	740.3	732.1
57.5°	725.3	717.1	695.3	675.5	668.8
60°	660.5	654.0	630.8	612.5	607.5
62.5°	597.5	585.9	569.4	552.7	546.1
65°	532.9	522.8	506.3	491.3	483.1
67.5°	466.4	458.0	443.3	431.6	425.0
70°	405.0	398.4	383.4	371.7	365.2
72.5°	342.0	335.3	327.0	315.4	310.4
75°	278.8	275.6	267.2	257.3	260.6
77.5°	222.4	215.7	212.4	207.4	202.5
80°	166.0	164.2	160.9	156.0	152.7
82.5°	112.9	112.9	111.3	104.6	104.6
85°	68.0	66.4	64.8	59.7	58.1
87.5°	29.9	26.6	23.3	18.3	16.5
90°	0.6	6.5	10.8	13.5	14.6
92.5°	13.5	11.4	13.0	14.1	14.6
95°	35.2	17.3	21.1	23.8	23.3
97.5°	63.3	19.0	27.6	29.3	29.8
100°	95.9	21.6	30.8	35.2	36.3
102.5°	131.6	130.5	31.9	37.9	39.6
105°	164.7	180.9	33.0	38.9	41.1
107.5°	203.2	216.6	34.2	40.0	42.3
110°	240.0	251.3	94.8	40.7	42.8



TEST NUMBER: P910643

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.6	284.3	275.1	41.7	43.4
115°	311.4	320.6	334.3	83.4	44.5
117.5°	343.3	354.2	363.4	286.0	144.1
120°	379.2	387.3	397.0	403.6	330.4
122.5°	409.4	418.1	429.0	432.2	432.8
125°	440.4	447.4	457.7	461.5	463.1
127.5°	468.6	476.1	484.3	489.6	490.2
130°	495.1	503.7	509.7	515.7	515.1
132.5°	522.1	529.2	535.1	540.0	539.5
135°	545.0	553.6	558.4	563.9	562.8
137.5°	568.7	575.2	580.7	586.1	584.4
140°	592.0	596.4	602.3	607.2	604.5
142.5°	611.5	615.4	622.4	626.7	623.9
145°	632.1	631.6	640.8	644.6	641.9
147.5°	650.0	648.3	657.5	660.2	658.1
150°	667.3	663.5	672.2	675.4	672.7
152.5°	681.9	677.6	685.7	689.0	685.1
155°	696.0	691.1	697.7	700.9	696.6
157.5°	707.4	703.1	708.0	711.8	707.4
160°	717.2	713.9	717.2	720.4	716.6
162.5°	725.7	722.5	725.3	729.1	724.2
165°	733.4	730.2	731.7	735.6	731.7
167.5°	739.4	736.0	737.7	741.6	736.6
170°	744.2	740.9	742.0	745.8	740.9
172.5°	747.5	744.2	745.4	749.1	744.2
175°	750.1	746.4	747.5	751.2	745.8
177.5°	751.2	747.5	748.0	751.8	746.9
180°	748.6	748.6	748.6	748.6	748.6

TEST NUMBER: P910643

CATALOG NUMBER: DFN2DIP-HX2F0-040D020US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.42	14.46	14.22	15.28	16.29	13.00	14.03	13.80	14.86	15.87
	3H	15.07	16.00	15.88	16.83	17.87	14.61	15.54	15.42	16.37	17.41
	4H	15.65	16.53	16.48	17.37	18.42	15.19	16.07	16.02	16.91	17.96
	6H	16.04	16.85	16.88	17.69	18.76	15.58	16.39	16.42	17.24	18.30
	8H	16.14	16.91	16.99	17.77	18.84	15.68	16.45	16.53	17.32	18.38
	12H	16.18	16.92	17.04	17.78	18.87	15.72	16.46	16.58	17.32	18.41
4H	2H	13.89	14.77	14.73	15.61	16.66	13.56	14.43	14.39	15.27	16.32
	3H	15.75	16.48	16.59	17.35	18.42	15.36	16.10	16.21	16.97	18.04
	4H	16.45	17.12	17.31	17.99	19.08	16.05	16.72	16.91	17.59	18.69
	6H	16.95	17.53	17.82	18.42	19.52	16.55	17.13	17.43	18.03	19.12
	8H	17.09	17.63	17.97	18.52	19.63	16.69	17.23	17.57	18.12	19.23
	12H	17.16	17.65	18.06	18.56	19.67	16.76	17.24	17.65	18.15	19.27
8H	4H	16.65	17.19	17.53	18.08	19.19	16.30	16.84	17.17	17.72	18.84
	6H	17.26	17.70	18.16	18.63	19.74	16.91	17.35	17.81	18.28	19.39
	8H	17.46	17.86	18.38	18.78	19.91	17.11	17.50	18.02	18.43	19.55
	12H	17.59	17.93	18.50	18.85	20.03	17.22	17.57	18.14	18.48	19.66
12H	4H	16.64	17.13	17.54	18.03	19.15	16.30	16.78	17.19	17.69	18.81
	6H	17.28	17.68	18.20	18.60	19.73	16.94	17.34	17.86	18.26	19.39
	8H	17.51	17.86	18.43	18.78	19.96	17.17	17.52	18.09	18.43	19.61