

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007865

Luminaire Tested: S125IP-B610UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B610UB2750-4F0-XX-W2A-1_4000K
Description: Define 5 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2040.0 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007865

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007865

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007865

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.1	0.1
90°-100°	48.6	2.4
100°-110°	144.3	7.1
110°-120°	244.8	12.0
120°-130°	322.2	15.8
130°-140°	361.1	17.7
140°-150°	353.9	17.3
150°-160°	297.3	14.6
160°-170°	197.6	9.7
170°-180°	69.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.1	0.1
90°-120°	437.7	21.5
90°-150°	1474.8	72.3
90°-180°	2039.0	100.0
0°-180°	2040.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	9	12	14	3
95°	37	38	44	48	49	39
105°	130	132	136	139	141	138
115°	245	247	248	248	247	242
125°	358	361	362	360	360	320
135°	465	468	469	469	467	358
145°	563	566	567	567	566	352
155°	645	645	645	648	645	297
165°	701	700	700	703	699	198
175°	729	727	727	730	726	69
180°	730	730	730	730	730	

TEST NUMBER: P1007865

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	5.1	9.1	11.9	13.6
92.5°	17.1	19.9	25.0	29.0	30.1
95°	37.0	38.1	43.8	47.8	48.9
97.5°	56.9	57.4	65.4	68.8	69.4
100°	79.6	79.6	87.0	92.1	93.2
102.5°	104.0	106.9	109.7	115.4	117.1
105°	129.6	132.5	135.9	139.3	141.0
107.5°	157.5	160.3	163.2	164.9	164.9
110°	186.5	189.3	191.0	192.7	192.2

TEST NUMBER: P1007865

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	216.0	217.2	219.4	220.0	218.9
115°	245.0	247.3	248.4	247.9	247.3
117.5°	274.6	275.2	276.3	276.9	274.6
120°	301.9	304.7	305.3	305.3	303.0
122.5°	331.4	332.0	333.7	333.1	331.4
125°	357.6	361.0	361.6	360.4	359.9
127.5°	386.6	388.3	388.9	388.3	387.2
130°	412.2	415.0	416.1	415.6	414.4
132.5°	437.8	442.9	442.3	441.7	440.0
135°	465.0	468.5	469.0	469.0	466.7
137.5°	490.6	494.0	495.2	495.7	492.9
140°	515.1	517.9	519.6	520.8	517.9
142.5°	539.5	541.8	544.1	544.6	541.8
145°	563.4	565.7	567.4	567.4	565.7
147.5°	585.6	587.3	588.4	590.1	585.6
150°	607.7	607.2	609.4	609.4	608.3
152.5°	625.9	627.1	627.6	629.3	627.1
155°	644.7	644.7	645.3	647.5	644.7
157.5°	661.7	660.6	661.2	663.5	659.5
160°	676.5	674.8	675.4	677.7	674.8
162.5°	689.6	688.5	688.5	691.3	687.9
165°	701.0	699.8	700.4	702.7	699.3
167.5°	711.2	708.9	708.9	712.3	708.9
170°	719.2	716.9	716.9	720.3	716.3
172.5°	724.8	722.6	722.6	726.0	722.6
175°	728.8	726.6	726.6	730.0	726.0
177.5°	731.7	729.4	728.8	732.2	728.3
180°	730.5	730.5	730.5	730.5	730.5

(END OF REPORT)