

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007873

Luminaire Tested: S125IP-B610UB2750-4F0-XX-W2A_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007873
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B610UB2750-4F0-XX-W2A_3000K
Description: Define 5 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2370.0 lumens
Efficiency: N/A
Efficacy: 153.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007873

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007873

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007873

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.1	0.0
90°-100°	26.2	1.1
100°-110°	174.1	7.3
110°-120°	313.4	13.2
120°-130°	402.3	17.0
130°-140°	432.7	18.3
140°-150°	406.1	17.1
150°-160°	328.5	13.9
160°-170°	212.4	9.0
170°-180°	73.3	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.1	0.0
90°-120°	513.6	21.7
90°-150°	1754.7	74.0
90°-180°	2369.0	100.0
0°-180°	2370.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	9	12	14	2
95°	33	31	9	12	12	40
105°	168	170	170	170	170	178
115°	316	318	319	317	313	313
125°	449	453	453	450	449	401
135°	560	563	562	561	557	431
145°	649	650	650	650	647	406
155°	715	711	712	714	709	329
165°	754	751	751	755	750	213
175°	771	768	768	773	768	73
180°	771	771	771	771	771	

TEST NUMBER: P1007873

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	5.1	9.1	12.0	13.7
92.5°	10.9	5.7	9.1	12.0	12.6
95°	32.6	30.9	9.1	12.0	12.0
97.5°	61.2	64.6	10.3	11.4	12.0
100°	95.5	97.2	99.5	14.3	12.0
102.5°	130.3	132.6	133.8	134.9	86.9
105°	168.1	170.4	170.4	170.4	169.8
107.5°	206.9	206.9	208.1	208.7	206.4
110°	244.7	244.7	245.8	244.1	244.7

TEST NUMBER: P1007873

CATALOG NUMBER: S125IP-B610UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	280.1	281.8	282.4	280.1	279.0
115°	315.6	318.4	319.0	316.7	313.3
117.5°	352.7	352.7	355.0	351.6	350.4
120°	387.0	386.4	388.2	387.0	384.2
122.5°	417.3	420.2	420.7	419.6	416.2
125°	448.8	452.8	452.8	450.5	448.8
127.5°	479.0	481.9	481.3	480.2	475.6
130°	506.5	509.3	509.9	508.2	505.3
132.5°	533.9	537.4	535.6	535.6	532.8
135°	559.7	563.1	561.9	560.8	557.4
137.5°	583.7	587.1	585.9	585.9	583.1
140°	607.1	608.2	607.7	608.8	605.4
142.5°	628.3	628.8	630.0	630.0	626.5
145°	648.8	650.0	650.0	650.5	647.1
147.5°	667.1	667.1	667.7	668.3	664.3
150°	684.3	683.1	684.3	685.4	680.8
152.5°	700.9	698.0	699.1	700.3	696.3
155°	714.6	711.1	712.3	714.0	709.4
157.5°	725.4	723.7	723.7	725.4	720.9
160°	736.9	733.4	734.0	736.3	731.7
162.5°	746.0	742.6	743.2	746.6	741.4
165°	754.0	750.6	751.2	754.6	750.0
167.5°	760.3	756.9	757.4	761.4	756.3
170°	765.4	761.4	762.0	766.6	761.4
172.5°	768.9	764.9	766.0	770.0	764.9
175°	771.2	767.7	768.3	772.9	767.7
177.5°	772.9	769.5	770.0	774.0	769.5
180°	771.2	771.2	771.2	771.2	771.2

(END OF REPORT)