

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P908280

Luminaire Tested: DFN2DIP-HX4F0-110D100US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P908280
REPORT IS A COMBINATION OF REPORTS P899421 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D100US840-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19934.7 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 170
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P908280

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P908280

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51
2	90	83	76	71	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	45	40	37	38	34	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	30	28
6	64	51	43	37	59	48	41	36	42	36	32	36	32	28	31	27	24
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3214	3214	3214
5°	3219	3169	3191
10°	3194	3127	3148
15°	3147	3076	3080
20°	3084	3005	3011
25°	3021	2920	2932
30°	2942	2840	2830
35°	2867	2747	2723
40°	2775	2652	2621
45°	2684	2557	2516
50°	2583	2458	2395
55°	2478	2343	2284
60°	2360	2206	2157
65°	2231	2066	2007
70°	2066	1893	1845
75°	1838	1687	1696
80°	1564	1425	1411
85°	1135	971	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2684 cd/sqm

TEST NUMBER: P908280

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.8	2.0
10°-20°	1144.7	5.7
20°-30°	1682.2	8.4
30°-40°	1953.7	9.8
40°-50°	1951.3	9.8
50°-60°	1701.5	8.5
60°-70°	1257.8	6.3
70°-80°	711.6	3.6
80°-90°	196.9	1.0
90°-100°	197.6	1.0
100°-110°	627.9	3.1
110°-120°	1074.6	5.4
120°-130°	1413.3	7.1
130°-140°	1586.4	8.0
140°-150°	1555.6	7.8
150°-160°	1304.9	6.5
160°-170°	865.4	4.3
170°-180°	302.5	1.5
0°-30°	3233.7	16.2
0°-40°	5187.4	26.0
0°-60°	8840.2	44.3
0°-90°	11006.5	55.2
90°-120°	1900.2	9.5
90°-150°	6455.4	32.4
90°-180°	8928.0	44.8
0°-180°	19934.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4322	4322	4322	4322	4322	
5°	4322	4306	4260	4293	4285	410
15°	4115	4090	4036	4052	4032	1159
25°	3724	3691	3620	3628	3620	1714
35°	3213	3172	3105	3080	3059	2006
45°	2614	2585	2523	2477	2461	2018
55°	1979	1954	1904	1854	1833	1769
65°	1334	1309	1268	1230	1210	1319
75°	698	690	669	644	653	745
85°	170	166	162	150	146	190
90°	3	35	94	89	92	19
95°	141	168	172	172	168	156
105°	580	587	593	598	598	612
115°	1078	1094	1089	1086	1078	1067
125°	1568	1593	1585	1576	1573	1402
135°	2029	2059	2064	2062	2054	1568
145°	2463	2482	2498	2500	2490	1539
155°	2816	2824	2833	2846	2838	1296
165°	3064	3061	3061	3080	3067	864
175°	3188	3180	3175	3194	3177	303
180°	3194	3194	3194	3194	3194	



TEST NUMBER: P908280

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4322.4	4322.4	4322.4	4322.4	4322.4
2.5°	4347.5	4326.8	4280.9	4322.4	4314.4
5°	4322.4	4306.1	4260.2	4293.2	4285.4
7.5°	4293.2	4268.6	4222.8	4256.3	4247.9
10°	4247.9	4218.7	4168.9	4201.9	4189.6
12.5°	4185.3	4160.5	4110.8	4131.5	4123.1
15°	4114.7	4090.0	4035.7	4052.5	4031.8
17.5°	4027.3	4002.7	3948.5	3969.2	3948.5
20°	3931.7	3907.0	3848.8	3861.1	3844.9
22.5°	3836.5	3798.9	3744.7	3744.7	3736.3
25°	3724.0	3691.0	3620.4	3628.3	3620.4
27.5°	3599.2	3570.1	3516.3	3503.9	3483.2
30°	3474.8	3441.3	3379.1	3366.8	3350.0
32.5°	3341.6	3317.0	3250.4	3225.2	3208.4
35°	3212.9	3171.5	3104.8	3079.7	3059.0
37.5°	3067.4	3029.9	2963.3	2934.2	2913.5
40°	2917.9	2884.4	2817.8	2780.8	2764.0
42.5°	2772.4	2738.9	2672.7	2630.8	2606.2
45°	2614.5	2585.4	2522.7	2477.4	2460.6
47.5°	2460.6	2431.6	2364.9	2319.1	2294.3
50°	2298.4	2277.7	2219.4	2161.2	2140.5
52.5°	2140.5	2111.3	2057.6	2011.7	1982.6
55°	1978.6	1953.5	1903.7	1853.8	1833.1
57.5°	1816.3	1795.6	1741.4	1691.5	1674.8
60°	1654.1	1637.8	1579.5	1533.7	1521.4
62.5°	1496.2	1467.1	1425.6	1384.2	1367.5
65°	1334.3	1309.2	1267.8	1230.3	1209.6
67.5°	1168.1	1147.0	1109.9	1080.9	1064.1
70°	1014.2	997.4	960.0	930.9	914.5
72.5°	856.4	839.6	818.9	789.8	777.4
75°	698.0	690.1	668.9	644.3	652.7
77.5°	556.9	540.2	531.8	519.5	507.2
80°	415.9	411.4	403.0	390.7	382.3
82.5°	282.7	282.7	278.7	262.0	262.0
85°	170.3	166.2	162.3	149.5	145.5
87.5°	74.9	66.6	58.2	45.8	41.4
90°	2.9	34.6	94.3	88.6	91.5
92.5°	59.7	80.9	83.8	86.6	86.6
95°	140.6	167.5	172.4	172.4	167.5
97.5°	234.0	259.0	269.6	269.6	269.6
100°	341.8	364.0	371.6	371.6	368.8
102.5°	455.4	471.8	482.4	485.2	482.4
105°	579.7	587.3	593.1	597.9	597.9
107.5°	702.9	714.5	714.5	716.4	702.9
110°	822.3	837.7	837.7	837.7	830.0

TEST NUMBER: P908280

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	951.3	967.7	964.8	957.0	951.3
115°	1078.4	1093.8	1089.0	1086.1	1078.4
117.5°	1204.6	1225.8	1212.2	1204.6	1196.8
120°	1331.6	1352.8	1331.6	1331.6	1323.0
122.5°	1447.1	1474.1	1460.7	1453.0	1447.1
125°	1568.5	1592.6	1584.9	1576.2	1573.4
127.5°	1687.0	1716.8	1706.2	1694.7	1687.0
130°	1797.7	1832.3	1827.6	1821.7	1811.2
132.5°	1921.9	1948.8	1950.8	1937.3	1929.6
135°	2028.7	2058.6	2064.4	2061.5	2053.8
137.5°	2148.2	2172.2	2177.1	2175.1	2163.5
140°	2253.1	2277.1	2290.7	2290.7	2280.1
142.5°	2361.0	2385.0	2392.7	2395.6	2385.0
145°	2463.0	2482.2	2497.7	2500.5	2489.9
147.5°	2554.5	2578.6	2590.1	2595.0	2584.3
150°	2648.9	2665.2	2675.8	2684.4	2675.8
152.5°	2732.6	2749.0	2762.5	2773.1	2762.5
155°	2816.4	2824.1	2832.8	2846.2	2837.5
157.5°	2888.6	2894.4	2899.2	2918.4	2905.0
160°	2953.1	2958.9	2961.7	2978.1	2966.6
162.5°	3012.8	3012.8	3015.7	3033.9	3020.5
165°	3063.8	3060.9	3060.9	3080.2	3066.8
167.5°	3110.1	3101.4	3101.4	3120.7	3107.2
170°	3144.7	3137.0	3134.1	3153.4	3137.0
172.5°	3168.8	3161.1	3158.2	3177.4	3161.1
175°	3188.0	3180.4	3174.6	3193.8	3177.4
177.5°	3198.6	3191.0	3185.1	3201.5	3185.1
180°	3193.8	3193.8	3193.8	3193.8	3193.8

TEST NUMBER: P908280

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.80	12.71	12.71	13.64	14.83	11.36	12.27	12.27	13.20	14.40
	3H	13.46	14.28	14.38	15.22	16.44	12.99	13.80	13.91	14.74	15.96
	4H	14.05	14.82	14.99	15.77	17.00	13.58	14.35	14.52	15.29	16.52
	6H	14.45	15.17	15.40	16.12	17.36	13.98	14.69	14.93	15.64	16.88
	8H	14.56	15.24	15.52	16.21	17.45	14.09	14.76	15.04	15.73	16.97
	12H	14.61	15.26	15.57	16.22	17.48	14.13	14.78	15.09	15.74	17.00
4H	2H	12.26	13.04	13.21	13.98	15.21	11.92	12.69	12.86	13.64	14.86
	3H	14.14	14.78	15.09	15.76	17.00	13.74	14.39	14.70	15.36	16.60
	4H	14.85	15.44	15.82	16.41	17.68	14.45	15.04	15.41	16.01	17.27
	6H	15.37	15.88	16.35	16.87	18.14	14.96	15.47	15.94	16.46	17.73
	8H	15.52	16.00	16.50	16.98	18.26	15.11	15.59	16.09	16.57	17.85
	12H	15.60	16.03	16.60	17.03	18.32	15.18	15.61	16.17	16.61	17.89
8H	4H	15.05	15.53	16.03	16.51	17.80	14.69	15.17	15.67	16.15	17.43
	6H	15.69	16.08	16.69	17.11	18.39	15.33	15.72	16.33	16.75	18.02
	8H	15.91	16.26	16.92	17.27	18.57	15.54	15.89	16.55	16.90	18.20
	12H	16.05	16.35	17.06	17.36	18.70	15.66	15.97	16.68	16.98	18.32
12H	4H	15.04	15.47	16.04	16.47	17.76	14.69	15.12	15.69	16.12	17.41
	6H	15.72	16.07	16.73	17.08	18.38	15.37	15.71	16.38	16.73	18.03
	8H	15.96	16.27	16.98	17.28	18.62	15.61	15.91	16.62	16.92	18.26