

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928198

Luminaire Tested: DFN2DIP-HX4F0-040D110US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928198
REPORT IS A COMBINATION OF REPORTS P900946 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11317.7 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 120.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928198

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928198

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	20	19	18
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	974	974	974
5°	975	958	964
10°	966	940	933
15°	952	909	884
20°	935	866	825
25°	917	818	768
30°	893	769	695
35°	869	716	631
40°	845	661	557
45°	817	601	491
50°	788	539	426
55°	758	474	363
60°	723	406	299
65°	683	336	269
70°	635	271	244
75°	574	239	222
80°	485	201	193
85°	339	135	145

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1509 cd/sqm

TEST NUMBER: P928198

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	1.1
10°-20°	336.9	3.0
20°-30°	473.0	4.2
30°-40°	515.5	4.6
40°-50°	473.8	4.2
50°-60°	372.1	3.3
60°-70°	242.2	2.1
70°-80°	124.7	1.1
80°-90°	37.0	0.3
90°-100°	96.9	0.9
100°-110°	361.4	3.2
110°-120°	958.5	8.5
120°-130°	1589.8	14.0
130°-140°	1688.7	14.9
140°-150°	1569.5	13.9
150°-160°	1261.8	11.1
160°-170°	813.1	7.2
170°-180°	279.9	2.5
0°-30°	932.5	8.2
0°-40°	1448.1	12.8
0°-60°	2294.1	20.3
0°-90°	2698.0	23.8
90°-120°	1416.9	12.5
90°-150°	6264.9	55.4
90°-180°	8620.0	76.2
0°-180°	11317.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1309	1309	1309	1309	1309	
5°	1309	1303	1288	1299	1295	124
15°	1245	1232	1192	1170	1158	351
25°	1130	1092	1014	966	948	520
35°	974	914	809	735	708	610
45°	796	717	592	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	2	26	42	53	57	10
95°	138	68	83	94	92	164
105°	647	711	130	153	162	691
115°	1223	1259	1313	328	175	1204
125°	1730	1757	1798	1813	1819	1543
135°	2140	2174	2193	2215	2211	1653
145°	2483	2481	2517	2532	2521	1553
155°	2734	2715	2740	2753	2736	1260
165°	2881	2868	2874	2889	2874	814
175°	2946	2932	2936	2951	2930	280
180°	2940	2940	2940	2940	2940	

TEST NUMBER: P928198

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.3	1309.3	1309.3	1309.3	1309.3
2.5°	1315.3	1309.3	1296.3	1308.2	1305.8
5°	1309.3	1303.4	1288.0	1298.6	1295.2
7.5°	1298.6	1291.6	1275.0	1279.6	1273.8
10°	1284.5	1276.1	1252.5	1248.8	1241.9
12.5°	1266.7	1256.0	1224.0	1216.9	1203.8
15°	1245.3	1232.3	1192.0	1169.5	1157.7
17.5°	1220.5	1201.5	1151.6	1125.7	1106.7
20°	1192.0	1168.3	1109.0	1079.5	1053.4
22.5°	1161.2	1134.0	1065.2	1024.9	1007.3
25°	1130.4	1092.5	1014.2	965.8	947.9
27.5°	1093.8	1053.4	966.9	911.2	883.9
30°	1054.6	1009.5	914.7	854.3	822.3
32.5°	1016.7	962.1	865.0	793.9	764.2
35°	974.1	913.6	809.3	734.7	708.5
37.5°	932.6	867.3	757.2	675.3	645.8
40°	888.7	817.7	702.7	618.6	587.7
42.5°	843.6	767.8	648.2	560.4	530.9
45°	796.3	716.8	592.5	508.3	479.9
47.5°	751.3	667.2	539.2	455.0	428.9
50°	701.5	617.4	487.0	405.2	380.4
52.5°	652.8	564.0	437.3	359.0	336.5
55°	605.5	513.1	385.1	314.0	291.5
57.5°	556.9	462.1	338.9	272.5	253.6
60°	507.1	412.3	290.3	229.9	211.0
62.5°	458.6	363.8	248.8	192.0	182.6
65°	408.8	312.8	206.2	165.9	162.3
67.5°	361.5	265.4	165.9	145.7	142.2
70°	311.7	219.2	137.4	125.6	120.8
72.5°	264.3	176.5	114.9	105.5	103.1
75°	218.0	135.0	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.7	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	2.1	25.5	42.5	53.3	57.3
92.5°	53.3	44.7	51.0	55.4	57.3
95°	138.2	68.0	82.8	93.7	91.5
97.5°	248.8	74.5	108.3	114.9	117.0
100°	376.7	85.1	121.3	138.2	142.5
102.5°	516.9	512.8	125.5	148.8	155.4
105°	646.7	710.7	129.9	153.1	161.7
107.5°	797.9	850.8	134.2	157.4	166.0
110°	942.6	987.1	372.4	159.7	168.0

TEST NUMBER: P928198

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1078.8	1116.9	1080.8	163.7	170.3
115°	1223.2	1259.4	1312.7	327.7	174.6
117.5°	1348.9	1391.3	1427.7	1123.2	565.9
120°	1489.3	1521.1	1559.5	1585.0	1297.8
122.5°	1608.3	1642.4	1685.1	1697.7	1700.0
125°	1729.6	1757.4	1797.8	1812.7	1819.0
127.5°	1840.2	1870.0	1902.1	1923.3	1925.4
130°	1944.5	1978.7	2001.9	2025.4	2023.4
132.5°	2050.9	2078.7	2102.0	2121.1	2119.2
135°	2140.4	2174.4	2193.4	2214.9	2210.6
137.5°	2233.8	2259.3	2280.8	2302.0	2295.7
140°	2325.3	2342.4	2365.7	2384.9	2374.3
142.5°	2402.1	2416.9	2444.5	2461.5	2450.8
145°	2482.9	2480.6	2516.7	2531.7	2521.1
147.5°	2552.9	2546.6	2582.7	2593.3	2585.0
150°	2621.1	2606.2	2640.3	2653.0	2642.3
152.5°	2678.5	2661.5	2693.4	2706.3	2691.4
155°	2733.8	2714.8	2740.3	2753.0	2736.0
157.5°	2778.5	2761.5	2780.8	2795.7	2778.5
160°	2816.9	2804.0	2816.9	2829.5	2814.6
162.5°	2850.7	2838.1	2848.7	2863.6	2844.5
165°	2880.6	2867.9	2874.2	2889.1	2874.2
167.5°	2904.0	2891.2	2897.8	2912.7	2893.5
170°	2923.3	2910.4	2914.6	2929.6	2910.4
172.5°	2935.9	2923.3	2927.5	2942.4	2923.3
175°	2946.5	2931.6	2935.9	2950.8	2929.6
177.5°	2950.8	2935.9	2938.2	2953.1	2933.9
180°	2940.2	2940.2	2940.2	2940.2	2940.2

TEST NUMBER: P928198

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.89	4.55	5.05	5.69	7.29	0.00	0.52	1.02	1.66	3.27
	3H	5.56	6.14	6.72	7.29	8.91	1.04	1.63	2.21	2.78	4.40
	4H	6.16	6.72	7.33	7.86	9.49	1.49	2.04	2.66	3.19	4.81
	6H	6.57	7.08	7.75	8.24	9.87	1.80	2.31	2.98	3.46	5.10
	8H	6.69	7.18	7.88	8.35	9.97	1.89	2.37	3.07	3.54	5.16
	12H	6.75	7.21	7.94	8.37	10.02	1.93	2.39	3.11	3.55	5.19
4H	2H	3.89	4.45	5.07	5.60	7.22	0.44	1.00	1.62	2.15	3.77
	3H	5.70	6.17	6.89	7.34	8.98	1.78	2.24	2.96	3.41	5.05
	4H	6.39	6.82	7.58	7.98	9.63	2.32	2.75	3.51	3.91	5.56
	6H	6.90	7.26	8.09	8.45	10.09	2.73	3.09	3.92	4.28	5.92
	8H	7.07	7.41	8.26	8.59	10.25	2.86	3.20	4.05	4.37	6.03
	12H	7.16	7.47	8.36	8.65	10.32	2.92	3.22	4.12	4.41	6.08
8H	4H	6.35	6.69	7.53	7.86	9.52	2.59	2.93	3.78	4.10	5.76
	6H	6.91	7.19	8.11	8.41	10.06	3.10	3.38	4.31	4.60	6.26
	8H	7.12	7.37	8.34	8.56	10.24	3.29	3.54	4.51	4.73	6.41
	12H	7.26	7.47	8.47	8.66	10.37	3.41	3.62	4.62	4.81	6.52
12H	4H	6.29	6.60	7.49	7.79	9.45	2.58	2.89	3.79	4.08	5.74
	6H	6.88	7.12	8.09	8.32	10.00	3.15	3.39	4.36	4.59	6.27
	8H	7.10	7.31	8.31	8.50	10.21	3.35	3.57	4.57	4.76	6.47

END OF REPORT