

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928814

Luminaire Tested: DFN2DIP-HX4F0-120D120US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928814
REPORT IS A COMBINATION OF REPORTS P900980 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D120US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17995.3 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 222.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928814

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928814

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3006	3006	3006
5°	3011	2958	2977
10°	2981	2900	2880
15°	2940	2805	2731
20°	2886	2673	2547
25°	2831	2525	2370
30°	2756	2373	2145
35°	2684	2210	1947
40°	2609	2042	1720
45°	2523	1854	1515
50°	2434	1665	1314
55°	2341	1463	1121
60°	2234	1252	923
65°	2110	1037	831
70°	1960	837	752
75°	1771	738	685
80°	1499	620	594
85°	1048	415	448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2523 cd/sqm

TEST NUMBER: P928814

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.8	2.1
10°-20°	1040.0	5.8
20°-30°	1460.1	8.1
30°-40°	1591.6	8.8
40°-50°	1462.8	8.1
50°-60°	1148.8	6.4
60°-70°	747.8	4.2
70°-80°	384.9	2.1
80°-90°	104.1	0.6
90°-100°	108.8	0.6
100°-110°	405.7	2.3
110°-120°	1076.0	6.0
120°-130°	1784.7	9.9
130°-140°	1895.8	10.5
140°-150°	1761.9	9.8
150°-160°	1416.5	7.9
160°-170°	912.8	5.1
170°-180°	314.2	1.7
0°-30°	2878.9	16.0
0°-40°	4470.4	24.8
0°-60°	7082.1	39.4
0°-90°	8318.8	46.2
90°-120°	1590.6	8.8
90°-150°	7033.0	39.1
90°-180°	9676.0	53.8
0°-180°	17995.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4042	4042	4042	4042	4042	
5°	4042	4024	3976	4009	3998	383
15°	3844	3804	3680	3610	3574	1083
25°	3490	3373	3131	2981	2926	1605
35°	3007	2820	2498	2268	2187	1882
45°	2458	2213	1829	1569	1481	1898
55°	1869	1584	1189	969	900	1670
65°	1262	966	636	512	501	1251
75°	673	417	293	267	264	712
85°	157	80	69	69	69	180
90°	2	29	48	60	64	17
95°	155	76	93	105	103	184
105°	726	798	146	172	182	776
115°	1373	1414	1474	368	196	1352
125°	1942	1973	2018	2035	2042	1732
135°	2403	2441	2462	2486	2482	1856
145°	2787	2785	2825	2842	2830	1743
155°	3069	3048	3076	3090	3072	1414
165°	3234	3220	3227	3243	3227	914
175°	3308	3291	3296	3313	3289	315
180°	3301	3301	3301	3301	3301	

TEST NUMBER: P928814

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-RLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4042.1	4042.1	4042.1	4042.1	4042.1
2.5°	4060.3	4042.1	4001.7	4038.6	4031.2
5°	4042.1	4023.8	3976.1	4009.1	3998.2
7.5°	4009.1	3987.3	3936.1	3950.5	3932.2
10°	3965.2	3939.6	3866.6	3855.4	3833.7
12.5°	3910.5	3877.5	3778.5	3756.8	3716.5
15°	3844.5	3804.2	3680.0	3610.4	3574.0
17.5°	3767.7	3709.1	3555.4	3475.1	3416.5
20°	3680.0	3606.6	3423.8	3332.6	3251.8
22.5°	3584.9	3500.7	3288.4	3164.2	3109.5
25°	3489.8	3372.6	3131.1	2981.4	2926.3
27.5°	3376.5	3251.8	2984.9	2813.0	2728.7
30°	3255.8	3116.5	2823.8	2637.5	2538.6
32.5°	3138.6	2970.1	2670.5	2450.9	2359.3
35°	3007.0	2820.3	2498.5	2268.1	2187.3
37.5°	2878.9	2677.5	2337.5	2084.9	1993.7
40°	2743.5	2524.2	2169.1	1909.5	1814.4
42.5°	2604.5	2370.5	2001.1	1730.2	1639.0
45°	2458.2	2213.0	1829.1	1569.1	1481.3
47.5°	2319.2	2059.7	1664.6	1404.6	1324.2
50°	2165.6	1906.0	1503.5	1250.9	1174.4
52.5°	2015.4	1741.0	1349.8	1108.4	1039.0
55°	1869.1	1583.9	1188.8	969.4	900.0
57.5°	1719.2	1426.7	1046.3	841.4	782.8
60°	1565.6	1272.9	896.1	709.9	651.3
62.5°	1415.8	1123.2	768.1	592.7	563.5
65°	1262.1	965.6	636.5	512.3	501.1
67.5°	1115.8	819.2	512.3	449.8	439.0
70°	962.1	676.9	424.2	387.7	372.9
72.5°	815.8	544.9	354.7	325.6	318.3
75°	672.9	416.8	292.7	267.0	263.5
77.5°	530.6	296.1	230.6	215.8	208.4
80°	398.6	212.3	175.4	161.0	161.0
82.5°	277.9	142.8	120.7	113.3	113.3
85°	157.2	80.4	69.4	69.4	69.4
87.5°	58.6	29.1	29.1	25.6	25.6
90°	2.3	28.6	47.7	59.8	64.4
92.5°	59.8	50.2	57.3	62.1	64.4
95°	155.1	76.3	93.0	105.2	102.7
97.5°	279.4	83.7	121.7	129.0	131.3
100°	422.8	95.6	136.1	155.1	160.0
102.5°	580.3	575.7	140.9	167.1	174.4
105°	726.0	797.8	145.8	171.9	181.5
107.5°	895.6	955.2	150.6	176.7	186.3
110°	1058.1	1108.1	418.0	179.2	188.6

TEST NUMBER: P928814

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1211.0	1253.8	1213.3	183.8	191.1
115°	1373.2	1413.8	1473.6	367.8	196.0
117.5°	1514.2	1561.9	1602.7	1260.9	635.3
120°	1671.9	1707.6	1750.7	1779.4	1456.9
122.5°	1805.5	1843.8	1891.7	1905.9	1908.4
125°	1941.6	1972.8	2018.2	2034.9	2042.0
127.5°	2065.8	2099.3	2135.3	2159.1	2161.4
130°	2182.9	2221.2	2247.3	2273.7	2271.4
132.5°	2302.3	2333.5	2359.6	2381.2	2378.9
135°	2402.7	2441.0	2462.3	2486.4	2481.6
137.5°	2507.7	2536.3	2560.4	2584.2	2577.1
140°	2610.4	2629.6	2655.7	2677.3	2665.4
142.5°	2696.5	2713.3	2744.2	2763.2	2751.3
145°	2787.3	2784.8	2825.3	2842.1	2830.1
147.5°	2865.9	2858.8	2899.4	2911.3	2901.9
150°	2942.4	2925.7	2964.0	2978.2	2966.3
152.5°	3006.8	2987.8	3023.6	3038.0	3021.3
155°	3068.9	3047.6	3076.3	3090.5	3071.5
157.5°	3119.1	3100.1	3121.7	3138.4	3119.1
160°	3162.2	3147.8	3162.2	3176.4	3159.7
162.5°	3200.3	3186.1	3198.0	3214.7	3193.2
165°	3233.7	3219.5	3226.6	3243.4	3226.6
167.5°	3260.1	3245.6	3253.0	3269.7	3248.2
170°	3281.6	3267.2	3272.0	3288.7	3267.2
172.5°	3295.8	3281.6	3286.5	3303.2	3281.6
175°	3307.7	3291.0	3295.8	3312.6	3288.7
177.5°	3312.6	3295.8	3298.4	3315.1	3293.6
180°	3300.7	3300.7	3300.7	3300.7	3300.7

TEST NUMBER: P928814

CATALOG NUMBER: DFN2DIP-HX4F0-120D120US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.61	11.41	11.60	12.41	13.74	6.58	7.38	7.58	8.38	9.71
	3H	12.28	13.00	13.29	14.01	15.36	7.77	8.48	8.78	9.50	10.84
	4H	12.89	13.57	13.91	14.58	15.94	8.22	8.90	9.24	9.91	11.27
	6H	13.31	13.94	14.34	14.96	16.32	8.54	9.16	9.57	10.18	11.55
	8H	13.44	14.03	14.47	15.07	16.43	8.63	9.22	9.67	10.26	11.62
	12H	13.50	14.06	14.54	15.09	16.48	8.67	9.24	9.71	10.27	11.65
4H	2H	10.62	11.30	11.65	12.31	13.67	7.17	7.85	8.20	8.87	10.22
	3H	12.45	13.01	13.48	14.06	15.43	8.52	9.09	9.56	10.13	11.50
	4H	13.14	13.66	14.18	14.69	16.08	9.07	9.59	10.11	10.62	12.01
	6H	13.66	14.10	14.71	15.16	16.54	9.49	9.93	10.54	10.99	12.38
	8H	13.83	14.24	14.88	15.30	16.70	9.62	10.03	10.67	11.08	12.49
	12H	13.93	14.30	15.00	15.36	16.77	9.68	10.06	10.75	11.12	12.53
8H	4H	13.11	13.52	14.16	14.57	15.97	9.35	9.76	10.40	10.81	12.22
	6H	13.67	14.02	14.75	15.11	16.51	9.87	10.21	10.94	11.30	12.70
	8H	13.89	14.19	14.97	15.27	16.69	10.06	10.36	11.14	11.44	12.86
	12H	14.03	14.29	15.11	15.36	16.83	10.18	10.44	11.27	11.52	12.98
12H	4H	13.06	13.43	14.13	14.50	15.90	9.35	9.73	10.42	10.79	12.20
	6H	13.65	13.95	14.73	15.03	16.45	9.92	10.22	11.00	11.29	12.71
	8H	13.87	14.13	14.95	15.21	16.67	10.13	10.39	11.21	11.46	12.92

END OF REPORT