

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007771

Luminaire Tested: S125IP-B1090UB27-4F0-XX-W2A

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125IP-B1090UB27-4F0-XX-W2A
Description: Define 5 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4063.0 lumens
Efficiency: N/A
Efficacy: 142.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007771

CATALOG NUMBER: S125IP-B1090UB27-4F0-XX-W2A

Luminous Intensity Polar Plot



TEST NUMBER: P1007771

CATALOG NUMBER: S125IP-B1090UB27-4F0-XX-W2A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007771

CATALOG NUMBER: S125IP-B1090UB27-4F0-XX-W2A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.0
90°-100°	44.9	1.1
100°-110°	298.4	7.3
110°-120°	537.3	13.2
120°-130°	689.7	17.0
130°-140°	741.8	18.3
140°-150°	696.2	17.1
150°-160°	563.1	13.9
160°-170°	364.2	9.0
170°-180°	125.6	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.0
90°-120°	880.5	21.7
90°-150°	3008.1	74.0
90°-180°	4061.0	100.0
0°-180°	4063.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	9	16	21	24	3
95°	56	53	16	21	21	68
105°	288	292	292	292	291	305
115°	541	546	547	543	537	536
125°	769	776	776	772	769	687
135°	959	965	963	961	956	740
145°	1112	1114	1114	1115	1109	696
155°	1225	1219	1221	1224	1216	564
165°	1293	1287	1288	1294	1286	365
175°	1322	1316	1317	1325	1316	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1007771

CATALOG NUMBER: S125IP-B1090UB27-4F0-XX-W2A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	8.8	15.7	20.6	23.5
92.5°	18.6	9.8	15.7	20.6	21.6
95°	55.9	52.9	15.7	20.6	20.6
97.5°	104.9	110.7	17.6	19.6	20.6
100°	163.7	166.6	170.5	24.5	20.6
102.5°	223.4	227.4	229.3	231.3	149.0
105°	288.1	292.0	292.0	292.0	291.1
107.5°	354.8	354.8	356.7	357.7	353.8
110°	419.4	419.4	421.4	418.5	419.4

TEST NUMBER: P1007771

CATALOG NUMBER: S125IP-B1090UB27-4F0-XX-W2A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	480.2	483.1	484.1	480.2	478.2
115°	541.0	545.9	546.8	542.9	537.0
117.5°	604.7	604.7	608.6	602.7	600.8
120°	663.5	662.5	665.4	663.5	658.6
122.5°	715.4	720.3	721.3	719.3	713.5
125°	769.3	776.2	776.2	772.3	769.3
127.5°	821.3	826.2	825.2	823.2	815.4
130°	868.3	873.2	874.2	871.2	866.3
132.5°	915.3	921.2	918.3	918.3	913.4
135°	959.4	965.3	963.4	961.4	955.5
137.5°	1000.6	1006.5	1004.5	1004.5	999.6
140°	1040.8	1042.7	1041.8	1043.7	1037.8
142.5°	1077.0	1078.0	1080.0	1080.0	1074.1
145°	1112.3	1114.3	1114.3	1115.3	1109.4
147.5°	1143.7	1143.7	1144.7	1145.6	1138.8
150°	1173.1	1171.1	1173.1	1175.0	1167.2
152.5°	1201.5	1196.6	1198.6	1200.5	1193.7
155°	1225.0	1219.1	1221.1	1224.0	1216.2
157.5°	1243.6	1240.7	1240.7	1243.6	1235.8
160°	1263.2	1257.4	1258.3	1262.3	1254.4
162.5°	1278.9	1273.0	1274.0	1279.9	1271.1
165°	1292.6	1286.8	1287.7	1293.6	1285.8
167.5°	1303.4	1297.5	1298.5	1305.4	1296.6
170°	1312.2	1305.4	1306.4	1314.2	1305.4
172.5°	1318.1	1311.3	1313.2	1320.1	1311.3
175°	1322.0	1316.2	1317.1	1325.0	1316.2
177.5°	1325.0	1319.1	1320.1	1326.9	1319.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)