

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913975

Luminaire Tested: DFN2DIP-PN3F0-070D030US927-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913975
REPORT IS A COMBINATION OF REPORTS P901040 AND P897955
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-070D030US927-RLLONL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7066.2 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913975

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P913975

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2679	2679	2679
5°	2682	2635	2652
10°	2654	2581	2565
15°	2616	2494	2431
20°	2566	2375	2266
25°	2515	2241	2107
30°	2446	2105	1906
35°	2379	1958	1729
40°	2311	1806	1527
45°	2232	1638	1343
50°	2151	1469	1164
55°	2065	1288	992
60°	1966	1099	815
65°	1852	908	733
70°	1713	729	661
75°	1539	638	599
80°	1287	530	516
85°	874	345	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2232 cd/sqm

TEST NUMBER: P913975

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	3.0
10°-20°	589.7	8.3
20°-30°	827.9	11.7
30°-40°	902.4	12.8
40°-50°	829.4	11.7
50°-60°	651.4	9.2
60°-70°	424.0	6.0
70°-80°	218.2	3.1
80°-90°	57.1	0.8
90°-100°	26.5	0.4
100°-110°	98.6	1.4
110°-120°	261.5	3.7
120°-130°	433.7	6.1
130°-140°	460.7	6.5
140°-150°	428.1	6.1
150°-160°	344.2	4.9
160°-170°	221.8	3.1
170°-180°	76.3	1.1
0°-30°	1632.3	23.1
0°-40°	2534.7	35.9
0°-60°	4015.5	56.8
0°-90°	4714.9	66.7
90°-120°	386.5	5.5
90°-150°	1709.0	24.2
90°-180°	2351.0	33.3
0°-180°	7066.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2282	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	1	7	12	15	16	7
95°	38	18	23	26	25	45
105°	176	194	35	42	44	188
115°	334	344	358	89	48	329
125°	472	479	490	494	496	421
135°	584	593	598	604	603	451
145°	677	677	687	691	688	424
155°	746	741	748	751	746	344
165°	786	782	784	788	784	222
175°	804	800	801	805	799	76
180°	802	802	802	802	802	

TEST NUMBER: P913975

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.9	2291.9	2291.9	2291.9	2291.9
2.5°	2302.2	2291.9	2269.0	2289.9	2285.7
5°	2291.9	2281.5	2254.5	2273.2	2267.0
7.5°	2273.2	2260.8	2231.8	2239.9	2229.6
10°	2248.3	2233.8	2192.4	2186.0	2173.7
12.5°	2217.2	2198.5	2142.5	2130.1	2107.2
15°	2179.8	2157.0	2086.5	2047.2	2026.5
17.5°	2136.3	2103.1	2015.9	1970.3	1937.1
20°	2086.5	2044.9	1941.3	1889.6	1843.8
22.5°	2032.7	1984.9	1864.5	1794.1	1763.1
25°	1978.7	1912.2	1775.4	1690.4	1659.2
27.5°	1914.5	1843.8	1692.4	1595.0	1547.2
30°	1846.0	1767.0	1601.1	1495.5	1439.4
32.5°	1779.6	1684.1	1514.2	1389.6	1337.7
35°	1704.9	1599.1	1416.7	1286.0	1240.2
37.5°	1632.4	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.9	1082.7	1028.7
42.5°	1476.8	1344.1	1134.6	981.0	929.3
45°	1393.8	1254.7	1037.1	889.7	839.9
47.5°	1315.0	1167.8	943.8	796.4	750.8
50°	1227.9	1080.7	852.5	709.2	665.9
52.5°	1142.7	987.1	765.3	628.4	589.1
55°	1059.8	898.0	674.0	549.7	510.3
57.5°	974.9	808.9	593.3	477.1	443.9
60°	887.7	721.8	508.1	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.6	547.5	360.9	290.5	284.1
67.5°	632.6	464.5	290.5	255.0	248.9
70°	545.5	383.7	240.5	219.8	211.4
72.5°	462.6	309.0	201.1	184.7	180.5
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.1	45.6	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	0.6	7.0	11.6	14.6	15.6
92.5°	14.6	12.2	13.9	15.1	15.6
95°	37.7	18.5	22.6	25.6	25.0
97.5°	67.9	20.4	29.5	31.4	31.9
100°	102.7	23.2	33.1	37.7	38.9
102.5°	141.0	139.9	34.2	40.6	42.4
105°	176.4	193.8	35.4	41.7	44.1
107.5°	217.6	232.1	36.6	42.9	45.3
110°	257.1	269.3	101.6	43.6	45.9

TEST NUMBER: P913975

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.3	304.7	294.8	44.7	46.4
115°	333.7	343.6	358.1	89.4	47.6
117.5°	368.0	379.5	389.4	306.4	154.4
120°	406.2	414.9	425.4	432.4	354.0
122.5°	438.7	448.1	459.7	463.1	463.7
125°	471.8	479.3	490.4	494.5	496.2
127.5°	502.0	510.1	518.9	524.7	525.2
130°	530.4	539.8	546.1	552.5	552.0
132.5°	559.4	567.0	573.4	578.6	578.1
135°	583.8	593.2	598.3	604.2	603.0
137.5°	609.3	616.3	622.2	628.0	626.2
140°	634.3	639.0	645.3	650.5	647.7
142.5°	655.3	659.3	666.9	671.5	668.6
145°	677.3	676.7	686.6	690.6	687.7
147.5°	696.4	694.7	704.6	707.4	705.1
150°	715.0	711.0	720.3	723.7	720.8
152.5°	730.6	726.0	734.7	738.2	734.2
155°	745.8	740.6	747.5	751.0	746.4
157.5°	758.0	753.4	758.6	762.6	758.0
160°	768.4	764.9	768.4	771.9	767.8
162.5°	777.7	774.2	777.1	781.2	775.9
165°	785.8	782.4	784.1	788.1	784.1
167.5°	792.2	788.7	790.4	794.6	789.3
170°	797.4	793.9	795.1	799.2	793.9
172.5°	800.9	797.4	798.6	802.6	797.4
175°	803.7	799.7	800.9	804.9	799.2
177.5°	804.9	800.9	801.5	805.6	800.3
180°	802.1	802.1	802.1	802.1	802.1

TEST NUMBER: P913975

CATALOG NUMBER: DFN2DIP-PN3F0-070D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.97	12.96	12.77	13.78	14.79	7.93	8.92	8.74	9.75	10.76
	3H	13.65	14.53	14.47	15.37	16.41	9.13	10.01	9.95	10.85	11.89
	4H	14.26	15.10	15.10	15.94	16.99	9.58	10.41	10.42	11.26	12.31
	6H	14.69	15.45	15.54	16.30	17.37	9.90	10.67	10.75	11.52	12.59
	8H	14.82	15.55	15.67	16.41	17.48	10.00	10.73	10.85	11.59	12.66
	12H	14.88	15.58	15.74	16.43	17.53	10.04	10.74	10.91	11.60	12.69
4H	2H	12.00	12.84	12.84	13.68	14.73	8.54	9.38	9.39	10.22	11.27
	3H	13.84	14.53	14.69	15.41	16.47	9.90	10.59	10.75	11.47	12.54
	4H	14.53	15.16	15.40	16.03	17.13	10.45	11.08	11.32	11.95	13.05
	6H	15.05	15.59	15.93	16.49	17.59	10.87	11.41	11.75	12.31	13.41
	8H	15.23	15.73	16.11	16.62	17.73	11.00	11.51	11.88	12.40	13.51
	12H	15.32	15.78	16.23	16.69	17.81	11.07	11.52	11.97	12.43	13.55
8H	4H	14.51	15.02	15.39	15.91	17.02	10.74	11.25	11.62	12.14	13.25
	6H	15.08	15.49	15.99	16.43	17.54	11.25	11.67	12.17	12.61	13.72
	8H	15.29	15.66	16.21	16.58	17.71	11.44	11.81	12.36	12.74	13.87
	12H	15.43	15.76	16.35	16.67	17.85	11.56	11.89	12.49	12.81	13.99
12H	4H	14.47	14.92	15.37	15.83	16.95	10.75	11.21	11.65	12.12	13.23
	6H	15.05	15.42	15.97	16.35	17.48	11.30	11.67	12.22	12.60	13.73
	8H	15.27	15.60	16.20	16.52	17.70	11.51	11.84	12.44	12.76	13.94