

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922226

Luminaire Tested: DFN2DIP-PN3F0-090D060US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922226
REPORT IS A COMBINATION OF REPORTS P899566 AND P896399
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN3F0-090D060US940-RLLFLL
Description: 3 foot, Pentagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11556.6 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.96' x L: 3.11' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 139
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922226

CATALOG NUMBER: DFN2DIP-PN3F0-090D060US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P922226

CATALOG NUMBER: DFN2DIP-PN3F0-090D060US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		64
1	100	96	92	89	94	90	87	84	78	76	74		68	66	64		58
2	92	85	79	74	86	79	74	70	69	65	62		60	57	55		52
3	84	75	68	62	78	70	64	59	62	57	53		54	50	47		46
4	77	67	59	53	72	63	56	51	55	50	46		48	44	41		42
5	71	60	52	46	66	56	49	44	50	44	40		44	39	36		38
6	66	54	46	40	61	51	44	39	45	39	35		40	35	32		35
7	61	49	41	36	57	46	39	34	41	35	31		36	32	28		32
8	57	45	37	32	53	42	35	30	38	32	28		33	29	25		29
9	53	41	34	29	50	39	32	27	35	29	25		31	26	23		27
10	50	38	31	26	47	36	29	25	32	27	23		29	24	21		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3877	3877	3877
5°	3881	3813	3839
10°	3841	3736	3712
15°	3785	3610	3517
20°	3713	3437	3279
25°	3639	3244	3049
30°	3541	3046	2758
35°	3444	2833	2502
40°	3345	2614	2209
45°	3231	2371	1944
50°	3113	2126	1685
55°	2989	1864	1436
60°	2845	1591	1180
65°	2680	1313	1061
70°	2479	1055	957
75°	2227	924	867
80°	1863	766	747
85°	1264	499	551

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3231 cd/sqm

TEST NUMBER: P922226

CATALOG NUMBER: DFN2DIP-PN3F0-090D060US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.9	2.7
10°-20°	853.4	7.4
20°-30°	1198.1	10.4
30°-40°	1306.0	11.3
40°-50°	1200.4	10.4
50°-60°	942.7	8.2
60°-70°	613.6	5.3
70°-80°	315.9	2.7
80°-90°	85.4	0.7
90°-100°	104.7	0.9
100°-110°	332.7	2.9
110°-120°	569.3	4.9
120°-130°	748.8	6.5
130°-140°	840.5	7.3
140°-150°	824.2	7.1
150°-160°	691.4	6.0
160°-170°	458.5	4.0
170°-180°	160.3	1.4
0°-30°	2362.4	20.4
0°-40°	3668.4	31.7
0°-60°	5811.5	50.3
0°-90°	6826.4	59.1
90°-120°	1006.7	8.7
90°-150°	3420.1	29.6
90°-180°	4730.0	40.9
0°-180°	11556.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3317	3317	3317	3317	3317	
5°	3317	3302	3263	3290	3281	315
15°	3155	3122	3020	2963	2933	889
25°	2864	2768	2570	2446	2401	1317
35°	2468	2314	2050	1861	1795	1544
45°	2017	1816	1501	1288	1216	1558
55°	1534	1300	975	796	738	1371
65°	1036	792	522	420	411	1027
75°	552	342	240	219	216	584
85°	129	66	57	57	57	148
90°	2	18	50	47	48	11
95°	74	89	91	91	89	83
105°	307	311	314	317	317	324
115°	571	580	577	575	571	565
125°	831	844	840	835	834	743
135°	1075	1091	1094	1092	1088	831
145°	1305	1315	1323	1325	1319	815
155°	1492	1496	1501	1508	1503	687
165°	1623	1622	1622	1632	1625	458
175°	1689	1685	1682	1692	1683	160
180°	1692	1692	1692	1692	1692	

TEST NUMBER: P922226

CATALOG NUMBER: DFN2DIP-PN3F0-090D060US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3316.9	3316.9	3316.9	3316.9	3316.9
2.5°	3331.9	3316.9	3283.7	3314.0	3308.0
5°	3316.9	3301.9	3262.8	3289.8	3280.9
7.5°	3289.8	3272.0	3230.0	3241.7	3226.7
10°	3253.9	3232.8	3173.0	3163.7	3145.9
12.5°	3208.9	3181.9	3100.7	3082.8	3049.6
15°	3154.8	3121.7	3019.8	2962.7	2932.8
17.5°	3091.7	3043.7	2917.5	2851.6	2803.5
20°	3019.8	2959.6	2809.5	2734.7	2668.4
22.5°	2941.8	2872.6	2698.4	2596.5	2551.6
25°	2863.7	2767.5	2569.5	2446.5	2401.3
27.5°	2770.7	2668.4	2449.4	2308.3	2239.2
30°	2671.7	2557.3	2317.2	2164.4	2083.1
32.5°	2575.4	2437.2	2191.4	2011.2	1936.0
35°	2467.5	2314.3	2050.3	1861.2	1794.9
37.5°	2362.4	2197.2	1918.2	1710.8	1636.0
40°	2251.3	2071.4	1779.9	1566.9	1488.9
42.5°	2137.3	1945.3	1642.0	1419.8	1344.9
45°	2017.2	1816.0	1500.9	1287.5	1215.6
47.5°	1903.2	1690.1	1365.9	1152.5	1086.6
50°	1777.1	1564.0	1233.8	1026.4	963.7
52.5°	1653.9	1428.7	1107.7	909.5	852.6
55°	1533.7	1299.7	975.4	795.6	738.5
57.5°	1410.9	1170.7	858.6	690.5	642.4
60°	1284.7	1044.5	735.4	582.5	534.4
62.5°	1161.8	921.7	630.3	486.3	462.4
65°	1035.6	792.4	522.3	420.4	411.2
67.5°	915.6	672.3	420.4	369.1	360.2
70°	789.5	555.4	348.1	318.2	306.0
72.5°	669.4	447.1	291.1	267.2	261.2
75°	552.2	342.1	240.1	219.1	216.2
77.5°	435.3	243.0	189.1	177.1	171.0
80°	327.1	174.2	143.9	132.2	132.2
82.5°	228.0	117.2	99.1	93.0	93.0
85°	128.9	65.9	57.0	57.0	57.0
87.5°	48.1	23.9	23.9	21.0	21.0
90°	1.5	18.4	50.0	46.9	48.4
92.5°	31.7	42.9	44.4	45.9	45.9
95°	74.5	88.7	91.3	91.3	88.7
97.5°	123.9	137.2	142.9	142.9	142.9
100°	181.1	192.8	196.9	196.9	195.4
102.5°	241.3	249.9	255.6	257.1	255.6
105°	307.1	311.2	314.2	316.8	316.8
107.5°	372.4	378.5	378.5	379.5	372.4
110°	435.7	443.8	443.8	443.8	439.7

TEST NUMBER: P922226

CATALOG NUMBER: DFN2DIP-PN3F0-090D060US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.0	512.6	511.1	507.0	504.0
115°	571.3	579.5	576.9	575.4	571.3
117.5°	638.2	649.4	642.2	638.2	634.1
120°	705.5	716.8	705.5	705.5	700.9
122.5°	766.7	781.0	773.8	769.8	766.7
125°	831.0	843.7	839.6	835.1	833.6
127.5°	893.8	909.5	903.9	897.9	893.8
130°	952.4	970.8	968.2	965.2	959.6
132.5°	1018.2	1032.5	1033.5	1026.4	1022.3
135°	1074.9	1090.7	1093.7	1092.2	1088.1
137.5°	1138.1	1150.8	1153.4	1152.4	1146.3
140°	1193.7	1206.5	1213.6	1213.6	1208.0
142.5°	1250.8	1263.6	1267.7	1269.2	1263.6
145°	1304.9	1315.1	1323.3	1324.8	1319.2
147.5°	1353.3	1366.1	1372.3	1374.7	1369.1
150°	1403.4	1412.0	1417.6	1422.2	1417.6
152.5°	1447.7	1456.4	1463.6	1469.2	1463.6
155°	1492.1	1496.2	1500.7	1508.0	1503.3
157.5°	1530.4	1533.5	1536.0	1546.2	1539.1
160°	1564.6	1567.6	1569.1	1577.8	1571.7
162.5°	1596.2	1596.2	1597.7	1607.4	1600.3
165°	1623.2	1621.7	1621.7	1631.9	1624.8
167.5°	1647.7	1643.2	1643.2	1653.3	1646.2
170°	1666.1	1662.0	1660.5	1670.6	1662.0
172.5°	1678.8	1674.7	1673.2	1683.4	1674.7
175°	1689.0	1685.0	1681.9	1692.1	1683.4
177.5°	1694.6	1690.6	1687.5	1696.1	1687.5
180°	1692.1	1692.1	1692.1	1692.1	1692.1

TEST NUMBER: P922226

CATALOG NUMBER: DFN2DIP-PN3F0-090D060US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.62	13.53	13.50	14.43	15.57	8.59	9.50	9.47	10.40	11.54
	3H	14.30	15.11	15.19	16.02	17.19	9.78	10.59	10.67	11.50	12.66
	4H	14.91	15.68	15.82	16.59	17.76	10.23	11.00	11.14	11.91	13.08
	6H	15.33	16.04	16.25	16.96	18.14	10.55	11.25	11.47	12.17	13.36
	8H	15.46	16.13	16.38	17.06	18.25	10.64	11.31	11.57	12.25	13.43
	12H	15.52	16.16	16.45	17.09	18.30	10.68	11.32	11.61	12.25	13.46
4H	2H	12.65	13.42	13.56	14.33	15.50	9.19	9.96	10.11	10.87	12.05
	3H	14.48	15.12	15.40	16.06	17.25	10.54	11.18	11.47	12.12	13.31
	4H	15.17	15.75	16.10	16.69	17.90	11.09	11.67	12.02	12.61	13.82
	6H	15.68	16.18	16.63	17.15	18.36	11.50	12.01	12.45	12.97	14.18
	8H	15.86	16.32	16.81	17.28	18.51	11.63	12.10	12.58	13.06	14.28
	12H	15.95	16.37	16.92	17.35	18.58	11.70	12.12	12.67	13.09	14.32
8H	4H	15.14	15.61	16.09	16.57	17.79	11.37	11.84	12.32	12.79	14.02
	6H	15.70	16.09	16.68	17.09	18.31	11.88	12.27	12.86	13.27	14.49
	8H	15.92	16.26	16.90	17.25	18.49	12.07	12.41	13.06	13.40	14.64
	12H	16.05	16.35	17.04	17.33	18.63	12.19	12.49	13.18	13.47	14.76
12H	4H	15.10	15.52	16.07	16.49	17.72	11.38	11.80	12.35	12.77	14.01
	6H	15.68	16.02	16.66	17.01	18.25	11.93	12.27	12.92	13.26	14.50
	8H	15.90	16.20	16.89	17.18	18.47	12.14	12.44	13.13	13.42	14.71