

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915834

Luminaire Tested: DFN2DIP-4P3F0-030D020US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915834
REPORT IS A COMBINATION OF REPORTS P899031 AND P895917
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P3F0-030D020US930-FLLFLL
Description: 3 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3864.5 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.07' x L: 3.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 41.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915834
CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915834

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	53	50	48	44
3	84	74	66	60	78	70	63	58	61	56	52	54	50	46	47	44	41	47	44	41	37
4	77	66	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	34	30	27	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	31	27	24	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	29	25	22	20
9	52	40	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1085	1085	1085
5°	1086	1069	1076
10°	1076	1054	1061
15°	1060	1036	1038
20°	1038	1011	1015
25°	1016	981	987
30°	988	954	953
35°	962	921	916
40°	930	889	881
45°	899	856	846
50°	864	821	804
55°	827	781	766
60°	786	734	723
65°	741	685	671
70°	683	625	616
75°	603	554	564
80°	507	462	466
85°	357	306	305

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 899 cd/sqm



TEST NUMBER: P915834

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	2.3
10°-20°	252.0	6.5
20°-30°	370.4	9.6
30°-40°	430.2	11.1
40°-50°	429.7	11.1
50°-60°	374.6	9.7
60°-70°	277.0	7.2
70°-80°	156.7	4.1
80°-90°	42.8	1.1
90°-100°	31.9	0.8
100°-110°	101.4	2.6
110°-120°	173.5	4.5
120°-130°	228.2	5.9
130°-140°	256.1	6.6
140°-150°	251.2	6.5
150°-160°	210.7	5.5
160°-170°	139.7	3.6
170°-180°	48.8	1.3
0°-30°	712.0	18.4
0°-40°	1142.2	29.6
0°-60°	1946.5	50.4
0°-90°	2422.9	62.7
90°-120°	306.8	7.9
90°-150°	1042.3	27.0
90°-180°	1442.0	37.3
0°-180°	3864.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	952	948	938	945	944	90
15°	906	901	889	892	888	255
25°	820	813	797	799	797	377
35°	707	698	684	678	674	442
45°	576	569	556	545	542	444
55°	436	430	419	408	404	390
65°	294	288	279	271	266	290
75°	154	152	147	142	144	164
85°	38	37	36	33	32	42
90°	0	6	15	14	15	4
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	



TEST NUMBER: P915834

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	951.7	951.7	951.7	951.7	951.7
2.5°	957.2	952.7	942.6	951.7	950.0
5°	951.7	948.1	938.0	945.3	943.5
7.5°	945.3	939.9	929.8	937.2	935.3
10°	935.3	928.9	917.9	925.2	922.5
12.5°	921.5	916.1	905.1	909.6	907.8
15°	906.0	900.6	888.6	892.3	887.7
17.5°	886.7	881.3	869.4	873.9	869.4
20°	865.7	860.2	847.4	850.1	846.5
22.5°	844.7	836.5	824.5	824.5	822.6
25°	819.9	812.7	797.1	798.9	797.1
27.5°	792.5	786.0	774.2	771.5	767.0
30°	765.1	757.7	744.0	741.3	737.6
32.5°	735.8	730.3	715.7	710.1	706.5
35°	707.4	698.3	683.6	678.1	673.5
37.5°	675.4	667.2	652.5	646.0	641.5
40°	642.5	635.1	620.4	612.3	608.6
42.5°	610.4	603.1	588.5	579.3	573.8
45°	575.7	569.2	555.5	545.4	541.8
47.5°	541.8	535.4	520.7	510.6	505.2
50°	506.1	501.5	488.7	475.9	471.3
52.5°	471.3	464.9	453.1	443.0	436.5
55°	435.7	430.2	419.1	408.2	403.7
57.5°	399.9	395.3	383.4	372.4	368.8
60°	364.2	360.6	347.8	337.7	335.0
62.5°	329.5	323.0	313.9	304.8	301.1
65°	293.8	288.3	279.2	270.9	266.4
67.5°	257.2	252.6	244.3	238.0	234.3
70°	223.3	219.6	211.4	205.0	201.4
72.5°	188.6	184.8	180.3	173.9	171.2
75°	153.7	152.0	147.3	141.9	143.7
77.5°	122.6	119.0	117.1	114.4	111.7
80°	91.6	90.6	88.7	86.0	84.2
82.5°	62.2	62.2	61.4	57.6	57.6
85°	37.5	36.6	35.7	32.9	32.0
87.5°	16.5	14.7	12.8	10.1	9.1
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0



TEST NUMBER: P915834

CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7



TEST NUMBER: P915834
 CATALOG NUMBER: DFN2DIP-4P3F0-030D020US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.61	9.60	9.45	10.46	11.54	8.17	9.16	9.01	10.02	11.10
	3H	10.28	11.17	11.13	12.04	13.14	9.79	10.68	10.64	11.55	12.65
	4H	10.87	11.71	11.74	12.59	13.70	10.38	11.22	11.25	12.09	13.21
	6H	11.27	12.05	12.15	12.93	14.06	10.77	11.55	11.65	12.43	13.56
	8H	11.38	12.12	12.27	13.02	14.15	10.88	11.62	11.77	12.52	13.65
	12H	11.43	12.13	12.33	13.03	14.18	10.92	11.62	11.82	12.52	13.67
4H	2H	9.09	9.93	9.96	10.80	11.92	8.73	9.57	9.61	10.45	11.56
	3H	10.96	11.66	11.84	12.57	13.70	10.55	11.25	11.44	12.16	13.29
	4H	11.68	12.31	12.57	13.22	14.38	11.25	11.89	12.15	12.80	13.95
	6H	12.19	12.75	13.10	13.68	14.83	11.76	12.31	12.67	13.24	14.40
	8H	12.34	12.86	13.26	13.78	14.96	11.91	12.42	12.82	13.35	14.52
	12H	12.42	12.89	13.35	13.83	15.01	11.97	12.44	12.91	13.38	14.56
8H	4H	11.88	12.39	12.79	13.32	14.49	11.50	12.02	12.42	12.94	14.11
	6H	12.51	12.94	13.45	13.90	15.07	12.12	12.55	13.07	13.52	14.69
	8H	12.73	13.11	13.68	14.06	15.25	12.33	12.71	13.28	13.67	14.86
	12H	12.86	13.19	13.82	14.14	15.38	12.45	12.78	13.40	13.73	14.97
12H	4H	11.87	12.33	12.80	13.28	14.45	11.50	11.97	12.43	12.91	14.09
	6H	12.54	12.92	13.49	13.87	15.06	12.17	12.54	13.12	13.50	14.69
	8H	12.78	13.11	13.74	14.06	15.30	12.40	12.73	13.35	13.68	14.92