

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910492

Luminaire Tested: DFN2DIP-4P4F0-040D050US850-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P910492  
REPORT IS A COMBINATION OF REPORTS P899106 AND P895967  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-4P4F0-040D050US850-RLLFLL  
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8677.9 lumens  
Efficiency: N/A  
Efficacy: 109.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 79  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P910492  
CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P910492

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44			44
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37			37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32			32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28			28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24			24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21			21
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22	19			19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17			17
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15			15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14			14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13			13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1189	1189	1189
5°	1191	1171	1178
10°	1180	1148	1141
15°	1164	1111	1082
20°	1142	1059	1009
25°	1120	1000	939
30°	1091	941	851
35°	1062	876	772
40°	1033	810	683
45°	998	736	602
50°	963	661	522
55°	926	581	446
60°	884	497	368
65°	835	412	331
70°	775	333	300
75°	701	294	275
80°	593	248	240
85°	414	168	183

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1327 cd/sqm



TEST NUMBER: P910492

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.8	2.0
10°-20°	471.7	5.4
20°-30°	662.3	7.6
30°-40°	721.9	8.3
40°-50°	663.5	7.6
50°-60°	521.1	6.0
60°-70°	339.2	3.9
70°-80°	174.6	2.0
80°-90°	49.6	0.6
90°-100°	108.5	1.3
100°-110°	344.8	4.0
110°-120°	590.1	6.8
120°-130°	776.0	8.9
130°-140°	871.0	10.0
140°-150°	854.2	9.8
150°-160°	716.5	8.3
160°-170°	475.2	5.5
170°-180°	166.1	1.9
0°-30°	1305.8	15.0
0°-40°	2027.7	23.4
0°-60°	3212.2	37.0
0°-90°	3775.6	43.5
90°-120°	1043.4	12.0
90°-150°	3544.6	40.8
90°-180°	4902.0	56.5
0°-180°	8677.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1833	1833	1833	1833	1833	
5°	1833	1825	1804	1818	1814	174
15°	1744	1726	1669	1638	1621	491
25°	1583	1530	1420	1352	1327	728
35°	1364	1279	1133	1029	992	854
45°	1115	1004	830	712	672	861
55°	848	718	539	440	408	758
65°	572	438	289	232	227	568
75°	305	189	133	121	120	323
85°	71	36	32	32	32	82
90°	2	19	52	49	50	9
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P910492

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1833.4	1833.4	1833.4	1833.4	1833.4
2.5°	1841.7	1833.4	1815.1	1831.8	1828.4
5°	1833.4	1825.1	1803.5	1818.4	1813.5
7.5°	1818.4	1808.6	1785.4	1791.8	1783.6
10°	1798.6	1786.9	1753.8	1748.7	1738.9
12.5°	1773.7	1758.8	1713.8	1704.0	1685.7
15°	1743.8	1725.5	1669.2	1637.7	1621.1
17.5°	1709.0	1682.4	1612.6	1576.2	1549.6
20°	1669.2	1635.9	1552.9	1511.6	1475.0
22.5°	1626.0	1587.9	1491.5	1435.2	1410.4
25°	1582.9	1529.8	1420.2	1352.3	1327.3
27.5°	1531.5	1475.0	1353.9	1275.9	1237.6
30°	1476.7	1413.5	1280.8	1196.3	1151.5
32.5°	1423.6	1347.2	1211.2	1111.7	1070.1
35°	1364.0	1279.2	1133.3	1028.7	992.1
37.5°	1305.8	1214.5	1060.2	945.6	904.3
40°	1244.4	1144.9	983.9	866.1	823.0
42.5°	1181.3	1075.2	907.6	784.7	743.4
45°	1115.0	1003.8	829.6	711.8	671.9
47.5°	1052.0	934.2	755.0	637.1	600.6
50°	982.2	864.5	681.9	567.4	532.7
52.5°	914.1	789.7	612.3	502.7	471.2
55°	847.8	718.4	539.2	439.7	408.2
57.5°	779.8	647.1	474.5	381.6	355.1
60°	710.1	577.3	406.4	321.9	295.4
62.5°	642.2	509.5	348.3	268.8	255.6
65°	572.5	437.9	288.7	232.3	227.2
67.5°	506.1	371.6	232.3	204.1	199.1
70°	436.4	307.0	192.4	175.9	169.1
72.5°	370.1	247.2	160.9	147.7	144.4
75°	305.2	189.1	132.7	121.1	119.6
77.5°	240.7	134.3	104.6	97.9	94.5
80°	180.8	96.3	79.5	73.1	73.1
82.5°	126.1	64.8	54.8	51.3	51.3
85°	71.3	36.5	31.5	31.5	31.5
87.5°	26.6	13.2	13.2	11.6	11.6
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P910492

CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P910492  
 CATALOG NUMBER: DFN2DIP-4P4F0-040D050US850-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.13	7.91	8.15	8.93	10.29	3.09	3.87	4.11	4.89	6.25
	3H	8.81	9.51	9.84	10.54	11.92	4.28	4.97	5.30	6.00	7.39
	4H	9.42	10.08	10.46	11.11	12.50	4.73	5.39	5.77	6.42	7.81
	6H	9.84	10.45	10.89	11.49	12.89	5.05	5.65	6.09	6.69	8.09
	8H	9.97	10.55	11.02	11.60	13.00	5.13	5.71	6.19	6.77	8.16
	12H	10.03	10.58	11.09	11.63	13.05	5.18	5.73	6.24	6.77	8.20
4H	2H	7.14	7.80	8.19	8.83	10.23	3.68	4.34	4.73	5.37	6.77
	3H	8.97	9.52	10.03	10.58	11.99	5.03	5.58	6.08	6.64	8.04
	4H	9.67	10.17	10.73	11.22	12.65	5.58	6.08	6.64	7.13	8.56
	6H	10.18	10.62	11.25	11.69	13.11	6.00	6.43	7.07	7.50	8.92
	8H	10.36	10.76	11.43	11.83	13.27	6.12	6.53	7.19	7.60	9.03
	12H	10.46	10.82	11.55	11.90	13.35	6.19	6.55	7.28	7.63	9.08
8H	4H	9.63	10.03	10.70	11.10	12.54	5.86	6.26	6.93	7.33	8.76
	6H	10.20	10.53	11.29	11.64	13.08	6.38	6.71	7.47	7.82	9.25
	8H	10.42	10.71	11.52	11.81	13.26	6.57	6.86	7.67	7.95	9.41
	12H	10.56	10.82	11.67	11.91	13.40	6.69	6.94	7.79	8.03	9.52
12H	4H	9.58	9.94	10.67	11.03	12.47	5.86	6.22	6.95	7.31	8.75
	6H	10.18	10.47	11.28	11.56	13.02	6.43	6.72	7.53	7.81	9.27
	8H	10.40	10.66	11.50	11.74	13.24	6.64	6.89	7.74	7.98	9.47