

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913321

Luminaire Tested: DFN2DIP-4P4F0-080D060US927-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913321
REPORT IS A COMBINATION OF REPORTS P900646 AND P897523
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-080D060US927-RLLONL
Description: 4 foot, 90deg - 4way Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10092.4 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 136.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913321
CATALOG NUMBER: DFN2DIP-4P4F0-080D060US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P913321

CATALOG NUMBER: DFN2DIP-4P4F0-080D060US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59	53
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	53	52	51	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	42	40	38	34
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	35	32	29	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23	29	26	23	21
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21	27	24	21	19
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19	25	22	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	23	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1699	1699	1699
5°	1702	1673	1684
10°	1685	1641	1629
15°	1662	1587	1545
20°	1632	1513	1442
25°	1600	1429	1342
30°	1558	1344	1215
35°	1517	1252	1104
40°	1475	1157	976
45°	1426	1051	860
50°	1376	944	746
55°	1324	830	637
60°	1263	711	525
65°	1193	589	473
70°	1108	476	429
75°	1001	421	392
80°	847	355	342
85°	592	240	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1426 cd/sqm



TEST NUMBER: P913321

CATALOG NUMBER: DFN2DIP-4P4F0-080D060US927-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.5	2.4
10°-20°	673.9	6.7
20°-30°	946.1	9.4
30°-40°	1031.3	10.2
40°-50°	947.9	9.4
50°-60°	744.4	7.4
60°-70°	484.5	4.8
70°-80°	249.4	2.5
80°-90°	66.5	0.7
90°-100°	52.9	0.5
100°-110°	197.2	2.0
110°-120°	523.0	5.2
120°-130°	867.4	8.6
130°-140°	921.3	9.1
140°-150°	856.3	8.5
150°-160°	688.4	6.8
160°-170°	443.6	4.4
170°-180°	152.7	1.5
0°-30°	1865.5	18.5
0°-40°	2896.8	28.7
0°-60°	4589.2	45.5
0°-90°	5389.6	53.4
90°-120°	773.0	7.7
90°-150°	3418.0	33.9
90°-180°	4703.0	46.6
0°-180°	10092.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2619	2608	2576	2598	2591	248
15°	2491	2465	2385	2340	2316	702
25°	2261	2186	2029	1932	1896	1040
35°	1948	1828	1619	1470	1417	1220
45°	1593	1434	1185	1017	960	1230
55°	1211	1026	770	628	583	1082
65°	818	626	412	332	325	811
75°	436	270	190	173	171	461
85°	102	52	45	45	45	117
90°	1	14	23	29	31	9
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	944	959	981	989	992	842
135°	1168	1186	1197	1208	1206	902
145°	1355	1353	1373	1381	1376	847
155°	1492	1481	1495	1502	1493	687
165°	1572	1565	1568	1576	1568	444
175°	1608	1599	1602	1610	1598	153
180°	1604	1604	1604	1604	1604	



TEST NUMBER: P913321

CATALOG NUMBER: DFN2DIP-4P4F0-080D060US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2619.3	2619.3	2619.3	2619.3	2619.3
2.5°	2631.1	2619.3	2593.1	2617.0	2612.2
5°	2619.3	2607.5	2576.5	2597.9	2590.8
7.5°	2597.9	2583.8	2550.6	2559.9	2548.1
10°	2569.4	2552.9	2505.6	2498.3	2484.2
12.5°	2534.0	2512.6	2448.5	2434.4	2408.2
15°	2491.3	2465.1	2384.6	2339.6	2315.9
17.5°	2441.4	2403.5	2303.9	2251.9	2213.8
20°	2384.6	2337.1	2218.7	2159.6	2107.2
22.5°	2323.0	2268.4	2130.9	2050.4	2014.9
25°	2261.4	2185.5	2029.0	1932.0	1896.2
27.5°	2187.9	2107.2	1934.2	1822.8	1768.2
30°	2109.7	2019.4	1829.9	1709.1	1645.0
32.5°	2033.8	1924.7	1730.5	1588.2	1528.8
35°	1948.5	1827.6	1619.1	1469.7	1417.4
37.5°	1865.5	1735.0	1514.7	1351.0	1291.9
40°	1777.8	1635.7	1405.6	1237.3	1175.7
42.5°	1687.7	1536.1	1296.6	1121.2	1062.0
45°	1592.9	1434.0	1185.3	1016.8	960.0
47.5°	1502.9	1334.7	1078.6	910.1	858.1
50°	1403.3	1235.1	974.3	810.6	761.0
52.5°	1306.0	1128.1	874.6	718.3	673.3
55°	1211.2	1026.3	770.3	628.2	583.2
57.5°	1114.1	924.5	678.0	545.3	507.2
60°	1014.5	824.9	580.7	459.9	422.0
62.5°	917.4	727.8	497.7	384.0	365.2
65°	817.8	625.7	412.4	332.0	324.6
67.5°	723.0	530.9	332.0	291.4	284.5
70°	623.4	438.6	274.9	251.2	241.7
72.5°	528.6	353.1	229.9	211.0	206.2
75°	436.1	270.1	189.6	173.0	170.8
77.5°	343.8	191.9	149.4	139.8	135.1
80°	258.3	137.6	113.7	104.3	104.3
82.5°	180.1	92.5	78.2	73.4	73.4
85°	101.9	52.0	45.0	45.0	45.0
87.5°	37.9	18.9	18.9	16.6	16.6
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.8	40.6	59.1	62.7	63.8
100°	205.5	46.4	66.1	75.4	77.7
102.5°	282.0	279.8	68.5	81.2	84.8
105°	352.8	387.7	70.8	83.5	88.2
107.5°	435.3	464.2	73.2	85.9	90.5
110°	514.3	538.5	203.2	87.1	91.7



TEST NUMBER: P913321

CATALOG NUMBER: DFN2DIP-4P4F0-080D060US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.5	609.3	589.6	89.3	92.9
115°	667.4	687.1	716.2	178.8	95.2
117.5°	735.9	759.1	778.9	612.8	308.7
120°	812.5	829.9	850.9	864.7	708.1
122.5°	877.4	896.0	919.3	926.2	927.5
125°	943.6	958.8	980.8	989.0	992.4
127.5°	1004.0	1020.3	1037.8	1049.3	1050.4
130°	1060.9	1079.5	1092.2	1105.0	1103.9
132.5°	1119.0	1134.1	1146.8	1157.2	1156.1
135°	1167.8	1186.4	1196.7	1208.4	1206.0
137.5°	1218.7	1232.6	1244.4	1255.9	1252.5
140°	1268.6	1278.0	1290.7	1301.2	1295.4
142.5°	1310.5	1318.7	1333.7	1342.9	1337.1
145°	1354.6	1353.4	1373.1	1381.2	1375.5
147.5°	1392.8	1389.3	1409.1	1414.8	1410.3
150°	1430.0	1421.9	1440.5	1447.4	1441.6
152.5°	1461.3	1452.1	1469.4	1476.5	1468.3
155°	1491.5	1481.1	1495.1	1502.0	1492.7
157.5°	1515.9	1506.6	1517.1	1525.3	1515.9
160°	1536.8	1529.8	1536.8	1543.7	1535.6
162.5°	1555.3	1548.4	1554.2	1562.3	1551.9
165°	1571.6	1564.7	1568.1	1576.3	1568.1
167.5°	1584.4	1577.4	1581.0	1589.1	1578.6
170°	1594.9	1587.8	1590.2	1598.3	1587.8
172.5°	1601.8	1594.9	1597.2	1605.4	1594.9
175°	1607.6	1599.4	1601.8	1609.9	1598.3
177.5°	1609.9	1601.8	1603.0	1611.1	1600.7
180°	1604.1	1604.1	1604.1	1604.1	1604.1



TEST NUMBER: P913321
 CATALOG NUMBER: DFN2DIP-4P4F0-080D060US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.32	10.18	10.26	11.13	12.35	5.28	6.14	6.22	7.09	8.31
	3H	11.01	11.77	11.95	12.73	13.98	6.47	7.24	7.42	8.20	9.45
	4H	11.62	12.35	12.58	13.31	14.56	6.93	7.65	7.89	8.61	9.87
	6H	12.05	12.72	13.02	13.68	14.95	7.25	7.92	8.22	8.88	10.15
	8H	12.18	12.81	13.16	13.80	15.06	7.34	7.98	8.32	8.96	10.23
	12H	12.24	12.85	13.23	13.82	15.11	7.39	7.99	8.37	8.97	10.26
4H	2H	9.34	10.07	10.31	11.03	12.29	5.88	6.61	6.85	7.57	8.83
	3H	11.18	11.78	12.16	12.77	14.05	7.24	7.84	8.21	8.83	10.10
	4H	11.88	12.43	12.86	13.41	14.71	7.79	8.34	8.77	9.32	10.62
	6H	12.40	12.87	13.40	13.88	15.18	8.21	8.68	9.21	9.69	10.99
	8H	12.58	13.02	13.58	14.02	15.33	8.34	8.78	9.34	9.78	11.09
	12H	12.68	13.08	13.70	14.09	15.41	8.41	8.81	9.43	9.82	11.14
8H	4H	11.85	12.29	12.85	13.29	14.60	8.07	8.52	9.07	9.52	10.82
	6H	12.42	12.79	13.44	13.83	15.14	8.60	8.96	9.62	10.00	11.31
	8H	12.64	12.96	13.67	13.99	15.32	8.79	9.11	9.82	10.14	11.46
	12H	12.79	13.07	13.82	14.09	15.46	8.91	9.19	9.94	10.22	11.59
12H	4H	11.80	12.20	12.82	13.22	14.53	8.08	8.48	9.10	9.50	10.81
	6H	12.40	12.72	13.43	13.75	15.07	8.65	8.97	9.68	10.00	11.32
	8H	12.62	12.91	13.66	13.93	15.30	8.86	9.14	9.89	10.17	11.54