

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924170

Luminaire Tested: DFN2DIP-4P4F0-060D030US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924170
REPORT IS A COMBINATION OF REPORTS P899085 AND P895967
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-4P4F0-060D030US950-FLLFLL
Description: 4 foot, 90deg - 4way Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8199.6 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 4.07' x L: 4.07' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924170
CATALOG NUMBER: DFN2DIP-4P4F0-060D030US950-FLLFL

Luminous Intensity Polar Plot





TEST NUMBER: P924170

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	83	83	83	74	74	74	69			
1	102	98	94	90	96	92	89	86	83	80	77	74	71	70	65	64	62	58			
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	52	49			
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45	41			
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	35			
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	31			
6	66	53	45	39	62	51	43	38	46	40	35	41	36	32	37	33	30	27			
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	26	24			
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24	22			
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	21	19			
10	50	37	30	25	47	36	29	24	32	27	22	30	25	21	27	23	20	18			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1445	1445	1445
5°	1447	1425	1435
10°	1436	1406	1416
15°	1415	1384	1386
20°	1386	1352	1356
25°	1358	1314	1320
30°	1323	1279	1275
35°	1289	1237	1227
40°	1248	1195	1182
45°	1206	1153	1135
50°	1161	1108	1081
55°	1114	1057	1032
60°	1061	996	976
65°	1003	933	909
70°	929	856	837
75°	826	765	772
80°	703	648	646
85°	510	445	436

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1206 cd/sqm



TEST NUMBER: P924170

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.6	2.6
10°-20°	589.8	7.2
20°-30°	866.8	10.6
30°-40°	1006.7	12.3
40°-50°	1005.5	12.3
50°-60°	876.7	10.7
60°-70°	648.1	7.9
70°-80°	366.7	4.5
80°-90°	99.4	1.2
90°-100°	56.0	0.7
100°-110°	178.0	2.2
110°-120°	304.6	3.7
120°-130°	400.5	4.9
130°-140°	449.6	5.5
140°-150°	440.9	5.4
150°-160°	369.8	4.5
160°-170°	245.3	3.0
170°-180°	85.7	1.0
<hr/>		
0°-30°	1666.2	20.3
0°-40°	2673.0	32.6
0°-60°	4555.2	55.6
0°-90°	5669.3	69.1
90°-120°	538.5	6.6
90°-150°	1829.5	22.3
90°-180°	2530.0	30.9
0°-180°	8199.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2227	2227	2227	2227	2227	
5°	2227	2219	2195	2212	2208	211
15°	2120	2108	2080	2088	2078	597
25°	1919	1902	1866	1870	1866	883
35°	1656	1634	1600	1587	1576	1034
45°	1347	1332	1300	1276	1268	1040
55°	1020	1007	981	955	945	912
65°	688	675	653	634	623	680
75°	360	356	345	332	336	384
85°	88	86	84	77	75	98
90°	1	10	27	25	26	8
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	



TEST NUMBER: P924170

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US950-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2227.2	2227.2	2227.2	2227.2	2227.2
2.5°	2240.2	2229.5	2205.8	2227.2	2223.1
5°	2227.2	2218.8	2195.2	2212.2	2208.1
7.5°	2212.2	2199.5	2175.9	2193.2	2188.9
10°	2188.9	2173.9	2148.1	2165.2	2158.8
12.5°	2156.6	2143.8	2118.2	2128.9	2124.6
15°	2120.2	2107.5	2079.5	2088.2	2077.5
17.5°	2075.2	2062.5	2034.6	2045.2	2034.6
20°	2025.9	2013.2	1983.2	1989.6	1981.2
22.5°	1976.9	1957.5	1929.6	1929.6	1925.3
25°	1918.9	1901.9	1865.5	1869.6	1865.5
27.5°	1854.6	1839.6	1811.8	1805.5	1794.9
30°	1790.6	1773.2	1741.2	1734.8	1726.2
32.5°	1721.9	1709.2	1674.8	1661.9	1653.3
35°	1655.6	1634.2	1599.9	1586.9	1576.2
37.5°	1580.6	1561.2	1527.0	1511.9	1501.2
40°	1503.5	1486.2	1452.0	1432.9	1424.2
42.5°	1428.5	1411.3	1377.2	1355.6	1342.9
45°	1347.2	1332.2	1299.9	1276.5	1267.9
47.5°	1267.9	1252.9	1218.6	1195.0	1182.2
50°	1184.3	1173.6	1143.7	1113.6	1102.9
52.5°	1102.9	1087.9	1060.2	1036.6	1021.6
55°	1019.5	1006.6	980.9	955.2	944.6
57.5°	936.0	925.3	897.3	871.7	863.0
60°	852.3	843.9	814.0	790.3	783.9
62.5°	770.9	755.9	734.6	713.2	704.6
65°	687.5	674.7	653.3	633.9	623.2
67.5°	601.9	591.0	571.9	556.9	548.3
70°	522.6	514.0	494.6	479.7	471.3
72.5°	441.2	432.6	422.0	407.0	400.6
75°	359.7	355.7	344.7	332.0	336.3
77.5°	287.0	278.4	274.0	267.7	261.3
80°	214.3	212.0	207.7	201.3	197.0
82.5°	145.7	145.7	143.6	135.0	135.0
85°	87.7	85.7	83.6	77.0	75.0
87.5°	38.6	34.3	30.0	23.7	21.4
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3



TEST NUMBER: P924170

CATALOG NUMBER: DFN2DIP-4P4F0-060D030US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2



TEST NUMBER: P924170
 CATALOG NUMBER: DFN2DIP-4P4F0-060D030US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.17	11.24	10.95	12.03	13.00	9.73	10.79	10.50	11.59	12.56
	3H	11.85	12.81	12.64	13.62	14.61	11.36	12.32	12.15	13.12	14.12
	4H	12.45	13.36	13.26	14.17	15.18	11.96	12.86	12.76	13.68	14.69
	6H	12.87	13.70	13.69	14.52	15.55	12.37	13.20	13.19	14.02	15.05
	8H	12.98	13.78	13.81	14.62	15.64	12.48	13.27	13.31	14.11	15.14
	12H	13.04	13.80	13.87	14.63	15.68	12.53	13.29	13.36	14.12	15.17
4H	2H	10.66	11.56	11.47	12.38	13.39	10.30	11.21	11.11	12.02	13.03
	3H	12.55	13.30	13.37	14.15	15.18	12.14	12.90	12.96	13.74	14.77
	4H	13.28	13.96	14.11	14.81	15.86	12.85	13.54	13.69	14.38	15.44
	6H	13.81	14.40	14.66	15.27	16.33	13.38	13.97	14.23	14.84	15.90
	8H	13.97	14.52	14.82	15.39	16.46	13.53	14.08	14.38	14.95	16.02
	12H	14.05	14.55	14.93	15.44	16.51	13.60	14.10	14.48	14.99	16.06
8H	4H	13.49	14.05	14.34	14.91	15.98	13.11	13.67	13.97	14.53	15.61
	6H	14.14	14.60	15.02	15.50	16.57	13.75	14.21	14.63	15.12	16.19
	8H	14.36	14.77	15.26	15.67	16.76	13.97	14.38	14.86	15.28	16.37
	12H	14.51	14.87	15.40	15.76	16.90	14.10	14.46	14.99	15.35	16.49
12H	4H	13.49	13.99	14.36	14.87	15.95	13.12	13.62	13.99	14.50	15.58
	6H	14.17	14.58	15.06	15.48	16.57	13.80	14.21	14.69	15.11	16.20
	8H	14.42	14.78	15.32	15.68	16.82	14.04	14.40	14.94	15.30	16.44