

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916103

Luminaire Tested: DFN2DIP-HX2F0-040D030US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916103
REPORT IS A COMBINATION OF REPORTS P900685 AND P897595
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX2F0-040D030US930-FLLONL
Description: 2 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5650.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 1.99' x L: 2.3' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916103

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916103

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	99	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53
2	91	83	77	72	84	77	72	67	67	63	59	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	59	54	50	51	47	44	43	40	38
4	76	65	57	50	70	61	53	48	53	47	43	45	41	38	39	35	33
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	29
6	64	52	44	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22
8	55	43	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18
10	48	36	28	24	45	34	27	22	30	24	20	26	22	18	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2990	2990	2990
5°	2990	2941	2963
10°	2961	2894	2917
15°	2912	2840	2849
20°	2849	2766	2779
25°	2785	2680	2700
30°	2707	2600	2600
35°	2633	2505	2495
40°	2542	2410	2395
45°	2451	2314	2292
50°	2351	2213	2173
55°	2247	2097	2063
60°	2128	1960	1936
65°	1998	1817	1787
70°	1832	1642	1625
75°	1605	1433	1469
80°	1329	1166	1186
85°	903	732	733

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2451 cd/sqm

TEST NUMBER: P916103

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	2.1
10°-20°	336.0	5.9
20°-30°	493.8	8.7
30°-40°	573.6	10.2
40°-50°	572.9	10.1
50°-60°	499.5	8.8
60°-70°	369.3	6.5
70°-80°	208.9	3.7
80°-90°	56.6	1.0
90°-100°	27.2	0.5
100°-110°	101.5	1.8
110°-120°	269.1	4.8
120°-130°	446.3	7.9
130°-140°	474.1	8.4
140°-150°	440.6	7.8
150°-160°	354.3	6.3
160°-170°	228.3	4.0
170°-180°	78.6	1.4
0°-30°	949.3	16.8
0°-40°	1522.9	27.0
0°-60°	2595.3	45.9
0°-90°	3230.0	57.2
90°-120°	397.8	7.0
90°-150°	1758.9	31.1
90°-180°	2420.0	42.8
0°-180°	5650.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	1	7	12	15	16	5
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	

TEST NUMBER: P916103

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2

TEST NUMBER: P916103

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5

TEST NUMBER: P916103

CATALOG NUMBER: DFN2DIP-HX2F0-040D030US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.58	12.51	12.47	13.42	14.59	11.15	12.08	12.05	13.00	14.16
	3H	13.22	14.05	14.12	14.97	16.16	12.76	13.59	13.66	14.51	15.70
	4H	13.79	14.58	14.71	15.51	16.71	13.33	14.12	14.25	15.05	16.25
	6H	14.18	14.90	15.11	15.84	17.05	13.72	14.44	14.65	15.38	16.59
	8H	14.27	14.97	15.21	15.92	17.13	13.81	14.51	14.75	15.46	16.67
	12H	14.31	14.97	15.26	15.92	17.16	13.85	14.51	14.80	15.46	16.69
4H	2H	12.04	12.83	12.96	13.75	14.95	11.70	12.49	12.62	13.42	14.61
	3H	13.88	14.54	14.82	15.50	16.71	13.50	14.16	14.43	15.11	16.33
	4H	14.58	15.18	15.52	16.13	17.37	14.18	14.78	15.13	15.74	16.98
	6H	15.07	15.59	16.03	16.57	17.81	14.68	15.20	15.64	16.17	17.41
	8H	15.21	15.70	16.17	16.67	17.92	14.82	15.30	15.78	16.27	17.52
	12H	15.28	15.71	16.26	16.70	17.96	14.87	15.31	15.85	16.30	17.56
8H	4H	14.77	15.25	15.73	16.22	17.48	14.42	14.90	15.38	15.87	17.13
	6H	15.37	15.77	16.36	16.79	18.04	15.02	15.42	16.01	16.44	17.69
	8H	15.58	15.93	16.57	16.93	18.20	15.22	15.58	16.22	16.58	17.85
	12H	15.70	16.01	16.70	17.00	18.32	15.33	15.64	16.33	16.63	17.95
12H	4H	14.76	15.19	15.74	16.18	17.44	14.41	14.85	15.39	15.84	17.09
	6H	15.40	15.75	16.39	16.75	18.02	15.06	15.41	16.05	16.41	17.68
	8H	15.63	15.94	16.63	16.93	18.25	15.28	15.59	16.28	16.59	17.90