

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P922297

Luminaire Tested: DFN2DIP-PN4F0-050D090US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P922297
REPORT IS A COMBINATION OF REPORTS P901221 AND P898053
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-PN4F0-050D090US940-FLLONL
Description: 4 foot, Pentagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12359.1 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.74' x L: 3.94' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 110.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P922297

CATALOG NUMBER: DFN2DIP-PN4F0-050D090US940-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P922297

CATALOG NUMBER: DFN2DIP-PN4F0-050D090US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	33	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	26	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	21	19
6	61	49	41	35	55	44	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1266	1266	1266
5°	1268	1249	1257
10°	1258	1232	1241
15°	1240	1212	1214
20°	1215	1184	1187
25°	1190	1151	1156
30°	1158	1119	1116
35°	1129	1083	1074
40°	1093	1045	1034
45°	1056	1008	993
50°	1017	969	946
55°	975	924	902
60°	928	870	852
65°	877	814	793
70°	812	747	730
75°	722	666	672
80°	613	563	560
85°	443	384	375

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1443 cd/sqm

TEST NUMBER: P922297

CATALOG NUMBER: DFN2DIP-PN4F0-050D090US940-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.3	1.3
10°-20°	459.4	3.7
20°-30°	675.2	5.5
30°-40°	784.2	6.3
40°-50°	783.2	6.3
50°-60°	682.9	5.5
60°-70°	504.8	4.1
70°-80°	285.6	2.3
80°-90°	80.1	0.6
90°-100°	89.3	0.7
100°-110°	332.9	2.7
110°-120°	883.0	7.1
120°-130°	1464.5	11.8
130°-140°	1555.6	12.6
140°-150°	1445.8	11.7
150°-160°	1162.4	9.4
160°-170°	749.0	6.1
170°-180°	257.8	2.1
0°-30°	1297.9	10.5
0°-40°	2082.0	16.8
0°-60°	3548.1	28.7
0°-90°	4418.8	35.8
90°-120°	1305.2	10.6
90°-150°	5771.2	46.7
90°-180°	7940.0	64.2
0°-180°	12359.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1735	1735	1735	1735	1735	
5°	1735	1728	1710	1723	1720	165
15°	1651	1642	1620	1627	1618	465
25°	1495	1481	1453	1456	1453	688
35°	1290	1273	1246	1236	1228	805
45°	1049	1038	1012	994	988	810
55°	794	784	764	744	736	710
65°	536	526	509	494	485	530
75°	280	277	268	259	262	299
85°	68	67	65	60	58	76
90°	2	24	39	49	53	11
95°	127	63	76	86	84	151
105°	596	655	120	141	149	637
115°	1127	1160	1209	302	161	1109
125°	1593	1619	1656	1670	1676	1421
135°	1972	2003	2020	2040	2036	1523
145°	2287	2285	2318	2332	2322	1431
155°	2518	2501	2524	2536	2520	1161
165°	2654	2642	2648	2662	2648	750
175°	2714	2700	2705	2718	2699	258
180°	2708	2708	2708	2708	2708	

TEST NUMBER: P922297

CATALOG NUMBER: DFN2DIP-PN4F0-050D090US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1734.8	1734.8	1734.8	1734.8	1734.8
2.5°	1744.9	1736.6	1718.2	1734.8	1731.7
5°	1734.8	1728.3	1709.9	1723.1	1720.0
7.5°	1723.1	1713.2	1694.9	1708.3	1705.0
10°	1705.0	1693.3	1673.3	1686.5	1681.6
12.5°	1679.8	1669.9	1649.9	1658.2	1654.8
15°	1651.4	1641.5	1619.8	1626.6	1618.2
17.5°	1616.4	1606.5	1584.7	1593.0	1584.7
20°	1578.1	1568.2	1544.8	1549.7	1543.2
22.5°	1539.8	1524.7	1503.0	1503.0	1499.6
25°	1494.7	1481.4	1453.0	1456.3	1453.0
27.5°	1444.6	1432.9	1411.3	1406.3	1398.0
30°	1394.6	1381.3	1356.3	1351.3	1344.6
32.5°	1341.2	1331.3	1304.6	1294.5	1287.8
35°	1289.5	1272.9	1246.2	1236.1	1227.8
37.5°	1231.1	1216.1	1189.4	1177.7	1169.4
40°	1171.2	1157.7	1131.0	1116.1	1109.4
42.5°	1112.8	1099.3	1072.7	1055.9	1046.0
45°	1049.4	1037.7	1012.5	994.3	987.6
47.5°	987.6	975.9	949.2	930.8	920.9
50°	922.5	914.2	890.8	867.5	859.1
52.5°	859.1	847.4	825.8	807.4	795.8
55°	794.2	784.1	764.0	744.0	735.8
57.5°	729.0	720.7	698.9	678.9	672.2
60°	663.9	657.4	634.0	615.5	610.6
62.5°	600.6	588.9	572.2	555.5	548.8
65°	535.6	525.5	508.8	493.8	485.4
67.5°	468.9	460.4	445.5	433.8	427.0
70°	407.1	400.4	385.3	373.6	367.1
72.5°	343.8	337.0	328.7	317.0	312.0
75°	280.2	277.0	268.5	258.6	262.0
77.5°	223.6	216.8	213.5	208.5	203.6
80°	166.9	165.1	161.8	156.9	153.5
82.5°	113.4	113.4	111.8	105.1	105.1
85°	68.3	66.7	65.1	60.0	58.4
87.5°	30.1	26.8	23.4	18.4	16.7
90°	1.9	23.5	39.1	49.1	52.8
92.5°	49.1	41.2	47.0	51.0	52.8
95°	127.3	62.6	76.3	86.3	84.3
97.5°	229.3	68.7	99.9	105.8	107.7
100°	347.0	78.5	111.7	127.3	131.3
102.5°	476.2	472.4	115.7	137.1	143.1
105°	595.8	654.7	119.6	141.1	148.9
107.5°	734.9	783.8	123.6	145.0	152.9
110°	868.3	909.3	343.0	147.0	154.8

TEST NUMBER: P922297

CATALOG NUMBER: DFN2DIP-PN4F0-050D090US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	993.7	1028.9	995.6	150.8	156.9
115°	1126.9	1160.1	1209.2	301.8	160.8
117.5°	1242.5	1281.7	1315.1	1034.7	521.3
120°	1371.9	1401.2	1436.6	1460.1	1195.5
122.5°	1481.6	1513.0	1552.3	1563.9	1566.0
125°	1593.2	1618.8	1656.1	1669.8	1675.6
127.5°	1695.1	1722.6	1752.2	1771.7	1773.6
130°	1791.3	1822.7	1844.1	1865.7	1863.9
132.5°	1889.3	1914.9	1936.3	1954.0	1952.1
135°	1971.7	2003.0	2020.5	2040.3	2036.4
137.5°	2057.8	2081.3	2101.0	2120.6	2114.8
140°	2142.0	2157.8	2179.3	2196.9	2187.2
142.5°	2212.8	2226.5	2251.8	2267.4	2257.7
145°	2287.2	2285.1	2318.4	2332.2	2322.4
147.5°	2351.7	2345.9	2379.2	2389.0	2381.2
150°	2414.6	2400.8	2432.2	2443.8	2434.1
152.5°	2467.4	2451.8	2481.1	2493.0	2479.2
155°	2518.4	2500.9	2524.3	2536.0	2520.4
157.5°	2559.6	2544.0	2561.6	2575.3	2559.6
160°	2594.9	2583.0	2594.9	2606.6	2592.8
162.5°	2626.1	2614.4	2624.2	2637.9	2620.3
165°	2653.6	2641.9	2647.8	2661.5	2647.8
167.5°	2675.2	2663.4	2669.3	2683.1	2665.4
170°	2692.9	2681.0	2684.9	2698.7	2681.0
172.5°	2704.6	2692.9	2696.8	2710.5	2692.9
175°	2714.3	2700.5	2704.6	2718.2	2698.7
177.5°	2718.2	2704.6	2706.6	2720.3	2702.7
180°	2708.5	2708.5	2708.5	2708.5	2708.5

TEST NUMBER: P922297

CATALOG NUMBER: DFN2DIP-PN4F0-050D090US940-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.62	7.36	7.69	8.43	9.90	6.18	6.92	7.25	7.99	9.46
	3H	8.27	8.94	9.35	10.02	11.50	7.79	8.45	8.87	9.54	11.01
	4H	8.86	9.49	9.95	10.57	12.06	8.37	9.00	9.46	10.08	11.57
	6H	9.25	9.84	10.35	10.92	12.42	8.76	9.34	9.86	10.43	11.93
	8H	9.35	9.91	10.46	11.01	12.50	8.86	9.42	9.96	10.52	12.01
	12H	9.40	9.93	10.51	11.02	12.54	8.90	9.43	10.01	10.52	12.04
4H	2H	7.06	7.70	8.16	8.78	10.27	6.71	7.35	7.81	8.43	9.91
	3H	8.92	9.45	10.03	10.56	12.06	8.52	9.05	9.62	10.16	11.66
	4H	9.63	10.12	10.74	11.22	12.74	9.22	9.70	10.33	10.80	12.32
	6H	10.15	10.56	11.26	11.69	13.20	9.72	10.14	10.84	11.26	12.77
	8H	10.29	10.68	11.41	11.80	13.33	9.87	10.25	10.98	11.37	12.90
	12H	10.36	10.72	11.50	11.84	13.37	9.92	10.28	11.06	11.40	12.93
8H	4H	9.82	10.21	10.94	11.33	12.85	9.45	9.84	10.57	10.95	12.48
	6H	10.45	10.77	11.59	11.93	13.45	10.08	10.40	11.21	11.55	13.08
	8H	10.67	10.95	11.82	12.09	13.64	10.29	10.57	11.43	11.71	13.25
	12H	10.80	11.05	11.95	12.18	13.76	10.40	10.65	11.55	11.78	13.36
12H	4H	9.80	10.15	10.94	11.28	12.81	9.44	9.79	10.57	10.92	12.45
	6H	10.48	10.76	11.62	11.90	13.44	10.12	10.40	11.26	11.53	13.08
	8H	10.72	10.97	11.87	12.10	13.68	10.35	10.59	11.50	11.73	13.31

END OF REPORT