

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927916

Luminaire Tested: DFN2DIP-HX4F0-060D040US850-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927916
REPORT IS A COMBINATION OF REPORTS P900823 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D040US850-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10979.0 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927916

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927916

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	90	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	44	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1925	1925	1925
5°	1928	1898	1911
10°	1913	1873	1885
15°	1885	1843	1845
20°	1847	1800	1804
25°	1809	1749	1756
30°	1762	1701	1695
35°	1718	1645	1631
40°	1662	1589	1570
45°	1608	1532	1507
50°	1547	1473	1435
55°	1485	1404	1368
60°	1414	1322	1292
65°	1336	1237	1202
70°	1238	1134	1105
75°	1101	1011	1016
80°	937	853	845
85°	679	581	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1608 cd/sqm

TEST NUMBER: P927916

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	2.2
10°-20°	685.6	6.2
20°-30°	1007.6	9.2
30°-40°	1170.3	10.7
40°-50°	1168.8	10.6
50°-60°	1019.2	9.3
60°-70°	753.4	6.9
70°-80°	426.3	3.9
80°-90°	115.1	1.0
90°-100°	49.4	0.4
100°-110°	184.0	1.7
110°-120°	488.1	4.4
120°-130°	809.5	7.4
130°-140°	859.9	7.8
140°-150°	799.2	7.3
150°-160°	642.5	5.9
160°-170°	414.0	3.8
170°-180°	142.5	1.3
0°-30°	1937.0	17.6
0°-40°	3107.2	28.3
0°-60°	5295.3	48.2
0°-90°	6590.0	60.0
90°-120°	721.5	6.6
90°-150°	3190.0	29.1
90°-180°	4389.0	40.0
0°-180°	10979.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	114
90°	1	13	22	27	29	10
95°	70	35	42	48	47	83
105°	329	362	66	78	82	352
115°	623	641	668	167	89	613
125°	881	895	915	923	926	785
135°	1090	1107	1117	1128	1126	842
145°	1264	1263	1281	1289	1284	791
155°	1392	1382	1395	1402	1393	641
165°	1467	1460	1464	1471	1464	414
175°	1500	1493	1495	1502	1492	143
180°	1497	1497	1497	1497	1497	

TEST NUMBER: P927916

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	1.0	13.0	21.6	27.2	29.2
92.5°	27.2	22.7	26.0	28.2	29.2
95°	70.3	34.6	42.1	47.7	46.6
97.5°	126.8	37.9	55.2	58.6	59.6
100°	191.7	43.4	61.8	70.3	72.5
102.5°	263.2	261.2	63.9	75.7	79.1
105°	329.3	361.9	66.1	78.0	82.3
107.5°	406.2	433.3	68.3	80.2	84.5
110°	480.0	502.6	189.6	81.3	85.5



TEST NUMBER: P927916

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	549.3	568.7	550.3	83.4	86.7
115°	622.8	641.2	668.4	166.8	88.9
117.5°	686.8	708.4	726.9	571.9	288.1
120°	758.3	774.5	794.0	807.1	660.9
122.5°	818.9	836.3	858.0	864.5	865.6
125°	880.7	894.9	915.4	923.0	926.2
127.5°	937.0	952.2	968.5	979.4	980.4
130°	990.1	1007.5	1019.3	1031.3	1030.3
132.5°	1044.2	1058.4	1070.3	1080.1	1079.1
135°	1089.8	1107.2	1116.9	1127.7	1125.6
137.5°	1137.4	1150.4	1161.3	1172.1	1168.9
140°	1184.0	1192.7	1204.6	1214.4	1208.9
142.5°	1223.1	1230.7	1244.7	1253.3	1248.0
145°	1264.3	1263.2	1281.4	1289.1	1283.7
147.5°	1299.9	1296.6	1315.1	1320.5	1316.3
150°	1334.6	1327.0	1344.4	1350.9	1345.4
152.5°	1363.8	1355.2	1371.4	1377.9	1370.4
155°	1392.0	1382.4	1395.3	1401.8	1393.1
157.5°	1414.8	1406.1	1416.0	1423.5	1414.8
160°	1434.3	1427.7	1434.3	1440.7	1433.2
162.5°	1451.6	1445.1	1450.6	1458.1	1448.4
165°	1466.8	1460.3	1463.5	1471.1	1463.5
167.5°	1478.7	1472.1	1475.5	1483.1	1473.3
170°	1488.5	1482.0	1484.1	1491.7	1482.0
172.5°	1494.9	1488.5	1490.7	1498.3	1488.5
175°	1500.3	1492.7	1494.9	1502.5	1491.7
177.5°	1502.5	1494.9	1496.0	1503.7	1493.9
180°	1497.2	1497.2	1497.2	1497.2	1497.2

TEST NUMBER: P927916

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.43	11.38	11.29	12.27	13.39	9.99	10.95	10.86	11.84	12.96
	3H	12.09	12.95	12.97	13.85	15.00	11.62	12.48	12.50	13.38	14.53
	4H	12.69	13.50	13.58	14.40	15.56	12.21	13.03	13.11	13.93	15.09
	6H	13.09	13.84	14.00	14.75	15.92	12.62	13.37	13.52	14.28	15.45
	8H	13.20	13.91	14.11	14.84	16.01	12.72	13.44	13.64	14.37	15.54
	12H	13.25	13.93	14.17	14.85	16.05	12.77	13.45	13.69	14.37	15.57
4H	2H	10.90	11.71	11.80	12.62	13.77	10.55	11.37	11.45	12.27	13.43
	3H	12.78	13.45	13.69	14.39	15.56	12.38	13.06	13.29	14.00	15.17
	4H	13.49	14.11	14.42	15.04	16.24	13.09	13.71	14.01	14.64	15.84
	6H	14.02	14.55	14.95	15.50	16.70	13.61	14.14	14.54	15.10	16.29
	8H	14.17	14.67	15.11	15.62	16.83	13.76	14.26	14.69	15.20	16.42
	12H	14.25	14.70	15.20	15.66	16.88	13.82	14.28	14.78	15.24	16.46
8H	4H	13.70	14.20	14.64	15.15	16.36	13.34	13.84	14.28	14.79	16.00
	6H	14.34	14.75	15.30	15.74	16.95	13.97	14.39	14.94	15.38	16.59
	8H	14.56	14.92	15.53	15.90	17.13	14.19	14.56	15.16	15.53	16.76
	12H	14.70	15.02	15.67	15.99	17.27	14.31	14.63	15.29	15.61	16.88
12H	4H	13.69	14.14	14.65	15.11	16.32	13.34	13.79	14.29	14.75	15.97
	6H	14.37	14.73	15.34	15.71	16.94	14.02	14.38	14.99	15.36	16.59
	8H	14.62	14.94	15.59	15.91	17.19	14.26	14.58	15.23	15.55	16.83

END OF REPORT