

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P911655

Luminaire Tested: DFN2DIP-SQ2F0-030D030US850-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P911655
REPORT IS A COMBINATION OF REPORTS P901292 AND P898215
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-SQ2F0-030D030US850-RLLONL
Description: 2 foot, Square Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6121.7 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.21' x L: 2.21' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9963
Total Harmonic Distortion (THDi): 0.065
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P911655

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US850-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P911655

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US850-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3023	3023	3023
5°	3023	2969	2990
10°	2988	2904	2889
15°	2942	2802	2735
20°	2882	2663	2547
25°	2821	2510	2365
30°	2741	2352	2137
35°	2662	2184	1936
40°	2581	2010	1707
45°	2488	1819	1499
50°	2391	1626	1297
55°	2290	1420	1103
60°	2172	1207	904
65°	2036	991	809
70°	1872	789	726
75°	1664	683	651
80°	1367	555	552
85°	890	344	393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2488 cd/sqm

TEST NUMBER: P911655

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US850-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	2.1
10°-20°	353.8	5.8
20°-30°	496.7	8.1
30°-40°	541.4	8.8
40°-50°	497.6	8.1
50°-60°	390.8	6.4
60°-70°	254.4	4.2
70°-80°	130.9	2.1
80°-90°	35.4	0.6
90°-100°	37.0	0.6
100°-110°	138.0	2.3
110°-120°	366.1	6.0
120°-130°	607.1	9.9
130°-140°	644.9	10.5
140°-150°	599.4	9.8
150°-160°	481.9	7.9
160°-170°	310.5	5.1
170°-180°	106.9	1.7
0°-30°	979.3	16.0
0°-40°	1520.7	24.8
0°-60°	2409.2	39.4
0°-90°	2829.9	46.2
90°-120°	541.1	8.8
90°-150°	2392.5	39.1
90°-180°	3292.0	53.8
0°-180°	6121.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	1	10	16	20	22	6
95°	53	26	32	36	35	63
105°	247	271	50	58	62	264
115°	467	481	501	125	67	460
125°	660	671	687	692	695	589
135°	817	830	838	846	844	631
145°	948	947	961	967	963	593
155°	1044	1037	1046	1051	1045	481
165°	1100	1095	1098	1103	1098	311
175°	1125	1120	1121	1127	1119	107
180°	1123	1123	1123	1123	1123	

TEST NUMBER: P911655

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US850-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	0.8	9.8	16.2	20.4	21.8
92.5°	20.4	17.1	19.5	21.2	21.8
95°	52.8	26.0	31.6	35.8	34.9
97.5°	95.0	28.5	41.4	43.9	44.7
100°	143.8	32.5	46.4	52.8	54.5
102.5°	197.4	195.8	47.9	56.8	59.3
105°	247.0	271.4	49.6	58.4	61.8
107.5°	304.6	324.9	51.2	60.1	63.4
110°	360.0	376.9	142.2	61.0	64.2

TEST NUMBER: P911655

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US850-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	412.0	426.5	412.8	62.5	65.0
115°	467.1	481.0	501.3	125.1	66.7
117.5°	515.1	531.3	545.2	429.0	216.1
120°	568.7	580.9	595.5	605.3	495.6
122.5°	614.2	627.3	643.6	648.3	649.2
125°	660.5	671.1	686.6	692.2	694.7
127.5°	702.8	714.1	726.4	734.5	735.3
130°	742.6	755.7	764.5	773.4	772.8
132.5°	783.2	793.8	802.7	810.0	809.2
135°	817.3	830.4	837.6	845.8	844.2
137.5°	853.0	862.8	871.0	879.1	876.7
140°	888.0	894.5	903.4	910.7	906.7
142.5°	917.4	923.0	933.6	940.0	936.0
145°	948.2	947.3	961.2	966.8	962.7
147.5°	974.9	972.5	986.3	990.3	987.1
150°	1001.0	995.3	1008.3	1013.1	1009.1
152.5°	1022.8	1016.4	1028.6	1033.5	1027.8
155°	1044.0	1036.8	1046.5	1051.3	1044.9
157.5°	1061.1	1054.7	1062.0	1067.6	1061.1
160°	1075.7	1070.9	1075.7	1080.6	1074.8
162.5°	1088.7	1083.8	1087.9	1093.6	1086.3
165°	1100.0	1095.2	1097.7	1103.3	1097.7
167.5°	1109.0	1104.1	1106.6	1112.3	1105.0
170°	1116.3	1111.4	1113.1	1118.8	1111.4
172.5°	1121.2	1116.3	1118.0	1123.6	1116.3
175°	1125.2	1119.5	1121.2	1126.9	1118.8
177.5°	1126.9	1121.2	1122.1	1127.7	1120.4
180°	1122.9	1122.9	1122.9	1122.9	1122.9

TEST NUMBER: P911655

CATALOG NUMBER: DFN2DIP-SQ2F0-030D030US850-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.51	11.31	11.51	12.32	13.64	6.47	7.27	7.47	8.28	9.60
	3H	12.17	12.88	13.17	13.90	15.24	7.64	8.36	8.65	9.37	10.72
	4H	12.76	13.44	13.78	14.45	15.81	8.08	8.75	9.10	9.77	11.12
	6H	13.17	13.79	14.20	14.81	16.18	8.38	9.00	9.41	10.02	11.39
	8H	13.28	13.88	14.32	14.91	16.28	8.46	9.05	9.50	10.09	11.45
	12H	13.34	13.90	14.38	14.93	16.32	8.50	9.06	9.54	10.09	11.48
4H	2H	10.52	11.20	11.55	12.21	13.57	7.05	7.73	8.08	8.75	10.10
	3H	12.33	12.89	13.36	13.93	15.30	8.38	8.94	9.41	9.99	11.36
	4H	13.00	13.52	14.04	14.55	15.94	8.91	9.43	9.95	10.46	11.85
	6H	13.50	13.94	14.55	15.00	16.38	9.31	9.75	10.36	10.81	12.20
	8H	13.66	14.07	14.71	15.12	16.53	9.43	9.84	10.48	10.89	12.29
	12H	13.74	14.12	14.81	15.18	16.59	9.48	9.85	10.55	10.92	12.33
8H	4H	12.96	13.38	14.01	14.43	15.83	9.18	9.59	10.23	10.64	12.04
	6H	13.51	13.85	14.58	14.94	16.34	9.67	10.01	10.75	11.10	12.50
	8H	13.71	14.01	14.79	15.09	16.50	9.85	10.15	10.93	11.22	12.64
	12H	13.83	14.10	14.92	15.17	16.63	9.95	10.21	11.04	11.29	12.75
12H	4H	12.91	13.29	13.98	14.35	15.76	9.18	9.55	10.25	10.62	12.02
	6H	13.48	13.78	14.56	14.86	16.28	9.71	10.01	10.80	11.09	12.51
	8H	13.69	13.95	14.77	15.02	16.48	9.91	10.17	10.99	11.24	12.70