

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928742

Luminaire Tested: DFN2DIP-HX4F0-100D120US930-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928742
REPORT IS A COMBINATION OF REPORTS P900976 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D120US930-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16609.7 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 195.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928742

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928742

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	43	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	46	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2505	2505	2505
5°	2509	2465	2481
10°	2484	2417	2400
15°	2450	2337	2275
20°	2405	2227	2122
25°	2359	2104	1975
30°	2297	1978	1787
35°	2236	1842	1622
40°	2174	1701	1434
45°	2103	1545	1262
50°	2029	1388	1095
55°	1951	1219	935
60°	1861	1043	769
65°	1758	864	693
70°	1633	697	627
75°	1476	615	571
80°	1249	517	495
85°	873	346	373

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2103 cd/sqm

TEST NUMBER: P928742

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	315.7	1.9
10°-20°	866.6	5.2
20°-30°	1216.7	7.3
30°-40°	1326.3	8.0
40°-50°	1219.0	7.3
50°-60°	957.3	5.8
60°-70°	623.1	3.8
70°-80°	320.8	1.9
80°-90°	87.7	0.5
90°-100°	108.8	0.7
100°-110°	405.7	2.4
110°-120°	1076.0	6.5
120°-130°	1784.7	10.7
130°-140°	1895.8	11.4
140°-150°	1761.9	10.6
150°-160°	1416.5	8.5
160°-170°	912.8	5.5
170°-180°	314.2	1.9
0°-30°	2399.0	14.4
0°-40°	3725.3	22.4
0°-60°	5901.7	35.5
0°-90°	6933.3	41.7
90°-120°	1590.6	9.6
90°-150°	7033.0	42.3
90°-180°	9676.0	58.3
0°-180°	16609.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3368	3368	3368	3368	3368	
5°	3368	3353	3313	3341	3332	319
15°	3204	3170	3067	3009	2978	903
25°	2908	2810	2609	2484	2439	1337
35°	2506	2350	2082	1890	1823	1568
45°	2048	1844	1524	1308	1234	1582
55°	1558	1320	991	808	750	1392
65°	1052	805	530	427	418	1043
75°	561	347	244	222	220	593
85°	131	67	58	58	58	150
90°	2	29	48	60	64	16
95°	155	76	93	105	103	184
105°	726	798	146	172	182	776
115°	1373	1414	1474	368	196	1352
125°	1942	1973	2018	2035	2042	1732
135°	2403	2441	2462	2486	2482	1856
145°	2787	2785	2825	2842	2830	1743
155°	3069	3048	3076	3090	3072	1414
165°	3234	3220	3227	3243	3227	914
175°	3308	3291	3296	3313	3289	315
180°	3301	3301	3301	3301	3301	

TEST NUMBER: P928742

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3368.4	3368.4	3368.4	3368.4	3368.4
2.5°	3383.6	3368.4	3334.7	3365.5	3359.3
5°	3368.4	3353.2	3313.4	3340.9	3331.8
7.5°	3340.9	3322.8	3280.0	3292.0	3276.9
10°	3304.3	3283.0	3222.2	3212.8	3194.7
12.5°	3258.8	3231.2	3148.8	3130.7	3097.0
15°	3203.8	3170.1	3066.6	3008.7	2978.3
17.5°	3139.7	3090.9	2962.9	2895.9	2847.0
20°	3066.6	3005.5	2853.2	2777.2	2709.9
22.5°	2987.4	2917.2	2740.3	2636.9	2591.2
25°	2908.2	2810.5	2609.3	2484.4	2438.6
27.5°	2813.7	2709.9	2487.4	2344.1	2273.9
30°	2713.1	2597.0	2353.1	2198.0	2115.5
32.5°	2615.5	2475.1	2225.4	2042.4	1966.0
35°	2505.8	2350.3	2082.2	1890.1	1822.7
37.5°	2399.1	2231.2	1947.9	1737.4	1661.4
40°	2286.2	2103.5	1807.6	1591.2	1512.0
42.5°	2170.4	1975.4	1667.6	1441.8	1365.8
45°	2048.5	1844.1	1524.3	1307.6	1234.5
47.5°	1932.8	1716.4	1387.1	1170.4	1103.5
50°	1804.7	1588.3	1252.9	1042.4	978.7
52.5°	1679.5	1450.9	1124.9	923.6	865.8
55°	1557.5	1319.9	990.6	807.9	750.0
57.5°	1432.8	1188.8	872.0	701.1	652.3
60°	1304.7	1060.8	746.8	591.5	542.7
62.5°	1179.8	935.9	640.0	493.9	469.6
65°	1051.8	804.6	530.4	426.9	417.5
67.5°	929.8	682.7	426.9	374.8	365.8
70°	801.7	564.1	353.5	323.1	310.8
72.5°	679.8	454.0	295.6	271.3	265.2
75°	560.8	347.4	243.8	222.5	219.6
77.5°	442.1	246.8	192.1	179.8	173.7
80°	332.1	176.9	146.2	134.2	134.2
82.5°	231.5	119.0	100.6	94.5	94.5
85°	131.0	66.9	57.9	57.9	57.9
87.5°	48.8	24.3	24.3	21.4	21.4
90°	2.3	28.6	47.7	59.8	64.4
92.5°	59.8	50.2	57.3	62.1	64.4
95°	155.1	76.3	93.0	105.2	102.7
97.5°	279.4	83.7	121.7	129.0	131.3
100°	422.8	95.6	136.1	155.1	160.0
102.5°	580.3	575.7	140.9	167.1	174.4
105°	726.0	797.8	145.8	171.9	181.5
107.5°	895.6	955.2	150.6	176.7	186.3
110°	1058.1	1108.1	418.0	179.2	188.6

TEST NUMBER: P928742

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1211.0	1253.8	1213.3	183.8	191.1
115°	1373.2	1413.8	1473.6	367.8	196.0
117.5°	1514.2	1561.9	1602.7	1260.9	635.3
120°	1671.9	1707.6	1750.7	1779.4	1456.9
122.5°	1805.5	1843.8	1891.7	1905.9	1908.4
125°	1941.6	1972.8	2018.2	2034.9	2042.0
127.5°	2065.8	2099.3	2135.3	2159.1	2161.4
130°	2182.9	2221.2	2247.3	2273.7	2271.4
132.5°	2302.3	2333.5	2359.6	2381.2	2378.9
135°	2402.7	2441.0	2462.3	2486.4	2481.6
137.5°	2507.7	2536.3	2560.4	2584.2	2577.1
140°	2610.4	2629.6	2655.7	2677.3	2665.4
142.5°	2696.5	2713.3	2744.2	2763.2	2751.3
145°	2787.3	2784.8	2825.3	2842.1	2830.1
147.5°	2865.9	2858.8	2899.4	2911.3	2901.9
150°	2942.4	2925.7	2964.0	2978.2	2966.3
152.5°	3006.8	2987.8	3023.6	3038.0	3021.3
155°	3068.9	3047.6	3076.3	3090.5	3071.5
157.5°	3119.1	3100.1	3121.7	3138.4	3119.1
160°	3162.2	3147.8	3162.2	3176.4	3159.7
162.5°	3200.3	3186.1	3198.0	3214.7	3193.2
165°	3233.7	3219.5	3226.6	3243.4	3226.6
167.5°	3260.1	3245.6	3253.0	3269.7	3248.2
170°	3281.6	3267.2	3272.0	3288.7	3267.2
172.5°	3295.8	3281.6	3286.5	3303.2	3281.6
175°	3307.7	3291.0	3295.8	3312.6	3288.7
177.5°	3312.6	3295.8	3298.4	3315.1	3293.6
180°	3300.7	3300.7	3300.7	3300.7	3300.7

TEST NUMBER: P928742

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.51	10.28	10.55	11.32	12.70	5.49	6.25	6.52	7.29	8.68
	3H	11.19	11.87	12.23	12.92	14.32	6.67	7.36	7.71	8.40	9.81
	4H	11.79	12.44	12.85	13.49	14.90	7.12	7.77	8.18	8.82	10.23
	6H	12.21	12.81	13.28	13.86	15.29	7.44	8.04	8.50	9.09	10.51
	8H	12.34	12.91	13.41	13.97	15.39	7.53	8.10	8.60	9.16	10.59
	12H	12.40	12.94	13.47	14.00	15.44	7.57	8.11	8.65	9.17	10.62
4H	2H	9.53	10.17	10.59	11.22	12.63	6.08	6.73	7.14	7.77	9.18
	3H	11.35	11.89	12.42	12.96	14.39	7.42	7.96	8.49	9.04	10.46
	4H	12.04	12.54	13.11	13.60	15.05	7.97	8.46	9.04	9.53	10.98
	6H	12.55	12.98	13.64	14.06	15.51	8.39	8.81	9.47	9.90	11.34
	8H	12.73	13.12	13.81	14.20	15.66	8.52	8.91	9.60	9.99	11.45
	12H	12.82	13.18	13.92	14.27	15.73	8.58	8.94	9.68	10.03	11.49
8H	4H	12.00	12.40	13.09	13.48	14.94	8.25	8.64	9.33	9.72	11.18
	6H	12.57	12.90	13.67	14.02	15.47	8.76	9.09	9.87	10.21	11.67
	8H	12.79	13.07	13.90	14.18	15.65	8.96	9.24	10.07	10.35	11.82
	12H	12.92	13.17	14.04	14.27	15.79	9.07	9.33	10.19	10.43	11.94
12H	4H	11.95	12.31	13.05	13.40	14.87	8.25	8.61	9.35	9.70	11.16
	6H	12.54	12.83	13.66	13.94	15.41	8.81	9.10	9.92	10.20	11.68
	8H	12.76	13.02	13.88	14.11	15.63	9.02	9.27	10.14	10.37	11.89