

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P929246

Luminaire Tested: DFN2DIP-HX4F0-060D120US940-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P929246
REPORT IS A COMBINATION OF REPORTS P900968 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D120US940-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15146.2 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 150.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P929246

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P929246

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	32
2	85	78	73	68	76	71	66	62	56	53	50	43	40	39	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	25	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1645	1645	1645
5°	1648	1619	1629
10°	1631	1587	1576
15°	1609	1535	1494
20°	1579	1463	1394
25°	1549	1382	1297
30°	1508	1299	1174
35°	1469	1210	1065
40°	1428	1117	941
45°	1381	1015	829
50°	1332	911	719
55°	1281	801	614
60°	1222	685	505
65°	1155	567	455
70°	1073	458	412
75°	970	404	375
80°	820	339	325
85°	573	227	245

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1856 cd/sqm

TEST NUMBER: P929246

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.3	1.4
10°-20°	569.1	3.8
20°-30°	799.0	5.3
30°-40°	871.0	5.8
40°-50°	800.5	5.3
50°-60°	628.7	4.2
60°-70°	409.2	2.7
70°-80°	210.6	1.4
80°-90°	60.1	0.4
90°-100°	119.1	0.8
100°-110°	444.1	2.9
110°-120°	1177.7	7.8
120°-130°	1953.3	12.9
130°-140°	2074.9	13.7
140°-150°	1928.4	12.7
150°-160°	1550.3	10.2
160°-170°	999.0	6.6
170°-180°	343.8	2.3
0°-30°	1575.4	10.4
0°-40°	2446.4	16.2
0°-60°	3875.6	25.6
0°-90°	4555.6	30.1
90°-120°	1740.9	11.5
90°-150°	7697.4	50.8
90°-180°	10591.0	69.9
0°-180°	15146.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2212	2212	2212	2212	2212	
5°	2212	2202	2176	2194	2188	210
15°	2104	2082	2014	1976	1956	593
25°	1910	1846	1714	1632	1601	878
35°	1646	1543	1367	1241	1197	1030
45°	1345	1211	1001	859	811	1039
55°	1023	867	650	531	492	914
65°	691	528	348	280	274	685
75°	368	228	160	146	144	390
85°	86	44	38	38	38	99
90°	2	31	52	66	70	14
95°	170	84	102	115	112	201
105°	795	873	160	188	199	849
115°	1503	1547	1613	403	214	1480
125°	2125	2159	2209	2227	2235	1895
135°	2630	2672	2695	2721	2716	2031
145°	3051	3048	3092	3111	3098	1908
155°	3359	3336	3367	3382	3362	1548
165°	3539	3524	3531	3550	3531	1000
175°	3620	3602	3607	3626	3599	345
180°	3612	3612	3612	3612	3612	

TEST NUMBER: P929246

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2212.0	2212.0	2212.0	2212.0	2212.0
2.5°	2222.0	2212.0	2189.9	2210.0	2206.0
5°	2212.0	2202.0	2175.9	2194.0	2188.0
7.5°	2194.0	2182.0	2154.0	2161.9	2151.9
10°	2169.9	2155.9	2116.0	2109.8	2097.9
12.5°	2140.0	2121.9	2067.7	2055.9	2033.8
15°	2103.9	2081.7	2013.8	1975.8	1955.8
17.5°	2061.9	2029.7	1945.6	1901.7	1869.6
20°	2013.8	1973.6	1873.6	1823.7	1779.5
22.5°	1961.8	1915.7	1799.5	1731.6	1701.6
25°	1909.8	1845.6	1713.5	1631.6	1601.4
27.5°	1847.8	1779.5	1633.4	1539.3	1493.3
30°	1781.7	1705.4	1545.3	1443.3	1389.2
32.5°	1717.5	1625.4	1461.5	1341.2	1291.1
35°	1645.6	1543.4	1367.3	1241.1	1197.0
37.5°	1575.5	1465.2	1279.2	1141.0	1091.0
40°	1501.3	1381.4	1187.0	1044.9	992.9
42.5°	1425.3	1297.2	1095.0	946.8	896.9
45°	1345.2	1211.0	1001.0	858.6	810.6
47.5°	1269.2	1127.1	910.9	768.6	724.7
50°	1185.1	1043.0	822.8	684.5	642.7
52.5°	1102.9	952.7	738.7	606.6	568.6
55°	1022.9	866.8	650.5	530.6	492.5
57.5°	940.9	780.7	572.6	460.5	428.3
60°	856.8	696.7	490.4	388.5	356.4
62.5°	774.8	614.7	420.3	324.3	308.4
65°	690.7	528.4	348.3	280.4	274.2
67.5°	610.6	448.3	280.4	246.2	240.2
70°	526.5	370.4	232.1	212.2	204.1
72.5°	446.4	298.2	194.1	178.2	174.1
75°	368.3	228.1	160.1	146.1	144.2
77.5°	290.3	162.1	126.1	118.1	114.1
80°	218.1	116.1	96.0	88.1	88.1
82.5°	152.1	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	2.5	31.3	52.2	65.5	70.5
92.5°	65.5	54.9	62.7	68.0	70.5
95°	169.7	83.5	101.8	115.2	112.4
97.5°	305.8	91.6	133.2	141.2	143.7
100°	462.8	104.6	149.0	169.7	175.1
102.5°	635.1	630.1	154.2	182.9	190.9
105°	794.6	873.2	159.6	188.1	198.6
107.5°	980.2	1045.4	164.8	193.4	203.9
110°	1158.1	1212.8	457.5	196.2	206.4

TEST NUMBER: P929246

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1325.4	1372.3	1327.9	201.1	209.2
115°	1502.9	1547.4	1612.8	402.6	214.5
117.5°	1657.2	1709.4	1754.1	1380.0	695.3
120°	1829.8	1868.9	1916.1	1947.5	1594.5
122.5°	1976.0	2018.0	2070.4	2085.9	2088.7
125°	2125.0	2159.2	2208.9	2227.1	2234.9
127.5°	2261.0	2297.6	2337.0	2363.1	2365.6
130°	2389.1	2431.1	2459.6	2488.5	2486.0
132.5°	2519.8	2554.0	2582.5	2606.2	2603.7
135°	2629.7	2671.6	2694.9	2721.3	2716.1
137.5°	2744.6	2775.9	2802.3	2828.4	2820.6
140°	2857.0	2878.0	2906.6	2930.2	2917.2
142.5°	2951.3	2969.6	3003.5	3024.2	3011.2
145°	3050.6	3047.9	3092.2	3110.6	3097.5
147.5°	3136.6	3128.9	3173.3	3186.3	3176.1
150°	3220.4	3202.1	3244.0	3259.5	3246.5
152.5°	3290.9	3270.1	3309.2	3325.0	3306.7
155°	3358.8	3335.5	3366.9	3382.5	3361.7
157.5°	3413.8	3393.0	3416.6	3434.9	3413.8
160°	3461.0	3445.2	3461.0	3476.5	3458.2
162.5°	3502.6	3487.1	3500.1	3518.4	3494.9
165°	3539.2	3523.7	3531.4	3549.8	3531.4
167.5°	3568.1	3552.2	3560.3	3578.6	3555.1
170°	3591.6	3575.8	3581.1	3599.4	3575.8
172.5°	3607.2	3591.6	3597.0	3615.3	3591.6
175°	3620.2	3601.9	3607.2	3625.5	3599.4
177.5°	3625.5	3607.2	3610.0	3628.3	3604.8
180°	3612.5	3612.5	3612.5	3612.5	3612.5

TEST NUMBER: P929246

CATALOG NUMBER: DFN2DIP-HX4F0-060D120US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.66	7.35	7.77	8.45	9.98	2.63	3.32	3.75	4.43	5.96
	3H	8.32	8.94	9.45	10.06	11.60	3.81	4.43	4.93	5.54	7.09
	4H	8.93	9.51	10.06	10.63	12.18	4.25	4.84	5.39	5.96	7.51
	6H	9.34	9.88	10.48	11.00	12.56	4.57	5.11	5.71	6.23	7.79
	8H	9.46	9.98	10.61	11.11	12.67	4.66	5.17	5.80	6.30	7.86
	12H	9.52	10.01	10.67	11.13	12.72	4.70	5.18	5.85	6.31	7.89
4H	2H	6.66	7.24	7.80	8.36	9.91	3.21	3.79	4.35	4.91	6.46
	3H	8.47	8.96	9.62	10.10	11.67	4.55	5.03	5.69	6.18	7.74
	4H	9.16	9.61	10.31	10.74	12.33	5.09	5.54	6.24	6.67	8.26
	6H	9.67	10.05	10.83	11.21	12.78	5.50	5.89	6.66	7.04	8.62
	8H	9.84	10.20	11.00	11.35	12.94	5.63	5.99	6.79	7.13	8.73
	12H	9.93	10.26	11.10	11.41	13.01	5.69	6.01	6.86	7.17	8.77
8H	4H	9.12	9.48	10.27	10.62	12.22	5.36	5.72	6.52	6.86	8.46
	6H	9.68	9.98	10.86	11.16	12.75	5.88	6.17	7.05	7.36	8.95
	8H	9.90	10.16	11.08	11.32	12.93	6.07	6.33	7.25	7.49	9.10
	12H	10.03	10.26	11.21	11.42	13.06	6.18	6.41	7.37	7.57	9.22
12H	4H	9.06	9.39	10.24	10.55	12.14	5.36	5.68	6.53	6.84	8.44
	6H	9.66	9.91	10.84	11.08	12.69	5.93	6.18	7.11	7.35	8.96
	8H	9.87	10.10	11.06	11.26	12.90	6.13	6.36	7.31	7.52	9.16

END OF REPORT